

Reductor EMGA-60-P-G12-SST-57

Cod: 8141765

FESTO



Fisa tehnica

Caracteristica	valoare
Transmisie flansa	60 mm
Motor cu flansa	57 mm
Joc de rasucire	0,17 deg
tipul reductorului	Angrenaj planetar
Raport de transmisie	12:1
Viteza maxima de intrare	13.000 1/min
Temperatura de operare reductor	-25 ... 90 °C
Conformitatea PWIS	VDMA24364-B2-L
Tip de protectie	IP54
Cuplu de actionare continua	44 Nm
Momentul de inertie al angrenajului	0,118 kgcm ²
Cuplu maxim iesire	70 Nm
Eficienta maxima	96 %
rigiditate la torsiune	2,8 Nm/arcmin
Greutate produs	1.100 g
Interfata reductor arbore de iesire	60G
Interfata reductor arbore de antrenare	57A
Indicatie material	conform RoHS