

Kruhov  valce DSNU-1 1 1/4"- -P-A

  slo dielu: 548488

FESTO



 dajov  list

Charakteristick� znak	Hodnota
Zdvih	0.4 in...20 in
Priemer piestu	1 1/4"
Z�vit na piestnej ty�i	3/8-24 UNF-2A
Zalo�en� na norme	ISO 6431
Tlmenie	elastick� tlmiace kr��zky/do�ti�ky, obojstrann�
Mont��na poloha	�ubovo�n�
Koniec piestnej ty�e	Vonkaj�� z�vit
Kon�trukcia	Piest Piestna ty�
Sn�manie polohy	pre bezdotykov� sn�ma�e
Varianty	jednostrann� piestna ty�
Prev�dzkov� tlak	0.1 MPa...1 MPa 1 bar...10 bar
Sp�sob fungovania	dvoj�inn�
Prev�dzkov� m�di�m	Stla�en� vzduch pod�a ISO 8573-1:2010 [7:4:4]
Pozn�mka o prev�dzkovom/riadiacom m�di�u	Prev�dzka s mazan�m mo�n� (potrebn� pri �al�ej prev�dzke)
Trieda odolnosti proti kor�zii KBK	2- mierne n�roky na odolnos� proti kor�zii
Zhoda s LABS	VDMA24364-B1/B2-L
Teplota okolia	-4 �F...176 �F
Energia n�razu v koncov�ch poloh�ch	0.295 ft lbf
Teoretick� sila pri 0,6MPa (6 bar, 87 psi), sp�tn� chod	83 lbf
Teoretick� sila pri 0,6 MPa (6 bar, 87 psi), vys�vanie	96.5 lbf
Pohybovan� hmotnos� pri zdvihu 0 mm	4.27 oz
N�rast hmotnosti pri zdvihu 10 mm	0.317 oz
Sp�sob upevnenia	s pr�slu�enstvom
Pneumatick� pr�poj	1/8 NPT
Pokyny k materi�lu	V zhode s RoHS
Materi�l veka	Hlin�kov� tv�rna zliatina
Materi�l tesnen�	NBR TPE-U(PU)
Materi�l piestnej ty�e	nehrdzavej�ca vysokolegovaná o�el�
Materi�l r�ry valca	vysokolegovaná o�el�, nehrdzavej�ca