


接頭

NPCK-C-D-G18-K8

料號: 1490383

FESTO



技術參數

特性	值
額定尺寸	4.9 mm
柱頭螺栓上的密封件類型	密封圈
裝配位置	任何
設計	直式結構
Operating pressure for entire temperature range	-0.095 ... 1.2 MPa
操作壓力的完整溫度範圍	-0.95 ... 12 bar
Operating pressure for entire temperature range	-13.775 ... 174 psi
操作壓力注意事項	Water: max. 0.6 MPa at 0 - 85 °C Water vapour: 0 - 0.15 MPa, 0 - 1.5 bar, 0 - 22 psi
操作介質	壓縮空氣符合 ISO8573-1:2010 [7:-:-] Water (liquid, free of ice) Water vapour
注意: 操作和嚮導介質	潤滑操作可行
耐腐蝕等級 CRC	4 - Very high corrosion stress
PWIS conformity	VDMA24364 zone III
RSBP classification to CD-0033	F1a
Food-safe	See Supplementary material information
Note on temperature of medium	Water vapour: max. 120°C
防護等級	IP69K
環境溫度	-20 ... 120 °C
Note on ambient temperature	The NPCK can be used from -40 to 60 °C when using suitable tubing and observing the maximum operating pressure of the tube.
額定鎖緊扭矩	6.5 Nm
Note on the nominal tightening torque	4 Nm +/-10% for NPCK to MPA-C
額定擰緊扭矩公差	± 10 %
產品重量	13.4 g
氣壓連接, 氣口 1	外螺紋 G1/8
氣壓連接, 氣口 2	For tubing outside diameter 8 mm
Material of union nut	高合金鋼, 耐腐蝕
Material of threaded plug	高合金鋼, 耐腐蝕
材料備註	符合 RoHS
Material sealing ring	PEEK