


Programavimo kabelis VAVE-P8-VPS

Gaminio numeris: 570971

FESTO



Tech. Duomenys

| Savybės | Reikšmė |
|--|---|
| Atitinka standartus | DIN 47100 EN 61076-2-101 |
| Konstrukcija | T-distributor with cable on controller side |
| Distributor type | 1 to 2 |
| Papildomos funkcijos | Programming interface for proportional pressure regulator |
| Cable identification | Without inscription label holder |
| Electrical connection 1, function | Field device side |
| Electrical connection 1, design | apvalus |
| Electrical connection 1, connection type | Kištuko lizdas |
| Electrical connection 1, cable outlet | Tiesus |
| Electrical connection 1, connection technology | M12x1, A-coded in accordance with EN 61076-2-101 |
| Electrical connection 1, number of pins/wires | 8 |
| Electrical connection 1, occupied pins/wires | 8 |
| Electrical connection 1, type of mounting | Screw locking with SW14 |
| Electrical connection 2, function | Controller side |
| Electrical connection 2, design | apvalus |
| Electrical connection 2, connection type | Kištukas |
| Electrical connection 2, cable outlet | Tiesus |
| Electrical connection 2, connection technology | M12x1, A-coded in accordance with EN 61076-2-101 |
| Electrical connection 2, number of pins/wires | 8 |
| Electrical connection 2, occupied pins/wires | 8 |
| Electrical connection 2, type of mounting | Screw locking with SW14 |
| Electrical connection 3, function | Controller side |
| Electrical connection 3, design | apvalus |
| Electrical connection 3, connection type | Kištuko lizdas |
| Electrical connection 3, cable outlet | Tiesus |
| Electrical connection 3, connection technology | M12x1, A-coded in accordance with EN 61076-2-101 |
| Electrical connection 3, number of pins/wires | 5 |
| Electrical connection 3, occupied pins/wires | 4 |
| Electrical connection 3, type of mounting | Screw lock |
| Nominalus DC įtampos lygis | 0 ... 30 V |
| Nominalus AC įtampos lygis | 0 ... 30 V |
| Leistina srovės apkrova prie 40°C | 2 A |
| Cable length 1 | 0,15 m |
| Kabelio priedas | Standartas |
| Cable diameter 1 | 6,3 mm |
| Tolerance for cable diameter 1 | ± 0,2 mm |
| Kabelio struktūra | 8x0,25 Ekranuotas |
| Nominalus laidininko skerspjūvis | 0,25 mm ² |
| Apsaugos klasė | IP65 IP67 |
| Note on degree of protection | Sumontuotas |
| Aplinkos temperatūra | -25 ... 80 °C |
| Aplinkos temperatūra esant lankščiai kabelių instaliacijai | -5 ... 80 °C |
| CE ženklas (žr. deklaraciją) | atitinka EU-EMV reikalvumus |

| Savybės | Reikšmė |
|--|-------------------------------|
| UKCA marking (see declaration of conformity) | To UK instructions for EMC |
| PWIS conformity | VDMA24364-B1/B2-L |
| Informacija | atitinka RoHS Be halogeno |
| Užterštumo laipsnis | 3 |
| Atsparumo korozijai klasė CRC | 2 - Moderate corrosion stress |
| Material cable sheath | TPE-U(PUR) |
| Kabelio apvalkalo spalva | pilkas |
| Material housing | TPE-U(PUR) |
| Korpuso spalva | Juodas |
| Material screw-type lock | Nickel-plated die-cast zinc |
| Material seals | NBR |
| Material electrical contact | Brass, gold-plated |