

Pajungimo kabelis NEBC-D12G4-ES-5-S-D12G4-ET

Gaminio numeris: 8040449

FESTO



Tech. Duomenys

Savybės	Reikšmė
Cable identification	With inscription label holder
Prijungimo dažnis	50
Produkto svoris	331,5 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	apvalus
Electrical connection 1, connection type	Kištukas
Electrical connection 1, cable outlet	Tiesus
Electrical connection 1, connection technology	M12x1, D-coded in accordance with EN 61076-2-101
Electrical connection 1, number of pins/wires	4
Electrical connection 1, occupied pins/wires	4
Electrical connection 1, type of mounting	Screw-type lock with hex A/F 13 mm and longitudinal knurl
Electrical connection 2, function	Controller side
Electrical connection 2, design	apvalus
Electrical connection 2, connection type	Kištukas
Electrical connection 2, cable outlet	Tiesus
Electrical connection 2, connection technology	M12x1, D-coded in accordance with EN 61076-2-101
Electrical connection 2, number of pins/wires	4
Electrical connection 2, occupied pins/wires	4
Electrical connection 2, type of mounting	Screw-type lock with hex A/F 13 mm and longitudinal knurl
Nominalus DC įtampos lygis	0 ... 30 V
Leistina srovės apkrova prie 40°C	4 A
Atsparumas smūgiams	0,8 kV
Note on surge resistance	Due to screening, a leakage flow of up to 20 mA is permissible.
Perdavimo nustatymai	In accordance with category 5, EN 50173, class D In accordance with category 5, ISO/IEC 11801, class D
Etherneto kabelio specifikacija	Tipas: CAT 5
Kabelio ilgis	5 m
Kabelio priedas	Suitable for energy chains
Laido bandymo sąlygos	Atsparumas lenkimui pagal Festo normas, bandymo sąlygos pagal užklausimą. Bandymas pagal užklausimą Energy chain > 2 million cycles, bending radius 100 mm
Bending radius, fixed cable installation	≥ 40 mm
Bending radius, flexible cable installation	≥ 100 mm
Kabelio skersmuo	6,7 mm
Kabelio skersmens tolerancija	± 0,3 mm
Kabelio struktūra	4 x 0.34 mm ² (star quad)
Nominalus laidininko skerspjūvis	0,34 mm ²
Nominal conductor cross section (AWG)	AWG22
Apsaugos klasė	IP65 IP67
Special characteristics	alyvai atsparūs
Aplinkos temperatūra	-25 ... 80 °C
Aplinkos temperatūra esant lankščiai kabelių instaliacijai	-20 ... 60 °C
Saugojimo temperatūra	-25 ... 80 °C
CE ženklas (žr. deklaraciją)	in accordance with EU RoHS directive

Savybės	Reikšmė
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Informacija	atitinka RoHS
Užterštumo laipsnis	3
Atsparumo korozijai klasė CRC	1 - Low corrosion stress
Material cable sheath	TPE-U(PUR)
Kabelio apvalkalo spalva	žalias
Material housing	TPE-U(PUR)
Korpuso spalva	Juodas
Material screw-type lock	Nickel-plated die-cast zinc
Material electrical contact	Žalvaris Auksoota
Material insulation	PE
Material threaded sleeve	Cinkuota