


連接電纜

NEBS-SM12G12-E-0.5-N-LE12

料號: 3947401

FESTO



技術參數

特性	值
符合標準	EN 61076-2-101
Cable identification	具配件
連接頻率	100
Electrical connection 1, function	Field device side
Electrical connection 1, design	圓形
Electrical connection 1, connection type	插頭
Electrical connection 1, cable outlet	直的
Electrical connection 1, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 1, number of pins/wires	12
Electrical connection 1, occupied pins/wires	12
Electrical connection 1, type of mounting	Screw locking with hex SW13
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	電纜
Electrical connection 2, connection technology	開放式終端
Electrical connection 2, number of pins/wires	12
Electrical connection 2, occupied pins/wires	12
工作電壓範圍 DC	0 ... 30 V
工作電壓範圍 AC	0 ... 30 V
在40°C時的可接受電流負載	1.5 A
浪湧強度	0.5 kV
電纜長度	0.5 m
電纜屬性	Suitable for energy chains
電纜的測試條件	視需求的測試條件
Bending radius, fixed cable installation	>= 32 mm
Bending radius, flexible cable installation	>= 65 mm
電纜直徑	6.5 mm
電纜結構	12x0,25
導體的額定截面	0.25 mm ²
導線末端	Cut off bluntly
防護等級	IP67
Note on degree of protection	裝配狀態
環境溫度	-5 ... 70 °C
Ambient temperature with flexible cable installation	-5 ... 70 °C
CE 符號 (參見符合的標準)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
材料備註	符合 RoHS
污染程度	3
耐腐蝕等級 CRC	1 - Low corrosion stress
Material cable sheath	TPE-U(PUR)
電纜外套顏色	黑色
Material housing	TPE-U(PUR)
外殼顏色	黑色
Material screw-type lock	Nickel-plated die-cast zinc
Material electrical contact	Brass, gold-plated