

# 塑料氣管

## PUN-4X0,75-BL-500

料號: 525746

FESTO

具有標準外徑的氣管，用於QS快插接頭，CN和CK 聚氨酯 接頭  
(不可用於食品行業)。



### 技術參數

特性	值
外徑	4 mm
與流量相關的彎曲半徑	17 mm
內徑	2.6 mm
最小彎曲半徑	8 mm
Instructions for use	TPE-U Ester based The plastic tubing can only be installed in contact with cables if the sheathing is free from phosphoric acid esters. Otherwise the plastic tubing can get damaged.
Tubing characteristics	Suitable for energy chains
Operating pressure for entire temperature range	-0.095 ... 0.7 MPa
操作壓力的完整溫度範圍	-0.95 ... 7 bar
Operating pressure for entire temperature range	-13.775 ... 101.5 psi
Temperature-dependent operating pressure	-0.095 ... 1 MPa
溫度取決於操作壓力	-0.95 ... 10 bar
Temperature-dependent operating pressure	-13.775 ... 145 psi
授權	TÜV
認證核發部門	B 013277 0506 00
操作介質	壓縮空氣符合 ISO8573-1:2010 [7:-:-]
Material fire test	UL94 HB
PWIS conformity	VDMA24364-B2-L
環境溫度	-35 ... 60 °C
產品重量視長度而定	0.0089 kg/m
氣壓連接	For push-in connector outside diameter 4 mm 用於倒鉤接頭內徑 3 mm 具螺母 用於倒鉤接頭內徑 3 mm
顏色	藍色
肖氏硬度	D 52 +/-3
材料備註	符合 RoHS
Material tubing	TPE-U(PU)