



連接電纜

NEBV-A1W3F-P-K-0.3-N-M12W3

料號: 3679771

FESTO



技術參數

特性	值
授權	c CSA us (OL)
工作狀態顯示	黃色 LED
附加功能	Protective circuit
Cable identification	Without inscription label holder
產品重量	60 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	有角的
Electrical connection 1, connection type	插頭插座
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connection technology	Plug pattern type A based on EN 175301-803
Electrical connection 1, number of pins/wires	4
Electrical connection 1, occupied pins/wires	4
Electrical connection 1, type of mounting	通過M3中心螺絲安裝在電磁閥上
Electrical connection 2, function	Controller side
Electrical connection 2, design	圓形
Electrical connection 2, connection type	插頭
Electrical connection 2, cable outlet	Angled
Electrical connection 2, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 2, number of pins/wires	5
Electrical connection 2, occupied pins/wires	3
Electrical connection 2, type of mounting	Screw locking with hex SW13
工作電壓範圍 DC	18 ... 30 V
額定工作電壓 DC	24 V
工作電壓範圍 AC	18 ... 30 V
額定工作電壓, AC	24 V
在40°C時的可接受電流負載	4 A
浪湧強度	0.8 kV
保護性接地	已可供應
電纜長度	0.3 m
電纜屬性	標準
電纜的測試條件	視需求的測試條件
電纜直徑	5.9 mm
電纜直徑公差	± 0,3 mm
電纜結構	3x0,75
防護等級	IP67
Note on degree of protection	裝配狀態
環境溫度	-25 ... 80 °C
Ambient temperature with flexible cable installation	-25 ... 80 °C
CE 符號 (參見符合的標準)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364 zone III
材料備註	符合 RoHS
污染程度	3
耐腐蝕等級 CRC	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PUR)
電纜外套顏色	灰色

特性	值
Material housing	TPE-U(PUR)
外殼顏色	黑色
Material of union nut	牙鑄鋅 鍍鎳
Material insulation	PP