


連接電纜


NEBC-C-S1WA9HS-K- -N-B-LE5-PT-S10

料號: 4106124

FESTO



代表範例



技術參數

特性	值
基於標準	DIN 47100
通訊協定	I-Port
Cable identification	Without inscription label holder
連接頻率	50
Electrical connection 1, function	Field device side
Electrical connection 1, design	有角的
Electrical connection 1, connection type	插頭插座
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connection technology	Sub-D
Electrical connection 1, number of pins/wires	9
Electrical connection 1, occupied pins/wires	5
Electrical connection 1, type of mounting	2 screws 4-40 UNC With seal
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	電纜
Electrical connection 2, connection technology	開放式終端
Electrical connection 2, number of pins/wires	5
工作電壓範圍 DC	0 ... 30 V
在40°C時的可接受電流負載	5.2 A
保護性接地	還未上市
電纜長度	0.5 ... 20 m
電纜屬性	標準
Bending radius, fixed cable installation	>= 26 mm
Bending radius, flexible cable installation	>= 78 mm
電纜直徑	6.5 mm
電纜直徑公差	± 0,1 mm
電纜結構	5x0,5
導體的額定截面	0.5 mm ²
防護等級	IP65 IP67 IP69K
Note on degree of protection	裝配狀態
Special characteristics	Easy to clean
環境溫度	-5 ... 60 °C
Ambient temperature with flexible cable installation	-5 ... 60 °C
儲藏溫度	-20 ... 40 °C
CE 符號 (參見符合的標準)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
材料備註	符合 RoHS
污染程度	3
耐腐蝕等級 CRC	3 - High corrosion stress
Material cable sheath	PVC
電纜外套顏色	灰色
Material housing	PA-加強
外殼顏色	灰色
Material screws	不鏽鋼
Material seals	EPDM
Material electrical contact	Gold-plated bronze
Material insulation	PVC