


編程電纜

VAVE-P8-VPS

料號: 570971

FESTO



技術參數

| 特性 | 值 |
|--|---|
| 符合標準 | DIN 47100 EN 61076-2-101 |
| 設計結構 | T-distributor with cable on controller side |
| Distributor type | 1 to 2 |
| 附加功能 | Programming interface for proportional pressure regulator |
| Cable identification | Without inscription label holder |
| Electrical connection 1, function | Field device side |
| Electrical connection 1, design | 圓形 |
| Electrical connection 1, connection type | 插頭插座 |
| Electrical connection 1, cable outlet | 直的 |
| Electrical connection 1, connection technology | M12x1, A-coded in accordance with EN 61076-2-101 |
| Electrical connection 1, number of pins/wires | 8 |
| Electrical connection 1, occupied pins/wires | 8 |
| Electrical connection 1, type of mounting | Screw locking with SW14 |
| Electrical connection 2, function | Controller side |
| Electrical connection 2, design | 圓形 |
| Electrical connection 2, connection type | 插頭 |
| Electrical connection 2, cable outlet | 直的 |
| Electrical connection 2, connection technology | M12x1, A-coded in accordance with EN 61076-2-101 |
| Electrical connection 2, number of pins/wires | 8 |
| Electrical connection 2, occupied pins/wires | 8 |
| Electrical connection 2, type of mounting | Screw locking with SW14 |
| Electrical connection 3, function | Controller side |
| Electrical connection 3, design | 圓形 |
| Electrical connection 3, connection type | 插頭插座 |
| Electrical connection 3, cable outlet | 直的 |
| Electrical connection 3, connection technology | M12x1, A-coded in accordance with EN 61076-2-101 |
| Electrical connection 3, number of pins/wires | 5 |
| Electrical connection 3, occupied pins/wires | 4 |
| Electrical connection 3, type of mounting | Screw lock |
| 工作電壓範圍 DC | 0 ... 30 V |
| 工作電壓範圍 AC | 0 ... 30 V |
| 在40°C時的可接受電流負載 | 2 A |
| Cable length 1 | 0.15 m |
| 電纜屬性 | 標準 |
| Cable diameter 1 | 6.3 mm |
| Tolerance for cable diameter 1 | ± 0,2 mm |
| 電纜結構 | 8x0,25 已屏蔽 |
| 導體的額定截面 | 0.25 mm ² |
| 防護等級 | IP65 IP67 |
| Note on degree of protection | 裝配狀態 |
| 環境溫度 | -25 ... 80 °C |
| Ambient temperature with flexible cable installation | -5 ... 80 °C |
| CE 符號 (參見符合的標準) | 根據 EU-EMV 指導原則 |

| 特性 | 值 |
|--|-------------------------------|
| UKCA marking (see declaration of conformity) | To UK instructions for EMC |
| PWIS conformity | VDMA24364-B1/B2-L |
| 材料備註 | 符合 RoHS 不含鹵素 |
| 污染程度 | 3 |
| 耐腐蝕等級 CRC | 2 - Moderate corrosion stress |
| Material cable sheath | TPE-U(PUR) |
| 電纜外套顏色 | 灰色 |
| Material housing | TPE-U(PUR) |
| 外殼顏色 | 黑色 |
| Material screw-type lock | Nickel-plated die-cast zinc |
| Material seals | NBR |
| Material electrical contact | Brass, gold-plated |