


旋轉驅動器

DAPS-0360-090-R-F0710

料號: 533423

FESTO

雙動，氣接口符合 VDI/VDE 3845, Namur 閥可直接法蘭安裝。



技術參數

特性	值
驅動器尺寸	0360
法蘭孔的樣式	F07 F10
擺動角度	90 deg
0°時的端點位置調節範圍	-1 ... 9 deg
軸連接深度	24.3 mm
連接件接口符合標準	ISO 5211
緩衝	無緩衝
裝配位置	任何
操作模式	雙動
設計結構	軛鐵動力學
位置檢測	無
關閉方向	右側-關閉
閥的接口符合標準	VDI/VDE 3845 (NAMUR)
安全完整性等級 (SIL)	產品可用於在 SRP/CS 高達 SIL2 的低需求
Operating pressure MPa	0.1 ... 0.84 MPa
操作壓力	1 ... 8.4 bar
Nominal operating pressure	0.56 MPa
額定操作壓力	5.6 bar
Max. swivel frequency at 0.6 MPa (6 bar, 87 psi)	1 Hz
CE 符號 (參見符合的標準)	根據 EU-Ex 防爆指導原則 (ATEX)
UKCA marking (see declaration of conformity)	To UK EX instructions
認證核發部門	TÜV Nord 212170801
ATEX(防爆) 標準-氣體	II 2G
ATEX(防爆) 標準-灰塵	II 2D
防氣爆	Ex h IIC T6...T3 Gb X
防塵爆	Ex h IIIC T85°C...T200°C Db X
周遭防爆溫度	-20°C ≤ Ta ≤ +60°C
操作介質	壓縮空氣符合 ISO8573-1:2010 [7:4:4]
注意: 操作和嚮導介質	潤滑操作可行 (隨後需要進一步操作)
耐腐蝕等級 CRC	3 - High corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
環境溫度	-20 ... 80 °C
額定操作壓力以及 0°旋轉角度時的扭矩	360 Nm
扭矩在額定操作壓力具 50° 擺動角度	180 Nm
扭矩在額定操作壓力具 90° 擺動角度	270 Nm
Note about the torque	The operating torque of the actuator must not be higher than the maximum permissible torque listed in ISO 5211, with reference to the size of the mounting flange and of the coupling.
Air consumption at 0.6 MPa (6 bar, 87 psi) per cycle 0°-nominal swivel angle-0°	12.6 l
產品重量	6,500 g
柱軸連接	T22
氣壓連接	G1/8
材料備註	符合 RoHS

特性	值
Material cover	鍛造鋁合金
Material seals	FPM NBR PUR
Material housing	鍛造鋁合金
Material screws	高合金鋼
Material shaft	高合金鋼
軸的材料編號	1.4305