


連接電纜

NEBV-S1W37-KM-5-LE27

料號: 543275

FESTO

用於多針腳插頭連接至閥島 VTSA 及 VTSA-F, 用於最多 22 個電磁線圈, 具Sub-D插頭插座, 27-pin.



技術參數

特性	值
應用領域	Only for multi-pin plug connection valve terminal VTSA/VTSA-F
符合標準	DIN 47100
Cable identification	With inscription label holder
產品重量	1,124 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	有角的
Electrical connection 1, connection type	插頭插座
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connection technology	Sub-D
Electrical connection 1, number of pins/wires	37
Electrical connection 1, occupied pins/wires	27
Electrical connection 1, type of mounting	3x M4 screws
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	電纜
Electrical connection 2, connection technology	開放式終端
Electrical connection 2, number of pins/wires	27
Electrical connection 2, occupied pins/wires	27
工作電壓範圍 DC	0 ... 30 V
在40°C時的可接受電流負載	2 A
浪湧強度	1 kV
電纜長度	5 m
電纜屬性	標準
電纜的測試條件	視需求的測試條件
Bending radius, fixed cable installation	>= 44 mm
Bending radius, flexible cable installation	>= 82 mm
電纜直徑	10.9 mm
電纜結構	27x0,34
導體的額定截面	0.34 mm ²
防護等級	IP65 NEMA 4
Note on degree of protection	裝配狀態
環境溫度	-5 ... 50 °C
CE 符號 (參見符合的標準)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
材料備註	符合 RoHS
耐腐蝕等級 CRC	2 - Moderate corrosion stress
Material cable sheath	PVC
電纜外套顏色	灰色
Material housing	PA
Material insulation	PVC