



編碼器電纜

NEBM-M12G12-RS-15-N-S1G15

料號: 571915

FESTO



技術參數

特性	值
符合標準	DIN 47100 EN 61984
Cable identification	Without inscription label holder
Electrical connection 1, function	Field device side
Electrical connection 1, design	圓形
Electrical connection 1, connection type	插頭插座
Electrical connection 1, cable outlet	直的
Electrical connection 1, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 1, number of pins/wires	12
Electrical connection 1, occupied pins/wires	11
Electrical connection 1, type of mounting	Screw locking with SW14
Electrical connection 2, function	Controller side
Electrical connection 2, design	有角的
Electrical connection 2, connection type	插頭
Electrical connection 2, cable outlet	直的
Electrical connection 2, connection technology	Sub-D
Electrical connection 2, number of pins/wires	15
Electrical connection 2, occupied pins/wires	11
Electrical connection 2, type of mounting	Screw locking with hexagonal SW18
工作電壓範圍 DC	0 ... 30 V
額定工作電壓 DC	24 V
工作電壓範圍 AC	0 ... 30 V
額定工作電壓, AC	24 V
在40°C時的可接受電流負載	1 A
電纜長度	15 m
電纜屬性	用於機器人
Bending radius, flexible cable installation	>= 70 mm
電纜直徑	7 mm
電纜結構	12x0,14 已屏蔽
導體的額定截面	0.14 mm ²
防護等級	IP67
Note on degree of protection	IP50 for plug connector Sub-D 裝配狀態
環境溫度	-25 ... 80 °C
Ambient temperature with flexible cable installation	0 ... 40 °C
CE 符號 (參見符合的標準)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
材料備註	符合 RoHS
污染程度	3
耐腐蝕等級 CRC	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PUR)
電纜外套顏色	黑色
Material housing	TPE-U(PUR)
Material of union nut	Nickel-plated die-cast zinc
Material seals	NBR
Material insulation	TPE-E