


pancake cylinder
DPCB-N-...-1 1/2"- -
料號: 8104882



代表範例

技術參數

整體數據表 – 個別數值取決於您的配置.

特性	值
行程	0.125 ... 4 "
活塞直徑	1 1/2"
活塞桿螺紋	3/8-24 UNF-2B 3/8-24 UNF-2A 3/8-16 UNC-2B 3/8-16 UNC-2A
緩衝	No cushioning P: 兩端具彈性緩衝環/板 Elastic cushioning rings/plates, at front Elastic cushioning rings/plates, at rear
裝配位置	任何
操作模式	雙動 單動 推的動作 拉的動作
活塞桿末端	外螺紋 內螺紋 No thread
設計結構	活塞 活塞桿 氣壓缸缸筒
位置檢測	用於近接感測器
多樣型	Increased chemical resistance 延伸活塞桿 低摩擦 雙出活塞桿 Through, hollow piston rod 溫度範圍 -40 - 80 °C Scraper made of NBR Reinforced end cap Square lid shape With sensor mounting rail with sensor mounting rail rotated 90° with sensor mounting rail rotated 180° with sensor mounting rail rotated 270° Compressed air connection, rotated 90° Compressed air connection, rotated 180° Compressed air connection, rotated 270°
防止扭轉/導向	Double piston rod with end plate Double piston rod with end plate rotated 90° Double piston rod with end plate with recess and through-hole Double piston rod with end plate with recess and through-hole rotated 90°
操作壓力	15 ... 150 Psi

特性	值
操作介質	壓縮空氣符合 ISO8573-1:2010 [7:4:4]
注意: 操作和嚮導介質	潤滑操作可行 (隨後需要進一步操作)
PWIS conformity	VDMA24364 zone III
環境溫度	-25 ... 221 °F
產品重量	9.22 ... 10.84 Pound
安裝類型	Direct mounting on end cap via thread Direct mounting on bearing cap via thread Direct mounting on both sides via thread with swivelling rod eye on end cap rotated 90° with swivelling rod eye on end cap With through-hole on end cap With through-hole on bearing cap With through-hole on both sides With threaded flange on bearing cap With trunnion mounting on end cap With trunnion mounting on bearing cap 具配件 選配
氣壓連接	Female thread 1/8 NPT
材料備註	符合 RoHS
Material cover	鍛造鋁合金
Material of dynamic seals	FPM NBR
Material piston rod	high-alloy stainless steel, hard chrome plated
Material cylinder barrel	Reinforced composite material