



馬達電纜

NEBM-SF1W31-EH-10-Q15N-LE28

料號: 8113309

FESTO



技術參數

特性	值
符合標準	DIN 47100
Cable identification	Without inscription label holder
連接頻率	30
產品重量	2,960 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	有角的
Electrical connection 1, connection type	插頭
Electrical connection 1, cable outlet	Angled
Electrical connection 1, note about the cable outlet	90°
Electrical connection 1, connection technology	Connection pattern F1
Electrical connection 1, number of pins/wires	31
Electrical connection 1, occupied pins/wires	31
Electrical connection 1, type of mounting	Snap-in locking
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	電纜
Electrical connection 2, connection technology	開放式終端
Electrical connection 2, number of pins/wires	28
Electrical connection 2, occupied pins/wires	28
工作電壓範圍 DC	0 ... 50 V
額定工作電壓 DC	24 V
在40°C時的可接受電流負載	0.5 A
浪湧強度	0.25 kV
電纜長度	10 m
電纜屬性	Suitable for energy chains
電纜的測試條件	視需求的測試條件
Bending radius, fixed cable installation	>= 49.5 mm
Bending radius, flexible cable installation	>= 74.25 mm
電纜直徑	9.9 mm
電纜直徑公差	± 0.2 mm
電纜結構	1x(6x0,35)+2x(4x0,15)
導體的額定截面	0.35 mm ² 0.15 mm ²
導線末端	導線末端套圈
防護等級	IP20
Note on degree of protection	裝配狀態
環境溫度	-20 ... 75 °C
Ambient temperature with flexible cable installation	-5 ... 70 °C
儲藏溫度	-25 ... 55 °C
CE 符號 (參見符合的標準)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364 zone III
材料備註	符合 RoHS
污染程度	1
耐腐蝕等級 CRC	1 - Low corrosion stress
Material cable sheath	TPE-U(PUR)
電纜外套顏色	黑色
Material housing	PA
外殼顏色	黑色
Material electrical contact	Copper alloy, tinned