


螺桿軸 ELGT-BS-120- -

料號: 8121225

FESTO



代表範例

技術參數

整體數據表 – 個別數值取決於您的配置。

特性	值
工作行程	100 ... 1,100 mm
尺寸	120
備用行程	0 mm
反向空隙	<= 0.15 µm
螺桿直徑	15 ... 16 mm
螺桿螺距	10 ... 20 mm/U
裝配位置	任何
導向	迴圈滾珠軸承導向
設計結構	機電式直線軸 具迴圈滾珠軸承螺桿
馬達類型	步進馬達 伺服馬達
螺桿類型	滾珠螺紋螺桿
多樣型	Recommended for production facilities for the manufacture of lithium-ion batteries
最大加速度	15 m/s ²
最高速度	3,000 1/min 0.5 ... 1 m/s
重複精度	±0,02 mm
循環功率	100 %
PWIS conformity	VDMA24364 zone III
RSBP classification to CD-0033	F1a
無塵室等級	ISO class 8
防護等級	IP20
環境溫度	0 ... 50 °C
固定的輸送力	805 ... 1,265 N
轉動面積矩 2nd 度ly	966E+03 mm ⁴
轉動面積矩 2nd 度lz	6,011E+03 mm ⁴
No-load torque at maximum travel speed	0.3 Nm
No-load torque at minimum travel speed	0.08 Nm
最大輸出力Fy	6,800 N
最大輸出力Fz	8,090 N
Fy with theoretical service life of 100 km (from a guide perspective only)	25,051 N
Fz with theoretical service life of 100 km (from a guide perspective only)	29,804 N
最大扭矩Mx	300 Nm
最大扭矩My	310 Nm
最大扭矩Mz	310 Nm
Mx with theoretical service life of 100 km (from a guide perspective only)	1,105 Nm
My with theoretical service life of 100 km (from a guide perspective only)	1,142 Nm

特性	值
Mz with theoretical service life of 100 km (from a guide perspective only)	1,142 Nm
驅動軸的最大徑向力	290 N
最大進給力 Fx	805 ... 1,265 N
質量慣性扭矩	506E+03 mm ⁴
每公尺行程的質量慣性力矩JH	0.2522 ... 0.3453 kgcm ²
每kg工作負荷的質量慣性力矩JL	0.0253 ... 0.1013 kgcm ²
質量慣性力矩, JO	0.1306 ... 0.2654 kgcm ²
JW 的質量慣性力矩用於額外滑軌	0.0448 ... 0.1793 kgcm ²
恆定進給	10 ... 20 mm/U
運動質量	2,019 ... 2,036 g
產品重量	6,454 ... 18,880 g
額外滑塊重量	1,770 g
0 mm行程時的基本重量	5,235 ... 5,259 g
每 10 mm 行程所增加的重量	124 g
Dynamic deflection (load moved)	0.05% of the axis length, max. 0.5 mm
Static deflection (load at standstill)	0.1% of the axis length
Interface code, actuator	T46
Material of end caps	Die-cast aluminium, painted
Material of profile	Anodised wrought aluminium alloy
材料備註	符合 RoHS
Material drive cover	Die-cast aluminium, painted
Material guide slide	鋼
Material guide rail	鋼
Material slide	Anodised wrought aluminium alloy
Material spindle nut	鋼
Material spindle	鋼