



連接電纜

NEBB-M12W5-P-5-LE3

料號: 8066680

FESTO



技術參數

特性	值
符合標準	Core colours and connection numbers to EN 60947-5-2 EN 61076-2-101
Cable identification	With inscription label holder
Electrical connection 1, function	Field device side
Electrical connection 1, design	圓形
Electrical connection 1, connection type	插頭插座
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 1, number of pins/wires	5
Electrical connection 1, occupied pins/wires	3
Electrical connection 1, type of mounting	Screw lock with A/F13
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	電纜
Electrical connection 2, connection technology	開放式終端
Electrical connection 2, number of pins/wires	3
Electrical connection 2, occupied pins/wires	3
工作電壓範圍 DC	0 ... 250 V
工作電壓範圍 AC	0 ... 250 V
在40°C時的可接受電流負載	4 A
浪湧強度	2.5 kV
電纜長度	5 m
電纜屬性	用於靜態應用
電纜的測試條件	視需求的測試條件
Bending radius, fixed cable installation	>= 12 mm
電纜直徑	3.8 mm
電纜結構	3x0,25
導體的額定截面	0.25 mm ²
導線末端	Sheath removed Cut off bluntly
防護等級	IP65 IP68 IP69K
Note on degree of protection	裝配狀態
環境溫度	-25 ... 70 °C
CE 符號 (參見符合的標準)	根據 EU 低電壓設備指導原則 in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
無塵室等級	ISO class 4
材料備註	符合 RoHS
污染程度	3
耐腐蝕等級 CRC	2 - Moderate corrosion stress
Material cable sheath	PVC
電纜外套顏色	灰色
Material housing	TPE-U(PU)

特性	值
外殼顏色	黑色
Material screw-type lock	Nickel-plated brass
Material seals	NBR
Material electrical contact	Gold-plated copper alloy
Material insulation	PVC