


電接口
VAEM-L1-S-12-AP
 料號: 8081922



技術參數

特性	值
尺寸 寬(W) x 長(L) x 高(H)	42 mm x 91 mm x 30 mm
連接的位置	於頂部
Diagnostics via LED	Diagnostics per module Power supply load
Diagnostics per internal communication	Load switch-off Electronics/sensors overvoltage Load overvoltage Electronics/sensors undervoltage Load undervoltage
閥位的最大數量	12
電磁線圈的最大數量	24
極性保護	是
Module parameters	Response in error state Configuration of voltage monitoring load supply PL
防護(短路)	每個通道的內部電子保險絲保護
Intrinsic current consumption at nominal operating voltage for electronics/sensors	典型的34 mA
Intrinsic current consumption at nominal operating voltage load	典型的 16 mA
Nominal operating voltage DC for electronics/sensors	24 V
額定工作電壓, DC 輸出	24 V
能源不足緩衝	10 ms
Mains buffering of load	3 ms
Permissible voltage fluctuations for electronics/sensors	± 25 %
Permissible voltage fluctuations, load	± 10 %
Max. power supply	2 x 4 A (external fuse required)
Power supply, function	Incoming electronics/sensors and load
Power supply, type of connection	插頭
Power supply, connection technology	M8x1, A-coded to EN 61076-2-104
Power supply, number of pins/wires	4
Power transmission, function	Outgoing electronics/sensors and load
Power transmission, connection type	插頭插座
Power transmission, connection technology	M8x1, A-coded to EN 61076-2-104
Power transmission, number of pins/wires	4
Communication interface, connection type	2x 插座
Communication interface, connection technology	M8x1, D-coded to EN 61076-2-114
Communication interface, number of pins/wires	4
Communication interface, function	System communication XF10 IN / XF20 OUT
Communication interface, protocol	AP-COM
Communication interface, screening	是
CE 符號 (參見符合的標準)	根據 EU-EMV 指導原則
UKCA marking (see declaration of conformity)	To UK instructions for EMC
KC mark	KC-EMV
最大行列長度	50 m system communication
耐腐蝕等級 CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
儲藏溫度	-20 ... 60 °C

特性	值
相對空氣濕度	5 - 95 % 非冷凝
直接和間接接觸保護	Protective extra-low voltage with safe disconnection (PELV) Protection by safety extra-low voltage (SELV)
Note regarding operating voltage	SELV/PELV fixed power supplies required Note voltage drop
防護等級	IP65 IP67
Note on degree of protection	裝配狀態 Unused connections sealed
環境溫度	-5 ... 60 °C
授權	RCM Mark c UL us - Recognized (OL)
Nominal altitude of use	<= 2000 m NHN
產品重量	76 g
安裝類型	收緊
Material housing	PA-加強
Material threaded sleeve	鍍鎳黃銅
材料備註	符合 RoHS