


Wide range of configuration options

→ www.festo.com/en/engineering



- Three sizes:
MS4 – grid
dimension 40 mm
MS6 – grid
dimension 62 mm
MS12 – grid
dimension 124 mm
- Modular
- Easy to assemble
- Broad range of functions
- Compact with high flow rates
- Modern design
- Wide choice of variants
- Integrated safety functions



Specified types in accordance with
ATEX directive for potentially
explosive atmospheres

→ www.festo.com/en/ex

MS series service units

Product range overview

FESTO

Type	Size	Pneumatic connection in housing	Connecting plate	Pressure regulation range [bar]						Grade of filtration [µm]			
				0.05 ... 0.7	0.05 ... 2.5	0.1 ... 4	0.3 ... 7	0.1 ... 12	0.5 ... 16	0.01	1	5	40
Code			AG...	D2	D4	D5	D6	D7	D8	A	B	C	E
Service units													
MSB-FRC 	4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	■	■	–	–	–	■	■
	6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	■	■	–	–	–	■	■
	12	–											
Service unit combinations (further variants can be ordered using the configurator → www.festo.com/en/engineering)													
MSB 	4	G1/4	G1/8, G1/4, G3/8	–	–	–	■	■	–	–	–	■	■
	6	G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	■	■	–	–	–	■	■
	12	–											
Individual devices													
Filter regulators MS-LFR 	4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	■	■	■	–	–	–	■	■
	6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	■	■	■	■	–	–	■	■
	12	–	G1, G1 1/4, G1 1/2, G2	–	–	–	■	■	■	–	–	■	■
Filters MS-LF 	4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	–	–	■	■
	6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	–	–	■	■
	12	–	G1, G1 1/4, G1 1/2, G2	–	–	–	–	–	–	–	–	■	■
Fine and micro filters MS-LFM 	4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	■	■	–	–
	6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	■	■	–	–
	12	–	G1, G1 1/4, G1 1/2, G2	–	–	–	–	–	–	■	■	–	–
Activated carbon filters MS-LFX 	4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	–	–	–	–
	6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	–	–	–	–
	12	–	G1, G1 1/4, G1 1/2, G2	–	–	–	–	–	–	–	–	–	–
Pressure regulators MS-LR 	4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	■	■	■	–	–	–	–	–
	6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	■	■	■	■	–	–	–	–
	12	–	G1, G1 1/4, G1 1/2, G2	–	–	–	■	■	■	–	–	–	–
Pressure regulators MS-LRB 	4	G1/4	G1/8, G1/4, G3/8	–	–	■	■	■	–	–	–	–	–
	6	G1/2	G1/4, G3/8, G1/2, G3/4	–	–	■	■	■	■	–	–	–	–
	12	–											
Precision pressure regulators MS-LRP 	4	–											
	6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	■	■	■	–	■	–	–	–	–	–
	12	–											
Precision pressure regulators MS-LRPB 	4	–											
	6	G1/2	G1/4, G3/8, G1/2, G3/4	■	■	■	–	■	–	–	–	–	–
	12	–											

MS series service units

Product range overview


FESTO

Type	Size	Bowl guard		Condensate drains				Pressure indicator					Actuator lock		Options		→ Page
		Plastic bowl guard	Metal bowl	Manual rotary	Semi-automatic	Fully automatic	External, fully-automatic, electrical	Cover plate (without pressure gauge)	Integrated MS pressure gauge	Adapter for EN pressure gauge G1/8	Adapter for EN pressure gauge G1/4	Pressure sensor with display	Rotary knob, lockable	Rotary knob, long	Silencer	Flow direction from right to left	
Code		R	U	M	H	V	E...	VS	AG	A8	A4	AD...	AS	LD	S	Z	
Service units																	
MSB-FRC	4	■	–	■	–	■	–	–	■	–	–	–	■	–	–	■	2-2
	6	■	■	■	–	■	–	–	■	–	–	–	■	–	–	■	
	12	–	–	–	–	–	–	–	–	–	–	–	–	–	–	–	
Service unit combinations																	
MSB	4	■	■	■	–	■	–	–	■	–	–	–	■	–	–	■	2-2
	6	■	■	■	–	■	–	–	■	–	–	–	■	–	–	■	
	12	–	–	–	–	–	–	–	–	–	–	–	–	–	–	–	
Individual devices																	
Filter regulators MS-LFR	4	■	■	■	■	■	–	■	■	■	■	■	■	■	–	■	3-2
	6	■	■	■	■	■	■	■	■	–	■	■	■	■	–	■	
	12	–	■	■	–	■	■	■	■	–	■	–	■	■	–	■	3-18
Filters MS-LF	4	■	■	■	■	■	–	–	–	–	–	–	–	–	–	■	4-2, 4-4
	6	■	■	■	■	■	■	–	–	–	–	–	–	–	–	■	
	12	–	■	■	–	■	■	–	–	–	–	–	–	–	–	■	4-26, 4-28
Fine and micro filters MS-LFM	4	■	■	■	■	■	–	–	–	–	–	–	–	–	–	■	4-2, 4-12
	6	■	■	■	■	■	■	–	–	–	–	–	–	–	–	■	
	12	–	■	■	–	■	■	–	–	–	–	–	–	–	–	■	4-26, 4-33
Activated carbon filters MS-LFX	4	■	■	■	–	–	–	–	–	–	–	–	–	–	–	■	4-2, 4-20
	6	■	■	■	–	–	–	–	–	–	–	–	–	–	–	■	
	12	–	■	–	–	–	–	–	–	–	–	–	–	–	–	■	4-26, 4-40
Pressure regulators MS-LR	4	–	–	–	–	–	–	■	■	■	■	■	■	■	–	■	5-2, 5-7
	6	–	–	–	–	–	–	■	■	–	■	■	■	■	–	■	
	12	–	–	–	–	–	–	■	■	–	■	–	■	■	–	■	5-58
Pressure regulators MS-LRB	4	–	–	–	–	–	–	■	■	■	■	■	■	■	–	■	5-2, 5-16
	6	–	–	–	–	–	–	■	■	–	■	■	■	■	–	■	
	12	–	–	–	–	–	–	–	–	–	–	–	–	–	–	–	
Precision pressure regulators MS-LRP	4	–	–	–	–	–	–	–	–	–	–	–	–	–	–	–	5-24, 5-29
	6	–	–	–	–	–	–	■	–	–	■	■	■	■	–	■	
	12	–	–	–	–	–	–	–	–	–	–	–	–	–	–	–	
Precision pressure regulators MS-LRPB	4	–	–	–	–	–	–	–	–	–	–	–	–	–	–	–	5-24, 5-38
	6	–	–	–	–	–	–	■	–	–	■	■	■	■	–	■	
	12	–	–	–	–	–	–	–	–	–	–	–	–	–	–	–	

MS series service units

Product range overview

FESTO

Type	Size	Pneumatic connection in housing	Connecting plate	Pressure regulation range [bar]				Supply voltage			
				0.3 ... 4	0.3 ... 7	0.5 ... 12	0.5 ... 16	24 V DC (connection pattern to EN 175301)	24 V DC (connection pattern M12 to DESINA)	110 V AC (connection pattern to EN 175301)	230 V AC (connection pattern to EN 175301)
Code			AG...	D5	D6	D7	D8	V24	V24P	V110	V230
Individual devices											
Electrical pressure regulators MS-LRE		4	–					–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	■	■	■	■	–	–	–
		12	–								
Lubricators MS-LOE		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	–
		12	–	G1, G1 1/4, G1 1/2, G2	–	–	–	–	–	–	–
On-off valves MS-EM(1)		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	–
		12	–	G1, G1 1/4, G1 1/2, G2	–	–	–	–	–	–	–
On-off valves MS-EE		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	■	–	■
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	■	–	■
		12	–	G1, G1 1/4, G1 1/2, G2	–	–	–	–	■	■	■
Soft-start valves MS-DL		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	–
		12	–	G1, G1 1/4, G1 1/2, G2	–	–	–	–	–	–	–
Soft-start valves MS-DE		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	■	–	■
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	■	–	■
		12	–	G1, G1 1/4, G1 1/2, G2	–	–	–	–	■	■	■
Membrane air dryers MS-LDM1		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	–
		12	–								
Branching modules MS-FRM		4	G1/8, G1/4	G1/8, G1/4, G3/8	–	–	–	–	–	–	–
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	–	–	–	–	–	–	–
		12	–	G1, G1 1/4, G1 1/2, G2	–	–	–	–	–	–	–
Flow sensors MS-SFE		4	–								
		6	G1/2	G1/2	–	–	–	–	–	–	–
		12	–								

MS series service units


Product range overview

FESTO

Type	Size	Bowl guard		Pressure indicator					Switch output		Options		→ Page
		Plastic bowl guard	Metal bowl	Cover plate (without pressure gauge)	Integrated MS pressure gauge	Adapter for EN pressure gauge G1/8	Adapter for EN pressure gauge G1/4	Pressure sensor with display	2x PNP	2x NPN	Silencer	Flow direction from right to left	
Individual devices													
Electrical pressure regulators MS-LRE	4	-											5-46
	6	-	-	■	■	-	■	-	-	-	-	■	
	12	-											
Lubricators MS-LOE	4	■	■	-	-	-	-	-	-	-	-	■	6-2
	6	■	■	-	-	-	-	-	-	-	-	■	
	12	-	■	-	-	-	-	-	-	-	-	-	■
On-off valves MS-EM(1)	4	-	-	■	■	■	■	■	-	-	■	■	7-2, 7-5
	6	-	-	■	■	-	■	■	-	-	■	■	
	12	-	-	■	■	-	■	-	-	-	■	■	7-30, 7-33
On-off valves MS-EE	4	-	-	■	■	■	■	■	-	-	■	■	7-2, 7-10
	6	-	-	■	■	-	■	■	-	-	■	■	
	12	-	-	■	■	-	■	-	-	-	■	■	7-30, 7-37
Soft-start valves MS-DL	4	-	-	■	■	■	■	■	-	-	-	■	7-2, 7-18
	6	-	-	■	■	-	■	■	-	-	-	■	
	12	-	-	■	■	-	■	-	-	-	-	■	7-30, 7-41
Soft-start valves MS-DE	4	-	-	■	■	■	■	■	-	-	-	■	7-2, 7-23
	6	-	-	■	■	-	■	■	-	-	-	■	
	12	-	-	■	■	-	■	-	-	-	-	■	7-30, 7-45
Membrane air dryers MS-LDM1	4	-	■	-	-	-	-	-	-	-	-	■	8-2
	6	-	■	-	-	-	-	-	-	-	-	■	
	12	-											
Branching modules MS-FRM	4	-	-	■	■	■	■	■	-	-	-	■	9-2
	6	-	-	■	■	-	■	■	-	-	-	■	
	12	-	-	■	-	-	-	-	-	-	-	-	9-14
Flow sensors MS-SFE	4	-											10-2
	6	-	-	-	-	-	-	-	■	■	-	■ ¹⁾	
	12	-											

1) To be ordered via configurator software only → www.festo.com/en/engineering

Wide range of configuration options
→ www.festo.com/en/engineering



- MS4 – grid
dimension 40 mm
MS6 – grid
dimension 62 mm
- Modular
- Easy to assemble
- Broad range of functions
- Compact with high flow rates
- Modern design
- Wide choice of variants
- Integrated safety functions


Specified types in accordance with
ATEX directive for potentially
explosive atmospheres
→ www.festo.com/en/ex



Service unit combinations MSB4/MSB6, MS series

Peripherals overview

FESTO



Note

The choice of accessories depends on the selected service unit combination.

Range of accessories

➔ Peripherals pages of the individual devices

Mounting attachments and accessories		➔ Page
1	Cover cap MS4/6-END	11-3
2	Connecting plate MS4/6-AG...	11-2
3	Module connector MS4/6-MV	11-7
4	Silencer U	11-10
5	Angled socket PEV-1/4-WD-LED	11-9
6	Plug socket MSSD-C-4P	11-9
7	Plug socket with cable KMEB	11-9
8	Plug socket MSSD-EB	11-9
9	Illuminating seal MEB-LD	11-9
10	Padlock LRVS-D	11-10
-	Mounting bracket (for service unit MSB-FRC) MS4/6-WP/WPB/WPM	11-5, 11-6

Service unit combinations MSB4/MSB6, MS series

Type codes

FESTO

		MSB	6	-	1/2	:	H7	N3	M2	-	WP
--	--	-----	---	---	-----	---	----	----	----	---	----

Series	
MSB	Service unit combination

Size	
4	Grid dimension 40 mm
6	Grid dimension 62 mm

Pneumatic connection	
1/4	Thread G1/4
1/2	Thread G1/2

Service unit combination	
On-off valve	→ 7-4
C3	MS...-EM1
Filters → 4-3	
H1	MS...-LF-ERV
H2	MS...-LF-ERM
H3	MS...-LF-CRM
H4	MS...-LF-CRV
H7	MS...-LF-EUV
H8	MS...-LF-EUM
Filter regulator → 3-3	
J1	MS...-LFR-D7-ERM-AS
J2	MS...-LFR-D7-ERV-AS
J3	MS...-LFR-D7-CRM-AS
J4	MS...-LFR-D7-CRV-AS
Pressure regulator → 5-6	
N2	MS...-LR-D6-AS
N3	MS...-LR-D7-AS
Soft-start valve → 7-4	
A1	MS...-DL
Lubricator → 6-3	
M1	MS...-LOE-R
M2	MS...-LOE-U
On-off valve → 7-4	
D1	MS...-EE-V24
D7	MS...-EE-10V24
Branching module → 9-4	
F3	MS...-FRM-Y

Type of mounting	
WP	Mounting bracket

Further variants can be ordered using the modular system

Service unit combinations → www.festo.com/en/engineering

- Connection size
- Connecting plates
- Service unit equipment
- Alternative flow direction


Service unit combinations MSB4/MSB6, MS series

Technical data


FESTO

Function

With condensate drain
manual rotary



With condensate drain
fully automatic



-  Flow rate
550 ... 2,300 l/min
-  Temperature range
-10 ... +60 °C
-  Pressure regulation
range
4 ... 12 bar



- On-off valve MS...-EM1
manually actuated
- Filter regulator MS...-LFR-D7
- Lubricator MS...-LOE-R
- On-off valve MS...-EE-10V24 or
MS...-EE-V24
solenoid actuated
- Soft-start valve MS...-DL
pneumatically actuated
- Branching module MS...-FRM-Y
with pressure switch without display
- Mounting bracket MS...-WP

- For filtered and lubricated compressed air
- Supply pressure can be opened and closed
- Output pressure is infinitely adjustable within the pressure regulation range
- Gradual pressure build-up prevents sudden, unpredictable movements
- To shut-off and vent the following device or the system
- Electrical pressure monitoring with adjustable switching pressure

General technical data		
Size	MSB4	MSB6
Pneumatic connection 1, 2, 3	G1/4	G1/2
Regulating function	With primary pressure compensation	
	With return flow function	
	With secondary venting	
	Output pressure constant	
Type of mounting	Via accessories	
Assembly position	Vertical ±5°	
Grade of filtration [µm]	5 (air purity class at the output 3.7.- to DIN ISO 8573-1)	
	40 (air purity class at the output 5.7.- to DIN ISO 8573-1)	
Bowl guard	Plastic bowl guard	
Condensate drain	Manual rotary	
	Fully automatic	
Actuator lock	Rotary knob with detent	
	Lockable with accessories	
Pressure regulation range [bar]	4 ... 9 (with on-off valve MS...-EE-10V24)	
	4 ... 12 (with on-off valve MS...-EE-V24)	
Pressure indicator	With pressure gauge	
Coil characteristics [V DC]	12	
Supply voltage [V DC]	24	

Standard nominal flow rate qnN [l/min]		
Size	MSB4	MSB6
Grade of filtration	5 µm	550
	40 µm	600
		2,100
		2,300

Service unit combinations MSB4/MSB6, MS series

FESTO

Technical data

Operating and environmental conditions								
	Pressure regulation range 4 ... 9 bar				Pressure regulation range 4 ... 12 bar			
Condensate drain	Manual rotary		Fully automatic		Manual rotary		Fully automatic	
Size	MSB4	MSB6	MSB4	MSB6	MSB4	MSB6	MSB4	MSB6
Supply pressure [bar]	4.5 ... 10	4.5 ... 10	4.5 ... 10	4.5 ... 10	4.5 ... 14	4.5 ... 18	4.5 ... 12	4.5 ... 12
Operating medium	Filtered compressed air, lubricated or unlubricated, grade of filtration 40 µm							
Ambient temperature [°C]	-10 ... +50		+5 ... +50		-10 ... +60		+5 ... +60	
Temperature of medium [°C]	-10 ... +50		+5 ... +50		-10 ... +60		+5 ... +60	
Storage temperature [°C]	-10 ... +60		-10 ... +60		-10 ... +60		-10 ... +60	
Corrosion resistance CRC ¹⁾	2							

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Weights [g]		
Size	MSB4	MSB6
Service unit combination	2,200	4,000
Mounting bracket	40	76

Note
Materials → Technical data of the individual devices



Standard flow rate qn as a function of output pressure p2

Pressure regulation range
4 ... 9 bar / 4 ... 12 bar
MSB4-1/4

Grade of filtration 5 µm



Grade of filtration 40 µm

Primary pressure p1 = 10 bar



MSB6-1/2

Primary pressure p1 = 10 bar



Service unit combinations MSB4/MSB6, MS series


Technical data

FESTO

Dimensions

Download CAD data → www.festo.com/en/engineering

With pressure gauge, display unit [bar]



Type	B1	B2	B3	B4	B5	B6	D1	L1	L2
MSB4	241.2	40.2	80.4	4	44	80	G $\frac{1}{4}$	201	87
MSB6	372	62	124	4.5	54	100	G $\frac{1}{2}$	285	134.5

Type	L3 Condensate drain		L4	L5	L6	L7	L8	L9	L10
	manual rotary	fully auto- matic							
MSB4	17.7	20.4	25	27	46.5	93.2	106	5.6	80
MSB6	15.8	18.5	68	39	71	142	158	6.6	130

Service unit combinations MSB4/MSB6, MS series

FESTO

Technical data

Ordering data								
Pressure regulation range 4 ... 9 bar								
Size	Condensate drain	Connection	Grade of filtration 5 µm			Grade of filtration 40 µm		
			Part No.	Type		Part No.	Type	
Plastic bowl guard								
MSB4	manual rotary	G¼	542 624	MSB4-¼:C3J3M1D7A1F3-WP	☰	542 619	MSB4-¼:C3J1M1D7A1F3-WP	☰
	fully automatic	G¼	542 626	MSB4-¼:C3J4M1D7A1F3-WP	☰	542 622	MSB4-¼:C3J2M1D7A1F3-WP	☰
MSB6	manual rotary	G½	542 640	MSB6-½:C3J3M1D7A1F3-WP	☰	542 636	MSB6-½:C3J1M1D7A1F3-WP	☰
	fully automatic	G½	542 642	MSB6-½:C3J4M1D7A1F3-WP	☰	542 638	MSB6-½:C3J2M1D7A1F3-WP	☰

Ordering data						
Pressure regulation range 4 ... 12 bar						
Size	Condensate drain	Connection	Grade of filtration 5 µm			Grade of filtration 40 µm
			Part No.	Type		Part No.
Plastic bowl guard						
MSB4	manual rotary	G¼	542 309	MSB4-¼:C3J3M1D1A1F3-WP		542 297 MSB4-¼:C3J1M1D1A1F3-WP
	fully automatic	G¼	542 315	MSB4-¼:C3J4M1D1A1F3-WP		542 303 MSB4-¼:C3J2M1D1A1F3-WP
MSB6	manual rotary	G½	542 285	MSB6-½:C3J3M1D1A1F3-WP		542 273 MSB6-½:C3J1M1D1A1F3-WP
	fully automatic	G½	542 291	MSB6-½:C3J4M1D1A1F3-WP		542 279 MSB6-½:C3J2M1D1A1F3-WP



MS series service units

Accessories


FESTO

Connecting plate MS4/6-AG...

(order code: AG...)

- Adapter for pneumatic connection
- MS6-AGE for implementing threaded connection G $\frac{3}{4}$

Material:
Aluminium




Dimensions and ordering data									
Size	B1	B2	B4	D1	D2	L1	Weight [g]	Part No.	Type
MS4	83.5	21.5	21	G $\frac{1}{8}$	16.8	42	128	526 068	MS4-AGA
				G $\frac{1}{4}$				526 069	MS4-AGB
				G $\frac{3}{8}$				526 070	MS4-AGC
MS6	115	26.5	31	G $\frac{1}{4}$	24	62	300	526 080	MS6-AGB
				G $\frac{3}{8}$				526 081	MS6-AGC
				G $\frac{1}{2}$				526 082	MS6-AGD
				G $\frac{3}{4}$				526 083	MS6-AGE

Connecting plate MS12-AG...

(order code: AG...)

- Adapter for pneumatic connection

Material:
Die-cast aluminium
Free of copper and PTFE



Dimensions and ordering data												
Size	B1	B2	B3	B4	B5	D1	L1	L2	L3	L4	Weight [g]	Part No. Type
MS12	162	124	12	99	184	G1	230	100	11	100	1,300	537 135 MS12-AGF
					184	G1 $\frac{1}{4}$						537 136 MS12-AGG
					184	G1 $\frac{1}{2}$						537 137 MS12-AGH
					196	G2						537 138 MS12-AGI

MS series service units

Accessories

FESTO


Cover cap MS4/6-END

- Can be used to cover the body sides of the first and last module if connecting plates are not used.

Material:

Reinforced polyamide

Free of copper and PTFE



Dimensions and ordering data						
Size	B1	B2	B4	L1	Part No.	Type
MS4	43.6	6	21	42	538 779	MS4-END
MS6	67	8	31	62	538 780	MS6-END

Mounting plate MS6-AEND


(order code: WBE; scope of delivery includes wall mounting plate MS6-WPB)

- In combination with wall mounting plate MS6-WP or MS6-WPB for mounting an individual unit on a wall with direct thread

Material:

Reinforced polyamide

Free of copper and PTFE



Dimensions and ordering data											
Size	B1	B2	B3	B4	L1	L2	L3	L4	CRC ¹⁾	Weight [g]	Part No. Type
MS6	79	62	4.5	90.5	158	71	6.6	71	2	17	535 408 MS6-AEND  New

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

MS series service units

Accessories

FESTO

Mounting bracket MS4/6-WP...

Clearances for mounting service unit combinations

1 unit

MS4-...: 40 mm

MS6-...: 62 mm

2 units

MS4-...: 80 mm

MS6-...: 124 mm with WP, WPB


138 mm with WPM-2D

1 Mounting bracket WP, WPB or WPM-D


2 Mounting bracket WP, WPB or WPM-2D

Number of units

1 2 3 4 5 6 7 8 9 10



Mounting dimensions



Type	B1	B2	B3	B4	B5	B6	L1	L2	L3	L4
MS4-WP	95.2	80	4	44	41.9	40	106	46.5	5.6	46.7
MS4-WPB				66						
MS4-WPM-...D				44			92.8	34.8		40
MS6-WP	141	124	4.5	54	64.5	62	158	71	6.6	71
MS6-WPB				90.5						
MS6-WPM-...D				54			98.6	41.3		41.3

MS series service units

Accessories

FESTO


Mounting bracket MS4/6-WP

(order code: WP)

- For connecting the modules for wall mounting
- In combination with a connecting plate MS4/6-AG... for mounting an individual unit on a wall
- In combination with mounting plate MS6-AEND or for mounting an individual unit with direct thread on a wall
- For pressure regulator LRB with angled outlet block B... at rear

Material:

Die-cast aluminium



Dimensions and ordering data

Size	B1	B2	B3	B4	B5	L1	L2	L3	L4	Weight [g]	Part No.	Type
MS4	55.2	40.2	4	44	83.4	106	46.5	5.6	46.7	39	532 184	MS4-WP
MS6	79	62	4.5	54	115	158	71	6.6	71	76	532 195	MS6-WP


Mounting bracket MS4/6-WPB

(order code: WPB)

- For connecting the modules for wall mounting
- In combination with a connecting plate MS4/6-AG... for mounting an individual unit on a wall
- In combination with mounting plate MS6-AEND or for mounting an individual unit with direct thread on a wall
- Provides large wall gap for pressure regulator

Material:

Die-cast aluminium



Dimensions and ordering data

Size	B1	B2	B3	B4	B5	L1	L2	L3	L4	Weight [g]	Part No.	Type
MS4	55.2	40.2	4	66	83.4	106	46.5	5.6	46.7	55	526 063	MS4-WPB
MS6	79	62	4.5	90.5	115	158	71	6.6	71	115	526 074	MS6-WPB

MS series service units

Accessories

FESTO




Mounting bracket MS4/6-WPM

(order code: WPM)

- For connecting the modules for wall mounting
- In combination with a connecting plate MS4/6-AG... for mounting an individual unit on a wall
- Speedy attachment and detachment
- For installation of modules with regulating knob pointing downwards

The distance piece D or 2D (designated in the type code) is included in the scope of delivery and ensures the correct clearance

Material:
Die-cast aluminium



Dimensions and ordering data													
Size	B1	B2	B3	B4	B5	L1	L2	L3	L4	Clearance	Weight [g]	Part No.	Type
MS4	55.2	40	4	44	83.4	92.8	34.8	5.6	45.2	40	45	526 060	MS4-WPM-D
	95.2	80			123.4					80	55	526 061	MS4-WPM-2D
MS6	99	69	17.5	54	129	98.6	41.3	6.6	41.3	62	144	526 073	MS6-WPM-D
	168	138			198					124	154	532 186	MS6-WPM-2D

MS series service units

Accessories

FESTO

Wall mounting plate MS12-WP


(order code: WP)

- For connecting the modules for wall mounting
- In combination with a connecting plate for mounting an individual unit on a wall

Material:

Die-cast aluminium

Free of copper and PTFE



Dimensions and ordering data

Size	B1	B2	B3	B4	L1	L2	L3	L4	Weight [g]	Part No.	Type
MS12	162	124	12	99	230	100	11	100	700	537 133	MS12-WP

Module connector MS...-MV

- For connecting modules

Material:

MS4/6: Stainless steel/polyacetate

MS12: Die-cast aluminium,
free of copper and PTFE



MS4/6



MS12

Ordering data


Size	Weight [g]	Part No.	Type
MS4	36	532 798	MS4-MV
MS6	54	532 799	MS6-MV
MS12	500	537 134	MS12-MV

Module connector MS4/6-MVM

- For installation of modules with regulating knob pointing downwards

Material:

Die-cast aluminium



MS4



MS6

Ordering data

Size	Part No.	Type
MS4	532 800	MS4-MVM
MS6	532 801	MS6-MVM

MS series service units

Accessories

FESTO

Filter cartridge MS4/6-LF...



MS...-LFM



MS...-LFP



MS...-LFX

Ordering data				
Size		Grade of filtration [μm]	Part No.	Type
MS4	Micro-filter cartridge	0.01	162 674	MS4/D-MINI-LFM-A
	Fine-filter cartridge	1	162 677	MS4/D-MINI-LFM-B
	Filter cartridge	5	534 501	MS4-LFP-C
	Filter cartridge	40	534 502	MS4-LFP-E
	Active carbon filter cartridge	Residual oil content ≤ 0.003 mg/m ³	532 912	MS4/D-MINI-LFX
MS6	Micro-filter cartridge	0.01	532 909	MS6-LFM-A
	Fine-filter cartridge	1	532 910	MS6-LFM-B
	Filter cartridge	5	534 499	MS6-LFP-C
	Filter cartridge	40	534 500	MS6-LFP-E
	Active carbon filter cartridge	Residual oil content ≤ 0.003 mg/m ³	532 911	MS6-LFX


Filter cartridge MS12-LF...



MS12-LFM-B



MS12-LFM-A



MS12-LFX

Ordering data				
Size		Grade of filtration [μm]	Part No.	Type
MS12	Micro-filter cartridge	0.01	537 146	MS12-LFM-A
	Fine-filter cartridge	1	537 145	MS12-LFM-B
	Filter cartridge	5	537 143	MS12-LFP-C
	Filter cartridge	40	537 144	MS12-LFP-E
	Active carbon filter cartridge	Residual oil content ≤ 0.003 mg/m ³	537 147	MS12-LFX


MS series service units

Accessories

FESTO

Ordering data – Angled socket PEV					Technical data → www.festo.com	
	Description	Operating voltage range	Electrical connection	Switching status display	Part No.	Type
	for PEV-1/4-...-OD	15 ... 30 V DC	4-pin	Yellow LED	164 274	PEV-1/4-WD-LED-24
		≤ 230 V AC	4-pin	Yellow LED	164 275	PEV-1/4-WD-LED-230
		≤ 180 V DC				

Ordering data – Plug socket MSSD					Technical data → www.festo.com	
	Description	Operating voltage range	Electrical connection	Type of mounting cable connection	Part No.	Type
	for PEV-1/4-...-OD	≤ 250 V AC/DC	3-pin	Clamping screws	171 157	MSSD-C-4P
	for MS4/6-EE/DE	≤ 250 V AC/DC	3-pin	Clamping screws	151 687	MSSD-EB
			4-pin	Insulation displacement technology	192 745	MSSD-EB-S-M14
	for MS12-EE/DE	≤ 250 V AC/DC	3-pin	Clamping screws	34 583	MSSD-C
			4-pin	Insulation displacement technology	192 748	MSSD-C-S-M16

Ordering data – Plug socket with cable KMEB/KMC					Technical data → www.festo.com	
	Description	Operating voltage range	Switching status display	Cable length [m]	Part No.	Type
	for MS4/6-EE/DE	24 V DC	LED	2.5	151 688	KMEB-1-24-2,5-LED
		24 V DC	LED	5	151 689	KMEB-1-24-5-LED
		24 V DC	LED	10	193 457	KMEB-1-24-10-LED
		230 V AC	–	2.5	151 690	KMEB-1-230AC-2,5
		230 V AC	–	5	151 691	KMEB-1-230AC-5
	for MS12-EE/DE	24 V DC	LED	2.5	30 931	KMC-1-24DC-2,5-LED
		24 V DC	LED	5	30 933	KMC-1-24DC-5-LED
		24 V DC	LED	10	193 459	KMC-1-24-10-LED
		230 V AC	–	2.5	30 932	KMC-1-230AC-2,5
		230 V AC	–	5	30 934	KMC-1-230AC-5

Ordering data – Illuminating seal MEB-LD/MC-LD				Technical data → www.festo.com	
	Description	Operating voltage range		Part No.	Type
	for plug socket with cable KMEB and plug socket MSSD-EB	12 ... 24 V DC		151 717	MEB-LD-12-24DC
		230 V DC/AC ±10%		151 718	MEB-LD-230AC
	for plug socket with cable KMC and plug socket MSSD-C	12 ... 24 V DC		19 145	MC-LD-12-24DC
		230 V DC/AC ±10%		19 146	MC-LD-230AC

Ordering data – Locking clip CPV18-HV				Technical data → www.festo.com	
	Description		Part No.	Type	PU ¹⁾
	for MS4/6-EE/DE-...-V24	Cover for manual override, the clip prevents actuation	530 056	CPV18-HV	10

1) Packaging unit quantity

MS series service units


Accessories

FESTO

Ordering data – Silencer U			Technical data → www.festo.com	
	Description	Pneumatic connection	Part No.	Type
	for MS4-EM1/EE	G1/4	6 842	U-1/4-B
	for MS6-EM1/EE	G1/2	6 844	U-1/2-B
	for MS12-EM/EE	G1	151 990	U-1-B

Ordering data – Double nipple ESK				
	Description	Pneumatic connection		Part No. Type
	Adjustable for angular compensation • For retro-fitting pressure switch PEV or pressure sensor SDE1 to branching module MS-FRM	R1/8	R1/4	534 151 ESK-1/8-1/4
		R1/4	R1/4	151 521 ESK-1/4-1/4
			R1/2	534 153 ESK-1/4-1/2

Ordering data – Padlock LRV5-D				
	Description	Weight [g]	Part No.	Type
	for filter or pressure regulators	120	193 786	LRV5-D

Ordering data – Special oil OFSW				
	Description	Scope of delivery	Part No.	Type
	for lubricators	1 litre	152 811	OFSW-32