

Cartridge fittings QSP, Quick Star

Technical data

Cartridge fittings QSP10


Material:

- Housing: Nickel plated brass

 - Ambient temperature
0 ... 60 °C

 - Operating pressure
–0.95 ... +10 bar

Certification:
Germanischer Lloyd



Dimensions and ordering data							
Tubing O.D.	D5 Ø	H1	H2	H3	Part No.	Type	PU ¹⁾
D1							
4	9.8	16.2	6.7	11.6	172972	QSP10-4	10
6	9.8	16.2	6.7	11.9	172973	QSP10-6	10

1) Packaging unit quantity.

Cartridge fittings QSPKG10

Material:


- Housing: Polyamide, fibreglass reinforced
- Release ring: Polyacetate
- Tubing seal: Nitrile rubber
- Tube retaining claw: High-alloy stainless steel

 - Ambient temperature
–5 ... +60 °C

 - Operating pressure
–0.95 ... +10 bar

Note on materials:
Conforms to RoHS

Certification:
Germanischer Lloyd



Dimensions and ordering data										
Tubing O.D.	Nominal size	D5 Ø	H1	H2	H3	CRC ¹⁾	Weight/piece	Part No.	Type	PU ²⁾
D1	[mm]						[g]			
3	1.6	9.75	16.1	6.7	11.6	1	1.5	132621	QSPKG10-3  New	10
4	2.3	9.75	16.1	6.7	11.6	1	1.4	132622	QSPKG10-4  New	10
6	3.7	10.55	18.1	6.7	11.9	1	1.8	132623	QSPKG10-6  New	10

1) Corrosion resistance class 1 to Festo standard 940 070

Components requiring low corrosion resistance. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.

2) Packaging unit quantity.

Cartridge fittings QSP, Quick Star

Technical data

FESTO

Cartridge fittings QSPLK10

Material:


- Housing: Polyamide, fibreglass reinforced
- Release ring: Polyacetate
- Tubing seal: Nitrile rubber
- Tube retaining claw: High-alloy stainless steel

 Ambient temperature
–5 ... +60 °C

 Operating pressure
–0.95 ... +10 bar

Note on materials:
Conforms to RoHS

Certification:
Germanischer Lloyd



Dimensions and ordering data												
Tubing O.D.	Nominal size	D5 Ø	D6 Ø	H1	H2	L1	L2	CRC ¹⁾	Weight/piece [g]	Part No.	Type	PU ²⁾
D1	[mm]											
4	2.3	9.75	9	13.4	6.7	19.4	19.4	1	2.3	132601	QSPLK10-4	10
6	3.6	9.75	11	14.4	6.7	20.3	11.9	1	2.9	132602	QSPLK10-6	10

- 1) Corrosion resistance class 1 to Festo standard 940 070
Components requiring low corrosion resistance. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.
- 2) Packaging unit quantity.

Cartridge fittings QSPLK10

Material:


- Housing: Polyamide, fibreglass reinforced
- Release ring: Polyacetate
- Tubing seal: Nitrile rubber
- Tube retaining claw: High-alloy stainless steel

 Ambient temperature
–5 ... +60 °C

 Operating pressure
–0.95 ... +10 bar

Note on materials:
Conforms to RoHS

Certification:
Germanischer Lloyd



Dimensions and ordering data												
Tubing O.D.	Nominal size	D5 Ø	D6 Ø	H1	H2	L1	L2	CRC ¹⁾	Weight/piece [g]	Part No.	Type	PU ²⁾
D1	[mm]											
4	2.3	9.75	9	23.4	6.7	19.4	11.6	1	2.5	132603	QSPLK10-4	10
6	3.6	9.75	11	26.4	6.7	20.3	11.9	1	3.4	132604	QSPLK10-6	10

- 1) Corrosion resistance class 1 to Festo standard 940 070
Components requiring low corrosion resistance. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.
- 2) Packaging unit quantity.

Cartridge fittings QSP, Quick Star

Technical data

FESTO

Cartridge fittings QSPK18

Material:

- Housing: Polyamide, fibreglass reinforced
- Release ring: Polyacetate
- Tubing seal: Nitrile rubber
- Tube retaining claw: High-alloy stainless steel

–  – Ambient temperature
–5 ... +60 °C


–  – Operating pressure
–0.95 ... +10 bar

Note on materials:
Conforms to RoHS


Certification:
Germanischer Lloyd




QSP18-4



QSP18-6 / QSP18-8



QSP18-10



Dimensions and ordering data										
Tubing O.D. D1	Nominal size [mm]	D5 Ø	H1	H2	H3	CRC ¹⁾	Weight/piece [g]	Part No.	Type	PU ²⁾
4	2.3	17.7	13.6	7.75	11.6	1	2.8	130839	QSPK18-4	10
6	3.8	17.7	13.7	7.75	11.9	1	3	130840	QSPK18-6	10
8	5.5	17.7	20.7	7.75	18.2	1	5.4	130841	QSPK18-8	10
10	6.7	17.7	24.5	7.75	20.2	1	8.1	130842	QSPK18-10	10

- 1) Corrosion resistance class 1 to Festo standard 940 070
Components requiring low corrosion resistance. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.
- 2) Packaging unit quantity.

Cartridge fittings QSP, Quick Star

Technical data

FESTO

Cartridge fittings QSPLK18

Material:


- Housing: Polyamide, fibreglass reinforced
- Release ring: Polyacetate
- Tubing seal: Nitrile rubber
- Tube retaining claw: High-alloy stainless steel

 Ambient temperature
–5 ... +60 °C

 Operating pressure
–0.95 ... +10 bar

Note on materials:
Conforms to RoHS

Certification:
Germanischer Lloyd



Dimensions and ordering data												
Tubing O.D.	Nominal size	D5	D6	H1	H2	L1	L2	CRC ¹⁾	Weight/piece	Part No.	Type	PU ²⁾
D1	[mm]	Ø	Ø						[g]			
4	2.3	17.7	9	15.3	7.75	19.4	11.6	1	3.2	130843	QSPLK18-4	10
6	3.6	17.7	11	16.3	7.75	20.3	11.9	1	3.9	130844	QSPLK18-6	10
8	5.2	17.7	15	18.3	7.75	27.2	18.2	1	7.5	130845	QSPLK18-8	10
10	–	17.7	17.7	19.6	7.75	29.5	20.2	1	11	132639	QSPLK18-10 	10

- 1) Corrosion resistance class 1 to Festo standard 940 070
Components requiring low corrosion resistance. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.
- 2) Packaging unit quantity.

Cartridge fittings QSPLLK18

Material:


- Housing: Polyamide, fibreglass reinforced
- Release ring: Polyacetate
- Tubing seal: Nitrile rubber
- Tube retaining claw: High-alloy stainless steel

 Ambient temperature
–5 ... +60 °C

 Operating pressure
–0.95 ... +10 bar

Note on materials:
Conforms to RoHS

Certification:
Germanischer Lloyd



Dimensions and ordering data												
Tubing O.D.	Nominal size	D5	D6	H1	H2	L1	L2	CRC ¹⁾	Weight/piece	Part No.	Type	PU ²⁾
D1	[mm]	Ø	Ø						[g]			
4	2.3	17.7	9	25.3	7.75	19.4	11.6	1	3.5	130846	QSPLLK18-4	10
6	3.6	17.7	11	38.3	7.75	20.3	11.9	1	4.3	130847	QSPLLK18-6	10
8	5.2	17.7	15	34.3	7.75	27.2	18.2	1	8.1	130848	QSPLLK18-8	10
10	–	17.7	17.7	38.3	7.75	29.5	20.2	1	12.1	132640	QSPLLK18-10 	10

- 1) Corrosion resistance class 1 to Festo standard 940 070
Components requiring low corrosion resistance. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.
- 2) Packaging unit quantity.