





- Wide variety of applications for handling functions
- Minimal installation space required
- Stroke end positions can be varied according to the depth of engagement of the cylinder
- Additional mounting attachments


Cartridge cylinders EGZ

Peripherals overview and type codes


FESTO



Installation without mounting attachments



Minimal installation space required



Mounting attachments and accessories					
	Brief description	Piston Ø 6 mm	Piston Ø 10 mm	Piston Ø 16 mm	→ Page/Internet
1	Swivel mounting WBN For cylinder housing between two hex nuts	–	■	■	6
2	Flange mounting FBN For cylinder housing between two hex nuts	–	■	■	5
3	Foot mounting HBN For cylinder housing between two hex nuts	–	■	■	5
4	Self-aligning rod coupler FK For compensating radial and angular deviations	–	■	■	6
5	Rod clevis SG Permits a swivelling movement of the cylinder in one plane	–	■	–	6
6	Rod eye SGS With spherical bearing	–	■	–	6
7	Push-in fitting QS For connecting compressed air tubing with standard external diameters	■	■	■	quick star


EGZ		–	16	–	10
Type					
Single acting, pushing					
EGZ	Cartridge cylinder				
Piston Ø [mm]					
Stroke [mm]					

Cartridge cylinders EGZ

Technical data

FESTO

Function



- $\varnothing$ - Diameter
6 ... 16 mm
- I - Stroke length
5 ... 15 mm



General technical data			
Piston $\varnothing$	6	10	16
Pneumatic connection	M3	M5	M5
End of piston rod Male thread	M3	M4	M5
Operating medium	Filtered compressed air, lubricated or unlubricated		
Constructional design	Piston		
	Piston rod		
Cushioning	None		
Position sensing	None		
Type of mounting	With lock nut		
	With accessories		
Mounting position	Any		

Operating and environmental conditions			
Piston $\varnothing$	6	10	16
Operating pressure [bar]	1.5 ... 8		
Ambient temperature [°C]	-20 ... +80		

Forces and permitted applied load [N]									
Piston $\varnothing$	6			10			16		
Stroke	5	10	15	5	10	15	5	10	15
Theoretical force at 6 bar, advancing	14			42			109		
Spring return force	1.5	2.1	1.6	4	3.5	3	10	8.8	7.5
Maximum applied load at the piston rod	0.10			0.15			0.20		

Materials	
Sectional view	

Cylinder	
1 Housing	Brass, nickel-plated
2 Cover	Polyacetal
3 Piston rod	High-alloy steel
- Note on materials	Conforms to RoHS



Cartridge cylinders EGZ

Technical data

FESTO

Dimensions

Download CAD data → www.festo.com



1 O-ring
+ = plus stroke length

Ø [mm]	AM	B1	BE	D1 Ø H7/f8	EE	KK	KV h13	KW	L1	L2	L3
6 ¹⁾	7	1.8	M10x1	7.6	M3	M3	13	3.5	1.5	6	2.4
6 ²⁾											
10	10	2.2	M16x1.5	12	M5	M4	19	4	2	7	3
16	12	2.7	M22x1.5	18.5	M5	M5	27	5	2	9	3.5

Ø [mm]	L4 - Y +1	L5 - Y -1	L6 - Y +1	Y		ZY	C1 h13	C2 h13
				min.	max. + stroke			
6 ¹⁾	9	11	15.5	6	5	15	5.5	8
6 ²⁾	11	13	17.5	6	7	17		
10	11	13	18.5	7	6	17.5	7	13
16	13	16	21	8	6	20.5	8	19

- 1) 5 mm stroke
2) 10 and 15 mm stroke

Ordering data¹⁾

Stroke [mm]	Part No.	Type	Stroke [mm]	Part No.	Type
Piston Ø 6 mm			Piston Ø 10 mm		
5	15 033	EGZ-6-5	5	15 036	EGZ-10-5
10	15 034	EGZ-6-10	10	15 037	EGZ-10-10
15	15 035	EGZ-6-15	15	15 038	EGZ-10-15
Piston Ø 16 mm					
5	15 039	EGZ-16-5			
10	15 040	EGZ-16-10			
15	15 041	EGZ-16-15			

1) Two hex nuts each for the male cylinder thread and for the piston thread are included in the scope of delivery.



Cartridge cylinders EGZ

Accessories

FESTO

Foot mounting HBN for piston Ø 10, 16 mm

Material:
Steel
Free of copper, PTFE and silicone




Dimensions and ordering data													
For Ø	Minimum stroke lengths	AB Ø	AH	AO	AT	AU	R1	TR	US	CRC ¹⁾	Weight [g]	Part No.	Type
10	5	5.5	20	6	4	14	13	32	42	2	40	5 125	HBN-12/16X1
16	7	6.6	25	8	5	17	20	40	54	2	90	5 127	HBN-20/25X1

- 1) Corrosion resistance class 2 according to Festo standard 940 070
Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents.

Flange mounting FBN for piston Ø 10, 16 mm

Material:
Steel
Free of copper, PTFE and silicone



Dimensions and ordering data										
For Ø	Minimum stroke lengths	AB Ø	AT	TF	UF	UR	CRC ¹⁾	Weight [g]	Part No.	Type
10	5	5.5	4	40	53	30	2	25	5 130	FBN-12/16
16	7	6.6	5	50	68	40	2	45	5 131	FBN-20/25

- 1) Corrosion resistance class 2 according to Festo standard 940 070
Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents.


Cartridge cylinders EGZ

Accessories

FESTO

Swivel mounting WBN
for piston Ø 10, 16 mm

Material:
Tempered steel



Dimensions and ordering data								
For Ø	Minimum stroke lengths	TD Ø m6	TK	TM	UM	UW	Weight [g]	Part No. Type
10	9	6	8	38	58	25	50	8 609 WBN-12/16
16	10	6	8	46	66	30	70	8 610 WBN-20/25

Ordering data – Piston rod attachments				Technical data → Internet: piston-rod attachment			
Designation	For Ø	Part No.	Type	Designation	For Ø	Part No.	Type
Rod eye SGS				Rod clevis SG			
	10	9 253	SGS-M4		10	6 532	SG-M4
Self-aligning rod coupler FK							
	10	6 528	FK-M4				
	16	30 984	FK-M5				