


Sensor boxes SRBP, binary

FESTO



Sensor boxes SRBP, binary

Key features

FESTO


General information

- Whether for transporting, metering or bottling gaseous, paste and liquid media or bulk materials, sensor boxes are used in the process industry as position indicators for the end positions of the semi-rotary actuator
- The binary sensor boxes SRBP not only convert the mechanical open and closed position of the actuator or process valve into electrical output signals, but also permit the optional sensing of a mid-position

Advantages


- Sturdy aluminium housing to IP65 and CRC 3 also enables use in harsh environments
- Mounting on DFPB without additional adapter kit as well as mounting on other actuators via adapter kits as per VDI/VDE 3845
- Clearly visible 3D position indicator offers the option of fast recognition of the current position of the semi-rotary actuator, including from a distance
- Correct indication of the flow direction (I, L, T) of the medium, even with 3-way valves
- Captive screws and name plates offer trouble-free assembly and ordering
- Version available for the ATEX zone 2/22
- Just one product for multiple applications thanks to the wide, adjustable swivel range of up to 270°
- Integrated reed contacts in N/O or changeover contact versions
- The innovative design makes setting the two end positions as well as the mid-position within the wide swivel range of up to 270° quick and easy
- Internal LEDs as setting aid during commissioning
- Optional sensing of the mid-position
- You can find information on the media resistance of the product at www.festo.com

1 cable connector



- Power supply for sensor box only


2 cable connectors



- Common power supply for sensor box and solenoid valve

Sensor boxes SRBP, binary

Peripherals overview



Mounting attachments and accessories		
	Brief description	→ Page/Internet
1	Adapter kit DASB-P1-HA-SB ¹⁾	Hole pattern 30x80 mm, height 20 mm dasb
2	Adapter kit DASB-P1-HL-SB	Hole pattern 30x130 mm, height 50 mm dasb
3	Adapter kit DASB-P1-HB-SB	Hole pattern 30x80 mm, height 30 mm dasb
4	Adapter kit DASB-P1-HC-SB	Hole pattern 30x130 mm, height 30 mm dasb
5	Coupling DARQ-C-S9	For direct mounting on semi-rotary actuators DFPB darq
	Coupling DARQ-C-S11	For direct mounting on semi-rotary actuators DFPB darq
	Coupling DARQ-C-S14	For direct mounting on semi-rotary actuators DFPB darq
	Coupling DARQ-C-S17	For direct mounting on semi-rotary actuators DFPB darq
	Coupling DARQ-C-S22	For direct mounting on semi-rotary actuators DFPB darq
	Coupling DARQ-C-S27	For direct mounting on semi-rotary actuators DFPB darq

1) The adapter kit DASB-P1-HA-SB can optionally be used for all DFPB actuators.

Sensor boxes SRBP, binary

Type codes

FESTO

		SRBP	-	M	-	CA1	-	BB270	-	MSA	-	1U	-	T2P20	-		-	EX2
Function																		
SRBP	Binary sensor box																	
Product version																		
M	Primarily metal																	
Design																		
C	Sensor box																	
Mechanical interface																		
A1	Direct mounting, hole pattern 30x80 mm																	
Indicator type																		
BB	Blue/black position indicator																	
GR	Green/red position indicator																	
YB	Yellow/black position indicator																	
Measuring range																		
270	0 ... 270°																	
Sensor principle																		
MS	Floating contact, N/O contact																	
FW	Floating contact, changeover contact																	
Mid-position sensing																		
	None																	
A	With sensing																	
Nominal operating voltage																		
20N	8.2 V DC																	
1U	24 V AC/DC																	
Electrical connection																		
T	Terminal box																	
Valve connection																		
	None																	
2	With valve connection																	
Cable connector																		
P20	M20x1.5, polymer																	
Temperature range																		
	Standard -20 ... +80 °C																	
EU certification																		
	None																	
EX2	II 3GD																	

Sensor boxes SRBP, binary

Technical data

- The binary sensor box is a so-called position sensor for semi-rotary actuators and reports the open and closed position of the actuator
- Sensors are based on reed technology



General technical data				... -20N	... -1U
Adjustment range for angle detection		[°]		0 ... 270	
Based on standard				VDI/VDE 3845 (NAMUR)	
Design				Angular	
Mounting position				Any	
Measured variable				Swivel angle	
Measuring principle				Magnetic reed	
Switching element function				→ Page 7	
Mid-position				→ Page 7	
Switching status display				→ Page 7	
Max. output current		[mA]		→ Page 7	
Idle current		[mA]		→ Page 7	
Position indicator				→ Page 7	
Reproducibility of switching point				+/- 1 deg	
Max. switching capacity	Direct voltage DC	[W]		–	10
	Alternating voltage AC	[VA]		–	10
Operating voltage range	Direct voltage DC	[V]		7.8 ... 8.6	19.2 ... 28.8
	Alternating voltage AC	[V]		–	19.2 ... 28.8
Insulation voltage		[V]		50	
Surge capacity		[kV]		0.8	
Voltage drop		[V]		–	0 ... 0.2
Protection against short circuit				No	
Protection against overloading				No	
Output signal				Digital	
Reverse polarity protection				For operating voltage	
Electrical connection				9-pin	
				Screw terminal	
				Plug-in	
Cable connector				M20x1.5	
Max. cable length		[m]		30	
Permissible cable diameter		[mm]		5 ... 13	
Connectable nominal conductor cross section		[mm ²]		2.5	
Product weight		[g]		1,000	
Housing material				Wrought aluminium alloy	
Note on materials				RoHS-compliant	

Operating and environmental conditions				... -20N	... -1U
Certification				C-Tick	
Ambient temperature		[°C]		–20 ... +80 °C	
Protection class				IP65	
CE mark (see declaration of conformity)				To EU EMC Directive	
Electrical protection class				III	
Degree of contamination				3	
Corrosion resistance class CRC ¹⁾				3	

1) Corrosion resistance class 3 according to Festo standard 940 070

Components subject to high corrosion stress. External visible parts in direct contact with industrial atmospheres or media such as solvents and cleaning agents, with a predominantly functional requirement for the surface.

Sensor boxes SRBP, binary

Technical data

FESTO


Operating and environmental conditions with explosion protection	... -20N	... -1U
Certification	C-Tick	
Ambient temperature [°C]	-20 ... +80 °C	
Protection class	IP65	
CE mark (see declaration of conformity)	To EU EMC Directive	
	To EU Explosion Protection Directive (ATEX)	
ATEX category for gas	II 3G	
Explosion ignition protection type for gas	Ex nA II T5 X	
ATEX category for dust	II 3D	
Explosion ignition protection type for dust	Ex tD A22 IP65 T90°C X	
Explosion-proof ambient temperature	-20 °C ≤ Ta ≤ +80 °C	
Electrical protection class	III	
Degree of contamination	3	
Corrosion resistance class CRC ¹⁾	3	

1) Corrosion resistance class 3 according to Festo standard 940 070

Components subject to high corrosion stress. External visible parts in direct contact with industrial atmospheres or media such as solvents and cleaning agents, with a predominantly functional requirement for the surface.

Dimensions – Sensor boxes SRBP, binary

Download CAD Data → www.festo.com/us/cad



Type	B1	B2	B3 ±1	B4	D1	H1	H2	H3	H4	L1	L2 ±1	L3	⌀
SRBP- ...	94	82	30	–	M5	112.7	80	74.5	7.8	148	120	80	24
SRBP- ... -T2P20	94	82	30	27	M5	112.7	80	74.5	7.8	148	120	80	24

Sensor boxes SRBP, binary

Technical data

Ordering data – Sensor boxes SRBP, binary without explosion protection

	Switching element function	Mid-position	Switching status	Max. output current [mA]	Idle current [mA]	Position indicator	Part No.	Type
	N/O contact	–	LED	500	0 ... 10	Green/red	570 402	SRBP-M-CA1-GR270-MS-1U-TP20
	N/O contact	Yes	LED	500	0 ... 10	Green/red	570 403	SRBP-M-CA1-GR270-MSA-1U-TP20
	N/O contact	–	LED	500	0 ... 10	Yellow/black	570 404	SRBP-M-CA1-YB270-MS-1U-TP20
	N/O contact	Yes	LED	500	0 ... 10	Yellow/black	570 405	SRBP-M-CA1-YB270-MSA-1U-TP20
	Changeover switch	–	LED	500	0 ... 10	Green/red	570 406	SRBP-M-CA1-GR270-MW-1U-TP20
	Changeover switch	Yes	LED	500	0 ... 10	Green/red	570 407	SRBP-M-CA1-GR270-MWA-1U-TP20
	Changeover switch	–	LED	500	0 ... 10	Yellow/black	570 408	SRBP-M-CA1-YB270-MW-1U-TP20
	Changeover switch	Yes	LED	500	0 ... 10	Yellow/black	570 409	SRBP-M-CA1-YB270-MWA-1U-TP20
	N/O contact	–	LED	500	0 ... 10	Green/red	570 410	SRBP-M-CA1-GR270-MS-1U-T2P20
	N/O contact	–	LED	500	0 ... 10	Yellow/black	570 411	SRBP-M-CA1-YB270-MS-1U-T2P20

Ordering data – Sensor boxes SRBP, binary with explosion protection

	Switching element function	Mid-position	Switching status	Max. output current [mA]	Idle current [mA]	Position indicator	Part No.	Type
	N/O contact	–	LED	500	0 ... 10	Blue/black	568 249	SRBP-M-CA1-BB270-MS-1U-TP20-Ex2
	N/O contact	–	–	–	–	Green/red	568 250	SRBP-M-CA1-GR270-MS-20N-TP20-Ex2
	N/O contact	Yes	–	–	–	Green/red	568 251	SRBP-M-CA1-GR270-MSA-20N-TP20-Ex2
	N/O contact	Yes	LED	500	0 ... 10	Green/red	568 254	SRBP-M-CA1-GR270-MSA-1U-TP20-Ex2
	N/O contact	–	LED	500	0 ... 10	Green/red	568 255	SRBP-M-CA1-GR270-MS-1U-TP20-Ex2
	N/O contact	–	–	–	–	Yellow/black	568 256	SRBP-M-CA1-YB270-MS-20N-TP20-Ex2
	N/O contact	Yes	–	–	–	Yellow/black	568 257	SRBP-M-CA1-YB270-MSA-20N-TP20-Ex2
	N/O contact	–	LED	500	0 ... 10	Yellow/black	568 261	SRBP-M-CA1-YB270-MS-1U-TP20-Ex2
	N/O contact	Yes	LED	500	0 ... 10	Yellow/black	568 262	SRBP-M-CA1-YB270-MSA-1U-TP20-Ex2
	Changeover switch	Yes	LED	500	0 ... 10	Green/red	568 266	SRBP-M-CA1-GR270-MWA-1U-TP20-Ex2
	Changeover switch	–	LED	500	0 ... 10	Green/red	568 267	SRBP-M-CA1-GR270-MW-1U-TP20-Ex2
	Changeover switch	–	LED	500	0 ... 10	Yellow/black	568 271	SRBP-M-CA1-YB270-MW-1U-TP20-Ex2
	Changeover switch	Yes	LED	500	0 ... 10	Yellow/black	568 272	SRBP-M-CA1-YB270-MWA-1U-TP20-Ex2
	N/O contact	–	LED	500	0 ... 10	Green/red	568 274	SRBP-M-CA1-GR270-MS-1U-T2P20-Ex2

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Canada

USA Customers:

For ordering assistance,

Call: 1.800.99.FESTO (1.800.993.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO (1.866.463.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com

Canadian Customers:

Call: 1.877.GO.FESTO (1.877.463.3786)

Fax: 1.877.FX.FESTO (1.877.393.3786)

Email: festo.canada@ca.festo.com

USA Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788, USA
www.festo.com/us

USA Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942, USA

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801, USA

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056, USA

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326, USA

New York

395 Moreland Road
Hauppauge, NY 11788, USA

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550, USA

United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788

Phone: 1.631.435.0800; Fax: 1.631.435.8026;

Email: info@festo-usa.com

www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4

Phone: 1.905.624.9000; Fax: 1.905.624.9001;

Email: festo.canada@ca.festo.com

www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,
54020 Tlalneapantla, Edo. de México

Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;

Email: festo.mexico@mx.festo.com

www.festo.com/mx

Central USA

Festo Corporation
1441 East Business
Center Drive
Mt. Prospect, IL 60056, USA
Phone: 1.847.759.2600
Fax: 1.847.768.9480



Western USA

Festo Corporation
4935 Southfront Road,
Suite F
Livermore, CA 94550, USA
Phone: 1.925.371.1099
Fax: 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com