




- Co-ordinated combinations
- Versatile range of combination options
- Sturdy and functional
- Stainless steel variants

Mounting components

Selection aid

FESTO

Mounting components												
Possible combinations	Swivel flange											→ Page/ Internet
	SNC	SNCB	SNCS	SNG	SNGB	SSNG	SUA	SZB	SZSB	SNCL		
												
Clevis foot												
LBN		-	-	-	-	-	-	■	-	■	■	4
LN		-	■	-	-	■	-	■	■	-	-	5
LNG		-	■	-	-	■	-	■	-	-	-	6
LBG		-	-	■	-	-	■	-	-	-	-	7
LSN		-	■	-	-	■	-	■	-	-	-	8
LSNG		■	-	-	■	-	-	-	-	-	-	9
LSNSG		■	-	-	■	-	-	-	-	-	-	10
LQG		-	-	■ ¹⁾	-	-	-	-	-	-	-	11
Threaded bolt												
GBS		For swivel mounting of drives – DSEU, ESEU (Ø 50/63 mm)										13

1) Not possible in combination LQG-125 with SNCS-125.

Possible combinations	Trunnion flange		Trunnion mounting kit	→ Page/ Internet	
	ZNCF	ZNG	ZNCM		
					
Trunnion supports					
LNZG		■	■	■	12

Mounting components

Selection aid

FESTO

Mounting components – Stainless steel					
Possible combinations	Swivel flange		Trunnion flange	→ Page/Internet	
	SNCB-R3	SNCL-R3	CRZNG		
					
Clevis foot					
CRLBN		–	■	–	4
CRLNG		■	–	–	6
Trunnion supports					
CRLNZG		–	–	■	12

Mounting components – Stainless steel		
	Brief description	→ Page/Internet
Clevis foot		
CRLBN	 For swivel mounting of drives – CRDSNU (Ø 12 ... 25 mm)	4

Mounting accessories		
	Brief description	→ Page/Internet
Slot nut		
NST	 For profile slots in linear units, drives and axes as well as passive guide axes	14
NST-HMV	 For multi-axis systems	14
NSTL	 For slides in linear drives and axes as well as passive guide axes	15
NSTH	 For slides in heavy-duty guides HD	15
Centring pin		
ZBS	 For device interfaces on drives, axes and grippers	16
Centring sleeve		
ZBH	 For device interfaces on drives, axes and grippers	16
Central mounting		
SLZZ	 For device interfaces on drives and axes	17
Slot cover		
ABP	 For mounting and sensor slots	17

Clevis feet LBN/CRLBN

Technical data

FESTO


Clevis foot LBN

Material:

Galvanised steel

Free of copper and PTFE

RoHS-compliant



Dimensions and ordering data												
For Ø	CM	EK Ø	FL	GL	HB Ø	LE	MR	RG	UX	CRC ¹⁾	Weight [g]	Part No. Type
[mm]												
8/10	8.1	4	24 +0.3/-0.2	13.8	4.5	21.5	5	12.5	20	2	22	6 057 LBN-8/10
12/16	12.1	6	27 +0.3/-0.2	13	5.5	24	7	15	25	2	40	6 058 LBN-12/16
20/25	16.1	8	30 +0.4/-0.2	16	6.6	26	10	20	32	2	81	6 059 LBN-20/25
32	16.1	10	35 +0.4/-0.2	18.5	6.6	31	11	24	35	2	109	195 860 LBN-32
40	18.1	12	40 +0.4/-0.2	24.5	9	35	13	30	45	2	192	195 861 LBN-40
50/63	21.1	16	45 +0.5/-0.2	28	9	39	14	34	50	2	302	195 862 LBN-50/63

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents.


Clevis foot CRLBN, stainless steel

Material:

High-alloy steel

Free of copper and PTFE

RoHS-compliant



Dimensions and ordering data												
For Ø	CM	EK Ø	FL	GL	HB Ø	LE	MR	RG	UX	CRC ¹⁾	Weight [g]	Part No. Type
[mm]												
12/16	12.1	6	27 +0.3/-0.2	13	5.5	24	7	15	25	4	55	161 862 CRLBN-12/16
20/25	16.1	8	30 +0.4/-0.2	16	6.6	26	10	20	32	4	62	161 863 CRLBN-20/25
32	16.1	10	35 +0.4/-0.2	18.5	6.6	31	11	24	35	4	107	195 866 CRLBN-32
40	18.1	12	40 +0.4/-0.2	24.5	9	35	13	30	45	4	184	195 867 CRLBN-40
50/63	21.1	16	45 +0.5/-0.2	28	9	39	14	34	50	4	289	195 868 CRLBN-50/63

1) Corrosion resistance class 4 according to Festo standard 940 070

Components requiring higher corrosion resistance. Parts used with aggressive media, e.g. food or chemical industry. These applications should be supported with special tests with the media if required.

Clevis feet LN

Technical data

FESTO

Clevis foot LN

Material:


Ø 32 ... 50: High-alloy steel

Ø 63 ... 320: Nodular graphite cast

iron

Free of copper and PTFE

RoHS-compliant



Dimensions and ordering data																	
For Ø	BR	BT	CK Ø	EB Ø H13	EM	GL	HB Ø H13	OF	PH	RA	TE	UL	UR	CRC ¹⁾	Weight [g]	Part No.	Type
[mm]																	
32	10	8	10 H9	–	25.8 –0.4	21	5.5	–	32	18	38	51	31	2	170	5 147	LN-32
40	11	10	12 H9	–	27.8 –0.4	24	5.5	–	36	22	41	54	35	2	220	5 148	LN-40
50	12	12	12 H9	–	31.8 –0.4	33	6.6	–	45	30	50	65	45	2	380	5 149	LN-50
63	14.5	12	16 H8	15	40 c11	37	6.6	10.8	50	35	52	67	51	2	505	5 150	LN-63
80	14.5	14	16 H8	20	50 c11	47	9	12.7	63	40	66	86	60	2	790	5 151	LN-80
100	18.5	15	20 H8	20	60 c11	55	9	13.7	71	50	76	96	70	2	1250	5 152	LN-100
125	22	20	25 H8	20	70 c11	70	11	18.6	90	60	94	124	90	2	2693	9 036	LN-125
160	31	25	30 H8	20	90 c11	97	14	23.6	115	88	118	156	126	2	6260	9 037	LN-160
200	31	30	30 H8	26	90 c11	105	16	28.5	135	90	122	162	130	2	7940	9 038	LN-200
250	38.5	35	40 H8	33	110 c11	128	22	33.5	165	110	150	200	160	2	13400	9 039	LN-250
320	44.5	40	45 H8	40	120 c11	150	26	38.5	200	122	170	234	186	2	21900	9 040	LN-320

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents.

Clevis feet LNG/CRLNG


Technical data

FESTO

Clevis foot LNG

Material:

Ø 32 ... 50: High-alloy steel
Ø 63 ... 200: Nodular graphite cast iron
Free of copper and PTFE
RoHS-compliant



Dimensions and ordering data																	
For Ø	BR	BT	CK Ø D11	EB Ø H13	EM	GL	HB Ø H13	OF	PH	RA	TE	UL	UR	CRC ¹⁾	Weight	Part No.	Type
[mm]															[g]		
32	10	8	10	–	25.8 –0.4	21	6.6	–	32	18	38	51	31	2	170	33 890	LNG-32
40	11	10	12	–	27.8 –0.4	24	6.6	–	36	22	41	54	35	2	190	33 891	LNG-40
50	12	12	12	–	31.8 –0.4	33	9	–	45	30	50	65	45	2	290	33 892	LNG-50
63	15	12	16	15	40 c11	37	9	10.8	50	35	52	67	50	2	450	33 893	LNG-63
80	15	14	16	18	50 c11	47	11	12.7	63	40	66	86	60	2	800	33 894	LNG-80
100	19	15	20	18	60 c11	55	11	13.7	71	50	76	96	70	2	1150	33 895	LNG-100
125	22	20	25	20	70 c11	70	14	18.6	90	60	94	124	90	2	2640	33 896	LNG-125
200	31	30	30	26	90 c11	105	18	28.5	135	90	122	162	130	2	8150	33 898	LNG-200


1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents.

Clevis foot CRLNG, stainless steel

Material:

Special steel casting
Free of copper and PTFE



Dimensions and ordering data																
For Ø	BR	BT	CK Ø	EM	GL	HB Ø	PH	RA	TE	UL	UR	CRC ¹⁾	Weight	Part No.	Type	
[mm]			D11	−0.4		H13							[g]			
32	10	8	10	25.8	21	6.6	32	18	38	51	31	4	120	161 840	CRLNG-32	
40	11	10	12	27.8	24	6.6	36	22	41	54	35	4	160	161 841	CRLNG-40	
50	12	12	12	31.8	33	9	45	30	50	65	45	4	280	161 842	CRLNG-50	
63	15	12	16	39.8	37	9	50	35	52	67	50	4	375	161 843	CRLNG-63	
80	15	14	16	49.8	47	11	63	40	66	86	60	4	580	161 844	CRLNG-80	
100	19	15	20	59.8	55	11	71	50	76	96	70	4	935	161 845	CRLNG-100	
125	22	20	25	69.8	70	14	90	60	94	124	90	4	2530	176 951	CRLNG-125	

1) Corrosion resistance class 4 according to Festo standard 940 070

Components requiring higher corrosion resistance. Parts used with aggressive media, e.g. food or chemical industry. These applications should be supported with special tests with the media if required.

Clevis feet LBG

Technical data

FESTO

Clevis foot LBG


The pivot pin is secured against rotation with a dowel pin.

Material:

Nodular graphite cast iron

Free of copper and PTFE

RoHS-compliant



Dimensions and ordering data																		
For Ø	CL	CM	EK Ø	FL	GL	HB Ø	L2	LE	MR	RF	RG	S1 Ø	UK	UX	CRC ¹⁾	Weight [g]	Part No.	Type
[mm]	±0.2																	
32	28	14.1	10	32	16±0.25	6.8	35	24	12	42	20±0.3	4.8	56	36	2	220	31 761	LBG-32
40	30	16.1	12	36	20±0.3	6.8	39	26	14	44	26±0.3	5.8	58	41.5	2	300	31 762	LBG-40
50	40	21.1	16	45	25±0.3	9.2	50	33	15	56	31±0.4	5.8	70	47	2	540	31 763	LBG-50
63	40	21.1	16	50	25±0.3	9	50	38	17	56	31±0.4	7.8	70	45	2	580	31 764	LBG-63
80	50	25.1	20	63	30	11	60	49	18	70	36	7.8	89	55	2	1050	31 765	LBG-80
100	50	25.1	20	71	41	11	60	56	22	70	46	9.8	89	65	2	1375	31 766	LBG-100
125	80	37.2	30	90	60	14	89	70	26	106	70	11.8	128	96	2	4140	31 767	LBG-125

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents.

Clevis feet LSN

Technical data

FESTO

Clevis foot LSN


with spherical bearing

Material:

Nodular graphite cast iron

Ø 32 ... 200: Free of copper and PTFE

RoHS-compliant



Dimensions and ordering data									
For Ø	BR	BT	CK Ø	EB Ø	EM	GL	HB Ø	LE	OF
[mm]	-1								
32	13	10	10 -0.008	10	25.8	21	5.5	16	4.5
40	15	10	12 -0.008	10	27.8	24	5.5	20	4.3
50	15	12	12 -0.008	11	31.8	33	6.6	22	5.2
63	20	12	16 -0.008	11	39.8	37	6.6	30	5.2
80	20	14	16 -0.008	15	49.8	47	9	31	5
100	24	15	20 -0.010	15	59.8	55	9	38	6
125	33	20	25 -0.010	22	69.8	70	11	-	18
160	36	25	30 -0.010	26	89.8	97	13.5	-	22
200	36	30	30 -0.010	30	89.8	105	16	-	27
250	43	35	40 -0.012	40	109.5	128	22	-	32
320	54	40	45 -0.012	48	119.8	150	26	-	37

For Ø	PH	RA	TE	UL	UR	CRC ¹⁾	Weight	Part No.	Type
[mm]	±0.5						[g]		
32	32	18	38	51	31	2	160	5 561	LSN-32
40	36	22	41	54	35	2	220	5 562	LSN-40
50	45	30	50	65	45	2	380	5 563	LSN-50
63	50	35	52	67	50	2	535	5 564	LSN-63
80	63	40	66	86	60	2	850	5 565	LSN-80
100	71	50	76	96	70	2	1280	5 566	LSN-100
125	90	60	94	124	90	2	2685	6 987	LSN-125
160	115	88	118	156	126	2	5545	6 988	LSN-160
200	135	90	122	162	130	2	7450	6 989	LSN-200
250	165	110	150	200	160	2	13410	6 990	LSN-250
320	200	122	170	234	186	2	16960	6 991	LSN-320

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents.

Clevis feet LSNG

Technical data

FESTO

Clevis foot LSNG

with spherical bearing


Material:

Ø 32 ... 50: High-alloy steel

Ø 63 ... 200: Nodular graphite cast

iron

RoHS-compliant



Dimensions and ordering data									
For Ø	BR	BT	CN Ø	EB Ø	EN	EU	GL	HB Ø	OF
[mm]				+0.5	-0.1	-0.2	js14	H13	
32	15	10 +0.2	10 +0.013	–	14	10.5	21	6.6	8.5 +0.8
40	17	10 +0.2	12 +0.015	–	16	12	24	6.6	8.5 +0.8
50	20	12 +0.2	16 +0.015	–	21	15	33	9	10.5 +0.8
63	21+1.5/-0.5	12 +0.6	16 +0.015	–	21	15	37	9	10.5 +0.8
80	26+1.5/-0.5	14 +0.6	20 +0.018	–	25	18	47	11	12 +0.8
100	29	15 +0.6	20 +0.018	–	25	18	55	11	13 +0.8
125	39	20 +0.7	30 +0.018	20	37	25	70	14	17 +1
160	42	25 +0.7	35 +0.021	20	43	28	97	14	21 +1
200	42	30 +0.7	35 +0.021	26	43	28	105	18	26.5 +1

For Ø	PH	RA	TE	UL	UR	CRC ¹⁾	Weight	Part No.	Type
[mm]	js14	js14	js14				[g]		
32	32	18	38	51	31	2	185	31 740	LSNG-32
40	36	22	41	54	35	2	245	31 741	LSNG-40
50	45	30	50	65	45	2	455	31 742	LSNG-50
63	50	35	52	67 ⁺¹	50 ⁺¹	2	585	31 743	LSNG-63
80	63	40	66	86 ⁺¹	60 ⁺¹	2	1025	31 744	LSNG-80
100	71	50	76	96 ₋₁	70 ₋₁	2	1390	31 745	LSNG-100
125	90	60	94	124 ₋₁	90 ₋₁	2	3137	31 746	LSNG-125
160	115	88	118	156 ₋₁	126 ₋₁	2	4273	152 599	LSNG-160
200	135	90	122	162 ₋₁	130 ₋₁	2	5908	152 600	LSNG-200

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents.

Clevis feet LSNSG

Technical data

FESTO

Clevis foot LSNSG



weld-on,
with spherical bearing

Material:

Ø 32 ... 100: Galvanised steel

Ø 125: Tempered steel, galvanised

RoHS-compliant



Dimensions and ordering data										
For Ø	CN Ø	EN	ER	EU	LO	PH	UL	CRC ¹⁾	Weight	Part No. Type
[mm]		-0.1	±0.5		±0.5	js15			[g]	
32	10 +0.013	14	15.5	10	27.5	32	28.5	2	105	31 747 LSNSG-32
40	12 +0.015	16	17.5	12	30.5	36	33.5	2	160	31 748 LSNSG-40
50	16 +0.015	21	20.5	15	40.5	45	43.5	2	300	31 749 LSNSG-50
63	16 +0.015	21	22.5	15	44.5	50	48	2	370	31 750 LSNSG-63
80	20 +0.018	25	28.5	18	57	63	58	2	700	31 751 LSNSG-80
100	20 +0.018	25	29.5	18	65	71	67.5	2	830	31 752 LSNSG-100
125	30 +0.018	37	39.5	25	85	90	87.5	2	1960	31 753 LSNSG-125

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents.

Clevis feet LQG

Technical data

FESTO

Right-angle clevis mounting LQG


The pivot pin is secured against rotation with a dowel pin.

Material:

Nodular graphite cast iron

Free of copper and PTFE

RoHS-compliant



Dimensions and ordering data											
For Ø	CK	CL	CM	EB	EM	FL	GL	H1	H2	H3	HB
[mm]	Ø h9		+0.2	Ø							Ø
32	10	27	14.2	11	25	32 ±0.3	22 ±0.3	45 ±0.5	9	14	6.6
40	12	31	16.2	11	25	36 js14	22 js14	52 ±0.5	9	15	6.6
50	16	41	21.2	15	32	45 js14	36 js14	66 ±0.5	9	20	9
63	16	41	21.2	15	36	50 js14	38 js14	71	12	20	9
80	20	51	25.1	18	36	63 js14	39 js14	89	14	25	11
100	20	51	25.1	18	42	71 js14	51 js14	97	14	25	11
125	30	80	37.1	19	50	90 ±0.4	60 js14	130	20	40	14

For Ø	LE	MR	RF	RG	S1	UK	UX	CRC ¹⁾	Weight	Part No.	Type
[mm]					Ø				[g]		
32	18	12.5	40 ±0.3	29 ±0.3	4.8	56	45	1	301	31 768	LQG-32
40	22	15	40 js14	29 js14	5.8	56	45	1	369	31 769	LQG-40
50	28	18	52 js14	40 js14	5.8	70	58	1	706	31 770	LQG-50
63	28	18	57 js14	47 js14	7.8	75	65	1	784	31 771	LQG-63
80	31	20	58 js14	48 js14	9.8	80	70	1	1125	31 772	LQG-80
100	34	22	64 js14	54 js14	9.8	90	80	1	1492	31 773	LQG-100
125	38	32	104 js14	70 js14	11.5	130	96	1	3774	31 774	LQG-125

1) Corrosion resistance class 1 according to Festo standard 940 070

Components with light corrosion exposure. Protection for transport and storage. Components without significant decorative function or surface, e.g. installed out of sight internally or behind covers.

Trunnion supports LNZG/CRLNZG

FESTO

Technical data

Trunnion support LNZG

Material:

Trunnion support:

32 ... 125: Anodised aluminium

160 ... 320: Galvanised steel


Plain bearing:

32 ... 200: Plastic

250 ... 320: Sintered bronze

32 ... 200: Free of copper and PTFE

RoHS-compliant



Dimensions and ordering data															
For Ø	CR	DA	FK	FN	FS	H1	HB	KE	NH	TH	UL	CRC ¹⁾	Weight	Part No.	Type
[mm]	Ø	Ø	Ø				Ø						[g]		
		H13					H13								
32	12 D11	11	15 ±0.1	30	10.5	15	6.6	6.8	18	32 ±0.2	46	2	83	32 959	LNZG-32
40/50	16 D11	15	18 ±0.1	36	12	18	9	9	21	36 ±0.2	55	2	129	32 960	LNZG-40/50
63/80	20 D11	18	20 ±0.1	40	13	20	11	11	23	42 ±0.2	65	2	178	32 961	LNZG-63/80
100/125	25 D11	20	25 ±0.1	50	16	24.5	14	13	28.5	50 ±0.2	75	2	306	32 962	LNZG-100/125
160/200	32 D11	26	30 ±0.2	60	22.5	36	18	17	40	60 ±0.3	92	2	659	35 780	LNZG-160/200
250	40 G7	33	35 ±0.2	70	27.5	45	22	21.5	50	90 ±0.3	140	2	2218	157 516	LNZG-250
320	50 G7	40	40 ±0.2	80	32.5	55	26	21.5	60	100 ±0.3	150	2	2934	157 517	LNZG-320

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents.



Trunnion support CRLNZG, stainless steel

Material:

High-alloy steel

Free of copper and PTFE

RoHS-compliant



Dimensions and ordering data													
For Ø	CR	FK	FN	FS	H1	HB	NH	TH	UL	CRC ¹⁾	Weight	Part No.	Type
[mm]	Ø	Ø				Ø							
	D11	±0.1				H13		±0.2			[g]		
32	12	15	30	10.5	15	6.6	18	32	46	4	205	161 874	CRLNZG-32
40/50	16	18	36	12	18	9	21	36	55	4	323	161 875	CRLNZG-40/50
63/80	20	20	40	13	20	11	23	42	65	4	435	161 876	CRLNZG-63/80
100	25	25	50	16	24.5	14	28.5	50	75	4	739	161 877	CRLNZG-100

1) Corrosion resistance class 4 according to Festo standard 940 070

Components requiring higher corrosion resistance. Parts used with aggressive media, e.g. food or chemical industry. These applications should be supported with special tests with the media if required.

Threaded bolts GBS

Technical data

FESTO


Threaded bolt GBS

for swivel mounting of drives with appropriate design

Material:

Case-hardened steel

Free of copper and PTFE



Dimensions and ordering data									
For Ø	D1	L1	L2	TD	≈C1	CRC ¹⁾	Weight	Part No.	Type
[mm]				Ø f8			[g]		
32	M8x1	14.5	6.5 ±0.1	10	5	2	10	9 236	GBS-32
40	M10x1	18.5	9 ±0.1	12	6	2	20	9 237	GBS-40
50	M12x1.5	23	12 ±0.2	14	6	2	40	9 238	GBS-50
63	M14x1.5	29	16 ±0.2	16	8	2	65	9 239	GBS-63

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents.

Slot nuts NST/NST-HMV

Technical data

FESTO


Slot nut NST

for profile slots in linear units, drives and axes as well as passive guide axes

Material:

Non-alloyed tempered steel

Free of copper and PTFE



Dimensions and ordering data						
D1	L1	L2	CRC ¹⁾	Weight	Part No.	Type
	±0.5			[g]		
M5	12	4	2	3	150 914	NST-5-M5
M6	22.5	6.25	2	11	150 915	NST-8-M6

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents.


Slot nut NST-HMV

for multi-axis systems

Material:

Non-alloyed tempered steel

Free of copper and PTFE



Dimensions and ordering data						
D1	L1	L2	CRC ¹⁾	Weight	Part No.	Type
	±0.5			[g]		
M4	—	—	2	2	526 091	NST-HMV-M4
M5	24	12.5	2	7	526 094	NST-HMV-5-2-M5
M8	50	26	2	22	526 093	NST-HMV-8-2-M8

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents.

Slot nuts NSTL/NSTH

Technical data

FESTO



Slot nut NSTL

for slides on linear drives and axes as well as passive guide axes

Material:

Non-alloyed tempered steel

Free of copper and PTFE



Dimensions and ordering data						
D1	L1 ±0.5	L2	L3	CRC ¹⁾	Weight [g]	Part No. Type
M5	100	13	15	2	23	158 410 NSTL-25
M5	128	14	15	2	30	158 411 NSTL-32
M5	166	25	20	2	40	158 412 NSTL-40
M8	199	24	20	2	138	158 413 NSTL-50
M8	229	30	35	2	160	158 414 NSTL-63
M8	319	30	35	2	228	161 356 NSTL-80

- 1) Corrosion resistance class 2 according to Festo standard 940 070
Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents.



Slot nut NSTH

for slides on heavy-duty guides HD

Material:

Non-alloyed tempered steel

Free of copper and PTFE



Dimensions and ordering data						
D1	L1 ±0.5	L2	L3	CRC ¹⁾	Weight [g]	Part No. Type
M3	89	15	15	2	7	161 018 NSTH-8
M5	119	15	15	2	28	161 019 NSTH-12
M5	159	25	20	2	38	161 020 NSTH-18
M8	209	25	20	2	146	161 021 NSTH-25
M8	259	30	35	2	184	161 022 NSTH-40

- 1) Corrosion resistance class 2 according to Festo standard 940 070
Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents.

Centring pins/centring sleeves

Technical data

FESTO


Centring pin ZBS

Material:

Corrosion resistant steel

Free of copper and PTFE

RoHS-compliant



Dimensions and ordering data						
D1	B1	CRC ¹⁾	Weight	Part No.	Type	PU ²⁾
Ø			[g]			
h8	-0.2					
2	5	2	1	525 273	ZBS-2	10
5	5	2	1	150 928	ZBS-5	10

- 1) Corrosion resistance class 2 according to Festo standard 940 070
Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents.
- 2) Packaging unit quantity


Centring sleeve ZBH

Material:

Corrosion resistant steel

Free of copper and PTFE

RoHS-compliant



Dimensions and ordering data						
D1	B1	D2	CRC ¹⁾	Weight	Part No.	Type
Ø		Ø		[g]		
h7	-0.2					PU ²⁾
5	2.4	3.2	2	1	189 652	ZBH-5
7	3	5.3	2	1	186 717	ZBH-7
9	4	6.4	2	1	150 927	ZBH-9
12	5	10.3 +0.1	2	1	189 653	ZBH-12
15	6	12.4	2	3	191 409	ZBH-15

- 1) Corrosion resistance class 2 according to Festo standard 940 070
Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents.
- 2) Packaging unit quantity


Central mountings/slot covers

FESTO

Technical data

Central mounting SLZZ

Material:
Corrosion resistant steel
Free of copper and PTFE




Dimensions and ordering data					
D1 Ø	B1	CRC ¹⁾	Weight [g]	Part No.	Type
h8	-0.2				
14	5	2	21	150 900	SLZZ-16/10
25	5.5	2	40	150 901	SLZZ-25/16
25	5.5	2	84	150 904	SLZZ-50/40

1) Corrosion resistance class 4 according to Festo standard 940 070
Components requiring higher corrosion resistance. Parts used with aggressive media, e.g. food or chemical industry. These applications should be supported with special tests with the media if required.

Slot cover ABP for mounting slots

Slot cover ABP-5-S for sensor slots

Material:
Acrylic butadiene styrene



Ordering data					
Slot type	Length [m]	Weight [g]	Part No.	Type	PU ¹⁾
Mounting slot	0.5	16	151 681	ABP-5	2
	0.5	42	151 682	ABP-8	2
Sensor slot	0.5	15	151 680	ABP-5-S	2
	0.5	13	563 360	ABP-5-S1	2

1) Packaging unit quantity