

Hand lever valves VHER, NPT

FESTO



Hand lever valves VHER, NPT

Key features

FESTO



Powerful

-  - Flow rate
600 ... 4,300 l/min

Versatile

- 4/3-way valve
Mid-position closed
Mid-position exhausted
- Connection NPT $\frac{1}{8}$ -27, NPT $\frac{1}{4}$ -18, NPT $\frac{1}{2}$ -14
- 3/3-way valve
The hand lever valve VHER can be used as a 3/3-way valve by sealing port 2

Practical

These valves can be used to stop single-acting cylinders (3/3-way valve) or double-acting cylinders (4/3-way valve) within the stroke range.







With the mid-position closed, the drive piston moves until the forces are balanced.

With the mid-position exhausted, the piston can be moved manually (only the frictional forces have to be overcome).

Hand lever valves VHER, NPT

FESTO

Product range overview

Function	Version	Type	Nominal flow rate	Lever		Connection size			→ Page/ Internet	
			[l/min]	Small	Large	NPT $\frac{1}{8}$ -27	NPT $\frac{1}{4}$ -18	NPT $\frac{1}{2}$ -14		
	Port underneath									
		VHER-AH-M04C-N18-UD	800	■	–	■	–	–	7	
		VHER-AH-M04C-N14-UD	1,500	–	■	–	■	–		
		VHER-AH-M04C-N12-UD	4,300	–	■	–	–	■		
		Port at side								
			VHER-AH-M04C-N18-LD	600	■	–	■	–	–	7
			VHER-AH-M04C-N14-LD	1,150	–	■	–	■	–	
VHER-AH-M04C-N12-LD			3,500	–	■	–	–	■		
	Port underneath									
		VHER-AH-M04E-N18-UD	800	■	–	■	–	–	7	
		VHER-AH-M04E-N14-UD	1,500	–	■	–	■	–		
		VHER-AH-M04E-N12-UD	4,300	–	■	–	–	■		
		Port at side								
			VHER-AH-M04E-N18-LD	600	■	–	■	–	–	7
			VHER-AH-M04E-N14-LD	1,150	–	■	–	■	–	
VHER-AH-M04E-N12-LD			3,500	–	■	–	–	■		

Hand lever valves VHER, NPT

FESTO

Type codes

		VHER	-	AH	-	M04C	-	N18	-	LD
Type										
VHER	Hand lever valve with detent									
Design										
AH	Metal lever									
Valve function										
M04C	4/3-way valve, mid-position closed									
M04E	4/3-way valve, mid-position exhausted									
Connection size										
N18	NPT $\frac{1}{8}$ -27									
N14	NPT $\frac{1}{4}$ -18									
N12	NPT $\frac{1}{2}$ -14									
Type of connection										
LD	To the side									
UD	Underneath									

Hand lever valves VHER, NPT

Overview of peripherals

FESTO



Control panel installation

Connection size (large): VHER...N14-LD, VHER...N12-LD

Type of connection: To the side

Connection size (small): VHER...N18-UD

Type of connection: Underneath



Component parts and accessories	Brief description	→ Page/Internet
1 Hand lever valve VHER	Connection size NPT $\frac{1}{4}$ -18 and NPT $\frac{1}{2}$ -14	7
2 Control panel	Not included in the scope of delivery	–
3 Mounting screws	Not included in the scope of delivery	–
4 Proximity sensors SME-10-... L, SME-10-... Q	Not included in the scope of delivery	sme
5 Hand lever valve VHER	Connection size NPT $\frac{1}{8}$ -27	7
6 Knurled nut	Control panel mounting	–
7 Actuating lever	Small, metal	
8 Actuating lever	Large, metal	

Hand lever valves VHER, NPT

Overview of peripherals

FESTO



Assembled valves with accessories

Connection size (large): VHER...N14-UD, VHER...N12-UD

Type of connection: Underneath

Connection size (small): VHER...N18-LD

Type of connection: To the side



Component parts and accessories	Brief description	→ Page/Internet
1 Hand lever valve VHER	Connection size NPT 1/4-18 and NPT 1/2-14 with metal lever	7
2 Hand lever valve VHER	Connection size NPT 1/8-27 with metal lever	7
3 Proximity sensors SME-10-... L, SME-10-... Q	Not included in the scope of delivery	sme

Hand lever valves VHER, NPT

FESTO

Technical data – VHER with metal lever

-  - Flow rate
600 ... 4,300 l/min

-  - Pressure
-0.95 ... +10 bar

-  - Temperature range
-20 ... +80 °C



General technical data					
Connection size			NPT1/8-27	NPT1/4-18	NPT1/2-14
Valve function			4/3-way, closed or exhausted		
Design			Rotary slide valve		
Sealing principle			Hard		
Type of mounting			Option of front panel mounting or via through-holes		
Type of control			Direct		
Actuation type			Manual		
Actuating lever			Metal		
Switching position display			Via accessories		
Mounting position			Any		
Direction of flow			Reversible		
Non-overlapping			Yes		
Exhaust function			Flow control		
Standard nominal flow rate	Port at side	[l/min]	600	1,150	3,500
	Port underneath	[l/min]	800	1,500	4,300
Nominal size		[mm]	6	8	12
Pneumatic connection 1,2,3,4			NPT1/8-27	NPT1/4-18	NPT1/2-14
Actuating torque at 10 bar		[Nm]	1.1	2.8	5

Operating and environmental conditions		
Operating medium		Compressed air in accordance with ISO 8573-1:2010 [7:4:4]
Note on operating/pilot medium		Operation with lubricated medium possible (in which case lubricated operation will always be required)
Operating pressure	[bar]	-0.95 ... 10
Ambient temperature	[°C]	-20 ... +80
Corrosion resistance	[CRC]	2 ¹⁾

1) Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Proximity sensors for switching position display			
Connection size	Connection direction	Type	
		SME-10-... L	SME-10-... Q
NPT1/8-27	Underneath (UD)	■	■
	At the side (LD)	-	■
NPT1/4-18	Underneath	■	■
	At the side	-	■
NPT1/2-14	Underneath	■	■
	At the side	-	■


Hand lever valves VHER, NPT

Technical data – VHER with metal lever

FESTO

Sectional view

Hand lever valve VHER-AH



Materials

1	Housing	Die-cast aluminium
–	Seals	Nitrile rubber
–		Contains PWIS (paint wetting impairment substances)
–		Free of copper and PTFE

Hand lever valves VHER, NPT


Technical data – VHER with metal lever

FESTO

Dimensions

Download CAD data → www.festo.com

Pneumatic connection NPT $\frac{1}{8}$ -27, at the side



Type	B1	B2	B3	D1	D2 Ø	H1	H2	H3	H4	L1	L2	L3	L4	T1
VHER-AH-...-N18-LD	51	45	28.5	$\frac{1}{8}$ NPT	3	94	45	15	7.5	85	60.5	54.5	3	2 ... 4

Hand lever valves VHER, NPT

Technical data – VHER with metal lever


FESTO

Dimensions

Download CAD data → www.festo.com

Pneumatic connection NPT $\frac{1}{8}$ -27, underneath

Mounting aperture



Type	B1	B3	B4	D1	D3 Ø	D4	H1	H2	H5	L1	L2	L5	L6	T1
VHER-AH-...-N18-UD	42	24	32	1/8NPT	5.5	M30	87	37	32.5	79	45	24	9	2 ... 4

Hand lever valves VHER, NPT


Technical data – VHER with metal lever

FESTO

Dimensions

Download CAD data → www.festo.com

Pneumatic connection NPT $\frac{1}{4}$ -18 and NPT $\frac{1}{2}$ -14, at the side



Type	B1	B2	B3	D1	D2 Ø	H1	H2	H3	H4	L1	L2	L3	L4
VHER-AH-...-N14-LD	66	57.5	37.5	1/4NPT	4.5	136	56	20.5	10.3	165	77	69.2	4
VHER-AH-...-N12-LD	95	85	57	1/2NPT	5.5	149	68	29	14.5	180	108.5	97.3	5.5

Hand lever valves VHER, NPT


Technical data – VHER with metal lever

FESTO

Dimensions

Download CAD data → www.festo.com

Pneumatic connection NPT $\frac{1}{4}$ -18 and NPT $\frac{1}{2}$ -14, underneath





1 Sensor slot for SME-10

Type	B1	B2	B3	B4	D1	D2	D3 Ø	D4 Ø	H1	H2	H5	L1	L2	L3	L4	L5	L6	T1
VHER-AH-...-N14-UD	56	42	33	42	1/4NPT	M5	5.5	40	130	49	43.5	157	60	42	7.2	33	11.4	12
VHER-AH-...-N12-UD	80	60	50	60	1/2NPT	M6	6.4	50	137	55.8	49.8	169	85	60	10	50	15	13

Hand lever valves VHER, NPT

FESTO

Accessories

Ordering data						
Circuit symbol	Description	Weight [g]	Connection direction	Connection size	Part No.	Type
4/3-way valve ¹⁾						
	Mid-position closed	260	At the side	NPT $\frac{1}{8}$ -27	545260	VHER-AH-M04C-N18-LD
		560		NPT $\frac{1}{4}$ -18	545264	VHER-AH-M04C-N14-LD
		1,010		NPT $\frac{1}{2}$ -14	545268	VHER-AH-M04C-N12-LD
		220	Underneath	NPT $\frac{1}{8}$ -27	545261	VHER-AH-M04C-N18-UD
		510		NPT $\frac{1}{4}$ -18	545265	VHER-AH-M04C-N14-UD
		860		NPT $\frac{1}{2}$ -14	545269	VHER-AH-M04C-N12-UD
	Mid-position exhausted	260	At the side	NPT $\frac{1}{8}$ -27	545262	VHER-AH-M04E-N18-LD
		560		NPT $\frac{1}{4}$ -18	545266	VHER-AH-M04E-N14-LD
		1,010		NPT $\frac{1}{2}$ -14	545270	VHER-AH-M04E-N12-LD
		220	Underneath	NPT $\frac{1}{8}$ -27	545263	VHER-AH-M04E-N18-UD
		510		NPT $\frac{1}{4}$ -18	545267	VHER-AH-M04E-N14-UD
		860		NPT $\frac{1}{2}$ -14	545271	VHER-AH-M04E-N12-UD

1) The hand lever valve can be used as a 3/3-way valve by sealing port 2.

Hand lever valves VHER, NPT


Accessories

FESTO

Ordering data				
	Description	Pneumatic connection	Part No.	Type
Blanking plug				
	For sealing ports	NPT $\frac{1}{8}$ -27	173985	B- $\frac{1}{8}$ -NPT
		NPT $\frac{1}{2}$ -14	31785	B- $\frac{1}{2}$ -NPT

Ordering data QS fittings					
Part No.	Type	Part No.	Type	Part No.	Type
VHER-...-N18-UD		VHER-...-N14-UD		VHER-...-N12-UD	
533271	QS-1/8-5/32-U	567772	QS-1/4-5/32-U	533283	QS-1/2-3/8-U
153903	QSM-1/8-1/8-U	533275	QS-1/4-3/16-U	533284	QS-1/2-1/2-U
190677	QSM-1/8-5/32-U	533276	QS-1/4-1/4-U	190698	QS-1/2-1/2-I-U
190688	QS-1/8-5/32-I-U	533277	QS-1/4-5/16-U		
190690	QS-1/8-1/4-I-U	190692	QS-1/4-1/4-I-U		
190691	QS-1/8-5/16-I-U	190693	QS-1/4-5/16-I-U		
190685	QSM-1/8-5/32-I-U	190694	QS-1/4-3/8-I-U		
190689	QSM-1/8-3/16-I-U	190680	QSM-1/4-1/8-U		
VHER-...-N18-LD		VHER-...-N14-LD		VHER-...-N12-LD	
190688	QS-1/8-5/32-I-U	190692	QS-1/4-1/4-I-U	190698	QS-1/2-1/2-I-U
190690	QS-1/8-1/4-I-U	190693	QS-1/4-5/16-I-U		
		190694	QS-1/4-3/8-I-U		

Ordering data Silencers					
Part No.	Type	Part No.	Type	Part No.	Type
VHER-...-N18-UD		VHER-...-N14-UD		VHER-...-N12-UD	
12638	U- $\frac{1}{8}$ -B-NPT	12639	U- $\frac{1}{4}$ -B-NPT	12741	U- $\frac{1}{2}$ -B-NPT
161419	UC- $\frac{1}{8}$	165004	UC- $\frac{1}{4}$		
VHER-...-N18-LD		VHER-...-N14-LD		VHER-...-N12-LD	
161419	UC- $\frac{1}{8}$	165004	UC- $\frac{1}{4}$	12741	U- $\frac{1}{2}$ -B-NPT
		12639	U- $\frac{1}{4}$ -B-NPT		

Ordering data Proximity sensors for VHER						
	Electrical connection		Cable length [m]	Connection direction	Part No.	Type
	Cable	Plug M8x1				
	N/O contact		2.5	In-line	173210	SME-10-KL-LED-24
	3-wire	–			173211	SME-10-KQ-LED-24
	–	3-pin	0.3	In-line	173212	SME-10-SL-LED-24
				Lateral	173213	SME-10-SQ-LED-24