

Pressure sensors SDE5

FESTO



Pressure sensors SDE5

Key features

FESTO

At a glance





SDE5-...-M8

Plug version, plug M8x1,
3-pin



SDE5-...-K

Cable version, 2.5 m long,
3-wire



Linkable wall bracket with clip-in facility for sensors
(included in the scope of delivery)

Product description

The pressure sensor SDE5 is a cost-effective alternative for simple and quick pressure monitoring. The “intelligent fitting” delivers instant information about the current pressure and is an equally effective device for object detection via back pressure as it is for pressure, regulation and vacuum detection.

Main applications

The pressure sensor SDE5 can be used wherever simple sensing of the current pressure is required:

- Compressed air monitoring
- Regulator monitoring
- Suction confirmation in vacuum technology
- Object detection via back pressure

Features


- Selectable output functions
- Teach-in function for programming
- Minimal assembly times thanks to QS fittings and linkable wall bracket
- Quick switching-point adjustment at the touch of a button
- Switching status indicated by an LED visible from all sides
- Relative pressure or differential pressure measurement
- Five pressure measuring ranges: 0 ... -1, -1 ... 1, 0 ... 2, 0 ... 6, 0 ... 10 bar
- Analogue output: 0 ... 10 V
- Electrical outputs: 1 switching output PNP or NPN

Pressure sensors SDE5


Key features

Application examples

Vacuum monitoring




- Pressure sensor SDE5 in combination with a vacuum generator VN for vacuum monitoring in the handling of bottles




- Pressure sensor SDE5 as suction monitoring in the handling of small parts, such as computer chips

Pressure monitoring



- Pressure sensor SDE5 as pressure monitor for the pressing in of punched parts




- Pressure sensor SDE5 as "inline variant" for pressure range monitoring on a compressed air screw driver

Pressure sensors SDE5

Peripherals overview

FESTO

Peripherals overview



Mounting attachments and accessories		→ Page/Internet
1	Pressure sensor SDE5-...-M8, plug version	6
2	Pressure sensor SDE5-...-K, cable version	6
3	Wall bracket (included in scope of delivery)	–
4	Connecting cable NEBU-M8W3 with angled plug socket	11
5	Connecting cable NEBU-M8G3 with straight plug socket	11

Pressure sensors SDE5

Type codes

		SDE5	-	D10	Z	-	FP	-	Q6	-	P	-	M8
Type													
SDE5	Pressure sensor												
Pressure measuring range													
V1	0 ... -1 bar												
D2	0 ... +2 bar												
D10	0 ... +10 bar												
Pressure input													
	Relative pressure												
Z	Differential pressure												
Output function													
Freely programmable													
FP	Selectable												
Threshold value with fixed hysteresis, 1 teach-in pressure													
O	N/O contact												
C	N/C contact												
Threshold value with fixed hysteresis, 2 teach-in pressures													
O1	N/O contact												
Threshold value with variable hysteresis, 2 teach-in pressures													
O2	N/O contact												
Window comparator with fixed hysteresis, 2 teach-in pressures													
O3	N/O contact												
C3	N/C contact												
Analogue output (no binary switching function)													
NF	Analogue output 0 ... 10 V												
Pneumatic connection													
Push-in connector at both ends													
Q4	For tubing O.D. 4 mm												
Q6	For tubing O.D. 6 mm												
Push-in connector at one end													
Q4E	For tubing O.D. 4 mm												
Q6E	For tubing O.D. 6 mm												
T14E	For tubing O.D. 1/4"												
Electrical output													
P	1 switching output PNP												
N	1 switching output NPN												
V	1 analogue output 0 ... 10 V												
Electrical connection													
K	Cable, 2.5 m long, 3-wire												
M8	Plug, M8x1, 3-pin												

Additional variants can be ordered using the modular system → 10

- Pressure measuring range
- Output function
- Pneumatic connection
- Electrical accessories
- X teach-in point permanently set
- Y teach-in point permanently set


Pressure sensors SDE5

Technical data


FESTO

Function



Switching output PNP



Analogue output



Switching output NPN



General technical data					
Type SDE5	-V1	-B2	-D2	-D6	-D10
General information					
Certification	C tick				
	cULus recognized (OL)				
CE mark (see declaration of conformity)	To EU EMC Directive				
Note on materials	RoHS-compliant				
Input signal/measuring element					
Measured variable	Relative pressure				
	Differential pressure				
Method of measurement	Piezoresistive pressure sensor				
Pressure measuring range [bar]	0 ... -1	-1 ... +1	0 ... +2	0 ... +6	0 ... +10
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:4:4]				
Note on operating/pilot medium	Operation with lubricated medium possible (in which case lubricated operation will always be required)				
Temperature of medium [°C]	0 ... +50				
Ambient temperature [°C]	0 ... +50				

Electrical data		
Output, general ¹⁾		
Repetition accuracy ±FS	[%]	0.3
Temperature coefficient ±FS/K	[%]	0.05
Switching output		
Accuracy	[%]	0.5
Switching output ±FS ¹⁾		
Switching output		PNP NPN
Switching function		Freely programmable (switching/teach-in function, N/O contact, N/C contact) Threshold value with fixed hysteresis Threshold value with variable hysteresis Window comparator with fixed hysteresis
Switching element function		N/C contact N/O contact Switchable
Max. output current	[mA]	100
Voltage drop	[V]	Max. 1.8
Inductive protective circuit		Adapted to MZ, MY, ME coils
Analogue output		
Output characteristic curve	[V]	0 ... 10
Accuracy	[%]	3 (ambient temperature 20 ... +25 °C) 4 (ambient temperature 0 ... +50 °C)
Analogue output ±FS ¹⁾		
Linearity error ±FS ¹⁾	[%]	0.3

1) % FS = % of the measuring range final value (full-scale)

Pressure sensors SDE5

Technical data

Electrical data		
Output, additional data		
Protection against short circuit	Yes	
Electronics		
Operating voltage range DC	[V]	15 ... 30
Protection against polarity reversal	For all electrical connections	
Electromechanics		
Electrical connection	Plug M8x1, 3-pin, round design, to EN 60947-5-2	
	Cable 2.5 m. 3-wire, to EN 60947-5-2	

Pin allocation		
Plug, M8x1, 3-pin	Pin	Meaning
	1	Operating voltage +24 V DC
	2/4	Switching output or analogue output
	3	0 V

Mechanics		
Type of mounting	Via accessories	
Mounting position	Any	
Pneumatic connection	QS-4	
	QS-6	
	QS-1/4"	
	QS-3/32"	
Product weight [g]	19 (plug version)	
	47 (cable version)	
Product weight of wall bracket [g]	5.5	
Material of housing	PA	
	POM	

Display/operation		
Switching output		
Switching status display	Yellow LED	
Threshold value setting range	[%]	0 ... 100
Analogue output		
Ready status display	Green LED	

Immissions/emissions		
Storage temperature [°C]	-20 ... +80	
Protection class	IP40	
Electrical protection class	III	
Corrosion resistance class CRC ¹⁾	2	

1) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Pressure sensors SDE5


Technical data

FESTO


Dimensions

Download CAD data → www.festo.com


SDE5-...-M8, plug version



SDE5 with wall bracket



SDE5-...-K, cable version



- 1 Plug M8x1, 3-pin or cable, 3-wire, 2.5 m long
- 2 LED display, visible from all sides
- 3 Pneumatic connection 1
- 4 Pneumatic connection 2 or blanking plug with SDE5-...E
- 5 Holder for wall mounting (included in scope of delivery)
- 6 2x through-hole for mounting screw
- 7 Connecting cable NEBU-M8W3 with angled plug socket
- 8 Connecting cable NEBU-M8G3 with straight plug socket

Type	B1	B2	B3	D1	D2	H1	H2	L1	L2	L3	L4	L5	L6	L7
SDE5-...-M8	16	23	21.4	–	4.5	24.5	40.3	38.5	45.5	56	73.5	–	38.5	20
SDE5-...-K				2.9			–		–	–	–	41.5		

Ordering data – Measured variable differential pressure

Freely programmable (switching/teach-in function, N/O contact, N/C contact)							
0 ... +10	Switchable	Switching output PNP	Plug, M8x1, 3-pin	–	QS-6	567460	SDE5-D10Z-FP-Q6-P-M8
Threshold value with fixed hysteresis, 1 teach-in pressure							
0 ... +10	N/O contact	Switching output PNP	Plug, M8x1, 3-pin	–	QS-6	567462	SDE5-D10Z-O-Q6-P-M8

Pressure sensors SDE5

Technical data

FESTO

Ordering data – Measured variable relative pressure								
Pressure measuring range [bar]	Switching element function	Electrical output	Electrical connection	Pneumatic connection		Part No.	Type	
				At one end	At both ends			
Freely programmable (switching/teach-in function, N/O contact, N/C contact)								
0 ... -1	Switchable	Switching output PNP	Plug, M8x1, 3-pin	–	QS-6	542887	SDE5-V1-FP-Q6-P-M8	
0 ... +10	Switchable	Switching output PNP	Plug, M8x1, 3-pin	QS-4	–	542900	SDE5-D10-FP-Q4E-P-M8	
				QS-6	–	542897	SDE5-D10-FP-Q6E-P-M8	
				QS-1/4	–	567467	SDE5-D10-FP-T14E-P-M8	
				–	QS-6	542898	SDE5-D10-FP-Q6-P-M8	
			Cable, 3-wire	QS-4	–	542901	SDE5-D10-FP-Q4E-P-K	
				–	QS-6	542899	SDE5-D10-FP-Q6-P-K	
Threshold value with fixed hysteresis, 1 teach-in pressure								
0 ... -1	N/O contact	Switching output PNP	Plug, M8x1, 3-pin	QS-4	–	527460	SDE5-V1-O-Q4E-P-M8	
				QS-6	–	527461	SDE5-V1-O-Q6E-P-M8	
				–	QS-4	527457	SDE5-V1-O-Q4-P-M8	
				–	QS-6	527458	SDE5-V1-O-Q6-P-M8	
0 ... +2	N/O contact	Switching output PNP	Cable, 3-wire	QS-6	–	542888	SDE5-D2-O-Q6E-P-K	
0 ... +10	N/O contact	Switching output PNP	Plug, M8x1, 3-pin	QS-4	–	527466	SDE5-D10-O-Q4E-P-M8	
				QS-6	–	527467	SDE5-D10-O-Q6E-P-M8	
				QS-1/4	–	567468	SDE5-D10-O-T14E-P-M8	
				–	QS-4	527463	SDE5-D10-O-Q4-P-M8	
				–	QS-6	527464	SDE5-D10-O-Q6-P-M8	
			Cable, 3-wire	QS-6	–	542890	SDE5-D10-O-Q6E-P-K	
	N/C contact	Switching output NPN	Plug, M8x1, 3-pin	–	QS-6	567473	SDE5-D10-O-Q6-N-M8	
			Cable, 3-wire	–	QS-6	567469	SDE5-D10-O-Q6-N-K	
			Switching output PNP	Plug, M8x1, 3-pin	QS-4	–	542889	SDE5-D10-C-Q4E-P-M8
					QS-6	–	542894	SDE5-D10-C-Q6E-P-M8
		Cable, 3-wire	QS-6	–	542895	SDE5-D10-C-Q6E-P-K		
Threshold value with fixed hysteresis, 2 teach-in pressures with mean value calculation								
0 ... -1	N/O contact	Switching output PNP	Plug, M8x1, 3-pin	–	QS-6	542886	SDE5-V1-O1-Q6-P-M8	
Threshold value with variable hysteresis, 2 teach-in pressures								
0 ... +10	N/O contact	Switching output PNP	Plug, M8x1, 3-pin	QS-6	–	542891	SDE5-D10-O2-Q6E-P-M8	
				–	QS-6	542892	SDE5-D10-O2-Q6-P-M8	
Window comparator with fixed hysteresis, 2 teach-in pressures								
0 ... +10	N/O contact	Switching output PNP	Cable, 3-wire	QS-6	–	542893	SDE5-D10-O3-Q6E-P-K	
	N/C contact	Switching output PNP	Cable, 3-wire	QS-6	–	542896	SDE5-D10-C3-Q6E-P-K	
Analogue output (no binary switching function)								
0 ... -1	–	Analogue output 0 ... 10 V	Plug, M8x1, 3-pin	QS-6	–	567463	SDE5-V1-NF-Q6E-V-M8	
				–	QS-6	567464	SDE5-V1-NF-Q6-V-M8	
			Cable, 3-wire	QS-6	–	567470	SDE5-V1-NF-Q6E-V-K	
0 ... +10	–	Analogue output 0 ... 10 V	Plug, M8x1, 3-pin	QS-6	–	567465	SDE5-D10-NF-Q6E-V-M8	
				–	QS-6	567466	SDE5-D10-NF-Q6-V-M8	
			Cable, 3-wire	QS-6	–	567471	SDE5-D10-NF-Q6E-V-K	
				–	QS-6	567472	SDE5-D10-NF-Q6-V-K	

Pressure sensors SDE5

Ordering data – Modular products

FESTO

Ordering table					
Size	5	Condi- tions	Code		Enter code
[M] Module No.	529027				529027
Function	Pressure sensor		SDE5		SDE5
Pressure measuring range [bar]	0 ... -1		-V1		
	-1 ... 1		-B2		
	0 ... 2		-D2		
	0 ... 6		-D6		
	0 ... 10		-D10		
Pressure input	Relative pressure				
	Differential pressure		Z		
Output function	Freely programmable (switching/teach-in function, N/O contact, N/C contact)		-FP		
	Threshold value with fixed hysteresis, 1 teach-in point, N/O contact		-O		
	Threshold value with fixed hysteresis, 1 teach-in point, N/C contact		-C		
	Threshold value with fixed hysteresis, 2 teach-in points, N/O contact		-O1		
	Threshold value with fixed hysteresis, 2 teach-in points, N/C contact		-C1		
	Threshold value with variable hysteresis, N/O contact		-O2		
	Threshold value with variable hysteresis, N/C contact		-C2		
	Window comparator with fixed hysteresis, N/O contact		-O3		
	Window comparator with fixed hysteresis, N/C contact		-C3		
	No binary switching function (analogue output)		-NF		
Pneumatic connection	Push-in connector 4 mm, at both ends		-Q4		
	Push-in connector 6 mm, at both ends		-Q6		
	Push-in connector $\frac{5}{32}$ ", at both ends		-T532		
	Push-in connector $\frac{1}{4}$ ", at both ends		-T14		
	Push-in connector 4 mm, at one end	[4]	-Q4E		
	Push-in connector 6 mm, at one end	[4]	-Q6E		
	Push-in connector $\frac{5}{32}$ ", at one end	[4]	-T532E		
	Push-in connector $\frac{1}{4}$ ", at one end	[4]	-T14E		
Electrical output	1 switching output PNP	[5]	-P		
	1 switching output NPN	[5]	-N		
	1 analogue output 0 ... 10 V	[6]	-V		
Electrical connection	Cable, 2.5 m		-K		
	Plug M8, 3-pin		-M8		
[O] Electrical accessories	Connecting cable, straight socket, 2.5 m	[1]	-G		
	Connecting cable, angled socket, 2.5 m	[1]	-W		
	Connecting cable, straight socket, 5 m	[1]	-G5		
	Connecting cable, angled socket, 5 m	[1]	-W5		
X teach-in point permanently set in bar	-0.85 ... 10 ¹	[2]	-...X		
X teach-in point negative	Negative range	[7]	V		
Y teach-in point permanently set in bar	-0.85 ... 10 ¹	[2] [3]	-...Y		
Y teach-in point negative	Negative range	[8]	V		

[1] G, W, G5, W5 Only in combination with M8

[2] X, Y Not in combination with FP, O1, C1, NF
Must have a value if O2, C2, O3, C3
and X or Y was selected

Only one decimal place permissible in combination with D10
Sensor without Edit button, switching point cannot be changed

[3] Y Not in combination with O, C

[4] Q4E, Q6E, T532E, T14E

Not in combination with pressure input Z

[5] P, N Not in combination with output function NF

[6] V Only in combination with output function NF

[7] V Only in combination with B2 and X teach-in point in the negative range,
but then mandatory entry

[8] V Only in combination with B2 and Y teach-in point in the negative range,
but then mandatory entry

1) Permitted value range. The value for the permanently set teach-in point must always be within the chosen pressure measuring range V1, B2, D2, D6, D10.

Note on V1: Enter the teach-in pressure without a sign.


Note on B2: Enter the teach-in pressure for vacuum without a sign, but with a suffixed "V", see **[7]** or **[8]**.

Transfer order code

529027 **SDE5** - - - - - - - - - - - -

Pressure sensors SDE5

Accessories

Ordering data – Connecting cable NEBU-M8					Technical data → Internet: nebu	
	Electrical connection	Number of wires	Cable length [m]	Order code ¹⁾	Part No.	Type
	M8x1, straight plug socket	3	2.5	G	541333	NEBU-M8G3-K-2.5-LE3
		3	5	G5	541334	NEBU-M8G3-K-5-LE3
	M8x1, angled plug socket	3	2.5	W	541338	NEBU-M8W3-K-2.5-LE3
		3	5	W5	541341	NEBU-M8W3-K-5-LE3

1) When ordering using the modular system → 10