

Sealing material

FESTO



Sealing material

Technical data



FESTO

Sealing ring O/CRO

Sealing ring CRO for use in the chemicals and food processing industries

 Pressure
-0.95 ... +10 bar

Material:
Sealing ring O: Polyvinyl chloride
Sealing ring O-M3-B: Polyamide
Note on materials:
Free of copper and PTFE
Conforms to RoHS (O-1/8 ... O-3/4 only)



Sealing ring CRO:
Polyvinylidene fluoride
Note on materials:
Conforms to RoHS

Dimensions and ordering data							
For thread	Temperature range [°C]	D1	D2	B1	Part No.	Type	PU*
Sealing ring O							
M3	-40 ... +100	2.8	4.8	0.3	30290	O-M3-B	1
M5	-10 ... +60	5.1	8	1	3565	O-M5	1
					534226	O-M5-500	500
G1/8		10	13	1.5	2223	O-1/8	1
					534227	O-1/8-500	500
G1/4		13.2	18	2	2224	O-1/4	1
					534228	O-1/4-200	200
G3/8		16.8	22	2	2225	O-3/8	1
					534229	O-3/8-200	200
G1/2		21	28	2	2226	O-1/2	1
					534230	O-1/2-100	100
G3/4		26.5	33	2	2227	O-3/4	1
G1		33.3	38.9	2	210893	O-1	1
Sealing ring CRO							
M5	-40 ... +80	5.1	8	1	165191	CRO-M5	1
G1/8		10	13	2	575895	CRO-1/8 	1
G1/4		13.2	18	2	165193	CRO-1/4	1
G3/8		16.8	22	2	165194	CRO-3/8	1
G1/2		21	28	2	165195	CRO-1/2	1
G3/4		26.5	33	2	165196	CRO-3/4	1
G1		33.3	38.9	2	165197	CRO-1	1

* Packaging unit quantity

Sealing material

Technical data

FESTO


Sealing ring OL with metal housing

- Based on ISO 16030 standard
- Seals at room temperature when tightened by hand
- Captive
- Reusable
- Compatible with the existing O and OK sealing rings

—  — Temperature range
–40 ... +100 °C

—  — Pressure
–0.95 ... +30 bar

Note on materials:
Free of copper and PTFE
Conforms to RoHS



Dimensions and ordering data												
For thread	Min. tightening torque [Nm]	Max. tightening torque [Nm]	D1	D2	D3	B1	B2	CRC ¹⁾	Weight [g]	Part No.	Type	PU*
Stainless steel, nitrile rubber												
M5	0.5	6	5.05	7.4	6.25	1.45	1	2	1	34634	OL-M5	1
										534231	OL-M5-500	500
G1/8	1	26	9.8	12.8	11.1	1.8	1.3	2	1	33840	OL-1/8	1
										534232	OL-1/8-500	500
G1/4	2	40	13.2	16.8	14.4	2.2	1.6	2	1	34635	OL-1/4	1
										534233	OL-1/4-200	200
Aluminium, nitrile rubber												
G3/8	10	50	16.65	20.5	17.9	2.95	1.95	2	2	34636	OL-3/8	1
										534234	OL-3/8-200	200
G1/2	18	80	21	25.5	22.2	2.6	1.95	2	2	34637	OL-1/2	1
										534235	OL-1/2-100	100
G3/4	–	120	26.5	32	28.4	2.6	1.95	2	2	34638	OL-3/4	1

1) Corrosion resistance class 2 according to Festo standard 940 070
Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

* Packaging unit quantity

Sealing material

Technical data

FESTO




Sealing ring OK with support ring

- Based on ISO 16030 standard
- Seals at room temperature when tightened by hand
- Captive design
- Compatible with the existing O and OL sealing rings

-  - Temperature range
-10 ... +60 °C

-  - Pressure
-0.95 ... +10 bar

Note on materials:
Free of copper and PTFE
Conforms to RoHS



Dimensions and ordering data										
For thread	Min. tightening torque [Nm]	Max. tightening torque [Nm]	D1	D2	B1	CRC ¹⁾	Weight [g]	Part No.	Type	PU*
Stainless steel, nitrile rubber										
M3	0.15	0.8	2.5	5.5	0.5	2	0.04	130849	OK-M3	1
M5	0.25	2.4	4.3	7.8	0.5		0.1	130850	OK-M5	1
M7	0.3	6.4	6.4	9.8	0.5		0.1	130851	OK-M7	1
Polyamide, thermoplastic polyurethane										
G1/8	2	5	9.9	13.15	1.60	2	0.12	531771	OK-1/8	1
G1/4	10	12	13.3	18.15	2.20		0.32	531772	OK-1/4	1
G3/8	10	15	16.8	22.15	2.20		0.44	531773	OK-3/8	1
G1/2	10	18	21.2	26.45	2.35		0.6	531774	OK-1/2	1
G3/4	30	40	26.7	32.45	2.95		1	531775	OK-3/4	1

1) Corrosion resistance class 2 according to Festo standard 940 070
Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

* Packaging unit quantity

Sealing material

Technical data

FESTO

Sealing ring assortment OL-S1

This polymer assortment box contains OL sealing rings ranging in size from M5 to G $\frac{3}{4}$.



Ordering data						
Contents	Quantity	Min. tightening torque [Nm]	Max. tightening torque [Nm]	Weight [g]	Part No.	Type
OL-M5	50	0.5	6	1	161355	OL-S1
OL-1/8	100	1	26	1		
OL-1/4	100	2	40	1		
OL-3/8	40	10	50	2		
OL-1/2	30	18	80	2		
OL-3/4	10	–	120	2		

Sealing ring assortment OK-S1

This assortment box contains OK sealing rings ranging in size from M3 to G $\frac{3}{4}$.

Note on materials:
Conforms to RoHS



Ordering data						
Contents	Quantity	Min. tightening torque [Nm]	Max. tightening torque [Nm]	Weight [g]	Part No.	Type
OK-M3	50	0.15	0.8	0.04	570465	OK-S1
OK-M5	100	0.25	2.4	0.1		
OK-M7	50	0.3	6.4	0.1		
OK-1/8	100	2	5	0.12		
OK-1/4	100	10	12	0.32		
OK-3/8	40	10	15	0.44		
OK-1/2	30	10	18	0.6		
OK-3/4	10	30	40	1		

Sealing material

Technical data

FESTO

Thread sealing tape **GWB-0,1**



Ordering data				
Width [mm]	Thickness [mm]	Length [m]	Part No.	Type
10	0.1	12.5	9076	GWB-0,1