

Threaded fittings NPFC

FESTO

Threaded fittings NPFC

Technical data

FESTO

Operating and environmental conditions	
Operating pressure [bar]	–0.95 ... 50
Operating medium	Compressed air to ISO 8573-1:2010 [–:–:–]
	Gases on request
	Liquids on request
Ambient temperature [°C]	–20 ... 150
Corrosion resistance class CRC ¹⁾	1

- 1) Corrosion resistance class 1 according to Festo standard 940 070
Components subject to low corrosion stress. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.

Materials	
Threaded fitting	Nickel-plated brass
Note on materials	RoHS-compliant

Threaded fittings NPFC

Product range overview

Design	Design	Type	Connection D1			Connection D2			→ Page/ Internet
			M thread	G thread ¹⁾	R thread ¹⁾	M thread	G thread ¹⁾	R thread ¹⁾	
Straight design	Sleeve								
		NPFC-S	M5	–	–	–	–	–	6
			–	G1/8					
				G1/4					
				G3/8					
				G1/2					
				G3/4					
	Reducing sleeve								
		NPFC-R	–	G1/8	–	–	G3/8	–	6
				G1/2			G3/4		
	Extension								
		NPFC-E...	–	G1/8	–	–	G1/8	–	7
				G1/4			G1/4		
				G3/8			G3/8		
				G1/2			G1/2		
	Double nipple								
		NPFC-D	M5	–	–	M5	–	–	8
			M7				G1/8		
			–	G1/8			G1/8, G1/4, G3/8		
				G1/4			G1/4, G3/8, G1/2		
				G3/8			G3/8, G1/2		
				G1/2			G1/2		
				–			R1/8		
							R1/4		
				R3/8					
				R1/2					
				R3/4					
				R1					
Reducing nipple – internal thread/external thread									
	NPFC-R	M5	–	–	–	G1/8	–	9	
		–	G1/8			G1/4, G3/8			
			G1/4			G3/8			
			G3/8			G1/2			
Reducing nipples – external thread/internal thread									
	NPFC-R	–	G1/8	–	M5	–	–	9	
			G1/4			–			G1/8
			G3/8						G1/8, G1/4
			G1/2						G1/4, G3/8
			G3/4						G1/2

1) Sealing with thread sealing tape, GWB-0,1 Part No. 9076, is recommended for the parallel thread of the threaded fitting NPFB.

Threaded fittings NPFC

Product range overview

FESTO

Design	Version	Type	Connection D1			Connection D2			→ Page/ Internet
			M thread	G thread ¹⁾	R thread ¹⁾	M thread	G thread ¹⁾	R thread ¹⁾	
L-shape	Elbow fitting – internal thread								
		NPFC-L	M5	–	–	–	–	–	10
			–	G1/8					
				G1/4					
				G3/8					
				G1/2					
				G3/4					
				G1					
	Elbow fitting – external thread/internal thread								
		NPFC-L	M5	–	–	M5	–	–	10
			–	G1/8		–	R1/8		
				G1/4			R1/4		
				G3/8			R3/8		
				G1/2			R1/2		
				G3/4			R3/4		
			G1			R1			
Elbow fitting – external thread									
	NPFC-L	M5	–	–	–	–	–	11	
		–		R1/8					
				R1/4					
				R3/8					
				R1/2					
				R3/4					
T-shape	T-fitting – internal thread								
		NPFC-T	–	G1/8	–	–	–	–	11
				G1/4					
				G3/8					
				G1/2					
				G3/4					
				G1					
	T-fitting – internal thread/external thread/internal thread								
		NPFC-T	M5	–	–	M5	–	–	12
			–	G1/8		–	R1/8		
				G1/4			R1/4		
				G3/8			R3/8		
				G1/2			R1/2		
				G3/4			R3/4		
				G1			R1		

1) Sealing with thread sealing tape, GWB-0,1 Part No. 9076, is recommended for the parallel thread of the threaded fitting NPFC.

Threaded fittings NPFC

Product range overview

Design	Version	Type	Connection D1			Connection D2			→ Page/ Internet
			M thread	G thread ¹⁾	R thread ¹⁾	M thread	G thread ¹⁾	R thread ¹⁾	
T-shape	T-fitting – internal thread/external thread/external thread								
		NPFC-T	–	G 1/8	–	–	–	R 1/8	12
				G 1/4				R 1/4	
				G 3/8				R 3/8	
				G 1/2				R 1/2	
	T-fitting – external thread								
		NPFC-T	–	–	R 1/4	–	–	–	13
				R 3/8					
				R 1/2					
	T-fitting – external thread/external thread/internal thread								
		NPFC-T	–	–	R 1/8	–	G 1/8	–	13
				R 1/4	G 1/4				
				R 1/2	G 1/2				
	T-fitting – external thread/internal thread/internal thread								
		NPFC-T	–	–	R 1/8	–	G 1/8	–	14
				R 1/4	G 1/4				
				R 3/8	G 3/8				
				R 1/2	G 1/2				
Y-shape	Y-fitting – internal thread								
		NPFC-Y	–	G 1/4	–	–	–	–	15
				G 3/8					
				G 1/2					
	Y-fitting – external thread/internal thread/internal thread								
		NPFC-Y	–	–	R 1/8	–	G 1/8	–	15
				R 1/4	G 1/4				
				R 3/8	G 3/8				
				R 1/2	G 1/2				
	X-shape	X-fitting – internal thread							
		NPFC-X	–	G 1/4	–	–	–	–	16
				G 3/8					
				G 1/2					
X-fitting – external thread/internal thread/internal thread/internal thread									
		NPFC-X	–	G 1/4	–	–	–	R 1/4	16
				G 1/2				R 1/2	



1) Sealing with thread sealing tape, GWB-0,1 Part No. 9076, is recommended for the parallel thread of the threaded fitting NPFB.

Threaded fittings NPFC

Technical data

FESTO



Sleeve NPFC-S



Dimensions and ordering data							
Connection	D5	L1	$\approx \zeta 1$	Weight/piece [g]	Part no.	Type	PU ¹⁾
D1	Ø						
M thread							
M5	7.5	11	8	–	8030290	NPFC-S-2M5-F	10
G thread							
G $\frac{1}{8}$	13.5	15	14	–	8030291	NPFC-S-2G18-F	10
G $\frac{1}{4}$	16.5	22	17	–	8030292	NPFC-S-2G14-F	10
G $\frac{3}{8}$	21.5	24	22	–	8030293	NPFC-S-2G38-F	10
G $\frac{1}{2}$	25.5	30	26	–	8030294	NPFC-S-2G12-F	10
G $\frac{3}{4}$	31.5	32	32	–	8030295	NPFC-S-2G34-F	10

1) Packaging unit quantity

Reducing sleeve NPFC-R





Dimensions and ordering data									
Connection	D2	D4	D5	L1	T1	$\approx \zeta 1$	Weight/piece [g]	Part no.	Type
D1		Ø	Ø						PU ¹⁾
G $\frac{1}{8}$	G $\frac{3}{8}$	13	20.5	20	10.5	22	–	8030296	NPFC-R-G38-G18-F
G $\frac{1}{2}$	G $\frac{3}{4}$	25	29.8	30	14.5	30	–	8030297	NPFC-R-G34-G12-F

1) Packaging unit quantity

Threaded fittings NPFC

Technical data

Extension NPFC-E...



Dimensions and ordering data											
Connection		D3	D5	L1	L2	T1	T2	Weight/piece [g]	Part no.	Type	PU ¹⁾
D1	D2	Ø	Ø								
E1											
G ¹ / ₈	G ¹ / ₈	5.5	13	22	6	7.5	14	–	8030298	NPFC-E1-2G18-FM	10
G ¹ / ₄	G ¹ / ₄	7	16.5	28	8	10	17	–	8030299	NPFC-E1-2G14-FM	10
G ³ / ₈	G ³ / ₈	11	21.8	32	9	10	22	–	8030300	NPFC-E1-2G38-FM	10
G ¹ / ₂	G ¹ / ₂	14	25.5	35	10	11	26	–	8030301	NPFC-E1-2G12-FM	10
E2											
G ¹ / ₈	G ¹ / ₈	5	13.5	32	6	6.5	14	–	8030302	NPFC-E2-2G18-FM	10
G ¹ / ₄	G ¹ / ₄	8	17	35	8	9.5	17	–	8030303	NPFC-E2-2G14-FM	10
E3											
G ¹ / ₈	G ¹ / ₈	5.5	13	42	6	7.5	14	–	8030304	NPFC-E3-2G18-FM	10
G ¹ / ₄	G ¹ / ₄	8	17	51	8	9.5	17	–	8030305	NPFC-E3-2G14-FM	10
E4											
G ¹ / ₈	G ¹ / ₈	5	13.5	51	6	6.5	14	–	8030306	NPFC-E4-2G18-FM	10





1) Packaging unit quantity

Threaded fittings NPFC

Technical data

FESTO

Double nipple NPFC-D



Dimensions and ordering data										
Connection	D2	D3 Ø	L1	L2	L3	$\approx \zeta 1$	Weight/piece [g]	Part no.	Type	PU ¹⁾
D1										
M thread										
M5	M5	2.5	11.5	4	4	8	–	8030267	NPFC-D-2M5-M	10
M7	G $\frac{1}{8}$	4	14.5	4	6	14	–	8030268	NPFC-D-M7-G18-M	10
G thread										
G $\frac{1}{8}$	G $\frac{1}{8}$	5.5	16.5	6	6	14	–	8030269	NPFC-D-2G18-M	10
	G $\frac{1}{4}$	5.5	19	6	8	17	–	8030270	NPFC-D-G18-G14-M	10
	G $\frac{3}{8}$	5.5	20	6	9	19	–	8030271	NPFC-D-G18-G38-M	10
G $\frac{1}{4}$	G $\frac{1}{4}$	8	21	8	8	17	–	8030272	NPFC-D-2G14-M	10
	G $\frac{3}{8}$	8	22	8	9	19	–	8030273	NPFC-D-G14-G38-M	10
	G $\frac{1}{2}$	8	23.5	8	10	24	–	8030274	NPFC-D-G14-G12-M	10
G $\frac{3}{8}$	G $\frac{3}{8}$	11	23	9	9	19	–	8030275	NPFC-D-2G38-M	10
	G $\frac{1}{2}$	11	24.5	9	10	24	–	8030276	NPFC-D-G38-G12-M	10
G $\frac{1}{2}$	G $\frac{1}{2}$	15	25.5	10	10	24	–	8030277	NPFC-D-2G12-M	10
R thread										
R $\frac{1}{8}$	R $\frac{1}{8}$	5.5	19.5	7.5	7.5	12	–	8030278	NPFC-D-2R18-M	10
	R $\frac{1}{4}$	5.5	23.5	7.5	11	14	–	8030279	NPFC-D-R18-R14-M	10
	R $\frac{3}{8}$	5.5	24	7.5	11.5	17	–	8030280	NPFC-D-R18-R38-M	10
R $\frac{1}{4}$	R $\frac{1}{4}$	8	27	11	11	14	–	8030281	NPFC-D-2R14-M	10
	R $\frac{3}{8}$	8	27.5	11	11.5	17	–	8030282	NPFC-D-R14-R38-M	10
	R $\frac{1}{2}$	8	30.5	11	14	22	–	8030283	NPFC-D-R14-R12-M	10
R $\frac{3}{8}$	R $\frac{3}{8}$	11	28	11.5	11.5	17	–	8030284	NPFC-D-2R38-M	10
	R $\frac{1}{2}$	11	31	11.5	14	22	–	8030285	NPFC-D-R38-R12-M	10
R $\frac{1}{2}$	R $\frac{1}{2}$	15	33.5	14	14	22	–	8030286	NPFC-D-2R12-M	10
	R $\frac{3}{4}$	15	37.5	14	16.5	27	–	8030287	NPFC-D-R12-R34-M	10
R $\frac{3}{4}$	R $\frac{3}{4}$	19	40	16.5	16.5	27	–	8030288	NPFC-D-2R34-M	10
R1	R1	24	46.5	19	19	34	–	8030289	NPFC-D-2R1-M	10



1) Packaging unit quantity

Threaded fittings NPFC

Technical data

Reducing nipple NPFC-R

Internal thread/external thread





Dimensions and ordering data											
Connection		D3	D5	L1	L2	T1	$\varnothing C1$	Weight/piece [g]	Part no.	Type	PU ¹⁾
D1	D2	$\varnothing$	$\varnothing$								
M5	G $\frac{1}{8}$	2.5	13.5	14.5	4	7.4	14	–	8030314	NPFC-R-G18-M5-FM	10
G $\frac{1}{8}$	G $\frac{1}{4}$	5.5	17	20.5	6	9.5	17	–	8030315	NPFC-R-G14-G18-FM	10
	G $\frac{3}{8}$	5.5	21.5	21.5	6	10.5	22	–	8030316	NPFC-R-G38-G18-FM	10
G $\frac{1}{4}$	G $\frac{3}{8}$	8	21.5	23.5	8	10.5	22	–	8030317	NPFC-R-G38-G14-FM	10
G $\frac{3}{8}$	G $\frac{1}{2}$	11	25	27.5	9	13	26	–	8030318	NPFC-R-G12-G38-FM	10

1) Packaging unit quantity

Reducing nipple NPFC-R

External thread/internal thread



Dimensions and ordering data											
Connection		L1	L2	$\varnothing C1$	Weight/piece [g]	Part no.	Type	PU ¹⁾			
D1	D2										
G $\frac{1}{8}$	M5	10.5	6	14	–	8030307	NPFC-R-G18-M5-MF	10			
G $\frac{1}{4}$	G $\frac{1}{8}$	13	8	17	–	8030308	NPFC-R-G14-G18-MF	10			
G $\frac{3}{8}$	G $\frac{1}{8}$	14	9	19	–	8030309	NPFC-R-G38-G18-MF	10			
	G $\frac{1}{4}$	14	9	19	–	8030310	NPFC-R-G38-G14-MF	10			
G $\frac{1}{2}$	G $\frac{1}{4}$	15.5	10	24	–	8030311	NPFC-R-G12-G14-MF	10			
	G $\frac{3}{8}$	15.5	10	24	–	8030312	NPFC-R-G12-G38-MF	10			
G $\frac{3}{4}$	G $\frac{1}{2}$	17.5	12	30	–	8030313	NPFC-R-G34-G12-MF	10			

1) Packaging unit quantity



Threaded fittings NPFC

Technical data

FESTO

Elbow fitting NPFC-L

Internal thread





Dimensions and ordering data										
Connection	D3	D5	H1	H2	T1	$\varnothing 1$	Weight/piece	Part no.	Type	PU ¹⁾
D1	$\varnothing$	$\varnothing$					[g]			
M5	4.2	8.5	15.3	11	4	9	–	8030208	NPFC-L-2M5-F	10
G $\frac{1}{8}$	6	13	27.5	21	7.4	11	–	8030209	NPFC-L-2G18-F	10
G $\frac{1}{4}$	8	16.5	33.8	25.5	9.5	13	–	8030210	NPFC-L-2G14-F	10
G $\frac{3}{8}$	11	20.5	38.3	28	10.5	17	–	8030211	NPFC-L-2G38-F	10
G $\frac{1}{2}$	15	25.5	44.8	32	13	20	–	8030212	NPFC-L-2G12-F	10
G $\frac{3}{4}$	19	32	52.5	36.5	14.5	27	–	8030213	NPFC-L-2G34-F	10
G1	24	39	64.5	45	16.5	30	–	8030214	NPFC-L-2G1-F	10

1) Packaging unit quantity

Elbow fitting NPFC-L

External thread/internal thread



Dimensions and ordering data															
Connection		D3	D4	D5	H1	H2	L1	L2	L3	T1	≡1	Weight/piece	Part no.	Type	PU ¹⁾
D1	D2	∅	∅	∅								[g]			
M5	M5	4.2	2	7.5	17	13.5	15.3	11.5	4	4	9	–	8030215	NPFC-L-2M5-MF	10
G1⁄8	R1⁄8	6	5.5	13	26	19	24.5	18	7.5	7.4	11	–	8030216	NPFC-L-R18-G18-MF	10
G1⁄4	R1⁄4	8	8	16.5	31.5	25.5	32.3	24	11	9.5	13	–	8030217	NPFC-L-R14-G14-MF	10
G3⁄8	R3⁄8	11	11	20.5	35.5	28	37.3	27	11.5	10.5	17	–	8030218	NPFC-L-R38-G38-MF	10
G1⁄2	R1⁄2	15	15	25.5	41.7	32	42.3	29.5	14	13	20	–	8030219	NPFC-L-R12-G12-MF	10
G3⁄4	R3⁄4	19	19	32	48.5	36.5	48	32	14.7	14.5	27	–	8030220	NPFC-L-R34-G34-MF	10
G1	R1	24	24	39	59.5	45	58.5	39	15.7	16.5	30	–	8030221	NPFC-L-R1-G1-MF	10



1) Packaging unit quantity

Threaded fittings NPFC

Technical data

Elbow fitting NPFC-L

External thread





Dimensions and ordering data									
Connection	D3	H1	H2	H3	$\varnothing 1$	Weight/piece	Part no.	Type	PU ¹⁾
D1	$\varnothing$					[g]			
M5	2	15.5	11.5	4	9	–	8030222	NPFC-L-2M5-M	10
R $\frac{1}{8}$	5.5	23	18	7.5	11	–	8030223	NPFC-L-2R18-M	10
R $\frac{1}{4}$	8	31	24	11	13	–	8030224	NPFC-L-2R14-M	10
R $\frac{3}{8}$	11	34.5	27	11.5	17	–	8030225	NPFC-L-2R38-M	10
R $\frac{1}{2}$	15	39.2	29.5	14	20	–	8030226	NPFC-L-2R12-M	10
R $\frac{3}{4}$	19	44	32	13	27	–	8030227	NPFC-L-2R34-M	10

1) Packaging unit quantity

T-fitting NPFC-T

Internal thread



Dimensions and ordering data											
Connection D1	D3 Ø	D5 Ø	H1	H2	L1	T1	≲G1	Weight/piece [g]	Part no.	Type	PU ¹⁾
G1⁄8	6	13	26	19.5	39	7.4	12	–	8030235	NPFC-T-3G18-F	10
G1⁄4	8	16.5	32.8	24.5	49	9.5	13	–	8030236	NPFC-T-3G14-F	10
G3⁄8	11	20.5	37.3	27	54	10.5	16	–	8030237	NPFC-T-3G38-F	10
G1⁄2	15	25.5	44.8	32	64	13	20	–	8030238	NPFC-T-3G12-F	10
G3⁄4	19	32	52.5	36.5	73	14.5	27	–	8030239	NPFC-T-3G34-F	10
G1	24	39	64.5	45	90	16.5	30	–	8030240	NPFC-T-3G1-F	10

1) Packaging unit quantity



Threaded fittings NPFC

Technical data

FESTO

T-fitting NPFC-T

Internal thread/external
thread/internal thread





Dimensions and ordering data															
Connection		D3	D4	D5	H1	H2	L1	L2	L3	T1	1/16	Weight/piece [g]	Part no.	Type	PU ¹⁾
D1	D2	Ø	Ø	Ø											
M5	M5	4.2	2	8.5	15.3	11.1	22.5	12	4	5	9	–	8030245	NPFC-T-3M5-FMF	10
G1/8	R1/8	6	6	13	26	19.5	37	17.5	7.5	7.4	12	–	8030246	NPFC-T-2G18-R18-FMF	10
G1/4	R1/4	8	8	16.5	32.8	24.6	47.5	23	11	9.5	13	–	8030247	NPFC-T-2G14-R14-FMF	10
G3/8	R3/8	11	11	20.5	37.3	27.1	52.5	25.5	11.5	10.5	16	–	8030248	NPFC-T-2G38-R38-FMF	10
G1/2	R1/2	15	15	25.5	44.8	32.1	61.5	29.5	14	13	20	–	8030249	NPFC-T-2G12-R12-FMF	10
G3/4	R3/4	19	19	32	52.5	36.5	68.5	32	14	14.5	27	–	8030250	NPFC-T-2G34-R34-FMF	10
G1	R1	24	24	39	64.5	45	84	39	16	16.5	30	–	8030251	NPFC-T-2G1-R1-FMF	10

1) Packaging unit quantity

T-fitting NPFC-T

Internal thread/external
thread/external thread



Dimensions and ordering data														
Connection		D3	D4	D5	H1	H2	L1	L2	T1	≡G1	Weight/piece	Part no.	Type	PU ¹⁾
D1	D2	Ø	Ø	Ø							[g]			
G1/8	R1/8	6	5.5	13	24.5	19.5	35	7.5	7.4	12	–	8030255	NPFC-T-G18-2R18-FMM	10
G1/4	R1/4	8	8	16.5	31	24.5	46	11	9.5	13	–	8030256	NPFC-T-G14-2R14-FMM	10
G3/8	R3/8	11	11	20.5	35.5	27	51.5	11.5	10.5	16	–	8030257	NPFC-T-G38-2R38-FMM	10
G1/2	R1/2	15	15	25.5	42.8	32	59	14	13	20	–	8030258	NPFC-T-G12-2R12-FMM	10



1) Packaging unit quantity

Threaded fittings NPFC

Technical data

T-fitting NPFC-T

External thread





Dimensions and ordering data										
Connection D1	D3 Ø	H1	H2	L1	L2	$\approx \zeta 1$	Weight/piece [g]	Part no.	Type	PU ¹⁾
R $\frac{1}{4}$	8	29.8	11	46	23	13	–	8030252	NPFC-T-3R14-M	10
R $\frac{3}{8}$	11	34.1	11.5	51.5	25.5	16	–	8030253	NPFC-T-3R38-M	10
R $\frac{1}{2}$	15	40.3	14	59	29.5	20	–	8030254	NPFC-T-3R12-M	10

1) Packaging unit quantity

T-fitting NPFC-T

External thread/external
thread/internal thread



Dimensions and ordering data														
Connection		D3	D4	D5	H1	H2	L1	L2	T1	≈ζ1	Weight/piece [g]	Part no.	Type	PU ¹⁾
D1	D2	Ø	Ø	Ø										
R1⁄8	G1⁄8	5.5	6	13	24	7.5	37	19.5	7.4	12	–	8030259	NPFC-T-2R18-G18-MMF	10
R1⁄4	G1⁄4	8	8	16.5	31.3	11	47.5	24.5	9.5	13	–	8030260	NPFC-T-2R14-G14-MMF	10
R1⁄2	G1⁄2	15	15	25.5	42.3	14	61.5	32	13	20	–	8030261	NPFC-T-2R12-G12-MMF	10

1) Packaging unit quantity



Threaded fittings NPFC

Technical data

FESTO

T-fitting NPFC-T

External thread/internal
thread/internal thread



Dimensions and ordering data

Connection		D3	D4	D5	H1	H2	H3	L1	L2	T1	≈G1	Weight/piece [g]	Part no.	Type	PU ¹⁾
D1	D2	Ø	Ø	Ø											
R ¹ / ₈	G ¹ / ₈	5.5	6	13	24	17.5	8	39	19.5	7.4	12	–	8030241	NPFC-T-R18-2G18-MFF	10
R ¹ / ₄	G ¹ / ₄	8	8	16.5	31.3	23	11	49	24.5	9.5	13	–	8030242	NPFC-T-R14-2G14-MFF	10
R ³ / ₈	G ³ / ₈	11	11	20.5	35.8	25.5	11.5	54	27	10.5	16	–	8030243	NPFC-T-R38-2G38-MFF	10
R ¹ / ₂	G ¹ / ₂	15	15	25.5	41.8	29	14	64	32	13	20	–	8030244	NPFC-T-R12-2G12-MFF	10



1) Packaging unit quantity

Threaded fittings NPFC

Technical data

Y-fitting NPFC-Y

Internal thread





Dimensions and ordering data											
Connection D1	D3 Ø	D5 Ø	H1	L1	T1	W1	≈C1	Weight/piece [g]	Part no.	Type	PU ¹⁾
G1/4	11.5	17	36.8	36.8	9.5	90°	17	–	8030228	NPFC-Y-3G14-F	10
G3/8	15	22	46	46	10.5	90°	22	–	8030229	NPFC-Y-3G38-F	10
G1/2	18.5	26	58	57.3	13	90°	26	–	8030230	NPFC-Y-3G12-F	10

1) Packaging unit quantity

Y-fitting NPFC-Y

External thread/internal
thread/internal thread



Dimensions and ordering data														
Connection		D3	D4	D5	H1	H2	L1	T1	W1	≈C1	Weight/piece	Part no.	Type	PU ¹⁾
D1	D2	Ø	Ø	Ø							[g]			
R1⁄8	G1⁄8	5.5	8.5	14	32.8	9	32.5	8.5	90°	14	–	8030231	NPFC-Y-R18-2G18-MFF	10
R1⁄4	G1⁄4	8	11.5	17	37	11	37	9.5	90°	17	–	8030232	NPFC-Y-R14-2G14-MFF	10
R3⁄8	G3⁄8	11	15	22	46	12.5	46	10.5	90°	22	–	8030233	NPFC-Y-R38-2G38-MFF	10
R1⁄2	G1⁄2	15	18.5	26	58	16.5	57.3	13	90°	26	–	8030234	NPFC-Y-R12-2G12-MFF	10

1) Packaging unit quantity



Threaded fittings NPFC

Technical data

FESTO

X-fitting NPFC-X

Internal thread





Dimensions and ordering data										
Connection	D3	D5	H1	T1	≈C1	Weight/piece	Part no.	Type	PU ¹⁾	
D1	Ø	Ø				[g]				
G ¹ / ₄	8	16.5	50	9.5	13	–	8030262	NPFC-X-4G14-F	10	
G ³ / ₈	11	20.5	56	10.5	17	–	8030263	NPFC-X-4G38-F	10	
G ¹ / ₂	15	25.5	64	13	20	–	8030264	NPFC-X-4G12-F	10	

1) Packaging unit quantity

X-fitting NPFC-X

External thread/internal
thread/internal thread/internal thread



Dimensions and ordering data														
Connection		D3	D4	D5	H1	L1	L2	L3	T1	≧C1	Weight/piece	Part no.	Type	PU ¹⁾
D1	D2	Ø	Ø	Ø							[g]			
G¼	R¼	8	8	16.5	50	48.5	23.5	11	9.5	13	–	8030265	NPFC-X-R14-3G14-MFFF	10
G½	R½	15	15	25.5	64	61	29	14	13	20	–	8030266	NPFC-X-R12-3G12-MFFF	10

1) Packaging unit quantity

Product Range and Company Overview

A Complete Suite and Company Overview

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support
and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors,
controllers & drivers



Pneumatics
Pneumatic linear and rotary actuators,
valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors
and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 16,000 employees in 60 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.




© Copyright 2013, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmental friendly printing plant.

Festo North America



**1 Festo Canada
Headquarters**
Festo Inc.
5300 Explorer Drive
Mississauga, ON
L4W 5G4

2 Montréal
5600, Trans-Canada
Pointe-Claire, QC
H9R 1B6

3 Québec City
2930, rue Watt#117
Québec, QC
G1X 4G3



**4 Festo United States
Headquarters**
Festo Corporation
395 Moreland Road
Hauppauge, NY
11788

5 Appleton
North 922 Tower View Drive, Suite N
Greenville, WI
54942

7 Detroit
1441 West Long Lake Road
Troy, MI
48098

6 Chicago
85 W Algonquin - Suite 340
Arlington Heights, IL
60005

8 Silicon Valley
4935 Southfront Road, Suite F
Livermore, CA
94550

Festo Regional Contact Center

Canadian Customers

Commercial Support:
Tel: 1 877 GO FESTO (1 877 463 3786)
Fax: 1 877 FX FESTO (1 877 393 3786)
Email: festo.canada@ca.festo.com

Technical Support:
Tel: 1 866 GO FESTO (1 866 463 3786)
Fax: 1 877 FX FESTO (1 877 393 3786)
Email: technical.support@ca.festo.com

USA Customers

Commercial Support:
Tel: 1 800 99 FESTO (1 800 993 3786)
Fax: 1 800 96 FESTO (1 800 963 3786)
Email: customer.service@us.festo.com

Technical Support:
Tel: 1 866 GO FESTO (1 866 463 3786)
Fax: 1 800 96 FESTO (1 800 963 3786)
Email: product.support@us.festo.com

Subject to change

Internet: www.festo.com/us