

## Feed separators HPV

**FESTO**



# Feed separators HPV


Key features at a glance

FESTO

## Separation of workpieces in the supply process


### Previously

- Required at least 2 drives, 2 valves and 4 proximity sensors
- Extensive programming required




### Today

- One unit (1 drive, 1 valve and 2 proximity sensors)
- More cost-effective
- Reliable
- No programming required



## High functionality

- 1 Corrosion-resistant thanks to stainless steel plungers
- 2 Optimum, accurate combination options with centring sleeves
- 3 Supply ports optionally at top or rear
- 4 Supports proximity sensors that can be integrated in the housing (SME/SMT-8)




 Note


An integrated mechanical locking mechanism between the two plungers ensures that one piston cannot retract until the other has advanced. Both plungers are briefly extended upon changeover and the part to be separated is surrounded.

## Function principle


Plunger A is retracted. The locking mechanism locks plunger B.




Plunger A advances.




Plunger B cannot retract from the locking mechanism until plunger A is fully advanced.



Plunger B advances.



Plunger A cannot retract from the locking mechanism until plunger B is fully advanced.




# Feed separators HPV

Peripherals overview and type codes

FESTO

## Peripherals overview



Accessories		
	Brief description	→ Page/Internet
1	Centring sleeve, connecting sleeve	For centring when mounting
2	Proximity sensor	For position sensing, sensor is integrated in sensor slot
3	QS push-in fitting	For connecting compressed air tubing with standard external diameter

## Type codes

		HPV	–	14	–	20	–	A
<b>Type</b>								
Double-acting								
HPV	Feed separator							
<b>Size [mm]</b>								
<b>Stroke [mm]</b>								
<b>Position sensing</b>								
A	Via proximity sensor							

# Feed separators HPV


Technical data

FESTO

Function



- Ø - Size  
10 ... 22
- I - Stroke length  
20 ... 60 mm



General technical data			
Size	10	14	22
Pneumatic connection	M5/M3	M5/M5	
Mode of operation	Double-acting		
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:4:4]		
Note on operating/pilot medium	Operation with lubricated medium possible (in which case lubricated operation will always be required)		
Design	Twin piston		
	Piston rod		
	Locking mechanism		
	Non-rotating		
Protection against torsion/guide	Square plungers		
Max. interchangeability [mm]	0.3		
Cushioning	None		
Position sensing	Via proximity sensor		
Type of mounting	Via through-holes		
	Via female thread		
Mounting position	Any		

Operating and environmental conditions			
Operating pressure [bar]	3 ... 8		
Ambient temperature [°C]	+5 ... +60		
Protection class	IP40		
Corrosion resistance class CRC <sup>1)</sup>	2		

- 1) Corrosion resistance class 2 to Festo standard 940 070  
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Forces [N]			
Size	10	14	22
Theoretical force at 6 bar Advancing	45	90	225
Theoretical force at 6 bar Retracting	35	75	180

Weights [g]					
Size	10	14		22	
Stroke	10	20	40	30	60
Product weight	135	290	460	950	1,500


# Feed separators HPV

Technical data

FESTO

## Materials

Sectional view



### Feed separator

1	Body	Wrought aluminium alloy (with CompCoat)
2	End cover	High-alloy steel
3	Plunger	High-alloy steel
4	Locking mechanism	Case-hardened steel
5	Piston rod	High-alloy steel
-	Seals	Nitrile rubber
Note on materials		Copper, PTFE and silicone-free
		Conforms to RoHS



Note

The plunger slideways in the housing are determined by the appropriate fit selected and cannot be adjusted. The

necessary basic lubrication is performed during assembly. We recommend that the feed separator

be re-lubricated after 2 million cycles.


## Cycle times [ms] without add-on plunger separators at 6 bar (unrestricted)

Half the cycle time:

Number 1 ... 3

Cycle time:

Number 1 ... 5



Size	10	14		22	
Stroke	10	20	40	30	60
Half the cycle time	26.5	111.5	234.2	152.4	398.1
Cycle time	52.5	223	468.4	304.8	796.1

## Max. permissible weight [g] of add-on plunger separators for unrestricted operation

Size	10	14	22
Add-on plunger separators <sup>1)</sup>	56	150	395

1) If the max. permissible weights of the add-on plunger separators are exceeded, the retracting and advancing times must be adapted in accordance with the table below using one-way flow control valves. Failure to do so may result in components of the feed separator being damaged.

## Retracting and advancing times [s] with add-on plunger separators as a function of the load [g] of the fingers


Size		10	14		22	
Stroke		10	20	40	30	60
Applied load	100 g	0.03	–	–	–	–
	200 g	0.04	0.03	0.05	–	–
	300 g	0.05	0.04	0.08	–	–
	400 g	0.06	0.05	0.11	0.24	0.48
	500 g	–	0.07	0.13	0.3	0.6
	600 g	–	–	–	0.36	0.72
	700 g	–	–	–	0.42	0.84
	800 g	–	–	–	0.48	0.96

# Feed separators HPV

Technical data


**FESTO**

## Permissible characteristic static load values at the plungers



Size		10	14	22
Force F	[N]	75	100	180
Torque Mx	[Nm]	3	5	9
Torque My	[Nm]	3	5	9
Torque Mr	[Nm]	3	5	9


## Plunger backlash



Size	10	14		22		
Stroke	10	20	40	30	60	
$S_x$	[mm]	0.05	0.05	0.05	0.05	0.05
$S_z$	[mm]	0.03	0.03	0.03	0.03	0.03
$\alpha_x$	[°]	0.12	0.12	0.07	0.06	0.04
$\alpha_y$	[°]	0.2	0.2	0.12	0.11	0.07
$\alpha_z$	[°]	0.262	0.175	0.175	0.12	0.12

## Minimum clearances

To prevent malfunctioning of the proximity sensors, the feed separators must comply with the minimum clearances specified in the table.




Size		10	14	22
For SME-8-...	[mm]	60	59	73
For SMT-8-...-B	[mm]	60	54	69

# Feed separators HPV

Technical data



## Projection of proximity sensors




Size		10	14	22
For SME-8-...	[mm]	14		
For SMT-8-...	[mm]	22		

## Mounting options


Only the mounting surface on the underside (opposite the supply ports) may be used.

### From above via through-holes




Size	10	14	22
Screw	M3	M4	M6
Permitted tightening torque	1.2	2.9	9.9

### From below via female threads



Size	10	14	22
Screw	M4	M5	M8
Permitted tightening torque	2.9	5.9	24

## Surface finish and positional accuracy of bearing surface




# Feed separators HPV

Technical data

FESTO

## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)



Type	B1	B2	B3	B4	B5	D1	D2	D3	D4	D5	D6	EE	EE1	H1
			±0.02	±0.05		∅		H8/h7 ∅	H13 ∅	H13 ∅	H13 ∅			
HPV-10-10-A	47	6	7	20	7	5.3	M4	7	6	–	3.2	M5	M3	78
HPV-14-20-A	60	12	10	30	10	5.3	M5	7	7.4	–	4.2	M5	M5	119
HPV-14-40-A	60	12	10	30	10	5.3	M5	7	7.4	–	4.2	M5	M5	189
HPV-22-30-A	78	13	14	38	11	8.4	M8	12	10.4	6.2	6.2	M5	M5	175
HPV-22-60-A	78	13	14	38	11	8.4	M8	12	10.4	6.2	6.2	M5	M5	280

Type	H2	H3	H4	H5 <sup>1)</sup>	H6	H7	H8	H9	L1	L2	T1	T2	T3	T5
			±0.1		±0.2	±0.1	±0.5				+0.1		min.	–0.3
HPV-10-10-A	53	24.5	16	30	7	4	10	7.5	18	9	1.6	3.1	4	1.4
HPV-14-20-A	79	36	20	30	10	5	20	36	19	7	1.6	4.6	5	1.4
HPV-14-40-A	129	56	20	60	10	5	40	56	19	7	1.6	4.6	5	1.4
HPV-22-30-A	115	48	40	60	14	8	30	48	32	16	2.6	6.1	5	2.4
HPV-22-60-A	190	78	40	120	14	8	60	78	32	16	2.6	6.1	5	2.4

1) Tolerance for centring hole ±0.02  
Tolerance for threaded and through-hole ±0.1

## Ordering data


Size	Stroke [mm]	Part No.	Type
10	10	550908	HPV-10-10-A
14	20	529351	HPV-14-20-A
	40	529352	HPV-14-40-A
22	30	529353	HPV-22-30-A
	60	529354	HPV-22-60-A




# Feed separators HPV


Accessories



**FESTO**


Ordering data			Technical data → Internet: zbh		
	For size	Part No.	Type	PU <sup>1)</sup>	
Centring sleeve ZBH					
	10, 14	<b>186717</b>	<b>ZBH-7</b>	10	
	22	<b>189653</b>	<b>ZBH-12</b>	10	


1) Packaging unit quantity

Ordering data – Proximity sensors for T-slot, magneto-resistive					Technical data → Internet: smt	
	Type of mounting	Switch output	Electrical connection	Cable length [m]	Part No.	Type
N/O contact						
	Insertable in the slot from above, flush with cylinder profile, short design	PNP	Cable, 3-wire	2.5	<b>574335</b>	<b>SMT-8M-A-PS-24V-E-2,5-OE</b>
			Plug M8x1, 3-pin	0.3	<b>574334</b>	<b>SMT-8M-A-PS-24V-E-0,3-M8D</b>

Ordering data – Proximity sensors for T-slot, magnetic reed					Technical data → Internet: sme	
	Type of mounting	Switch output	Electrical connection	Cable length [m]	Part No.	Type
N/O contact						
	Insertable in the slot lengthwise, flush with the cylinder profile	Via contact	Cable, 3-wire	2.5	<b>150855</b>	<b>SME-8-K-LED-24</b>
			Plug M8x1, 3-pin	0.3	<b>150857</b>	<b>SME-8-S-LED-24</b>

Ordering data – Connecting cables				Technical data → Internet: nebu	
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part No.	Type
	Straight socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	<b>541333</b>	<b>NEBU-M8G3-K-2.5-LE3</b>
			5	<b>541334</b>	<b>NEBU-M8G3-K-5-LE3</b>
	Straight socket, M12x1, 5-pin	Cable, open end, 3-wire	2.5	<b>541363</b>	<b>NEBU-M12G5-K-2.5-LE3</b>
			5	<b>541364</b>	<b>NEBU-M12G5-K-5-LE3</b>
	Angled socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	<b>541338</b>	<b>NEBU-M8W3-K-2.5-LE3</b>
			5	<b>541341</b>	<b>NEBU-M8W3-K-5-LE3</b>
	Angled socket, M12x1, 5-pin	Cable, open end, 3-wire	2.5	<b>541367</b>	<b>NEBU-M12W5-K-2.5-LE3</b>
			5	<b>541370</b>	<b>NEBU-M12W5-K-5-LE3</b>

Ordering data – Slot covers			
	Mounting	Length [m]	Part No. Type
	Inserted from above	2 x 0.5	<b>151680</b> <b>ABP-5-S</b>

Ordering data – One-way flow control valves				Technical data → Internet: grla-m5-qs	
	Connection		Material	Part No.	Type
	Thread	For tubing outer Ø			
	M5	3	Metal design	<b>193137</b>	<b>GRLA-M5-QS-3-D</b>
		4		<b>193138</b>	<b>GRLA-M5-QS-4-D</b>
		6		<b>193139</b>	<b>GRLA-M5-QS-6-D</b>