



Solenoid coils MSF/MSN1/MD-2/MH-2

FESTO

Product range overview

Version	Type	For valve series										→ Page/ Internet
		MFH	MOFH	JMFH	JMFDH	NVF3	MUFH	MN1H	JMN1H	JMN1DH	VZWM-L	
F solenoid coil												
	MSF	■	■	■	■	■	■	-	-	-	-	4
F solenoid coil for explosive atmospheres (with ATEX certification)												
	MSF...EX	■	■	■	■	■	■	-	-	-	-	6
N1 solenoid coil												
	MSN1 ¹⁾	-	-	-	-	-	-	■	■	■	-	8
H solenoid coil												
	MH-2	-	-	-	-	-	-	-	-	-	■	10
D solenoid coil												
	MD-2	-	-	-	-	-	-	-	-	-	■	10

1) Free of copper, PTFE and silicone

Note

ATEX certification is only effective in combination with other ATEX-certified components.

→ www.festo.com/en/ex

Solenoid coils MSF/MSN1/MD-2/MH-2

Selection aid

FESTO

Solenoid valves and corresponding solenoid coils														
Valve series	Valve type	Solenoid coil												
		D	E	EB	F	H	N1	N2	V	Y	Z	ZB	ZC	
ISO 15407-1	MN2H, JMN2H, JMN2DH	–	–	–	–	–	–	–	■	–	–	–		
ISO 5599-1	MN1H, JMN1H, JMN1DH	–	–	–	–	–	–	■	–	–	–	–	–	–
	MFH, JMFH, JMFDH	–	–	–	■	–	–	–	–	–	–	–	–	–
	MDH, JMDH	■	–	–	–	–	–	–	–	–	–	–	–	–
	MEBH, JMEBH, JMEBDH	–	–	■	–	–	–	–	–	–	–	–	–	–
Namur	NVF3	–	–	–	■	–	–	–	–	–	–	–	–	–
	MN1H	–	–	–	–	–	■	–	–	–	–	–	–	–
Compact Performance	CPE10-M1BH, CPE14-M1BH	–	–	–	–	–	–	–	–	–	–	–	–	■
	CPE18, CPE24	–	–	■	–	–	–	–	–	–	–	–	–	–
Tiger 2000	MFH, JMFH	–	–	–	■	–	–	–	–	–	–	–	–	–
	MVH, JMVH	–	–	–	–	–	–	–	■	–	–	–	–	–
Tiger Classic	MFH, MOFH, JMFH, JMFDH	–	–	–	■	–	–	–	–	–	–	–	–	–
Midi Pneumatic	MEBH, MOEBH, JMEBH	–	–	■	–	–	–	–	–	–	–	–	–	–
	MEH, MOEH, JMEH	–	■	–	–	–	–	–	–	–	–	–	–	–
Directly actuated solenoid valves	MZBH, MOZBH	–	–	–	–	–	–	–	–	–	–	–	■	–
	MEBH, MOEBH	–	–	■	–	–	–	–	–	–	–	–	–	–
	MVH, MOVH	–	–	–	–	–	–	–	■	–	–	–	–	–
	MDH, MODH	■	–	–	–	–	–	–	–	–	–	–	–	–
Miniature valves	MH1	–	–	–	–	–	–	–	–	–	–	–	–	■
Fast-switching valves	MH2, MH3	–	–	–	–	–	–	–	–	–	–	–	–	■
	MH4	–	–	■	–	–	–	–	–	–	–	–	–	–
Smart Cubic	CPASC1	–	–	–	–	–	–	–	–	–	–	–	–	■
VB series	VUVB	–	–	■	–	–	–	–	–	–	–	–	–	–
Micro/Mini Pneumatic	MZH, MOZH, JMZH	–	–	–	–	–	–	–	–	–	–	■	–	–
	MYH, MOYH, JMYH	–	–	–	–	–	–	–	–	■	–	–	–	–
M5 Compact system	MUFH	–	–	–	■	–	–	–	–	–	–	–	–	–
Process directional control valves	VZWM-L	■	–	–	–	■	–	–	–	–	–	–	–	–

Solenoid coils MSF/MSN1

Type codes

FESTO

Solenoid coils

Type	MSFG	24DC	OD
MSFG	F solenoid coil, for DC voltage		
MSFW	F solenoid coil, for AC voltage		
MSN1G	N1 solenoid coil, for DC voltage		
MSN1W	N1 solenoid coil, for AC voltage		
Operating voltage			
12DC	12 V DC		
24DC	24 V DC		
24AC/12DC	12 V DC/24 V AC		
24DC/42AC	24 V DC/42 V AC		
42DC	42 V DC		
24AC	24 V AC		
48AC	48 V AC		
110AC	110 V AC		
230AC	230 V AC		
240AC	240 V AC		
Scope of delivery			
OD	Without plug socket		

Solenoid coils, explosion-proof

Type	MSFG	24DC	K5	M	EX
MSFG	F solenoid coil, for DC voltage				
MSFW	F solenoid coil, for AC voltage				
Operating voltage					
24	24 V DC				
24DC	24 V DC				
24AC	24 V AC				
24-50/60	24 V AC, 50/60 Hz				
110AC	110 V AC				
110-50/60	110 V AC, 50/60 Hz				
230AC	230 V AC				
230-50/60	230 V AC, 50/60 Hz				
Cable length					
	1 m				
K5	5 m				
KX	On request				
ATEX specification					
	II 3 GD EEx nA II T1 30°C X				
M	II 2 GD EExm II T5				
Explosion protection					
EX	Explosion-proof to EN 50 028				

Solenoid coils MSF

FESTO

Technical data


Voltage

12 ... 42 V DC
24 ... 240 V AC

Temperature range

–5 ... +40 °C

- In compliance with VDE regulation 0580, insulation class F
- Can be replaced without interrupting the pneumatic circuit
- Low power consumption and temperature rise



General technical data		
Type of mounting	Via knurled nut	
Mounting position	Any (can be rotated 360° on the armature tube)	
Max. tightening torque of plug socket	[Nm]	0.4
Product weight	[g]	55

Materials	
Solenoid coil	Duroplastic, copper, steel
Note on materials	RoHS-compliant

Electrical data								
Type	MSFG-12	MSFG-42	MSFG-24/42	MSFW-24	MSFW-48	MSFW-110	MSFW-230	MSFW-240
Electrical connection	3-pin							
	Plug vanes with connection pattern to Festo standard for MSSD-F							
Min. starting time	[ms]	10						
Permissible voltage fluctuations	[%]	±10						
Permissible frequency fluctuations	[%]	–		±5				
Duty cycle	[%]	100						
Power factor cosφ		–		0.7				
Switching position display		No						
Protection class to EN 60529		IP65 with plug socket						

Coil characteristics								
Type	MSFG-12	MSFG-42	MSFG-24/42	MSFW-24	MSFW-48	MSFW-110	MSFW-230	MSFW-240
Output	12 V DC, 4.1 W	42 V DC, 5.5 W	24 V DC, 4.5 W	–	–	–	–	–
Switching power	50/60 Hz	–	42 V AC, 9 VA	24 V AC, 9 VA	48 V AC, 9 VA	110 V AC, 9 VA	230 V AC, 9 VA	240 V AC, 9 VA
Holding capacity	50/60 Hz	–	42 V AC, 7 VA	24 V AC, 7 VA	48 V AC, 7 VA	110 V AC, 7 VA	230 V AC, 7 VA	240 V AC, 7 VA

Operating and environmental conditions								
Type	MSFG-12	MSFG-42	MSFG-24/42	MSFW-24	MSFW-48	MSFW-110	MSFW-230	MSFW-240
Ambient temperature	[°C]	–5 ... +40						
CE mark (see declaration of conformity)		–					To EU Low Voltage Directive	


Solenoid coils MSF

Technical data

FESTO

Dimensions

Download CAD Data → www.festo.com/us/cad





- 1 Retaining nut
- 2 Solenoid coil
(can be rotated 360°
on the armature tube)
- 3 Plug vanes for plug sockets
MSSD-F, KMF

Note

Can only be operated on aluminium valves with valve body dimensions $\geq 26 \times 16 \times 14$ mm

Ordering data

Description		Part No.	Type
Solenoid coil			
	Without plug socket, with disc-spring washer and knurled nut	12 V DC	34410 MSFG-12DC-OD
		24 V DC, 42 V AC	34411 MSFG-24/42-50/60-OD
		42 V DC	34413 MSFG-42DC-OD
		24 V AC	34415 MSFW-24AC-OD
		48 V AC	34418 MSFW-48AC-OD
		110 V AC	34420 MSFW-110AC-OD
		230 V AC	34422 MSFW-230AC-OD
		240 V AC	34424 MSFW-240AC-OD
Plug socket			
	Cable connection via clamping screws	34431	MSSD-F
	Cable connection via insulation displacement technology	192746	MSSD-F-S-M16
Plug socket with cable			
	Operating voltage 24 V DC, switching status display via LED	Cable length 2.5 m	30935 KMF-1-24DC-2,5-LED
		Cable length 5 m	30937 KMF-1-24DC-5-LED
		Cable length 10 m	193458 KMF-1-24DC-10-LED
	Operating voltage up to 240 V	Cable length 2.5 m	30936 KMF-1-230AC-2,5
		Cable length 5 m	30938 KMF-1-230AC-5
Illuminating seal			
	Operating voltage 12 ... 24 V DC	19143	MF-LD-12-24DC
	Operating voltage 230 V DC/V AC	19144	MF-LD-230AC
Inscription label			
	Scope of delivery: 35 pieces in frame	33362	KMC/F/V-BZ-35X

Solenoid coils MSF...-EX

FESTO

Technical data



Voltage

24 V DC
24 ... 240 V AC

Temperature range

–5 ... +40 °C

- In compliance with ATEX directive
- In compliance with VDE regulation 0580, insulation class F
- Cable or plug connection
- Can be replaced without interrupting the pneumatic circuit
- Manifold mounting permissible (minimum clearance from coil to coil 5 mm)



General technical data		
Min. starting time	[ms]	10
Type of mounting	Via knurled nut	
Mounting position	Any (can be rotated 360° on the armature tube)	
Product weight	[g]	170
		55

Materials		
Type	MSF...-M	MSF
Solenoid coil	Steel, copper, aluminium, epoxy resin	Steel, copper, duroplastic
Winding	Copper	Copper
Note on materials	RoHS-compliant	RoHS-compliant

Electrical data				
Type	MSFG-...-M-EX	MSFW-...-M-EX	MSFG-24-EX	MSFW-...-50/60-EX
Electrical connection	–		3-pin	
	Cable		Plug vanes with connection pattern to Festo standard for MSSD-F	
Conductor nominal cross section	[mm ²]	0.75	–	
Min. starting time	[ms]	10		
Permissible voltage fluctuations	[%]	±10		
Permissible frequency fluctuations	[%]	–	±5	–
Duty cycle	[%]	100		
Power factor cosφ		–	0.7	
Switching position display	No			
Protection class to EN 60529	IP65 with plug socket			

Coil characteristics								
Type	MSFG-24DC-...-M-EX	MSFW-24 AC-...-M-EX	MSFW-110 AC-...-M-EX	MSFW-230 AC-...-M-EX	MSFG-24-EX	MSFW-24-50/60-EX	MSFW-110-50/60-EX	MSFW-230-50/60-EX
Output	24 V DC, 4.3 W	24 V AC, 4.4 VA	110 V AC, 4.4 VA	230 V AC, 4.2 VA	24 V DC, 4.5 W	–	–	–
Switching power	50/60 Hz	–	–	–	–	24 V AC, 9 VA	110 V AC, 9 VA	230 V AC, 9 VA
Holding capacity	50/60 Hz	–	–	–	–	48 V AC, 7 VA	110 V AC, 7 VA	230 V AC, 7 VA

Solenoid coils MSF...-EX

Technical data


FESTO

Operating and environmental conditions				
Type	MSFG-...-M-EX	MSFW-...-M-EX	MSFG-24-EX	MSFW-...-50/60-EX
Ambient temperature [°C]	-20 ... +40		-5 ... +40	
ATEX temperature rating [°C]	-20 ≤ Ta ≤ +40 IP65		-5 ≤ Ta ≤ +40	
ATEX specification	II 2 GD EEx m II T5 T95°C		II 3 GD EEx nA II T130°C X	
CE mark	To EU Explosion Protection Directive (ATEX)			
(see declaration of conformity)	–	To EU Low Voltage Directive	–	To EU Low Voltage Directive

Dimensions Download CAD Data → www.festo.com/us/cad

MSF...-M	
Technical drawing of the MSF...-M solenoid coil. Dimensions shown: 35, 30, 13.3, 57, 33.6, 50, 11, 22, 5. Callouts: 1 (Solenoid coil), 2 (Protective earth conductor connection), 3 (Heat-resistant rubber tubing, Ø 6.1 ... 7.9 mm), 4 (Mounting nut (tightening torque 100 ... 150 Ncm)), 5 (Cable length).	Note Can only be operated on aluminium valves with valve body dimensions ≥ 25 x 25 x 17 mm

MSF	
Technical drawing of the MSF solenoid coil. Dimensions shown: 29.5, 12.5, 22, 33.8, 29. Callouts: 1 (Retaining nut), 2 (Solenoid coil (can be rotated 360° on the armature tube)), 3 (Plug vanes for plug sockets MSSD-F, KMF).	Note Can only be operated on aluminium valves with valve body dimensions ≥ 26 x 16 x 14 mm

Ordering data					
Description				Part No.	Type
Solenoid coil					
	ATEX specification: II 2 GD EEx m II T5, with connecting cable, explosion-proof, moulded-in cable, with disc-spring washer and knurled nut	24 V DC	Cable length 1 m	535619	MSFG-24DC-M-EX
			Cable length 5 m	535621	MSFG-24DC-K5-M-EX
			Cable length on request	538215	MSFG-24DC-KX-M-EX
		24 V AC	Cable length 1 m	535623	MSFW-24AC-M-EX
			Cable length on request	538216	MSFW-24AC-KX-M-EX
		110 V AC	Cable length 1 m	535622	MSFW-110AC-M-EX
			Cable length 5 m	535624	MSFW-110AC-K5-M-EX
			Cable length on request	538218	MSFW-110AC-KX-M-EX
		230 V AC	Cable length 1 m	535620	MSFW-230AC-M-EX
			Cable length 5 m	535625	MSFW-230AC-K5-M-EX
Cable length on request	538217		MSFW-230AC-KX-M-EX		
	ATEX specification: II 3 GD EEx nA II T130°C X, with plug vanes, explosion-proof, without plug socket, with disc-spring washer and knurled nut	24 V DC		536931	MSFG-24-EX
		24 V AC		536932	MSFW-24-50/60-EX
		110 V AC		536933	MSFW-110-50/60-EX
		230 V AC		536934	MSFW-230-50/60-EX
Plug socket					
	Cable connection via clamping screws			34431	MSSD-F

Solenoid coils MSN1

FESTO

Technical data

Voltage

12 V DC
24 V DC
24 ... 230 V AC

Temperature range

–10 ... +50 °C

- In compliance with VDE regulation 0580, insulation class F
- Can be replaced without interrupting the pneumatic circuit
- Connection pattern to EN 175301-803, type A
- Free of copper, PTFE and silicone



General technical data	
Type of mounting	Clamped via retaining clamp
Mounting position	Any (can be rotated 360° on the armature tube)
Product weight [g]	80

Materials	
Housing	PA
Pin contact	Steel
Winding	Copper
Note on materials	Free of copper and PTFE

Electrical data				
Type	MSN1G-24DC-OD	MSN1W-110AC-OD	MSN1W-230AC-OD	MSN1W-24AC/12DC
Electrical connection	Plug vanes, 3-pin, with connection pattern to EN 175301-803, type A			
	–	–	–	Clip
Min. starting time [ms]	10			
Permissible voltage fluctuations [%]	–15 / +10	At 50 Hz: ±10 At 60 Hz: –10 ... +20	±10	At 50 Hz: ±10 At 60 Hz: –10 ... +20
Duty cycle [%]	100			
Power factor cosφ	–	0.7	0.7	0.7
Protection class to EN 60529	IP65 with plug socket			

Coil characteristics				
Type	MSN1G-24DC-OD	MSN1W-110AC-OD	MSN1W-230AC-OD	MSN1W-24AC/12DC
Output	24 V DC, 2.5 W	–	–	12 V DC, 5 W
Switching power	50 Hz	–	110 V AC, 7.5 VA	230 V AC, 7.5 VA
	60 Hz	–	110 V AC, 5.0 VA	230 V AC, 5.0 VA
Holding capacity	50 Hz	–	110 V AC, 5.0 VA	230 V AC, 5.0 VA
	60 Hz	–	110 V AC, 3.7 VA	230 V AC, 3.7 VA

Operating and environmental conditions				
Type	MSN1G-24DC-OD	MSN1W-110AC-OD	MSN1W-230AC-OD	MSN1W-24AC/12DC
Ambient temperature [°C]	–10 ... +50			
Temperature of medium [°C]	–10 ... +50			
CE mark (see declaration of conformity)	–	To EU Low Voltage Directive		–
Certification	cULus recognized (OL)	Germanischer Lloyd	Germanischer Lloyd	–


Solenoid coils MSN1

Technical data

FESTO

Dimensions


Download CAD Data → www.festo.com/us/cad



- 1 Solenoid coil
(can be rotated 360°
on the armature tube)
- 2 Safety clip

- 3 Plug vanes with connection
pattern to EN 175301-803,
type A

Ordering data

Description		Part No.	Type
Solenoid coil			
	Without plug socket, with mounting clip, connection pattern to EN 175301-803, type A	24 V DC	123060 MSN1G-24DC-OD
		12 V DC, 24 V AC	170152 MSN1W-24AC/12DC
		110/120 V AC	123061 MSN1W-110AC-OD
		230 V AC	123062 MSN1W-230AC-OD
Plug socket			
	Cable connection via clamping screws	34583	MSSD-C
	Cable connection via insulation displacement technology	192748	MSSD-C-S-M16
Plug socket with cable			
	Operating voltage 24 V DC, switching status display via LED	Cable length 2.5 m	30931 KMC-1-24DC-2,5-LED
		Cable length 5 m	30933 KMC-1-24DC-5-LED
		Cable length 10 m	193459 KMC-1-24DC-10-LED
	Operating voltage up to 240 V	Cable length 2.5 m	30932 KMC-1-230AC-2,5
		Cable length 5 m	30934 KMC-1-230AC-5
Illuminating seal			
	Operating voltage 12 ... 24 V DC	19145	MC-LD-12-24DC
	Operating voltage 230 V DC/V AC	19146	MC-LD-230AC
Inscription label			
	Scope of delivery: 35 pieces in frame	33362	KMC/F/V-BZ-35X

Solenoid coils MD-2/MH-2

FESTO

Technical data

Voltage

24 V DC
110, 230 V AC

- Can be replaced without interrupting the pneumatic circuit
- Connection pattern to EN 175301-803, type A

Temperature range

–20 ... +50 °C



General technical data		
Type	MD-2 (system 8)	MH-2 (system 13)
Type of mounting	Via knurled nut	Via lock nut
Max. tightening torque of fitting [Nm]	0.5	2
Mounting position	Any	
Product weight [g]	110	150

Materials		
Type	MD-2 (system 8)	MH-2 (system 13)
Solenoid coil	Duroplastic, copper, steel	
Winding	Copper	
Note on materials	–	Contains PWIS (paint-wetting impairment substances)

Electrical data				
Type	MD-2-24VDC	MD-2-...110VAC	MH-2-24VDC	MH-2-...110VAC
Electrical connection	Plug vanes with connection pattern to EN 175301-803, type A			
Min. starting time [ms]	–		12	
Permissible voltage fluctuations [%]	±10			
Permissible frequency fluctuations [%]	–	±10		
Duty cycle [%]	100			
Power factor cosφ	–	0.7	0.7	
Switching position display	No			
Protection class to EN 60529	IP65 with plug socket			

Coil characteristics						
Type	MD-2-24VDC	MD-2-110VAC	MD-2-230VAC	MH-2-24VDC	MH-2-110VAC	MH-2-230VAC
Output	24 V DC, 6.8 W	–	–	24 V DC, 7.6 W	110 V AC, 14 VA	230 V AC, 14 VA
Switching power 50/60 Hz	–	110 V AC, 14.5 VA	230 V AC, 14.5 VA	–	–	–
Holding capacity 50/60 Hz	–	110 V AC, 10.5 VA	230 V AC, 10.5 VA	–	–	–

Operating and environmental conditions				
Type	MD-2-24VDC	MD-2-...VAC	MH-2-24VDC	MH-2-...VAC
Ambient temperature [°C]	–20 ... +50			
CE mark (see declaration of conformity)	–	To EU Low Voltage Directive	–	To EU Low Voltage Directive

Solenoid coils MD-2/MH-2


Technical data

FESTO

Dimensions


Download CAD Data → www.festo.com/us/cad

MD-2 (system 8)




- 1 Knurled nut M8x0.75
- 2 Plug pattern to EN 175301-803, type A
- 3 Solenoid coil

MH-2 (system 13)



- 1 Hex nut G1/8
- 2 Plug pattern to EN 175301-803, type A
- 3 Solenoid coil

Ordering data

Ordering data		Description	Part No.	Type
Solenoid coil				
	System 8, without plug socket, connection pattern to EN 175301-803, type A	24 V DC	549903	MD-2-24VDC-PA
		110 V AC	549904	MD-2-110VAC-PA
		230 V AC	549905	MD-2-230VAC-PA
	System 13, without plug socket, connection pattern to EN 175301-803, type A	24 V DC	549906	MH-2-24VDC-PA
		110 V AC	549907	MH-2-110VAC-PA
		230 V AC	549908	MH-2-230VAC-PA
Plug socket				
	3-pin, square design MSF	550067	MSSD-N	

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Canada

USA Customers:

For ordering assistance,

Call: 1.800.99.FESTO (1.800.993.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO (1.866.463.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com

Canadian Customers:

Call: 1.877.GO.FESTO (1.877.463.3786)

Fax: 1.877.FX.FESTO (1.877.393.3786)

Email: festo.canada@ca.festo.com

USA Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788, USA
www.festo.com/us

USA Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942, USA

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801, USA

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056, USA

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326, USA

New York

395 Moreland Road
Hauppauge, NY 11788, USA

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550, USA

United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788

Phone: 1.631.435.0800; Fax: 1.631.435.8026;

Email: info@festo-usa.com

www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4

Phone: 1.905.624.9000; Fax: 1.905.624.9001;

Email: festo.canada@ca.festo.com

www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,
54020 Tlalneapantla, Edo. de México

Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;

Email: festo.mexico@mx.festo.com

www.festo.com/mx

Central USA

Festo Corporation
1441 East Business
Center Drive
Mt. Prospect, IL 60056, USA
Phone: 1.847.759.2600
Fax: 1.847.768.9480



Western USA

Festo Corporation
4935 Southfront Road,
Suite F
Livermore, CA 94550, USA
Phone: 1.925.371.1099
Fax: 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com