


## Position transmitters SMAT-8M, for T-slot

**FESTO**



# Position transmitters SMAT-8M, for T-slot

Key features

FESTO

## Design

### General

The SMAT-8M is a position transmitter for the contactless sensing of the piston position of drives that can be detected magnetically. It supplies a displacement-proportional analogue

output signal in the position measuring range. It is connected directly to the analogue PLC inputs without any accessories. With its extremely compact design,

the SMAT-8M is the ideal solution for grippers, short-stroke cylinders and all applications in which installation space is restricted.

### Note


It can be used with Festo cylinders with T-slot (profile slot 8) as well as round cylinders and tie-rod cylinders with mounting kits. A selection aid with suitable drives can be found on the following pages.

## Position measuring range

The SMAT-8M supplies a displacement-proportional analogue output signal of 0 ... 10 V in the position measuring range of up to 40 mm (depending on the drive used). In other words, the output voltage increases when the piston moves in the direction of the piston rod. When the piston retracts, the output voltage drops.

The installation direction of the SMAT-8M is irrelevant in this case. To achieve the best possible function on the drive in question, the position measuring range must be initialised on the drive during installation.

As a visual aid, the green LED lights up within the position measuring range (B) and the red LED lights up outside of the measuring range (A)/(C) in normal operation.




## Repetition accuracy

The repetition accuracy is  $\pm 0.025$  mm on grippers and  $\pm 0.1$  mm on standard drives.

With standard drives, the repetition accuracy in the centre of the measuring range is lower than at the edge. It is  $\pm 0.06$  mm at a distance of  $\pm 5$  mm from the centre, for example. For critical applications, it is recommended that the SMAT-8M be mounted so as to have the relevant measuring points close to 5.5 V.

### Repetition accuracy as a function of position measuring range S



# Position transmitters SMAT-8M, for T-slot

FESTO

Selection aid

Drive/gripper	Usability on drive	Position measuring range approx. [mm]
Standards-based cylinders		
Standard cylinder DSNU/ESNU-8	+	19
Standard cylinder DSNU/ESNU-10	+	22
Standard cylinder DSNU/ESNU-12	+	21
Standard cylinder DSNU/ESNU-16	+	21
Standard cylinder DSNU/ESNU-20	+	20
Standard cylinder DSNU/ESNU-25	+	28
Round cylinder DSNU/ESNU-32	+	25
Round cylinder DSNU/ESNU-40	+	29
Round cylinder DSNU/ESNU-50	+	31
Round cylinder DSNU/ESNU-63	+	36
Standard cylinder DNCB-32	+	25
Standard cylinder DNCB-40	+	28
Standard cylinder DNCB-50	+	30
Standard cylinder DNCB-63	+	32
Standard cylinder DNCB-80	+	35
Standard cylinder DNCB-100	+	29
Standard cylinder DNC-32	+	29
Standard cylinder DNC-40	o <sup>1)</sup>	–
Standard cylinder DNC-50	o <sup>1)</sup>	–
Standard cylinder DNC-63	+	34
Standard cylinder DNC-80	+	35
Standard cylinder DNC-100	+	37
Standard cylinder DNC-125	+	38
Standard cylinder DNG-32	+	28
Standard cylinder DNG-40	+	34
Standard cylinder DNG-50	o <sup>1)</sup>	–
Standard cylinder DNG-63	+	32
Standard cylinder DNG-80	+	32
Standard cylinder DNG-100	+	32
Compact cylinder ADN/AEN-12	+	22
Compact cylinder ADN/AEN-16	+	26
Compact cylinder ADN/AEN-20	+	30
Compact cylinder ADN/AEN-25	+	27
Compact cylinder ADN/AEN-32	+	31
Compact cylinder ADN/AEN-40	+	28
Compact cylinder ADN/AEN-50	+	25
Compact cylinder ADN/AEN-63	+	31
Compact cylinder ADN/AEN-80	o <sup>1)</sup>	–
Compact cylinder ADN/AEN-100	+	28
Compact cylinder ADN/AEN-125	+	37

Drive/gripper	Usability on drive	Position measuring range approx. [mm]
Cylinders with piston rod		
Short-stroke cylinder ADVC/AEVC-32	+	Stroke < position measuring range SMAT-8M
Short-stroke cylinder ADVC/AEVC-40	+	
Short-stroke cylinder ADVC/AEVC-50	+	
Short-stroke cylinder ADVC/AEVC-63	+	
Short-stroke cylinder ADVC/AEVC-80	+	
Short-stroke cylinder ADVC/AEVC-100	+	
Compact cylinder ADVU/AEVU-12	+	23
Compact cylinder ADVU/AEVU-16	+	20
Compact cylinder ADVU/AEVU-20	+	29
Compact cylinder ADVU/AEVU-25	+	25
Compact cylinder ADVU/AEVU-32	+	27
Compact cylinder ADVU/AEVU-40	+	24
Compact cylinder ADVU/AEVU-50	+	22
Compact cylinder ADVU/AEVU-63	+	32
Compact cylinder ADVU/AEVU-80	+	35
Compact cylinder ADVU/AEVU-100	+	33
Compact cylinder ADVU/AEVU-125	+	35
Flat cylinder DZF-12	+	29
Flat cylinder DZF-18	+	26
Flat cylinder DZF-25	+	28
Flat cylinder DZF-32	+	26
Flat cylinder DZF-40	o <sup>1)</sup>	–
Flat cylinder DZF-50	o <sup>1)</sup>	–
Flat cylinder DZF-63	o <sup>1)</sup>	–
Rodless cylinders		
Linear drive DGC-18	+	30
Linear drive DGC-25	o <sup>1)</sup>	–
Linear drive DGC-32	o <sup>1)</sup>	–
Linear drive DGC-40	o <sup>1)</sup>	–
Function-oriented drives		
Linear/swivel clamp CLR-12	+	22
Linear/swivel clamp CLR-16	+	26
Linear/swivel clamp CLR-20	+	30
Linear/swivel clamp CLR-25	+	27
Linear/swivel clamp CLR-32	+	31
Linear/swivel clamp CLR-40	+	28
Linear/swivel clamp CLR-50	+	25
Linear/swivel clamp CLR-63	+	31

+ Unrestricted use

o On request

1) Different from technical data. Usability on request.

2012/02 – Subject to change

→ Internet: [www.festo.com/catalog/...](http://www.festo.com/catalog/...)

3

# Position transmitters SMAT-8M, for T-slot

Selection aid

**FESTO**

Drive/gripper	Usability on drive	Position measuring range approx. [mm]
Drives with linear guides		
Guided drive DFM-12	+	21
Guided drive DFM-16	+	15
Guided drive DFM-20	+	24
Guided drive DFM-25	+	26
Guided drive DFM-32	+	25
Guided drive DFM-40	o <sup>1)</sup>	–
Guided drive DFM-50	+	21
Guided drive DFM-63	+	31
Guided drive DFM-80	+	30
Guided drive DFM-100	+	25
Guided drive DFM-12-B	+	16
Guided drive DFM-16-B	+	20
Guided drive DFM-20-B	+	26
Guided drive DFM-25-B	+	24
Guided drive DFM-32-B	+	29
Guided drive DFM-40-B	+	30
Guided drive DFM-50-B	+	31
Guided drive DFM-63-B	+	33
Linear unit SLE-10	+	22
Linear unit SLE-16	+	21
Linear unit SLE-20	+	20
Linear unit SLE-25	+	28
Linear unit SLE-32	+	25
Linear unit SLE-40	+	29
Linear unit SLE-50	+	31

Drive/gripper	Usability on drive	Position measuring range approx. [mm]
Handling units		
Linear module HMPL-12	+	Stroke < position measuring range SMAT-8M
Linear module HMPL-16	+	
Linear module HMPL-20	+	
Three-point gripper DHDS-32	+	
Three-point gripper DHDS-50	+	
Parallel gripper DHPS-10	+	
Parallel gripper DHPS-16	+	
Parallel gripper DHPS-20	+	
Parallel gripper DHPS-25	+	
Parallel gripper DHPS-35	+	
Parallel gripper HGPL-63	o <sup>1)</sup>	
Parallel gripper HGPT-40-B	+	
Parallel gripper HGPT-50-B	+	
Parallel gripper HGPT-63-B	+	16
Parallel gripper HGPT-80-B	+	16
Angle gripper DHWS-16	+	Stroke < position measuring range SMAT-8M
Angle gripper DHWS-25	+	
Angle gripper DHWS-32	+	
Angle gripper DHWS-40	+	
Radial gripper DHRS-16	+	
Radial gripper DHRS-25	+	
Radial gripper DHRS-32	+	
Radial gripper DHRS-40	+	
Radial gripper HGRT-40-A-G2	+	
Radial gripper HGRT-50-A-G2	o <sup>1)</sup>	

+ Unrestricted use


o On request

1) Different from technical data. Usability on request.

# Position transmitters SMAT-8M, for T-slot

Peripherals overview

FESTO



Accessories	→ Page/Internet
1 Connecting cable NEBU-M8G4	10
2 Connecting cable NEBU-M8W4	10
3 Inscription label ASLR	10
4 Mounting kit SMBR-8-8/100-S6, heat-resistant	10
5 Mounting kit SMBR	10
6 Mounting SMBZ-8	10
7 Connecting cable NEBU-M8G4	10
8 Three-point gripper DHDS	dhds
Three-point gripper HGDD	hgdd
Parallel gripper DHPS	dhps
Parallel gripper HGPD	hgpd
Parallel gripper HGPT	hgpt
Angle gripper DHWS	dhws
Radial gripper DHRS	dhrs
Radial gripper HGRT	hgrr

Accessories	→ Page/Internet
9 Standard cylinder DNCB	dncb
Standard cylinder DNC	dnc
Compact cylinder ADN	adn
Short-stroke cylinder ADVC/AEVC	advc
Compact cylinder ADVU/AEUV	advu
Flat cylinder DZF	dzf
Linear drive DGC	dgc
Linear/swivel clamp CLR	clr
Guided drive DFM	dfm
Linear module HMPL	hmpl
10 Standard cylinder/round cylinder DSNU	dsnu
Linear unit SLE	sle
11 Standard cylinder DNG	dng
12 Signal converter SVE4	sve4

## Position transmitters SMAT-8M, for T-slot

Type codes

**FESTO**

		SMAT	-	8	M	-	U	-	E	-	0,3	-	M8D
<b>Type</b>													
SMAT	Position transmitter, magnetic												
<b>Design</b>													
8	For T-slot												
<b>Sensor design</b>													
M	Insertable in slot, centre clamping												
<b>Switching input/output</b>													
U	0 ... 10 V												
<b>Cable characteristics</b>													
E	Suitable for energy chains/robot applications												
<b>Cable length</b>													
0,3	0.3 m												
<b>Electrical connection</b>													
M8D	M8 plug, 4-pin, rotatable thread												


# Position transmitters SMAT-8M, for T-slot

FESTO

Technical data

Function

Normal operation



General technical data	
Design	For T-slot
Certification	C-tick
CE marking (see declaration of conformity)	To EU EMC Directive <sup>1)</sup>
Note on materials	RoHS-compliant
	Cable, halogen-free
	Cable, oil resistant

- 1) For information about the applicability of the component see the manufacturer's EC declaration of conformity at: [www.festo.com](http://www.festo.com) → Support → User documentation.  
If the component is subject to restrictions on usage in residential, office or commercial environments or small businesses, further measures to reduce the emitted interference may be necessary.

Input signal/measuring element	
Measuring principle	Magnetic
Position measuring range [mm]	≤ 40 <sup>2)</sup>

- 2) Depending on drive/gripper used.

Signal processing	
Max. speed of travel [m/s]	3

Output, general	
Displacement resolution [mm]	≤ 0.05 <sup>2)</sup>
Repetition accuracy [mm]	±0.1 on cylinders <sup>3)</sup>
	±0.025 on grippers <sup>3)</sup>

- 2) Depending on drive/gripper used.  
3) Use of a non-rotating piston rod or a mechanical structure to protect against rotation is recommended.

Analogue output	
Typical linearity error [mm]	±1 on cylinders <sup>2)</sup>
	±0.2 on grippers <sup>2)</sup>

- 2) Depending on drive/gripper used.

Electrical outputs	
Analogue output [V]	0 ... 10
Protection against short circuit	Yes
Protection against overloading	Yes
Output signal	Analogue

# Position transmitters SMAT-8M, for T-slot

Technical data

**FESTO**

Electronics		
Operating voltage range	[V DC]	15 ... 30
Typical scanning interval	[ms]	2.8
Protection against polarity reversal		For all electrical connections

Electromechanics		
Electrical connection		Cable with plug, M8x1, knurled ring, 4-pin
Ambient temperature with flexible cable installation	[°C]	−5 ... +70
Cable length	[m]	0.3
Cable characteristics		Energy chain + robots
Cable test conditions		Energy chain: 5 million cycles, bending radius 28 mm
		Torsional strength: >300,000 cycles, ±270°/0.1 m
		Resistance to bending: to Festo standard; test conditions on request
Information on materials for cable sheath		TPE-U(PU)

Mechanical components		
Type of mounting		Secured with screw, insertable in the slot from above
Product weight	[g]	10
Information on housing materials		Reinforced PA6

Display/operation		
Status display		LED red, green

Immissions/emissions		
Ambient temperature	[°C]	−25 ... +75
Protection class		IP65, IP68
Corrosion resistance class	CRC <sup>4)</sup>	2

4) Corrosion resistance class 2 as per Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Pin allocation		
Normal operation	Initialisation	Plug

- 1 Operating voltage
- 2 Analogue output 0 V
- 3 0 V
- 4 Analogue output 0 ... 10 V

Wire colours		
BN = brown	BU = blue	
BK = black	WH = white	




# Position transmitters SMAT-8M, for T-slot

Technical data

**FESTO**


## Dimensions

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)



B1	D1	D2	D3	H1	L1	L2	L3	L4	L5	⌀
5	M8x1	9.6	2.9	4.6	300	34.8	31.8	41.1	23	1.5




## Ordering data




Size	Analogue output [V]	Electrical connection	Cable length [m]	Part No.	Type
	0 ... 10	M8 plug, 4-pin, rotatable thread	0.3	553744	SMAT-8M-U-E-0,3-M8D


## Position transmitters SMAT-8M, for T-slot

**FESTO**

Accessories

Ordering data – Mounting attachments			
	For piston diameter	Part No.	Type
Mounting kit SMBR-8-8/100-S6, heat-resistant			
	8 ... 100	538937	SMBR-8-8/100-S6
Mounting kit SMBR			
	8	175091	SMBR-8-8
	10	175092	SMBR-8-10
	12	175093	SMBR-8-12
	16	175094	SMBR-8-16
	20	175095	SMBR-8-20
	25	175096	SMBR-8-25
	32	175097	SMBR-8-32
	40	175098	SMBR-8-40
	50	175099	SMBR-8-50
	63	175100	SMBR-8-63
Mounting SMBZ			
	32 ... 100	537806	SMBZ-8-32/100
	125 ... 320	537808	SMBZ-8-125/320

Ordering data – Connecting cable NEBU-M8				Technical data → Internet: nebu	
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part No.	Type
	Straight socket, M8x1, 4-pin	Cable, open end, 4-wire	2.5	541342	NEBU-M8G4-K-2.5-LE4
			5	541343	NEBU-M8G4-K-5-LE4
	Straight socket, M8x1, 4-pin	Straight socket, M8x1, 4-pin	2.5	554035	NEBU-M8G4-K-2.5-M8G4
	Angled socket, M8x1, 4-pin	Cable, open end, 4-wire	2.5	541344	NEBU-M8W4-K-2.5-LE4
			5	541345	NEBU-M8W4-K-5-LE4

Ordering data – Inscription label ASLR				
	Size	Part No.	Type	PU <sup>1)</sup>
	23x4 mm	541598	ASLR-L-423	34

1) Packaging unit in quantity per frame

## Product Range and Company Overview

### A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



**Custom Automation Components**  
Complete custom engineered solutions



**Custom Control Cabinets**  
Comprehensive engineering support and on-site services



**Complete Systems**  
Shipment, stocking and storage services

### The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



**Electromechanical**  
Electromechanical actuators, motors, controllers & drives



**Pneumatics**  
Pneumatic linear and rotary actuators, valves, and air supply



**PLCs and I/O Devices**  
PLC's, operator interfaces, sensors and I/O devices

### Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

### Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

# Festo North America

## Festo Regional Contact Center

5300 Explorer Drive  
Mississauga, Ontario L4W 5G4  
Canada

### USA Customers:

For ordering assistance,

**Call:** 1.800.99.FESTO (1.800.993.3786)

**Fax:** 1.800.96.FESTO (1.800.963.3786)

**Email:** [customer.service@us.festo.com](mailto:customer.service@us.festo.com)

For technical support,

**Call:** 1.866.GO.FESTO (1.866.463.3786)

**Fax:** 1.800.96.FESTO (1.800.963.3786)

**Email:** [product.support@us.festo.com](mailto:product.support@us.festo.com)

### Canadian Customers:

**Call:** 1.877.GO.FESTO (1.877.463.3786)

**Fax:** 1.877.FX.FESTO (1.877.393.3786)

**Email:** [festo.canada@ca.festo.com](mailto:festo.canada@ca.festo.com)

## USA Headquarters

Festo Corporation  
395 Moreland Road  
P.O. Box 18023  
Hauppauge, NY 11788, USA  
[www.festo.com/us](http://www.festo.com/us)

## USA Sales Offices

### Appleton

North 922 Tower View Drive, Suite N  
Greenville, WI 54942, USA

### Boston

120 Presidential Way, Suite 330  
Woburn, MA 01801, USA

### Chicago

1441 East Business Center Drive  
Mt. Prospect, IL 60056, USA

### Dallas

1825 Lakeway Drive, Suite 600  
Lewisville, TX 75057, USA

### Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320  
Auburn Hills, MI 48326, USA

### New York

395 Moreland Road  
Hauppauge, NY 11788, USA

### Silicon Valley

4935 Southfront Road, Suite F  
Livermore, CA 94550, USA

## United States



**USA Headquarters, East:** Festo Corp., 395 Moreland Road, Hauppauge, NY 11788

Phone: 1.631.435.0800; Fax: 1.631.435.8026;

Email: [info@festo-usa.com](mailto:info@festo-usa.com)

[www.festo.com/us](http://www.festo.com/us)

## Canada



**Headquarters:** Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4

Phone: 1.905.624.9000; Fax: 1.905.624.9001;

Email: [festo.canada@ca.festo.com](mailto:festo.canada@ca.festo.com)

[www.festo.ca](http://www.festo.ca)

## Mexico



**Headquarters:** Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,  
54020 Tlalneapantla, Edo. de México

Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;

Email: [festo.mexico@mx.festo.com](mailto:festo.mexico@mx.festo.com)

[www.festo.com/mx](http://www.festo.com/mx)

## Central USA

Festo Corporation  
1441 East Business  
Center Drive  
Mt. Prospect, IL 60056, USA  
Phone: 1.847.759.2600  
Fax: 1.847.768.9480



## Western USA

Festo Corporation  
4935 Southfront Road,  
Suite F  
Livermore, CA 94550, USA  
Phone: 1.925.371.1099  
Fax: 1.925.245.1286



## Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark  
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia  
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore  
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

[www.festo.com](http://www.festo.com)