

## Piezo valves VEAE

**FESTO**




Key features




Special characteristics

- Energy consumption < 0.1 W at 5 Hz
  - No self-heating
  - No operating noise
- Extremely long service life
  - For use with gases, including oxygen
  - Small and lightweight


Mode of operation

Description			
	[1] Port 1, pressure supply port	The VEA is a proportional 2/2-way valve in which a piezo actuator is controlled electrically.	In the normal position, the valve is closed. Pressure supplied at port 1 supports the closing function.
	[2] Port 2, working port		
	[3] Electrical connection	The flow rate can be controlled via a closed-loop control circuit by integrating a flow sensor in the outlet line.	

Control response


	No voltage No flow rate	The piezo actuator is controlled using variable voltage to give proportional closed-loop control.	The piezo valve VEA exhibits the typical hysteresis behaviour of a proportional valve. Linear behaviour can be achieved by combining control electronics with a flow sensor.	
	Medium voltage Medium flow rate			
	High voltage High flow rate			
		This allows either the pressure or flow rate to be controlled, depending on the design.		
		The pressure or flow behaviour is controlled by integrating a sensor in the outlet line of the closed-loop control circuit.		

Low energy consumption

	Compared with solenoid valves, proportional valves with piezo technology require virtually no energy to maintain an active state thanks to their capacitive principle. The piezo valve operates like a capacitor: it needs current only at the start in order to charge the piezoceramics. No further energy is needed to maintain its state. The valves therefore generate no heat.		
	They consume up to 95% less energy than solenoid valves, which permanently require an electrical current. For an EMERGENCY OFF circuit, in which the valve is meant to close, the piezo valve connection needs to be earthed. In the event of a simple separation of the connection, the piezo actuator remains in its current position for a while due to its capacitive principle.		


Peripherals overview

Example of VEAE with manifold rail



Designation		→ Page/Internet
[1]	Piezo valves VEAE	12
[2]	Manifold block VABS	12
[3]	Seal assortment VABD	12

## Product range overview




Function	Description	Nominal width	Flow rate	Operating pressure	Operating voltage	
		[mm]	[l/min]	[bar]	0 ... 300 V	
Sub-base valve		2/2-way valve, normally closed, monostable				
		Flange	1.2	55	0 ... 6	■
		2/2-way valve, normally closed, monostable				
		Flange	1.5	70	0 ... 6	■
		2/2-way valve, normally closed, monostable				
		Flange	1.7	55	0 ... 3	■

## Type codes

001	Series	
VEAE	Piezo valve	
002	Directional control valve type	
B	Sub-base valve	
003	Inflow direction	
B	Over seat	
004	Valve function	
6	2/2-way valve, normally closed	

005	Nominal width [mm]	
1.2	1.2	
1.5	1.5	
1.7	1.7	
006	Pressure range [bar]	
D22	0 ... 3	
D9	0 ... 6	
007	Pneumatic connection	
X4	CX connection 4 mm	

## Data sheet

-  Flow rate  
55 ... 70 l/min
-  Voltage  
300 V
-  Operating pressure  
0 ... 3 bar  
0 ... 6 bar



General technical data		VEAE-BB-6-12-D9-X4	VEAE-BB-6-15-D9-X4	VEAE-BB-6-17-D22-X4
Valve function		2/2-way valve, single solenoid		
Normal position		Normally closed		
Reset method		Mechanical spring		
Standard nominal flow rate	[l/min]	55	70	55
Total leakage	[l/h]	0.4		
Type of control		Direct		
Sealing principle		Soft		
Dimensions W x L x H	[mm]	64 x 24 x 12		
Nominal width	[mm]	1.2	1.5	1.7
Grid dimension	[mm]	20.5		
Pneumatic connection 1, 2		Flange		
Actuation type		Electric		
Type of mounting		Via through-hole		
Mounting position		Any		
Flow direction		Non-reversible		
Product weight	[g]	10		
Special characteristics		Oxygen-compatible to DIN EN 1797		

Operating and environmental conditions		VEAE-BB-6-12-D9-X4	VEAE-BB-6-15-D9-X4	VEAE-BB-6-17-D22-X4
Operating pressure	[bar]	0 ... 6	0 ... 6	0 ... 3
Burst pressure	[bar]	25		
Nominal operating pressure	[bar]	5	5	3
Medium		<ul style="list-style-type: none"> <li>Compressed air to ISO 8573-1:2010 [5:3:1]</li> <li>Inert gases</li> <li>Oxygen (oxygen applications to IEC 60601-1 only on request)</li> </ul>		
Note on the medium		Lubricated operation not possible		
Ambient temperature	[°C]	-10 ... 60		
Temperature of medium	[°C]	-10 ... 60		
Storage temperature	[°C]	-20 ... 70		
Relative humidity	[%]	0 ... 60		
		Non-condensing		
Pressure dew point	[°C]	≤ -20		
Grade of filtration	[µm]	≤ 5		
Degree of protection		IP40, in assembled state		
Corrosion resistance class (CRC)		2 - Moderate corrosion stress		

1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

## Data sheet


Electrical data		VEAE-BB-6-12-D9-X4	VEAE-BB-6-15-D9-X4	VEAE-BB-6-17-D22-X4
Nominal operating voltage	[V DC]	300		
Operating voltage range	[V DC]	0 ... 300		
Electrical connection		Plug		
		Flexible circuit board connector, pitch 2.5 mm		
		3-pin		
Max. electrical power consumption	[W]	0.1 at 5 Hz		
Max. current consumption	[mA]	11		
Max. switching frequency	[Hz]	12		
Duty cycle	[%]	100		


Safety data	
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Vibration resistance	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6

1) For information about the area of use, see the EC declaration of conformity at: [www.festo.com/sp](http://www.festo.com/sp) → Certificates.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.





Materials	
Seals	EPDM
Housing	Reinforced PA
Note on materials	RoHS-compliant
	Contains paint-wetting impairment substances

Design	
Circuit symbol	
	<ul style="list-style-type: none"> <li>2/2-way valve, normally closed</li> </ul>


Pin allocation		Pin	Allocation	
			Analogue	
	1	Power supply 0 ... 300 V	The charge and discharge current must be limited to 11 mA. If the current is not regulated by the controller, this can be achieved using a 27 kOhm resistor connected in series.	
	2	GND		
	3	GND		

## Data sheet

## VEAE-BB-6-12-D9-X4

Flow rate  $q_n$  as a function of voltage at an operating pressure of 5 barFlow rate  $q_n$  as a function of operating pressure at 300 VFlow rate  $q_n$  as a function of switch-on point at 300 V and an operating pressure of 5 barFlow rate  $q_n$  as a function of ambient temperature at 300 V





Voltage to open and close the valve as a function of operating pressure at 300 V






## Data sheet

## VEAE-BB-6-15-D9-X4

Flow rate  $q_n$  as a function of voltage at an operating pressure of 5 barFlow rate  $q_n$  as a function of operating pressure at 300 VFlow rate  $q_n$  as a function of switch-on point at 300 V and an operating pressure of 5 barFlow rate  $q_n$  as a function of ambient temperature at 300 V


Voltage to open and close the valve as a function of operating pressure at 300 V




Data sheet

VEAE-BB-6-17-D22-X4


Flow rate  $q_n$  as a function of voltage at an operating pressure of 3 bar




Flow rate  $q_n$  as a function of operating pressure at 300 V




Flow rate  $q_n$  as a function of switch-on point at 300 V and an operating pressure of 3 bar



Flow rate  $q_n$  as a function of ambient temperature at 300 V




Voltage to open and close the valve as a function of operating pressure at 300 V



## Data sheet

## Dimensions


Piezo valves VEA

Download CAD data → [www.festo.com](http://www.festo.com)

Type	B1	B2	B3	D1 Ø	D2 Ø	H1	H2	H3	L1	L2	L3	L4	L5
VEAE	24	20	16.4	4.2	2.2	7.9	3	0.3	63.3	19	14.4	10	8

## Dimensions




Manifold block VABS

Download CAD data → [www.festo.com](http://www.festo.com)

Type	B1	B2	B3	B4	D1 Ø	D2	D3	D4	H1	H2	H3
VABS	26	14	10	10	6.7	M5	M4	M2x7	11	5.5	1.2

Type	L1	L2	L3	L4	L5	L6	L7	L8	T1	T2	T3	T4	T5
VABS	35	27	4	24	6.4	14.4	10	6	8	8	4	2	8

## Accessories

Ordering data					
	Description	Nominal width [mm]	Operating pressure [bar]	Part no.	Type
Sub-base valve					
	2/2-way valve, closed, single solenoid	1.2	0 ... 6	8078916	VEAE-BB-6-12-D9-X4
		1.5	0 ... 6	8078914	VEAE-BB-6-15-D9-X4
		1.7	0 ... 3	8078917	VEAE-BB-6-17-D22-X4
Sub-base					
	For 2/2-way valve, with 2 pneumatic connections M5			8097804	VABS-P16-10S-M5
Sealing ring assortment					
	200 pieces (for 100 VEAЕ valves), oxygen-compatible			8097798	VABD-P16-S