

Connecting cables for valves, socket type A, EN 175301-803

Type codes – Connecting cable with PUR cable sheath

		NEBV	-	A1	W	3	F	-	P	-	K	-	0.6	-	N	-	LE		3
Function																			
NEBV	Connecting cables for valves																		
Connection technology on left, field device side																			
A1	Plug socket type A, EN 175301-803																		
Cable outlet, left																			
W	Angled																		
Number of pins/wires, left																			
3	3-pin																		
Display																			
-	None																		
F	Signal status LED																		
Circuitry																			
-	None																		
P	Integrated protective circuit																		
Cable characteristic																			
K	Standard																		
Cable length																			
0.3	0.3 m																		
0.6	0.6 m																		
Cable identification																			
N	Without inscription label holder																		
Connection technology on right, control side																			
LE	Open end																		
M12	Plug connector M12x1, A-coded, EN 61076-2-101																		
Cable outlet, right																			
-	Open end																		
W	Angled																		
Number of pins/wires, right																			
3	3-pin																		

Connecting cables for valves, socket type A, EN 175301-803

FESTO

Type codes – Connecting cable with PVC cable sheath

		KMC	-	1	-	24	-	10	-	LED
Function/connection technology on left, field device side										
KMC	Connecting cables for valves Plug socket type A, EN 175301-803									
Series										
1	Series 1									
Operating voltage										
24	24 V DC									
24DC	24 V DC									
230AC	230 V AC									
Cable length										
2,5	2.5 m									
5	5 m									
10	10 m									
Display										
LED	Signal status LED									


Connecting cables for valves, socket type A, EN 175301-803

FESTO

Technical data – Connecting cable with PUR cable sheath

Connecting cable NEBV-A1W3

- Connecting cable
- Pre-assembled at one or both ends
- For connecting valves



General technical data		
Electrical connection 1		
Function	Field device side	
Connection type	Socket	
Cable outlet	Angled	
Design	Square	
Connection technology	Connection pattern type A, EN 175301-803	
Number of pins/wires	4	
Assigned pins/wires	4	
Type of mounting	On solenoid valve via central screw M3	
Electrical connection 2		
Function	Controller side	
Connection type	Cable	Plug connector
Cable outlet	–	Angled
Design	–	Round
Connection technology	Open end	M12x1, A-coded, to EN 61076-2-101
Number of pins/wires	3	5
Assigned pins/wires	3	3
Type of mounting	–	Screw locking with spanner size 13 (hexagonal)

Technical data – Electrical				
Nominal operating voltage	[V AC/DC]	24	110	230
Nominal operating voltage	[V AC/DC]	24	110	230
Operating voltage range	[V AC]	18 ... 30	0 ... 110	0 ... 230
	[V DC]	18 ... 30	0 ... 110	0 ... 230
Surge resistance	[kV]	0.8	1.5	4
Current rating at 40 °C	[A]	4	1	10
Degree of contamination		3	3	3
Display		Yellow LED, signal status display	–	–
Additional functions		Protective circuit	–	–
Protective earth connection		Yes	Yes	Yes

Technical data – Cable		
Cable composition	[mm ²]	3 x 0.75
Cable diameter	[mm]	5.9
Cable diameter tolerance	[mm]	±0.3
Cable characteristic		Standard
Cable test conditions		Test conditions on request
Cable identification		Without inscription label holder

Connecting cables for valves, socket type A, EN 175301-803




FESTO

Technical data – Connecting cable with PUR cable sheath

Materials		
Electrical connection 2	Connection technology	
	Open end	M12x1, A-coded, to EN 61076-2-101
Housing	TPE-U (PUR)	TPE-U (PUR)
Housing colour	Black	Black
Union nut	–	Nickel-plated die-cast zinc
Insulating sheath	PP	PP
Cable sheath	TPE-U (PUR)	TPE-U (PUR)
Cable sheath colour	Grey	Grey
Note on materials	RoHS compliant	RoHS compliant
	Contains paint-wetting impairment substances	Contains paint-wetting impairment substances

Operating and environmental conditions				
Nominal operating voltage	[V AC/DC]	24	110	230
Ambient temperature	[°C]	–25 ... +80	–25 ... +80	–25 ... +80
Ambient temperature with flexible cable installation	[°C]	–25 ... +80	–25 ... +80	–25 ... +80
CE mark (see declaration of conformity) ¹⁾	–	To EU Low Voltage Directive	To EU Low Voltage Directive	To EU Low Voltage Directive
Certification	c CSA us (OL)	c CSA us (OL)	c CSA us (OL)	c CSA us (OL)
Degree of protection	IP67	IP67	IP67	IP67
Note on degree of protection	In mounted state	In mounted state	In mounted state	In mounted state

1) Additional information www.festo.com/sp → Certificates.

Circuitry (view of socket/plug connector)				
Electrical connection 1	Pin	Wire colour ¹⁾	Pin	Electrical connection 2
Electrical connection 2, connection technology open end				
	1	BK	–	Open end
	2	BK	–	Open end
	GND	GNYE	–	Open end
Electrical connection 2, connection technology M12x1 A-coded to EN 61076-2-101				
	1	BK	3	
	2	BK	4	
	GND	GN YE	5	

1) To IEC 757

Connecting cables for valves, socket type A, EN 175301-803


FESTO

Technical data – Connecting cable with PUR cable sheath


Dimensions

Download CAD data → www.festo.com

Electrical connection 2, connection technology open end



Electrical connection 2, connection technology plug connector M12x1



Type	B1	B2	D1 Ø	D2	D3 Ø	H1	H2	L2	L3	L4	L5	≈C1
NEBV-A1W3-...-LE3	27	18	5.9	–	–	30	–	45	–	27	18	–
NEBV-A1W3-...-M12W3	27	18	5.9	M12x1	15	30	31	45	39	27	18	13


Connecting cables for valves, socket type A, EN 175301-803

FESTO

Technical data – Connecting cable with PVC cable sheath

Connecting cable KMC

- Connecting cable
- Pre-assembled at one end
- For connecting valves



General technical data	
Electrical connection 1	
Function	Field device side
Connection type	Socket
Cable outlet	Angled
Design	Square
Connection technology	Connection pattern type A, EN 175301-803
Number of pins/wires	4
Assigned pins/wires	4
Type of mounting	On solenoid valve via central screw M3
Electrical connection 2	
Function	Controller side
Connection type	Cable
Connection technology	Open end
Number of pins/wires	3
Assigned pins/wires	3

Technical data – Electrical		
Nominal operating voltage	[V]	24 DC
Nominal operating voltage	[V]	230 AC
Operating voltage range	[V AC]	–
	[V DC]	20.4 ... 27.6
Current rating at 40 °C	[A]	4
Degree of contamination		3
Display		Yellow LED, signal status display
Protective earth connection		Yes

Technical data – Cable	
Cable composition	[mm ²] 3 x 0.75
Cable diameter	[mm] 6
Cable characteristic	Standard
Cable test conditions	Test conditions on request
Cable identification	Without inscription label holder

Connecting cables for valves, socket type A, EN 175301-803


FESTO

Technical data – Connecting cable with PVC cable sheath

Materials	
Housing	PC
Cable sheath	PVC
Pin contacts	Bronze

Operating and environmental conditions		
Nominal operating voltage	[V]	24 DC
		230 AC
Ambient temperature	[°C]	–20 ... +80
		–20 ... +80
CE mark (see declaration of conformity) ¹⁾		–
		To EU Low Voltage Directive
Degree of protection		IP67
		IP67
Note on degree of protection		In mounted state
		In mounted state
Maritime classification ¹⁾		–
		See certificate

1) Additional information www.festo.com/sp → Certificates.

Circuitry (view of socket/plug connector)				
Electrical connection 1	Pin	Wire colour ¹⁾	Pin	Electrical connection 2
	1	BK	–	Open end
	2	BK	–	Open end
	GND	GNYE	–	Open end

1) To IEC 757


Connecting cables for valves, socket type A, EN 175301-803

FESTO

Technical data – Connecting cable with PVC cable sheath

Dimensions

Download CAD data → www.festo.com






Type	B1	D1 Ø	D2 Ø	H1	H2	H3	L1	L2	L3	L4
KMC-1-...-2,5	27	6	M3	28	22.5	1.5	2550	50	42	27
KMC-1-...-5							5050			
KMC-1-...-10							10050			



Connecting cables for valves, socket type A, EN 175301-803

FESTO

Ordering data

Ordering data – Connecting cable with PUR cable sheath						
	Nominal operating voltage [V]		Cable length [m]	Weight [g]	Part No.	Type
Electrical connection 2, connection technology open end						
	24 AC/DC	• Signal status display • Protective circuit	0.6	80	3679776	NEBV-A1W3F-P-K-Q.6-N-LE3
	230 AC/DC	–	0.6	80	3579466	NEBV-A1W3-K-Q.6-N-LE3
Electrical connection 2, connection technology M12x1 A-coded to EN 61076-2-101						
	24 AC/DC	• Signal status display • Protective circuit	0.3	60	3679771	NEBV-A1W3F-P-K-Q.3-N-M12W3
			0.6	100	3679772	NEBV-A1W3F-P-K-Q.6-N-M12W3
	110 AC/DC	–	0.3	60	3579461	NEBV-A1W3-K-Q.3-N-M12W3
			0.6	100	3579462	NEBV-A1W3-K-Q.6-N-M12W3

Ordering data – Connecting cable with PVC cable sheath						
	Nominal operating voltage [V]		Cable length [m]	Weight [g]	Part No.	Type
Electrical connection 2, connection technology open end						
	24 DC	Signal status display	2.5	170	30931	KMC-1-24DC-2,5-LED
			5	320	30933	KMC-1-24DC-5-LED
			10	620	193459	KMC-1-24-10-LED
	230 AC	–	2.5	170	30932	KMC-1-230AC-2,5
			5	320	30934	KMC-1-230AC-5

Ordering data – Accessories						
					Part No.	Type
	Inscription clips for placing on a cable with diameter 5 ... 8 mm		11x20 mm		33361	KM-BZ
	Inscription labels for connecting cable KMF, 64 per frame		6x10 mm		18576	IBS-6x10

Connecting cables for valves, socket type A, EN 175301-803

FESTO

Ordering data – Modular product system

Ordering table				
		Condi- tions	Code	Entry code
M	Module no.	8003577		
	Connecting cable	Connecting cables for valves	NEBV	NEBV
	Connection technology on left, field device side	Plug socket type A, EN 175301-803	-A1	-A1
	Cable outlet, left	Angled	W	W
	Number of pins/wires, left	3-pin	3	3
O	Display	None		
		Signal status LED	F	
	Circuitry	None		
		Integrated protective circuit	-P	
M	Cable characteristic	Standard	-K	-K
	Cable length [m]	0.3	-0.3	
	[m]	0.6	-0.6	
	Cable identification	Without inscription label holder	-N	-N
	Connection technology on right, control side	Open end	-LE	
		Plug connector M12x1, A-coded, EN 61076-2-101	-M12	
O	Cable outlet, right	None		
		Angled	W	
M	Number of pins/wires, right	3-pin	3	3

1 -0.3, W Only with connection technology on right M12

M Mandatory data
O Options

Transfer order code

8003577 NEBV - A1 W 3 - - K - N - 3

Festo - Your Partner in Automation



1 Festo Inc.
5300 Explorer Drive
Mississauga, ON L4W 5G4
Canada

Festo Customer Interaction Center
Tel: 1 877 463 3786
Fax: 1 877 393 3786
Email: customer.service.ca@festo.com



2 Festo Pneumatic
Av. Ceylán 3,
Col. Tequesquináhuac
54020 Tlalneantla,
Estado de México

Multinational Contact Center
01 800 337 8669
ventas.mexico@festo.com



3 Festo Corporation
1377 Motor Parkway
Suite 310
Islandia, NY 11749

Festo Customer Interaction Center
1 800 993 3786
1 800 963 3786
customer.service.us@festo.com



4 Regional Service Center
7777 Columbia Road
Mason, OH 45040

Connect with us

www.festo.com/socialmedia



www.festo.com

Subject to change