

One-way flow control valves VFOF

FESTO




One-way flow control valves VFOF

Key features and product range overview

FESTO

Features

- Minimal height
- High flow rate
- Can be rotated horizontally through 360° in assembled state
- Actuation direction **1** can be changed by repositioning the housing
- Greater functionality thanks to function combinations




 Note

The following sequence must be observed when assembling the individual components:

- 1) Press thrust ring **2** into the housing until it fits tightly.
- 2) Insert hollow bolt **3** into the opening.
- 3) Push sealing ring OK **4** over the thread of the hollow bolt.

Product range overview

Function	Valve function	Design	Type	Pneumatic connection 1	Pneumatic connection 2	qn ¹⁾ [l/min]	Adjusting element	→ Page/ Internet
One-way flow control valves	Function combination							
	Exhaust air one-way flow control function		VFOF	QS-6, QS-8	G1/8, G1/4	240 ... 590	Internal hex	3

1) Standard nominal flow rate in flow control direction.

One-way flow control valves VFOF, function combination

Type codes


		VFOF	-	L	E	-	BA	H	-	G18	-	Q6
Type												
VFOF	One-way flow control valve, flat design											
Design												
L	L-shaped outlet											
Valve function												
E	Exhaust air one-way flow control function											
Additional function												
BA	Piloted non-return function, manual exhaust function											
Adjusting element												
H	Internal hex											
Pneumatic connection 2												
G18	Thread G1/8											
G14	Thread G1/4											
Pneumatic connection 1												
Q6	Push-in connector QS-6											
Q8	Push-in connector QS-8											

One-way flow control valves VFOF, function combination

FESTO

Technical data

One-way flow control function
Exhaust air



-  - Standard nominal flow rate
240 ... 590 l/min
-  - Temperature range
-10 ... +60 °C
-  - Operating pressure
0.2 ... 10 bar



The one-way flow control valve VFOF-LE-BAH is a valve with a function combination consisting of an exhaust air one-way flow control function and a piloted non-return function with manual exhaust function. The exhaust air one-way flow control

function is used to manually adjust the advance/return speed of the piston rod of a pneumatic drive. The flow control function is realised by means of an adjustable annular gap in the housing. This gap can be

increased or decreased by turning the regulating screw with internal hex. The piloted non-return function can be used for a temporary intermediate stop. If a pilot signal is applied, exhaust air flow control is active. If no

pilot signal is applied, the valve shuts off the exhaust air from the drive and the drive stops temporarily. The integrated manual exhaust function can be used to manually vent a pneumatic drive.

General technical data				
Valve function		Exhaust air one-way flow control function		
Pneumatic connection 2		G½/8	G¼	
Pneumatic connection 1		QS-6	QS-8	
Pilot air connection 21		QS-6	QS-8	
Adjusting element		Internal hex		
Actuation type		Manual		
Type of actuation, piloted non-return function		Pneumatic		
Manual exhaust function		Non-detenting		
Type of mounting		Screw-in		
Mounting position		Any		
Switching time	Off	[ms]	9	11
	On	[ms]	6	8
Nominal tightening torque		[Nm]	3 ±20%	11 ±20%
Perm. actuation torque for regulating screw		[Nm]	1	
Rotatability		[°]	360 (continuous rotation not permitted)	

Operating and environmental conditions		
Operating pressure	[bar]	0.2 ... 10
Pilot pressure	[bar]	2 ... 10
Operating/pilot medium	Compressed air according to ISO 8573-1:2010 [7:4:4]	
Note on operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)	
Ambient temperature	[°C]	-10 ... +60
Temperature of medium	[°C]	-10 ... +60
Storage temperature	[°C]	-20 ... +70
Corrosion resistance class CRC ¹⁾	2	

1) Corrosion resistance class CRC 2 to Festo standard FN 940070
Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.


One-way flow control valves VFOF, function combination

FESTO

Technical data

Materials


Sectional view




One-way flow control valve

1	Housing	PBT
2	End cap	PBT
3	Hollow bolt	Wrought aluminium alloy
4	Sleeve	Wrought aluminium alloy
5	Regulating screw	Brass
6	Releasing ring	POM
-	Cover	ES-BE
-	Seals	NBR
Note on materials		RoHS-compliant

Standard nominal flow rate q_{nN} in flow control direction at 6 $\rightarrow$ 5 bar as a function of turns of the adjusting screw n



Standard flow rate q_n in flow control direction at 6 $\rightarrow$ 0 bar as a function of turns of the adjusting screw n



Minimum pilot pressure p_{21} as a function of operating pressure p_1




One-way flow control valves VFOF, function combination

Technical data

FESTO

Dimensions

Download CAD data → www.festo.com



Type	Connection D1	Tubing O.D. D2	B1	B2	H1	H2	H3	H4	L1	L2	L3	L4	L5	⌀ 1	⌀ 2
VFOF-...-G18-Q6	G $\frac{1}{8}$	QS-6	29.5	15	19.4	5	14.1	1.5	60.3	52.8	23.8	9.7	7.5	12	2.5
VFOF-...-G14-Q8	G $\frac{1}{4}$	QS-8	39.5	20.5	28.2	5.6	21	2	76.8	66.8	30	11.1	10	15	2.5

Ordering data – Exhaust air one-way flow control function

	Pneumatic connection		Pilot air connec- tion	Standard nominal flow rate q _N at 6 bar → 5 bar		Standard flow rate q _n at 6 bar → 0 bar		Weight	Part No.	Type
				In flow con- trol direction	In non-return direction	In flow con- trol direction	In non-return direction			
	2	1	21	[l/min]	[l/min]	[l/min]	[l/min]	[g]		
	G $\frac{1}{8}$	QS-6	QS-6	240	150 ... 230 120 ... 220 ¹⁾	420	400 ... 460 400 ... 460 ¹⁾	28.6	8001459	VFOF-LE-BAH-G18-Q6
	G $\frac{1}{4}$	QS-8	QS-8	590	315 ... 540 310 ... 540 ¹⁾	940	830 ... 1,000 840 ... 1,000 ¹⁾	73.9	1927030	VFOF-LE-BAH-G14-Q8

1) Unactuated

Festo - Your Partner in Automation



1 Festo Inc.
5300 Explorer Drive
Mississauga, ON L4W 5G4
Canada

Festo Customer Interaction Center

Tel: 1 877 463 3786
Fax: 1 877 393 3786
Email: customer.service.ca@festo.com



2 Festo Pneumatic
Av. Ceylán 3,
Col. Tequesquináhuac
54020 Tlalneantla,
Estado de México

Multinational Contact Center

01 800 337 8669
ventas.mexico@festo.com



3 Festo Corporation
1377 Motor Parkway
Suite 310
Islandia, NY 11749

Festo Customer Interaction Center

1 800 993 3786
1 800 963 3786
customer.service.us@festo.com



4 Regional Service Center
7777 Columbia Road
Mason, OH 45040

Connect with us



www.festo.com/socialmedia



www.festo.com

Subject to change