


Proximity switches SDBT for T-slot



★	Festo Core Range Solves the majority of your automation tasks	With the Festo Core Range, we have selected the most important products and functions from our broad product catalogue, and added the quickest delivery.	
Worldwide:	Quickest delivery – wherever, whenever	The Core Range offers you the best value for your automation tasks.	
Simply good:	Expected high Festo quality		
Fast:	Easy and fast to select		


Product range overview

Design	Type of mounting	Measuring principle	Type	Operating voltage range	Switching output	Switching element function	→ Page
For T-slot	Standard						
	Screw-clamped, inserted in the slot from above	Magnetic Hall	SDBT-MSX	10 ... 30 V DC	PNP/NPN, switchable	N/O/ N/C contact, switchable	–
	Inserted in the slot from above, flush with the cylinder profile	Magneto-resistive	SMT-8M-A	5 ... 30 V DC	PNP	N/O contact	–
						N/C contact	
					NPN	N/O contact	
		Non-contacting, 2-wire	N/O contact				
	Inserted in the slot from above, flush with the cylinder profile	Magnetic reed	SME-8M	5 ... 30 V AC/DC	Contacting, bipolar	N/O contact	–
						N/C contact	
	Inserted in the slot lengthwise, flush with the cylinder profile	Magnetic reed	SME-8	12 ... 30 V AC/DC	Contacting, bipolar	N/O contact	–
						N/C contact	
		3 ... 230 V AC/DC	N/O contact	–			
	Insertable in the slot lengthwise	Magneto-resistive	SMT-8G	10 ... 30 V DC	PNP, NPN	N/O contact	–
		Magneto-resistive	SMT-8-SL	10 ... 30 V DC	PNP	N/O contact	–
	With accessories	Magneto-resistive	SMT0-8E	10 ... 30 V DC	PNP	N/O contact	–
					NPN		
	Corrosion-resistant						
	Inserted in the slot from above, flush with the cylinder profile	Magneto-resistive	CRSMT-8M	5 ... 30 V DC	PNP	N/O contact	–
	Welding-field-resistant						
	Inserted in the slot from above, screw-clamped	Magneto-resistive	SDBT-BSW	10 ... 30 V DC	PNP	N/O contact	7
					NPN		
					Non-contacting, 2-wire		
	With accessories	Magneto-inductive	SMTSO-8E	10 ... 30 V DC	PNP	N/O contact	–
					NPN		
	Heat-resistant up to 120°C						
	Inserted in the slot lengthwise, flush with the cylinder profile	Magnetic reed	SME-8-...S6	0 ... 30 V AC/DC	Contacting, bipolar	N/O contact	–
With accessories	Magnetic reed	SME0-8E-...S6	0 ... 30 V DC	Contacting	N/O contact	–	
			0 ... 30 V AC				
To EU Explosion Protection Directive (ATEX)							
Inserted in the slot from above, screw-clamped	Magneto-resistive	SDBT-MS-...-EX6	8.2 V DC	NAMUR	NAMUR	12	

Product range overview

Design	Type of mounting	Measuring principle	Type	Operating voltage range	Switching output	Switching element function	→ Page
For C-slot	Standard						
	Inserted in the slot from above, flush with the cylinder profile	Magneto-resistive	SMT-10M	10 ... 30 V DC	PNP	N/O contact	C-slot
					NPN		
					Non-contacting, 2-wire		
	Insertable in the slot lengthwise	Magnetic reed	SME-10M	5 ... 30 V AC/DC	Contacting, bipolar	N/O contact	
		Magneto-resistive	SMT-10G	10 ... 30 V DC	PNP	N/O contact	
		Magnetic reed	SME-10	12 ... 27 V AC/DC	Contacting	N/O contact	

Peripherals overview



Peripherals overview

Mounting attachments and accessories			→ Page	Mounting attachments and accessories			→ Page
Proximity switches				Mounting kits and accessories			
[1]	SDBT-MS-...-EX6, with explosion protection		12	[6]	Mounting kit SMBR-8-8/100-S6, heat resistant		15
[2]	SDBT-BSW, welding-field-resistant		7	[8]	Mounting kit SMBR		15
				[9]	Mounting kit CRSMB, corrosion-resistant		16
				[10]	Mounting kit SMB-8-FENG		16
				[12]	Sensor bracket DASP-M4-...		17
				[14]	Mounting kit SMB-8-C		17
				[16]	Sensor tester SM-TEST-1		19
				–	Positioning element SMM-8		18
				–	Clip SMBK-8		19
				–	Inscription label ASLR		19
				–	Safety clip NEAU		19
Connecting cables				Drives			
[3]	NEBU-M...G...		19	[5]	Drives with T-slot		–
[4]	NEBU-M...W...		19	[7]	Round cylinders		–
				[11]	Standards-based cylinders DSBC		–
				[13]	Drives with tie or mounting rod		–
				[15]	Standards-based cylinders DSBF		–

Type codes

001	Series
SDBT	Sensor, position, binary, T series

002	Sensor version
B	Can be inserted in the slot, clamping at rear
M	Can be inserted in the slot

003	Sensor principle
S	Contactless (solid state)

004	Additional features
	None
B	Basic
W	Welding field immune
X	Automatic teach-in and programmable

005	Nominal operating voltage
1	24 V DC
20N	8.2 V DC (Namur)

006	Display
L	LED

007	Digital switching output
NU	3-wire N/O contact, NPN
PU	3-wire N/O contact, PNP
ZN	2-wire, Namur
ZU	2-wire N/O contact

008	Cable characteristic
E	Suitable for energy chains/robot applications
K	Standard/suitable for energy chains
W	Resistant to welding spatter

009	Cable length [m]
0.3	0.3 m
2	2 m
2.5	2.5 m
5	5 m
10	10 m

010	Cable identification
	With label holder
N	Without label holder


011	Electrical connection
LE	Open end
M8	Plug M8, A-coded
M12	Plug M12, A-coded

012	EU certification
	None
EX6	II 1GD

Data sheet – Magneto-resistive




Function

...-PU-...-LE



- Oil-resistant
- Welding-field-resistant,
AC 50 ... 60 Hz, MFDC 1000 Hz
- Resistant to welding spatter
- UV-resistant

...-NU-...-M12

**Note**

- For contactless piston-rod position sensing on Festo pneumatic cylinders, in particular the hinge cylinder DWx for AMI, in low and medium frequency welding installations (50/60 Hz, 1000 Hz) with strong constant or alternating magnetic fields.
- When using the SDBT-BSW on drives other than the DWx series, multiple switching can occur.
- The SDBT-BSW-...-ZU-... (2-wire version for 50/60 Hz AC) can be used on all drives.
- The SDBT-BSW-...-PU/NU-... (3-wire version for 50/60 Hz AC and 1000 Hz MFDC) can be used on the following drives (see table). For drives that are not listed, reliable functioning cannot be guaranteed. The application range should be checked where necessary.

SDBT-BSW-...-PU/NU-... (3-wire version for 50/60 Hz AC and 1000 Hz MFDC)

Drive	Ø	[mm]	8	10	12	16	18	20	25	32	40	50	63	80	100
DW/DWA/DWB			–	–	–	–	–	–	–	–	–	■	■	■	–
ADN			–	–	■	■	–	■	■	■	■	■	–	–	–
ADVU			–	–	■	■	–	■	■	■	■	■	–	–	–
DFM			–	–	■	■	–	■	■	■	■	■	■	–	–
DGC-K			–	–	–	–	■	–	■	–	–	–	–	–	–
DSBC			–	–	–	–	–	–	–	■	■	–	–	–	–
DSBG			–	–	–	–	–	–	–	■	■	■	■	–	■
DSNU			■	■	■	■	–	■	■	■	■	■	–	–	–

General technical data

Design	For T-slot
Based on standard	EN 60947-5-2
Certification	RCM compliance mark c UL us listed (OL)
Special characteristics	Oil-resistant Welding-field-resistant Resistant to welding spatter UV-resistant
Application information	Support / Overview of actuator sensors "The right sensor for the actuator"
Switching characteristics during the welding process	Output signal freezes
CE marking (see declaration of conformity)	To EU EMC Directive To EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
KC mark	KC EMC
Note on materials	Free of copper and PTFE, RoHS-compliant

Input signal/measuring element

Measuring principle	Magneto-resistive
Measured variable	Position
Ambient temperature [°C]	–25 ... +85

Signal processing

Max. speed of travel [m/s]	1
----------------------------	---

Data sheet – Magneto-resistive

Switching output		...-PU-...	...- NU-...	...-ZU-...
Switching element function		N/O contact		
Repetition accuracy	[mm]	0.2		
Switch-on time	[ms]	≤15		
Switch-off time	[ms]	≤25		
Max. switching frequency	[Hz]	25		
Max. output current	[mA]	100		80
Max. output current in mounting kits	[mA]	100		80
Max. switching capacity DC	[W]	2.8		1.9
Max. switching capacity DC in mounting kits	[W]	2.8		1.9
Voltage drop	[V]	< 1.5		< 6
Minimum load current	[mA]	0		2.4
Off-state current	[mA]	< 0.005	< 0.14	< 0.7
Output, additional data				
Short circuit current rating		Yes, pulsed		
Overload protection		Present		
Electronics				
Switching output		PNP		
Rated operating voltage	[V DC]	24		
Operating voltage range	[V DC]	10 ... 30		
Reverse polarity protection		For all electrical connections		
Electromechanics				
		...-PU/ NU-...-M12	...-PU/ NU-...-LE	...-ZU-...-LE
Electrical connection				
Connection type		Cable with plug	Cable	Cable
Connection technology		M12x1, A-coded to EN 61076-2-101	Open end	Open end
Number of pins/wires		3	3	2
Type of mounting		Screw-type lock	–	–
Outlet direction of connection		In-line		
Cable characteristic		Resistant to welding spatter		
Cable test conditions		Test conditions on request		

Data sheet – Magneto-resistive

Mechanics		...-PU/ NU-...-M12	...-PU/ NU-...-LE	...-ZU-...-LE
Type of mounting		Screw-clamped, inserted in the slot from above		
Mounting position		Any		
Max. tightening torque	[Nm]	0.6		
Information on materials				
Housing		Epoxy resin, high-alloy stainless steel, PA reinforced, black		
Union nut		Nickel-plated brass	–	–
Cable sheath		PVC, irradiated grey		
Insulating sheath		PVC		
Plug housing		TPE-U(PU)	–	–
Wire ends		–	Wire end sleeve	Wire end sleeve
Pin contacts		Nickel-plated and gold-plated brass	–	–


Display/operation	
Switching status indication	Yellow LED
Function reserve indication	Orange LED

Immission/emission	
Ambient temperature with flexible cable installation	[°C] –5 ... +80
Degree of protection	IP65 IP68
Inductive protective circuit	Adapted to MZ, MY, ME coils
Immunity to interference from magnetic fields	Design insensitive to permanent magnetic fields < Bon
	[ZU] Insensitive to alternating magnetic fields (50 ... 60 Hz) < 160 mT
	[PU/NU] Insensitive to MFDC magnetic fields (1000 Hz) < 200 mT Insensitive to alternating magnetic fields (50 ... 60 Hz) < 200 mT

Pin allocation to EN 60947-5-2			
M12x1, 3-pin			
N/O contact			
	Pin	Wire colour	Allocation
	1	Brown	+
	3	Blue	–
	4	Black	Output


Data sheet – Magneto-resistive

Dimensions, open end Download CAD data → www.festo.com



Type	B1	B2	D1 Ø	H1	H2	H3	L1	L2	L3	L4	L5
SDBT-BSW-1L-PU-W-5-N-LE	8.5	3.5	4	14.5	10.5	6	5000	50	34	10	7
SDBT-BSW-1L-ZU-W-5-N-LE											
SDBT-BSW-1L-NU-W-5-N-LE											

Dimensions with plug Download CAD data → www.festo.com



Type	B1	B2	D1 Ø	D2	D3 Ø	H1	H2	H3	L1	L2	L3	L4
SDBT-BSW-1L-PU-W-0,3-N-M12	8.5	3.5	4	M12	15	14.5	10.5	6	300	54.5	34	10
SDBT-BSW-1L-NU-W-0,3-N-M12												



Data sheet – Magneto-resistive

Ordering data					
	Switching output	Cable length	Weight	Part no.	Type
		[m]	[g]		
N/O contact					
	3-wire, NPN	0.3	23.3	2427615	SDBT-BSW-1L-NU-W-0.3-N-M12
	3-wire, PNP	5	119.4	2427616	SDBT-BSW-1L-PU-W-5-N-LE
	3-wire, NPN	5	119.4	2427618	SDBT-BSW-1L-NU-W-5-N-LE
	3-wire, PNP	0.3	23.3	2476855	SDBT-BSW-1L-PU-W-0.3-N-M12
	2-wire, contactless	5	116.9	2427617	SDBT-BSW-1L-ZU-W-5-N-LE

Data sheet – Magneto-resistive

Function

• ATEX 1GD



General technical data

Design	For T-slot
Based on standard	EN 60947-5-6
Certification	RCM compliance mark
Special characteristics	Oil-resistant
Max. input voltage U_i	[V] 28
Max. input current I_i	[A] 0.25
Max. input power P_i	[mW] T4: 350 mW T6: 72 mW
Effective internal inductance L_i	[μH] 30
Effective internal capacitance C_i	[nF] 79
Certificate issuing authority	PTZ 16 ATEX 0010 X IECEX PTZ 18.0008X DNV 17.0027 X GYJ20.1106X 21-AV4BO-0130X 21-AV4BO-0131X
CE marking (see declaration of conformity)	To EU EMC Directive To EU Explosion Protection Directive (ATEX) To EU RoHS Directive
KC mark	KC EMC

Input signal/measuring element

Measured variable	Position
Measuring principle	Magneto-resistive
Ambient temperature	[°C] -40 ... +85
Ambient temperature with flexible cable installation	[°C] -20 ... +85

ATEX

ATEX category for gas	II 1G
Type of ignition protection for gas	Ex ia IICT 4 ... T6 Ga
ATEX category for dust	II 1D
Type of ignition protection for dust	Ex ia IIIC T135°C Da
Explosion-proof ambient temperature	T4, with fixed cable installation: -40°C ≤ Ta ≤ +85°C T4: -20°C ≤ Ta ≤ +85°C T6, with fixed cable installation: -40°C ≤ Ta ≤ +45°C T6: -20°C ≤ Ta ≤ +45°C
Explosion protection certification outside the EU	EPL Da (BR) EPL Da (CN) EPL Da (IEC-EX) EPL Da (KR) EPL Ga (BR) EPL Ga (CN) EPL Ga (IEC-EX) EPL Ga (KR)


Data sheet – Magneto-resistive

Materials		
Housing	High-alloy stainless steel	
	PA reinforced, black	
Cable sheath	TPE-U(PUR), blue	
Insulating sheath	PP	
Note on materials	Free of copper and PTFE	
	RoHS-compliant	
	Halogen-free	
PWIS conformity	VDMA24364-B2-L	
Switching output		
Switching element function	NAMUR	
Repetition accuracy	[mm]	0.2
Switch-on time	[ms]	< 1
Switch-off time	[ms]	< 1
Max. switching frequency	[Hz]	330
Off-state current	[mA]	0.4 ... 1
Electronics		
Rated operating voltage	[V DC]	8.2
Operating voltage range	[V DC]	7.5 ... 18
Residual ripple	[%]	10
Reverse polarity protection	For all electrical connections	
Electromechanics		
Electrical connection		
Connection type	Cable	
Connection technology	Open end	
Number of pins/wires	2	
Outlet direction of connection	In-line	
Cable characteristic	Suitable for robot applications and energy chains	
Cable test conditions	Test conditions on request	
	Bending strength according to Festo standard	
Mechanics		
Type of mounting	Screw-clamped	
Mounting position	Any, inserted in slot from above	
Tightening torque	[Nm]	0.1 ... 0.6
Max. tightening torque	[Nm]	0.6
Wire ends	Wire end sleeve	
Display/operation		
Switching status indication	Yellow LED	
Immission/emission		
Degree of protection	IP65	
	IP68	

Data sheet – Magneto-resistive

Dimensions, open end

Download CAD data → www.festo.com




Type	B1	D1 ø	H1	L1	L2 ±5	L3	L4	≈ 1
SDBT-MS-20NL-ZN-E-2.5-LE-EX6	5.1	2.9	4.6	2500	50	34.8	31.8	1.5
SDBT-MS-20NL-ZN-E-5-LE-EX6				5000				
SDBT-MS-20NL-ZN-E-10-LE-EX6				10000				
SDBT-MS-20NL-ZN-E-20-LE-EX6				20000				

Ordering data		Cable length	Weight	Part no.	Type
Switching output		[m]	[g]		
N/O contact					
	2-wire, NAMUR	2.5	28	8185110	SDBT-MS-20NL-ZN-E-2.5-LE-EX6
		5	53	579071	SDBT-MS-20NL-ZN-E-5-LE-EX6
		10	104	579072	SDBT-MS-20NL-ZN-E-10-LE-EX6
		20	206	8185111	SDBT-MS-20NL-ZN-E-20-LE-EX6

Accessories

Mounting kit SMBR-8-8/100-S6

Material:
Rail: Anodised wrought aluminium alloy
Clamping strap, screws: High-alloy stainless steel
Free of copper and PTFE
RoHS-compliant




Dimensions and ordering data											Part no.	Type
For piston Ø	B1	B2	D1	H1	L1	L2	L3	≈ 1	CRC ¹⁾			
8 ... 100	27.4	0.2	M3	22.4	34	10	7.9	2.5	4	★ 538937		SMBR-8-8/100-S6

1) Corrosion resistance class CRC 4 to Festo standard FN 940070

Particularly high corrosion stress. Outdoor exposure under extreme corrosive conditions. Parts exposed to aggressive media, e.g. in the chemical or food industries. Such applications may need to be safeguarded by means of special testing (→ also FN 940082), using appropriate media.

Mounting kit SMBR

Material:
Polyacetal
RoHS-compliant




Dimensions and ordering data							
For piston Ø	B1	B2	H1	L2	L3	Part no.	Type
8	18.9	12.3	17.5	19	7	175091	SMBR-8-8
10	20.4	13.7	19.9	19	7	175092	SMBR-8-10
12	22.7	14.3	21.9	19	7	★ 175093	SMBR-8-12
16	28.2	16.9	25.7	19	8	★ 175094	SMBR-8-16
20	34.5	20.8	30.4	19	9	★ 175095	SMBR-8-20
25	36.7	22.7	35.6	19	9	★ 175096	SMBR-8-25
32	41.7	24.6	42.7	19	9	175097	SMBR-8-32
40	47.1	26.5	50.7	19	9	175098	SMBR-8-40
50	56.4	28.6	61.5	19	9	175099	SMBR-8-50
63	69.4	32	74.5	19	9	175100	SMBR-8-63

Accessories

Mounting kit CRSMB

Design: for round cylinders
Type of mounting: any
Type of mounting: glued
Degree of protection: IP65, IP68, IP69K
Ambient temperature: -40 ... +90°C
Material:
Housing: anodised aluminium,
TPE-U(PU)
Free of copper and PTFE
RoHS-compliant
PWIS conformity:
VDMA24364-B2-L





Ordering data							
For piston Ø	B1	B2	H1	L1	CRC ¹⁾	Part no.	Type
32 ... 100	15.8	11.8	9.3	35	4	525565	CRSMB-8-32/100

1) Corrosion resistance class CRC 4 to Festo standard FN 940070
Particularly high corrosion stress. Outdoor exposure under extreme corrosive conditions, e.g. in the chemical or food industries. Such applications may need to be safeguarded by means of special testing (→ also FN 940082), using appropriate media.

Mounting kit
SMB-8-FENG

Material:
Wrought aluminium alloy
Free of copper and PTFE



[1] Threaded pin

Dimensions and ordering data									
For piston Ø	B1	B2	D1	H1	L1	L2	Tightening torque [Nm]	Part no.	Type
32/40	35.1	8.7	M3	15.5	27	17	0.2	175705	SMB-8-FENG-32/40
50/63	47	12.3	M4	20	27	17	0.5	175706	SMB-8-FENG-50/63
80/100	64.3	15.7	M5	24.3	27	17	0.7	175707	SMB-8-FENG-80/100

Accessories

Mounting kit SMB-8-C

Temperature: -40 ... 120°C


Material:

Retaining bracket: Anodised wrought aluminium alloy

Screws: High-alloy stainless steel

Free of copper and PTFE,

RoHS-compliant



Dimensions and ordering data												
Type	B1	B2	B3	D1	H1	L1	±G 1	Tightening torque [Nm]	CRC ¹⁾	Weight [g]	Part no.	Type
SMB-8-C	17	7	5.5	M3	7.8	20	1.5	0.2 ... 0.6	3	3.5	1806790	SMB-8-C

1) Corrosion resistance class CRC 3 to Festo standard FN 940070

High corrosion stress. Outdoor exposure under moderate corrosive conditions. Externally visible parts with primarily functional surface requirements which are in direct contact with a normal industrial environment.


Sensor bracket DASP-M4-...-A

Material:

Anodised wrought aluminium alloy

Screws: High-alloy stainless steel

RoHS-compliant



Dimensions and ordering data										
Type	B1	D1	H1	L1	±G 1	Tightening torque [Nm]	CRC ¹⁾	Weight [g]	Part no.	Type
DASP-M4-125-A	32.5	M5	28	45.4	2.5	1	3	26.5	1451483	DASP-M4-125-A
DASP-M4-160-A	32.5	M6	44.7	69.4	3	1	3	41.5	1553813	DASP-M4-160-A
DASP-M4-250-A	32.5	M6	56.3	88	3	1	3	60	1456781	DASP-M4-250-A
DASP-M4-320-A	32.5	M6	56.3	88	3	1	3	60	3015256	DASP-M4-320-A

1) Corrosion resistance class CRC 3 to Festo standard FN 940070


High corrosion stress. Outdoor exposure under moderate corrosive conditions. Externally visible parts with primarily functional surface requirements which are in direct contact with a normal industrial environment.

Accessories

Positioning element SMM
Insertable in the slot lengthwise

Ambient temperature: -40 ... +120°C

Materials:
Housing: Anodised wrought aluminium alloy
Screws: High-alloy stainless steel
Note on materials: RoHS-compliant



Dimensions and ordering data								
B1	H1	H2	L1	⌀G1	CRC ¹⁾	Part no.	Type	PU ²⁾
6.3	5.0	4.0	4.0	1.5	3	547941	SMM-8	10

1) Corrosion resistance class CRC 3 to Festo standard FN 940070
High corrosion stress. Outdoor exposure under moderate corrosive conditions. Externally visible parts with primarily functional surface requirements which are in direct contact with a normal industrial environment.

2) Packaging unit

Accessories

Ordering data – Connecting cables

Number of wires

Cable length [m]

Part no.

Type

Data sheets → Internet: nebu/sim

Socket M8x1, 3-pin					
	For SMT/SME-8... and SMT0/SMTSO/SME0-8E	3	2.5	★ 541333	NEBU-M8G3-K-2.5-LE3
			5	★ 541334	NEBU-M8G3-K-5-LE3
	For SMT/SME-8... and SMT0/SMTSO/SME0-8E	3	2.5	★ 541338	NEBU-M8W3-K-2.5-LE3
			5	★ 541341	NEBU-M8W3-K-5-LE3
Socket M12x1, 5-pin					
	For SMT/SME-8M and SMT0/SMTSO/SME0-8E	3	2.5	★ 541363	NEBU-M12G5-K-2.5-LE3
			5	★ 541364	NEBU-M12G5-K-5-LE3
	For SMT/SME-8M and SMT0/SMTSO/SME0-8E	3	2.5	541367	NEBU-M12W5-K-2.5-LE3
			5	541370	NEBU-M12W5-K-5-LE3

Ordering data – Safety clip for ATEX zone

Size

Description

Part no.

Type

PU¹⁾

	M8	- Protects "equipment that is not intrinsically safe" in zones 2 and 22 against simple disconnection - ATEX category: gas: II 3G / dust: II 3D	548067	NEAU-M8-GD	1
	M12		548068	NEAU-M12-GD	1

1) Packaging unit

Ordering data – Mounting components

Description

Part no.

Type

	For fixing connecting cables in place	534254	SMBK-8
--	---------------------------------------	--------	--------

Ordering data – Sensor tester

Description

Part no.

Type

	- Testing the functionality of proximity switches using the integrated voltage supply - Adjusting proximity switches on the cylinder	158481	SM-TEST-1
---	---	--------	-----------

Ordering data – Inscription labels

Size

Part no.

Type

PU¹⁾

	23x4 mm	541598	ASLR-L-423	34
---	---------	--------	------------	----

1) Packaging unit