

Swivel/gripper units HGDS



Swivel/gripper units HGDS


Key features

At a glance

Combination of parallel gripper and swivel module

The power transmission from the linear motion to the gripper motion takes place via the piston rod, which opens and closes the gripper jaws housed in the gripper housing via 2 reversing levers.


The swivel motion takes place via a swivel drive. It can be adjusted almost infinitely via 2 stops (max. 210°). The rotary motion is cushioned either via a flexible cushioning buffer or a hydraulic shock absorber. The swivel angle can be finely adjusted by means of a precision adjustment facility.




- 1 Flexible cushioning or hydraulic shock absorbers
- 2 Slot for proximity sensor SME/SMT-10 for sensing the swivel position
- 3 Gripper compressed air connection, closing
- 4 Slot for proximity sensor SME/SMT-10 for sensing the gripper position
- 5 Gripper compressed air connection, opening
- 6 Gripper jaw
- 7 Adjustable stop plates for the swivel motion, with magnet
- 8 Precise end stop with flexible cushioning or integrated shock absorber
- 9 Rotary vane
- 10 Piston rod for gripping motion
- 11 Piston with magnet

Mounting options


Direct mounting




Dovetail connection




 Note
Swivel/gripper units are not suitable for the following or similar applications:



- Machining
- Aggressive media



- Grinding dust





- Welding spatter

Swivel/gripper units HGDS

Peripherals overview and type codes

Peripherals overview

System product for handling and assembly technology



Accessories			
Type	Brief description	→ Page/Internet	
1	Cushioning P	Non-adjustable, flexible cushioning. Is used for smaller loads	-
2	Cushioning YSRT	Self-adjusting, hydraulic shock absorber	-
3	Proximity sensor SME/SMT-10	For sensing the gripper and rotary vane position	12
4	Push-in fitting QS	For connecting compressed air tubing with standard external diameters	quick star
5	Centring sleeve ZBH	For centring the gripper when mounting (2 included in scope of delivery)	12
6	-	Drive/gripper connections	adapter kit

Type codes

HGDS		-	PP		-	16		-	YSRT		-	A	
Type													
HGDS		Swivel/gripper unit											
Gripper function													
PP		Parallel gripping											
Size													
Cushioning													
P		Flexible cushioning											
YSRT		Hydraulic cushioning											
Position sensing													
A		For proximity sensing											


Swivel/gripper units HGDS

Technical data

FESTO

Function

Swivelling/Gripping



- N- Size
12, 16, 20
- T- Stroke
5, 9, 14 mm

General technical data			
Size	12	16	20
Design	Semi-rotary drive Parallel gripper with drive		
Mode of operation	Double-acting		
Pneumatic connection	M5		
Type of mounting	With threaded hole and centring hole Via through-holes Clamped in dovetail slot		
Fitting position	Any		
Relubrication intervals of guide	10 million switching cycles		
Product weight [g]	465	660	1120

Operating and environmental conditions	
Operating pressure [bar]	3 ... 8
Operating medium	Filtered compressed air, lubricated or unlubricated
Ambient temperature ¹⁾ [°C]	+5 ... +60
Corrosion resistance class CRC ²⁾	2


1) Note operating range of proximity sensors

2) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents

Materials

Sectional view



Swivel/gripper unit	
1	Gripper jaw Wrought aluminium alloy, nickel-plated
2	Lever Hardened steel
3	Stop Wrought aluminium alloy, hard-anodised
4	Piston rod Stainless steel
5	Housing Wrought aluminium alloy, hard-anodised
6	Piston Nitrile rubber, polyurethane
-	Rubber buffer Nitrile rubber

Swivel/gripper units HGDS







Technical data

Technical data – Swivelling

Size	12	16	20
Swivel angle	[°] 0 ... 210 → 10		
Theoretical torque ¹⁾	[Nm] 0.85	1.25	2.5
Repetition accuracy ¹⁾	P cushioning	[°] < 0.2	
	YSRT cushioning	[°] < 0.02	
Cushioning	→ 6		
Max. swivelling frequency ¹⁾	P cushioning	[Hz] 2	
	YSRT cushioning	[Hz] 1.5	
Position sensing	For proximity sensing		

1) At 6 bar

Mass moments of inertia J at 6 bar as a function of swivel time t and swivel angle




Dependency between operating pressure and swivel time

When the operating pressure of the gripper drive is reduced, the permissible swivel time at the same mass moment of inertia must be increased by 15% per bar of operating pressure.

Example:
 Given:
 $J = 40 \text{ kgm}^2 \times 10^{-4}$
 Operating pressure 4 bar (gripper drive)

Swivel time at 6 bar = 0.4 s, see graph opposite
 This yields a swivel time at 4 bar:
 $t = 0.4 + 2 \times 15\% = 0.52 \text{ s}$
 Cushioning time of the shock absorber = 0.1 s
 This yields a swivel time of
 $t_{\text{tot.}} = 0.52 \text{ s} + 0.1 \text{ s} = 0.62 \text{ s}$



Swivel/gripper units HGDS

Technical data


Precision adjustment of the swivel angle

The swivel angle can be adjusted roughly by means of two stop plates → 2. The precision adjustment works as follows:


Variants P and YSRT differ in only one component. The retainer and the fine

adjustment are identical. In both variants, the rotary vane travels to a metallic stop, which can be adjusted with great accuracy via the adjustable sleeve for P cushioning or the shock absorber for YSRT cushioning.

- 1) Loosen the locking screw underneath the cushioning element




- 2) Adjust the cushioning element as required. Observe the minimum and maximum settings.




Size	12	16	20	
Precision adjustment range	P cushioning [°]	-6		
	YSRT cushioning [°]	-2.5		
Swivel angle adjuster per revolution	[°]	3.1	2.8	2.2

Min. setting range, to the inner stop



Max. setting range, to the notch



Swivel/gripper units HGDS

Technical data

FESTO

Technical data – Gripping

Size	12	16	20
Gripper function	Parallel		
Number of gripper fingers	2		
Max. weight force per external gripper finger ¹⁾ [N]	0.3	0.5	1.0
Stroke per gripper jaw [mm]	2.5	4.5	7
Max. gripper jaw backlash [mm]	0		
Max. gripper jaw angular backlash [°]	0		
Repetition accuracy [mm]	< 0.02		
Max. operating frequency [Hz]	4		
Position sensing	Via proximity sensor		


1) Valid for unthrottled operation

Gripping force [N] at 6 bar

Size	12	16	20
Gripping force per gripper jaw			
Opening	29	56.5	85
Closing	26	45	65
Total gripping force			
Opening	58	113	170
Closing	52	90	130

Gripping force F_{Grip} per gripper jaw as a function of operating pressure p

Gripping forces related to operating pressure and lever arm can be determined for the various sizes using the following graphs. The characteristic curves apply for external and internal gripping.




Note


The gripping force is practically independent of the lever arm. Fluctuation at max. lever arm and max. operating pressure approx. 10%.

for unthrottled operation:


HGDS-12 (max. lever arm x 40 mm)



HGDS-16 (max. lever arm x 50 mm)



HGDS-20 (max. lever arm x 70 mm)



— Opening
 - - - - - Closing

Swivel/gripper units HGDS



Technical data



Opening and closing times [ms] at 6 bar

With gripper jaws

With additional gripper fingers



The indicated opening and closing times [ms] have been measured at room temperature and at 6 bar operating pressure with horizontally mounted gripper without external

gripper fingers. The grippers must be throttled for greater applied loads. Opening and closing times must then be adjusted correspondingly.


with additional gripper fingers as a function of weight force

Size	12	16	20	
Max. weight force	0.3 N	0.5 N	1.0 N	
HGDS-...-A unthrottled	Opening	20	50	70
	Closing	30	50	100

with additional gripper fingers as a function of weight force

Size	12		16		20			
	1.0 N	2.0 N	1.0 N	2.0 N	1.0 N	2.0 N		
HGDS-...-A throttled	Closing		100	150	100	200	100	250

Eccentricity y as a function of lever arm x



The dependency on the lever arm and the maximum permissible off-centre point of force application can be determined for the various sizes using the following graphs.

The gripping forces apply, see above.

It is vital that you adhere to the mass moment of inertia $\rightarrow 5$ when making your selection.


Calculation example

Lever arm $x = 40$ mm

To be found: Eccentricity y

- Move along the horizontal axis to the point of intersection
- Then move vertically downwards until you intersect the scale
- Read the eccentricity

Max. eccentricity = 30 mm




Swivel/gripper units HGDS

Technical data


Eccentricity y as a function of lever arm x

for unthrottled operation:


HGDS-12 (max. lever arm 40 mm)




HGDS-16 (max. lever arm 50 mm)



HGDS-20 (max. lever arm 70 mm)



Characteristic load values per gripper jaw



The indicated permissible forces and torques refer to a single gripper jaw. The indicated values include the lever arm, additional applied loads caused by the workpiece or external gripper fingers, as well as forces which occur during movement.

The zero coordinate line (gripper finger guide) must be taken into consideration for the calculation of torques.

Size		12	16	20
Max. permissible force F_z	[N]	20	30	60
Max. permissible torque M_x	[Nm]	1.5	4	8
Max. permissible torque M_y	[Nm]	1.5	4	8
Max. permissible torque M_z	[Nm]	1.5	4	8


Swivel/gripper units HGDS

Technical data


FESTO

Dimensions

Download CAD Data → www.festo.com/us/cad



Swivel angle




Swivel/gripper units HGDS


Technical data

Cross-section at 1 → 10


Size 12



Size 16



Size 20



Size	B1	B2	B3	B4	B5	B6	B7	D1	D2	D3	D4	D5
[mm]		±0.03	±0.02*		±0.02	±0.02	±0.1		∅ H13	∅ H13		∅ H8
12	30	48	20	11.5	8	8	12.5	M6x0.5	4.5	7.5	M3	2
16	34	55	30	13	10	10	16	M8x1	-	-	M3	2
20	40	68	30	16	12	12	20	M10x1	-	-	M4	2.5

Size	D6	EE	H1	H2	H3	H4	H5	H6	H7	H8	H9
[mm]	∅ H8		+1/-0.6	+0.8/-0.4	+1.3/-0.2	+0.8/-0.2	±0.02	±0.12	±0.1	±0.1	
12	2	M5	113.4	111.9	85.1	58.2	2	5	30	23	7.5
16	2	M5	121.7	120.1	92.1	64.3	3	5	34.5	26	8.3
20	2.5	M5	154.8	152.8	112.3	81.7	3	7	43	34.6	8.3

Size	H10	H11	H12	H13	H14	L1	L2	L3	L4	L5	L6
[mm]		-0.1		+1/-0.2	+1/-0.2	±0.5	±0.5	±0.5	±0.1		±0.05
12	13.5	9.7	4.5	51.3	79.8	46	41	38	34	36	24
16	14	8	-	58.2	86.7	58	49	47	-	40.5	27.5
20	19	9	-	73.1	105.6	78	64	61	-	40.5	34


Size	L7	L8		L9	L10	T1	T4	T5	T6	T7
[mm]	±0.03	±1		±0.02			min.			min.
		P	YSRT							
12	48	59.5	69.3	8	10	4.6	5	5	4	5
16	55	68.5	80.5	8	10	-	6.5	6	5	5
20	68	85.4	96.4	12	14	-	10	8	7	7

* Tolerance valid for centring hole ∅ 9^{H7}

Swivel/gripper units HGDS

Technical data and accessories

FESTO

Ordering data					
	Size [mm]	With flexible P cushioning Cushioning element		With hydraulic YSRT cushioning Shock absorber	
		Part No.	Type	Part No.	Type
	12	534 278	HGDS-PP-12-P-A ¹⁾	534 279	HGDS-PP-12-YSRT-A ¹⁾
	16	534 280	HGDS-PP-16-P-A ¹⁾	534 281	HGDS-PP-16-YSRT-A ¹⁾
	20	534 282	HGDS-PP-20-P-A ¹⁾	534 283	HGDS-PP-20-YSRT-A ¹⁾

1) Two centring sleeves are included in the scope of delivery

Ordering data – Accessories					Technical data → Internet: zbh	
	For size [mm]	Weight [g]	Part No.	Type	PU ¹⁾	
Centring sleeve						
	12, 16, 20	1	150 927	ZBH-9	10	

1) Packaging unit quantity

Ordering data – Proximity sensors for C-slot, magneto-resistive						Technical data → Internet: smt	
	Type of mounting	Switch output	Electrical connection, connection direction	Cable length [m]	Part No.	Type	
N/O contact							
	insertable in the slot from above	PNP	Cable, 3-wire, lateral	2.5	551 374	SMT-10M-PS-24V-E-2,5-Q-OE	
			Plug M8x1, 3-pin, lateral	0.3	551 376	SMT-10M-PS-24V-E-0,3-Q-M8D	

Ordering data – Proximity sensors for C-slot, magnetic reed						Technical data → Internet: sme	
	Type of mounting	Switch output	Electrical connection, connection direction	Cable length [m]	Part No.	Type	
N/O contact							
	insertable in the slot from above	Contacting	Plug M8x1, 3-pin, lateral	0.3	551 368	SME-10M-DS-24V-E-0,3-Q-M8D	
			Cable, 3-wire, lateral	2.5	551 366	SME-10M-DS-24V-E-2,5-Q-OE	

Swivel/gripper units HGDS

Accessories




If the swivel/gripper unit is mounted **on the front**, proximity sensors with the connecting cable **at right angles** should be used.

When proximity sensors with in-line connecting cables are used, the sensors project beyond the swivel/gripper unit after the switching point has been set.

Projection:
 With proximity switch SMT-...:
 HGDS-PP-12: 8,3 mm
 HGDS-PP-16: 7,1 mm
 HGDS-PP-20: 4,4 mm

 With proximity switch SME-...:
 HGDS-PP-12: 2,7 mm
 HGDS-PP-16: 2,1 mm
 HGDS-PP-20: 0 mm



Ordering data – Proximity sensors for C-slot, magneto-resistive					Technical data → Internet: smt	
	Type of mounting	Switch output	Electrical connection, connection direction	Cable length [m]	Part No.	Type
N/O contact						
	Insertable in the slot from above	PNP	Cable, 3-wire, in-line	2.5	551 373	SMT-10M-PS-24V-E-2,5-L-OE
			Plug M8x1, 3-pin, in-line	0.3	551 375	SMT-10M-PS-24V-E-0,3-L-M8D

Ordering data – Proximity sensors for C-slot, magnetic reed					Technical data → Internet: sme	
	Type of mounting	Switch output	Electrical connection, connection direction	Cable length [m]	Part No.	Type
N/O contact						
	Insertable in the slot from above	Contacting	Plug M8x1, 3-pin, in-line	0.3	551 367	SME-10M-DS-24V-E-0,3-L-M8D
			Cable, 3-wire, in-line	2.5	551 365	SME-10M-DS-24V-E-2,5-L-OE
			Cable, 2-wire, in-line	2.5	551 369	SME-10M-ZS-24V-E-2,5-L-OE

Ordering data – Connecting cables				Technical data → Internet: nebu	
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part No.	Type
	Straight socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541 333	NEBU-M8G3-K-2.5-LE3
			5	541 334	NEBU-M8G3-K-5-LE3
	Angled socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541 338	NEBU-M8W3-K-2.5-LE3
			5	541 341	NEBU-M8W3-K-5-LE3

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices


Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Canada

USA Customers:

For ordering assistance,

Call: 1.800.99.FESTO (1.800.993.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO (1.866.463.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com

Canadian Customers:

Call: 1.877.GO.FESTO (1.877.463.3786)

Fax: 1.877.FX.FESTO (1.877.393.3786)

Email: festo.canada@ca.festo.com

USA Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788, USA
www.festo.com/us

USA Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942, USA

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801, USA

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056, USA

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326, USA

New York

395 Moreland Road
Hauppauge, NY 11788, USA

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550, USA

United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788

Phone: 1.631.435.0800; Fax: 1.631.435.8026;

Email: info@festo-usa.com

www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4

Phone: 1.905.624.9000; Fax: 1.905.624.9001;

Email: festo.canada@ca.festo.com

www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,
54020 Tlalneantla, Edo. de México

Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;

Email: festo.mexico@mx.festo.com

www.festo.com/mx

Central USA

Festo Corporation
1441 East Business
Center Drive
Mt. Prospect, IL 60056, USA
Phone: 1.847.759.2600
Fax: 1.847.768.9480



Western USA

Festo Corporation
4935 Southfront Road,
Suite F
Livermore, CA 94550, USA
Phone: 1.925.371.1099
Fax: 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com