
Water separators MS-LWS, MS series

FESTO



MS series service unit components

Key features

FESTO

MS series service unit components

Solutions for every application

With its large product range, highly functional components and a wide choice of services, the MS series from Festo offers a complete concept for compressed air preparation. Suitable for simple standard applications as well as application-specific solutions to the highest quality standards.

Available as individual components, pre-assembled combinations ex-stock, application-specific combinations or complete turnkey solutions. The five sizes in the MS series achieve maximum flow rates with minimum space requirements.

Freely combinable function modules

Pressure regulators, on/off and softstart valves with safety function, filter, pressure and flow sensors, dryers, sensors and lubricators. All these allow a suitable solution to be assembled for every task. Their modular structure means that the components are freely combinable. A simple connection system saves time when replacing individual modules without dismantling the entire combination. What's more, many of the components are certified to UL and ATEX.

CAD models and configurator

Convenient aids for planning and selecting application-specific individual devices and combinations. The product configurator lets you configure customised solutions quickly and transfer the order data with no hassle.

Engineering tools

Selection tool for choosing the right service unit without oversizing, and with the right air quality class:

→ www.festo.com/engineering/wartungseinheit




Integrated sensors Pressure and flow sensors

Safety functions Soft-start/quick exhaust valves MS6-SV/MS9-SV

Energy savings Service units MSE6

Intelligent mix of sizes





- Reliable compressed air preparation and supply for systems
- Integrable or stand-alone
- Easy to connect with M8/M12 plug



- Fast and reliable exhausting of systems up to Performance Level e, certified to EN ISO 13849-1
- Integrated soft-start function



- Fully automatic monitoring and regulation of compressed air supply
- Automatic shut-off of the compressed air in stand-by mode
- Detection and notification of leakages
- Condition monitoring of relevant process data



- Optimum flow rate with up to 18% smaller size
- Excellent energy efficiency
- Cost-optimised combinations save up to 30%!

Size differences						
Size		MS2	MS4	MS6	MS9	MS12
Grid dimension	[mm]	25	40	62	90	124
Port sizes		M5, QS-6	G¹/8, G¹/4, G³/8	G ¹ / ₄ , G ³ / ₈ , G ¹ / ₂ , G ³ / ₄	G½, G¾, G1, G1¼, G1½	G1, G1¼, G1½, G2
Standard nominal flow rate qnN ¹⁾	[l/min]	350	1800	6500	20000	22000

¹⁾ Using pressure regulator MS-LR as an example

MS series service unit components



Key features

Note

Information

The next few pages provide a brief overview of the complete product range for the MS series service unit components.

You can find detailed information and all of the technical data in the documentation for the corresponding service unit component.

Accessories such as connection plates or mounting brackets can be ordered either via the configurator or separately.

Structure of a service unit

The order of the individual components within a service unit is relevant for safety and functionality. It is not possible to assemble the service unit components in any order in the flow direction. There are restrictions and rules.

The configurator for service unit MSB is a reliable and convenient way of arranging individual service unit components. This ensures that the applicable rules are complied with. As a result, you get a completely assembled combination with UL or ATEX certification if you need it. When arranging a combination of individually configured and ordered service unit components, the points on the right must be adhered to under all circumstances.

- Regulators MS-LFR/LR/LRP/LRE are only permissible in the flow direction with the same or decreasing pressure regulation range
- Filters MS-LFR/LF/LFM/LFX are only permissible in the flow direction with an increasing grade of filtration
- Lubricators MS-LOE are not permitted in the flow direction upstream of a filter MS-LFR/LFM/LF/LFX, water separator MS-LWS or membrane air dryer MS-LDM1
- A micro filter MS-LFM must be installed upstream of an activated carbon filter MS-LFX or membrane air dryer MS-LDM1 in the flow direction
- A flow sensor SFAM cannot be installed directly downstream of a regulator MS-LFR/LR; a branching module MS-FRM must be positioned between them
- A soft-start/quick exhaust valve MS-SV must be the last service unit component in the flow direction

Туре	Description	Size	e Pneumatic connection							
			Push-in	Female thread			Connection plate with thread			
			connector	M	G	NPT	G	NPT		
Combination	is									
Service units	MSB-FRC						Technica	l data 🗲 Internet: ms		
. 0.	Combinations of filter regulator	4	-	-	1/8, 1/4	-	-	-		
and it	and lubricator	6	-	-	1/4, 3/8, 1/2	-	-	-		
ervice units	s MSB						Technical	l data 🗲 Internet: ms		
-91	7 combinations, predefined	4	-	 -	1/4	-	_	-		
		6	-	-	1/2	-	_	-		
4										
O del	Combinations freely configurable	4	-	-	1/8, 1/4	-	1/8, 1/4, 3/8	1/8, 1/4, 3/8		
	TU .	6	-	-	1/4, 3/8, 1/2	-	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4		
	Î	9	-	-	3/4, 1	3/4, 1	1/2, 3/4, 1, 11/4, 11/2	1/2, 3/4, 1, 11/4, 11/2		
. III w	7									
Service units		1.		_	1	1		data → Internet: mse		
Labor.	Combinations with fieldbus con-	6	-	-	-	-	1/2	-		
(ATE	nection for measuring pressure,									
	flow rate and consumption									

MS series service unit componentsKey features



Гуре	Description	Size	Pneumatic	connection					
			Push-in	Female thread			Connection plate with thread		
			connector	M	G	NPT	G	NPT	
ndividual de									
ilter regulat	ors MS-LFR		-				Technical o	lata → Internet: ms-l	
	Filter and pressure regulator in a	2	QS-6	M5	-	-	-	-	
1671	single device,	4	-	-	1/8, 1/4	-	1/8, 1/4, 3/8	1/8, 1/4, 3/8	
- 10	grade of filtration 5 or 40 µm	6	-	-	1/4, 3/8, 1/2	-	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4	
- 110		9	-	-	3/4, 1	3/4, 1	1/2, 3/4, 1, 11/4, 11/2	1/2, 3/4, 1, 11/4, 11/	
Ψ		12	-	-	-	-	1, 11/4, 11/2, 2	-	
ilters MS-LI	•						Tochnical	data → Internet: ms	
illeis M3-Li	Grade of filtration 5 or 40 µm	4			1/8, 1/4		1/8, 1/4, 3/8	1/8, 1/4, 3/8	
1	Grade of Illitation 5 of 40 µm	4	_	-		_			
-		6		-	1/4, 3/8, 1/2	-	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4	
		9		-	3/4, 1	3/4, 1	1/2, 3/4, 1, 11/4, 11/2	1/2, 3/4, 1, 11/4, 11/	
		12	_	-	_	-	1, 11/4, 11/2, 2	_	
ine and mic	ro filters MS-LFM							ata → Internet: ms-lí	
0	Grade of filtration 0.01 or 1 μm	4	-	-	1/8, 1/4	-	1/8, 1/4, 3/8	1/8, 1/4, 3/8	
<u> </u>		6	-	-	1/4, 3/8, 1/2	-	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4	
10		9	-	-	3/4, 1	3/4, 1	1/2, 3/4, 1, 11/4, 11/2	1/2, 3/4, 1, 11/4, 11/	
- 10		12	-	-	-	-	1, 11/4, 11/2, 2	-	
ctivated ca	rbon filters MS-LFX						Technical c	ata → Internet: ms-	
-	For removing liquid and gaseous	4	T_	T_	1/8, 1/4	_	1/8, 1/4, 3/8	1/8, 1/4, 3/8	
3	oil particles	6	_	_	1/4, 3/8, 1/2	_	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4	
1	5.1. p.s	9	_	_	3/4, 1	3/4, 1	1/2, 3/4, 1, 11/4, 11/2	1/2, 3/4, 1, 11/4, 11/	
ų.		12		_	-	-	1, 11/4, 11/2, 2	-	
			•		1		<u>'</u>	-	
Vater separa	ators MS-LWS						Technical da	ata → Internet: ms-lv	
Bio.	Remove condensed water from	6	-	-	1/4, 3/8, 1/2	-	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4	
	compressed air, maintenance-free	9	-	-	3/4, 1	3/4, 1	1/2, 3/4, 1, 11/4, 11/2	1/2, 3/4, 1, 11/4, 11/	
- 111		12	-	-	-	-	1, 11/4, 11/2, 2	_	
- 4			'	*	1	•	·		

MS series service unit components Key features



		Size	Pneumatic connection					
			Push-in	Female thread			Connection plate wit	h thread
			connector	M	G	NPT	G	NPT
dividual de	vices							
ressure regu	ılators MS-LR						Technical	data 🗲 Internet: ms
-	For setting the required operating	2	QS-6	M5	-	-	-	_
	pressure,	4	-	-	1/8, 1/4	-	1/8, 1/4, 3/8	1/8, 1/4, 3/8
51 B	4 pressure regulation ranges	6	-	-	1/4, 3/8, 1/2	-	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
40		9	-	-	3/4, 1	3/4, 1	1/2, 3/4, 1, 11/4, 11/2	1/2, 3/4, 1, 11/4, 11/4
		12		-		-	1, 11/4, 11/2, 2	-
occuro rogi	ulators MS-LRB						Tochnical d	ata → Internet: ms-
essure regu	For creating a regulator manifold	4	_	1_	1/4	1-	1/8, 1/4, 3/8	
- 68	with independent pressure regula-	6		-	1/2	_	1/4, 3/8, 1/2, 3/4	_
100		О	-	_	*/2	_	1/4, 3/8, 1/2, 3/4	-
AND D	tion ranges. Pressure output is to the front or rear.							
	the none of real.							
ecision pre	ssure regulators MS-LRP							ata → Internet: ms-
	For precise setting of the required	6	-	-	1/4, 3/8, 1/2	-	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
	operating pressure,							
100	4 pressure regulation ranges,							
	pressure hysteresis 0.02 bar							
ecision pre	ssure regulators MS-LRPB						Technical da	ta → Internet: ms-lr
	For configuring a regulator	6	T-	T_	1/2	T_	1/4, 3/8, 1/2, 3/4	-
	manifold with independent				/		74, 70, 72, 74	
	pressure regulation ranges.							
90	Pressure output is to the front or							
	rear.							
ectrical pres	ssure regulators MS-LRE							ata → Internet: ms-
	Electrically adjustable pressure	6	-	-	1/4, 3/8, 1/2	-	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
	regulator,							
	4 pressure regulation ranges							
-								
bricators N	IS-LOE						Technical d	ata → Internet: ms-l
	Add a precisely adjustable amount	4	-	-	1/8, 1/4	-	1/8, 1/4, 3/8	1/8, 1/4, 3/8
400	of oil to the compressed air. The oil		_	_		_	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
N)					3/4, 1	3/4, 1	1/2, 3/4, 1, 11/4, 11/2	1/2, 3/4, 1, 11/4, 11/4
	mist component is proportional to	9	_	_	74.1	74, 1	72, 74, 1, 174, 172	1/2, 7/4, 1. 1 1/4, 1 1
ubricators M	Add a precisely adjustable amount	6	-	-	1/4, 3/8, 1/2	-	1/8, 1/4, 3/8 1/4, 3/8, 1/2	3, 3/4

MS series service unit componentsKey features



Туре	range for MS series service unit compor Description	Size	Pneumatic	connectio	n			
-,,,-			Push-in	Female thread			Connection plate wit	h thread
			connector	M	G	NPT	G	NPT
Individual dev	rices							
On/off valves							Technical d	ata → Internet: ms-em
-	Manually operated on/off valve for	4	T -	_	1/8, 1/4	-	1/8, 1/4, 3/8	1/8, 1/4, 3/8
- 4	pressurising and exhausting	6	_	_	1/4, 3/8, 1/2	_	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
9	pneumatic installations.	9	_	_	3/4, 1	3/4, 1	1/2, 3/4, 1, 11/4, 11/2	1/2, 3/4, 1, 11/4, 11/2
	·	12	-	-	-	-	1, 11/4, 11/2, 2	_
On/off valves	MS-EE						Technical c	lata → Internet: ms-ee
	Solenoid actuated on/off valve for	4	-	-	1/8, 1/4	-	1/8, 1/4, 3/8	1/8, 1/4, 3/8
	pressurising and exhausting	6	-	-	1/4, 3/8, 1/2	-	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
2	pneumatic installations.	9	-	-	3/4, 1	3/4, 1	1/2, 3/4, 1, 11/4, 11/2	1/2, 3/4, 1, 11/4, 11/2
•		12		-	-	-	1, 11/4, 11/2, 2	-
Soft-start val	ves MS-DL						Technical o	data → Internet: ms-d
-	Pneumatically actuated soft-start	4	_	_	1/8, 1/4	-	1/8, 1/4, 3/8	1/8, 1/4, 3/8
	valve for slowly pressurising and	6	_	_	1/4, 3/8, 1/2	-	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
	exhausting pneumatic	12	_	_	-	-	1, 11/4, 11/2, 2	-
	installations.							•
	No DE						-	
Soft-start valv					1/ 1/	T		lata → Internet: ms-de
•	Solenoid actuated soft-start valve	4	-	-	1/8, 1/4	-	1/8, 1/4, 3/8	1/8, 1/4, 3/8
100	for slowly pressurising and	6	-	-	1/4, 3/8, 1/2	-	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
40	exhausting pneumatic installations.	12	-	-		-	1, 11/4, 11/2, 2	_
Soft-start/qui	ck exhaust valves MS-SV						Technical o	data → Internet: ms-sv
	For building up pressure gradually	6	-	_	1/2	-	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
	and reducing pressure quickly	9	-	_	3/4, 1	3/4, 1	1/2, 3/4, 1, 11/4, 11/2	1/2, 3/4, 1, 11/4, 11/2
<u> </u>	and safely in pneumatic piping							
- 11	systems.							
U	Up to category 1, PL c.							
9	Up to category 3, PL d.	6	-	-	1/2	-	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
SH	Up to category 4, PL e in the case		1					
#	of optional extension.							
-	Up to category 4, PL e.	6	_	-	1/2	-	1/4, 3/8, 1/2, 3/4	_
T T			,		1	1		

MS series service unit components Key features




pe	Description	Size	Pneumatic	connectio	n			
			Push-in	Female	thread		Connection plate with thread	
			connector	M	G	NPT	G	NPT
dividual d	evices							
embrane a	air dryers MS-LDM1							ta → Internet: ms-lo
1	Wear-free membrane dryer with	4	-	-	1/8, 1/4	-	1/8, 1/4, 3/8	1/8, 1/4, 3/8
Ï	internal air consumption	6	_	-	1/4, 3/8, 1/2	-	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
anching m	nodules MS-FRM						Technical da	ata → Internet: ms-f
(2)	Compressed air distributor with	4	-	-	1/8, 1/4	-	1/8, 1/4, 3/8	-
E	4 connections	6	-	-	1/4, 3/8, 1/2	-	1/4, 3/8, 1/2, 3/4	-
		9	-	-	3/4, 1	3/4, 1	1/2, 3/4, 1, 11/4, 11/2	1/2, 3/4, 1, 11/4, 11
		12	-	-	-	-	1, 11/4, 11/2, 2	-
stributor b	blocks MS-FRM-FRZ	1		,	T	,	Technical data	→ Internet: ms-frm-
The said	Compressed air distributor with	4	-	-	-	-	-	-
4	4 connections and half the grid dimension width	6	-	-	-	-	_	_
	umension width							
ow sensor:	s SFAM						Technical	data → Internet: sfa
-	For absolute flow rate information	6	-	_	-	-	1/2	1/2
0 5	and accumulated air consumption	9	-	-		-	1, 11/2	1, 11/2
	measurement		,	1	,	1		ч

Water separators MS6-LWS, MS series Peripherals overview



Water separator MS6-LWS



Note

Additional accessories:

- Module connector for combination with size MS4/MS6 or size MS9 → Internet: amv, rmv, armv
- Adapter for mounting on profiles → Internet: ipm-80, ipm-40-80, ipm-80-80


Moun	ting attachments and accessories					
		Individual device		Combination	→ Page/Internet	
		Without connecting	With connecting	Without connecting	With connecting	
		plate	plate	plate	plate	
1	Cover cap					ms6-end
	MS6-END	-	_	-	_	
2	Mounting plate	1)	_	1)	_	ms6-aend
	MS6-AEND	-	_	- /	_	
3	Connecting plate-SET		1)		1)	ms6-ag
	MS6-AG	_	- /	_	• ′	
	Connecting plate-SET		1)		1)	ms6-aq
	MS6-AQ	_	= 2)	_	-	
4	Mounting bracket					ms6-wb
	MS6-WB	-	-	_	_	
5	Module connector					ms6-mv
	MS6-MV	_	-	-	-	
6	Mounting bracket					ms6-wp
	MS6-WP	-	-	-	-	
	Mounting bracket (not illustrated)	_		_		ms6-wp
	MS6-WPB/WPE/WPM	-	•	-	-	
7	Fully automatic, electrically actuated			_		15
	condensate drain E2/E3/E4	-	•	-	-	

¹⁾ Module connector MS6-MV 5 or mounting bracket MS6-WP/WPB/WPE/WPM 6 is required for mounting.

Water separators MS6-LWS, MS series



Type codes



Further variants can be ordered using the modular system → 15

- Pneumatic connection
- Condensate drain
- Type of mounting
- EU certification
- UL certification
- Flow direction

FESTO

Condensate drain, fully automatic





Flow rate 2,400 ... 3,800 l/min



Temperature range +1 ... +60 °C



Operating pressure 0.8 ... 16 bar



www.festo.com



The maintenance-free water separator removes condensate from the compressed air.

- Constantly high condensate separation (99%) up to the maximum flow rate
- Metal bowl
- Available with fully automatic or fully automatic, electrically actuated condensate drain
- Optional device variant EX4 for use in potentially explosive areas in zones 1, 2, 21 and 22

General technical data	
Size	MS6
Pneumatic connection 1, 2	
Female thread	G½, G¾ or G½
Connecting plate AG	G½, G¾, G½ or G¾
Connecting plate AQ	NPT ¹ / ₄ , NPT ³ / ₈ , NPT ¹ / ₂ or NPT ³ / ₄
Constructional design	Centrifugal separator
Type of mounting	Via accessories
	In-line installation
Mounting position	Vertical ±5°
Air purity class at the output	Compressed air in accordance with ISO 8573-1:2010 [7:7:4] (with variant E2, E3 or E4: [-:7:4])
Bowl guard	Integrated as metal bowl
Condensate drain	Fully automatic
	Fully automatic, electrically actuated
Degree of condensate [%]	99
separation	
Max. condensate volume [ml]	38

Note: This product conforms to ISO 1179-1 and to ISO 228-1

Standard nominal flow rate qnN ¹⁾							
Size		MS6					
Pneumatic connection		G1/4/NPT1/4	G3/8/NPT3/8	G½/NPT½			
qnN	[l/min]	2,400	3,500	3,800			

¹⁾ Measured at p1 = 6 bar and $\Delta p = 1$ bar



Operating and environmen	ntal condition	ıs	
Condensate drain		Fully automatic	Fully automatic, electrical
		V	E2/E3/E4
Size		MS6	MS6
Operating pressure	[bar]	2 12 (2 10) ¹⁾	0.8 16 (0.8 10) ¹⁾
Operating medium		Compressed air in accordance with ISO 8573-1:2010	Compressed air in accordance with ISO 8573-1:2010
		[7:-:-]	[-:-:-]
		Inert gases	
Ambient temperature	[°C]	+5 +60	+1 +60
Temperature of medium	[°C]	+5 +60	+1 +60
Storage temperature	[°C]	-10 +60	+1 +60
Corrosion resistance class	CRC ²⁾	2	
Food-safe ³⁾		See supplementary material information	-
UL certification ³⁾		cULus recognized (OL)	

- 1) Value in brackets applies to MS6-LWS with UL certification.
- Value in brackets applies to mose-two with of certification.
 Corrosion resistance class CRC 2 to Festo standard FN 940070
 Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.

 Additional information www.festo.com/sp → Certificates.


ATEX	
EU certification	EX4
ATEX category gas	II 2G
Ex-ignition protection type gas	Ex h IIC T6 Gb X
ATEX category dust	II 2D
EX-ignition protection type dust	Ex h IIIC T60°C Db X
ATEX ambient temperature	+5 °C ≤ Ta ≤ +60 °C
CE mark (see declaration of conformity) ¹⁾	To EU Explosion Protection Directive (ATEX)

1) Additional information www.festo.com/sp → Certificates.

Weight [g]	
Size	MS6
Water separator	820
Water separator with fully automatic,	1,800
electrically actuated condensate drain	
E2/E3/E4	


Materials

Sectional view




Wate	Water separator						
1	Housing	Die-cast aluminium					
2	Bowl	Wrought aluminium alloy					
	Inspection window	PA					
-	Seals	NBR					
Note	on materials	RoHS-compliant					
		Free of copper and PTFE					







Pneumatic connection G1/4/NPT1/4



Pneumatic connection G3/8/NPT3/8




Pneumatic connection G½/NPT½



4 bar --- 6 bar -- 10 bar


----- 14 bar





Note: This product conforms to ISO 1179-1 and to ISO 228-1





Ordering data				
Size	Condensate drain	Connection	Part No.	Туре
Integrated as r	netal bowl			
MS6	Fully automatic	G1/4	564868	MS6-LWS-1/4-U-V
		G3/8	564869	MS6-LWS-3/8-U-V
		G ¹ / ₂	564870	MS6-LWS-1/2-U-V

Water separators MS6-LWS, MS series Ordering data – Modular products



id dimension	[mm] 62	Condi- tions	Code	Enter code
Module No.	564858	tions		code
Series	Standard		MS	MS
Size	6		6	6
Function	Water separator		-LWS	-LWS
Pneumatic connection	Female thread G1/4	1	-1/4	
	Female thread G3/8	1	-3/8	
	Female thread G½	1	-1/2	
	Connecting plate G ¹ / ₄		-AGB	
	Connecting plate G3/8		-AGC	
	Connecting plate G ¹ / ₂		-AGD	
	Connecting plate G3/4		-AGE	
	Connecting plate NPT ¹ / ₄	1	-AQN	
	Connecting plate NPT3/8	1	-AQP	
	Connecting plate NPT ¹ / ₂	1	-AQR	
	Connecting plate NPT3/4	1	-AQS	
Bowl guard	Metal bowl		-U	-U
Condensate drain	Fully automatic (P1 max. 12 bar)		-V	
External,	fully 115 V AC, terminals (P1 max. 16 bar)	1	-E2	
automati	230 V AC, terminals (P1 max. 16 bar)	1	-E3	
electric	24 V DC, terminals (P1 max. 16 bar)	1	-E4	
Type of mounting	Mounting bracket standard design	2	-WP	
	Mounting bracket for attaching the service units	1 2	-WPM	
	Mounting bracket centrally at rear (wall mounting top and bottom), connecting plates required	not	-WB	
EU certification	II 2GD to EU Explosion Protection Directive (ATEX)		-EX4	
UL certification	cULus, ordinary location for Canada and USA		-UL1	
Flow direction	Flow direction from right to left		-Z	

^{1 1/4, 3/8, 1/2,} AQN, AQP, AQR, AQS, E2, E3, E4, WPM

Not with EU certification EX4


M	Mandatory data
0	Options

I ransfer order	code												
564858	MS	6] -	LWS] - [-	U	-	-[-	-	-[

² **WP, WPM** Only with connecting plate AGB, AGC, AGD, AGE, AQN, AQP, AQR or AQS.

Water separators MS9-LWS, MS series Peripherals overview





Note

Additional accessories:


- Module connector for combinations with size MS6, MS9 or MS12
 - → Internet: rmv, armv

Moun	ting attachments and accessories					
		Individual device			Combination	→ Page/
		With female thread	With connecting pla	ite AG/AQ	Module without connect-	Internet
			Without EU	With EU	ing thread, without	
			certification EX4	certification EX4	connecting plate G	
1	Connecting plate-SET		_	_	_	ms9-ag
	MS9-AG	_	-	-	-	
	Connecting plate-SET		_			ms9-aq
	MS9-AQ	_	-	_	-	
2	Module connector					ms9-mv
	MS9-MV	_	_	_	-	
3	Mounting bracket		_		_	ms9-wp
	MS9-WP	_	_	_	_	
4	Mounting bracket		_		_	ms9-wp
	MS9-WPB	-	-	-	-	
5	Mounting bracket		_		_	ms9-wp
	MS9-WPM	-	•	_	-	
6	Condensate drain, fully automatic, electrically	_	_		_	23
	actuated E2/E3/E4	-		_	•	

Water separators MS9-LWS, MS series

FESTO

Type codes




Additional variants can be ordered using the modular product system → 23

- Pneumatic connection
- Condensate drain
- Type of mounting
- EU certification
- UL certification
- Flow direction

FESTO

Condensate drain, fully automatic





Flow rate 12,000 ... 15,000 l/min



Operating pressure 0.8 ... 16 bar



The water separator removes condensate from the compressed air.

- Constantly high condensate separation (99%) up to the maximum flow rate
- Metal bowl
- Available with fully automatic or fully automatic, electrically actuated condensate drain
- Optional device variant EX4 for use in potentially explosive areas in zones 1, 2, 21 and 22

General tech	nical data				
Size		MS9			
Pneumatic co	nnection 1, 2				
	Female thread	G3/4, G1, NPT3/4 or NPT1			
-	Connecting plate AG	G½, G¾, G1, G1¼ or G1½			
-	Connecting plate AQ	NPT½, NPT¾, NPT1¼ or NPT1½			
-	Module without connecting	-			
	thread/plate G				
Design		Centrifugal separator			
Type of moun	ting	Via accessories			
		In-line installation			
Mounting pos	sition	Vertical ±5°			
Air purity class	ss at the output	Compressed air in accordance with ISO 8573-1:2010 [-:7:4]			
Bowl guard		Integrated as metal bowl			
Condensate of	Irain	Fully automatic			
		Fully automatic, electrically actuated			
Degree of con	densate separation [%]	99			
Max. condens	sate volume [ml]	220			

Note: This product conforms to ISO 1179-1 and to ISO 228-1

Standard nominal flow rate qnN ¹⁾ [I/min]									
Pneumatic connection		G ³ / ₄ /NPT ³ / ₄	· '	Module without connecting thread, without connecting plate G					
qnN	[l/min]	12,000 ±15%	15,000 ±15%	15,000 ±15%					

¹⁾ Measured at p1 = 6 bar and $\Delta p = 1$ bar



Operating and environmental conditions							
Condensate drain		Fully automatic	Fully automatic, electrically actuated				
		V	E2/E3/E4				
Operating pressure	[bar]	2 12	0.8 16				
Operating medium		Compressed air in accordance with ISO 8573-1:2010 [-:-	-:-]				
Ambient temperature	[°C]	+5 +60	+1 +60				
Temperature of medium	[°C]	+5 +60	+1 +60				
Storage temperature	[°C]	+5 +60	+1 +60				
Corrosion resistance class	CRC ¹⁾	2					
UL certification ²⁾		cULus recognized (OL)					

¹⁾ Corrosion resistance class CRC 2 to Festo standard FN 940070
Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.

Additional information www.festo.com/sp → Certificates.


ATEV	
ATEX	
EU certification	EX4
ATEX category gas	II 2G
Ex-ignition protection type gas	Ex h IIC T6 Gb X
ATEX category dust	II 2D
EX-ignition protection type dust	Ex h IIIC T60°C Db X
ATEX ambient temperature	+5 °C ≤ Ta ≤ +60 °C
CE mark (see declaration of conformity) ¹⁾	To EU Explosion Protection Directive (ATEX)

¹⁾ Additional information www.festo.com/sp → Certificates.

Weight [g]					
Water separator	2,000				
Water separator with condensate drain,	2,400				
fully automatic, electrically actuated					
E2/E3/E4					


Materials


Sectional view



Wate	Water separator						
1	Housing	Die-cast aluminium					
2	Bowl	Wrought aluminium alloy					
	Inspection window	PA					
3	Spin disc	POM					
4	Isolating disc	POM					
-	Cover	PA reinforced					
-	Connecting plate, module	Die-cast aluminium					
	connector, mounting bracket						
-	Seals	NBR					
Note	on materials	RoHS-compliant					








Water separators MS9-LWS, MS series




Technical data



 $[\]parallel$ Note: This product conforms to ISO 1179-1 and to ISO 228-1





Ordering data									
Size	Condensate drain	Connection	Part No.	Туре					
MS9	Fully automatic	-	571468	MS9-LWS-G-U-V					

22

Water separators MS9-LWS, MS series Ordering data – Modular products



Ordering table irid dimension [mn	ıll 90	Condi-	Code	Enter
na aimension (iniii	90	tions	Code	
7		tions		code
Module No.	567857			
Series	Standard		MS	MS
Size	9		9	9
Function	Water separator		-LWS	-LWS
Pneumatic connection	Female thread G3/4	1	-3/4	
	Female thread G1	1	-1	
	Connecting plate G½		-AGD	
	Connecting plate G3/4		-AGE	
	Connecting plate G1		-AGF	
	Connecting plate G1 ¹ / ₄		-AGG -AGH	
	Connecting plate G1½			
	Female thread NPT3/4	1	-N3/4	
	Female thread NPT1	1	-N1	
	Connecting plate NPT ¹ / ₂	1	-AQR	
	Connecting plate NPT ³ / ₄	1	-AQS	
	Connecting plate NPT1	1	-AQT	
	Connecting plate NPT11/4	1	-AQU	
	Connecting plate NPT1½	1	-AQV	
	Module without connecting thread, without connecting plate	1	-G	
Bowl	Metal bowl		-U	-U
Condensate drain	Fully automatic (P1 max. 12 bar)		-V	
External, fully	115 V AC, terminals (P1 max. 16 bar)	1	-E2	
automatic,	230 V AC, terminals (P1 max. 16 bar)	1	-E3	
electric	24 V DC, terminals (P1 max. 16 bar)	1	-E4	
Type of mounting	Mounting bracket standard design	2	-WP	
	Mounting bracket for attaching the service units	12	-WPM	
	Mounting bracket for large wall gap	2	-WPB	
EU certification	II 2GD to EU Explosion Protection Directive (ATEX)		-EX4	
UL certification	cULus, ordinary location for Canada and USA		-UL1	
Flow direction	Flow direction from right to left		-Z	

1	3/4, 1,	N3/4,	N1, AQR,	AQS, AQT,	AQU, AQV,	G, E2	, E3, E4,	WPM


Not with EU certification EX4 2 WP, WPM, WPB Not with pneumatic connection G

M	Mandatory data
0	Options

Transfer order c	ode										
567857	MS	9	- LWS	-	- U	-	_	-	-	-[

Water separators MS12-LWS, MS series Peripherals overview






Note Additional accessories: - Module connector for combination with size MS9 → Internet: armv

Moun	Mounting attachments and accessories						
		→ Page/Internet					
1	Connecting plate-SET	ms12-ag					
	MS12-AG						
	Connecting plate-SET	ms12-aq					
	MS12-AQ						
2	Mounting bracket	ms12-wp					
	MS12-WP						
3	Module connector	ms12-mv					
	MS12-MV						
4	Fully automatic, electrically actuated condensate drain	30					
	E2/E3/E4						

Water separators MS12-LWS, MS series

FESTO

Type codes



Additional variants can be ordered using the modular product system → 30


- Pneumatic connection
- Condensate drain
- Type of mounting
- Flow direction




Condensate drain, fully automatic











The water separator removes condensate from the compressed air.

- Constantly high condensate separation (99%) up to the maximum flow rate
- Metal bowl

• Available with fully automatic or fully automatic, electrically actuated condensate drain

General technical data			
Pneumatic connection 1, 2			
Connecting plate AG	G1, G1¼, G1½ or G2		
Connecting plate AQ	NPT1, NPT1¼, NPT1½ or NPT2		
Module without connecting	-		
thread/plate G			
Design	Centrifugal separator		
Type of mounting	Via accessories		
	In-line installation		
Mounting position	Vertical ±5°		
Air purity class at the output	Compressed air to ISO 8573-1:2010 [-:7:4]		
Bowl guard	Integrated as metal bowl		
Condensate drain	Fully automatic		
	Fully automatic, electrically actuated		
Degree of condensate [%]	99		
separation			
Max. condensate volume [ml]	400		

Note: This product conforms to ISO 1179-1 and to ISO 228-1

Flow rates		
Standard nominal flow rate $q_{nN}^{1)}$	[l/min]	25,000 ±15%
Max. standard flow rate	[l/min]	40,000 ±15%
$q_{n max.}$		

1) Measured at p1 = 6 bar and Δp = 0.5 bar




Operating and environmer	ntal conditio	ıs			
Condensate drain		Fully automatic	Fully automatic, electrically actuated		
		V	E2/E3/E4		
Operating pressure	[bar]	2 12	0.8 16		
Operating medium		Compressed air to ISO 8573-1:2010 [-:-:-]			
Ambient temperature	[°C]	+5 +60	+1 +60		
Temperature of medium	[°C]	+5 +60	+1 +60		
Storage temperature	[°C]	+5 +60	+1 +60		
Corrosion resistance class	CRC ¹⁾	2			

¹⁾ Corrosion resistance class CRC 2 to Festo standard FN 940070
Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.

Weight [g]					
Water separator	6,300				
Water separator with fully automatic,	7,000				
electrically actuated condensate drain					
E2/E3/E4					
Accessories					
Connecting plate AG	1,300				
Mounting bracket WP	700				

Materials

Sectional view





Wate	er separator	
1	Housing	Die-cast aluminium
2	Bowl	Wrought aluminium alloy
	Inspection window	PA
3	Spin disc	POM
4	Separating plate	POM
-	Cover	PA reinforced
-	Connecting plate, module	Die-cast aluminium
	connector, mounting bracket	
-	Seals	Nitrile rubber
Note	on materials	RoHS-compliant

FESTO

Standard flow rate qn as a function of differential pressure $\Delta p1-2$


Pneumatic connection G1½/G2/NPT1½/NPT2





L1





Туре	B1	D6	H1	L1	L2	L3	L6
MS12-LWSV		5.6		-	-	-	36
MS12-LWSE2/E3/E4	72	İ	179	140	108	15	-

Ordering data	Ordering data											
Size	Condensate drain	Connection	Part No.	Туре								
MS12	Fully automatic	-	8005550	MS12-LWS-G-U-V								

Water separators MS12-LWS, MS series Ordering data – Modular products



Ordering table				
Grid dimension [mm]	124	Condi- tions	Code	Enter code
M Module No.	569827			
Series	Standard		MS	MS
Size	12		12	12
Function	Water separator		-LWS	-LWS
Pneumatic connection	Connecting plate G1		-AGF	
	Connecting plate G1¼		-AGG	
	Connecting plate G1½		-AGH	
	Connecting plate G2		-AGI	
	Connecting plate NPT1		-AQT	
	Connecting plate NPT11/4		-AQU	
	Connecting plate NPT1½		-AQV	
	Connecting plate NPT2		-AQW	
	Module without connecting thread, without connecting plate	1	-G	
Bowl	Metal bowl		-U	-U
Condensate drain	Fully automatic (P1 max. 12 bar)		-V	
External, fully	115 V AC, terminals (P1 max. 16 bar)		-E2	
automatic,	230 V AC, terminals (P1 max. 16 bar)		-E3	
electric	24 V DC, terminals (P1 max. 16 bar)		-E4	
Type of mounting	Mounting bracket standard design	2	-WP	
Flow direction	Flow direction from right to left		-Z	

1	G	Not with mounting type WP

M	Mandatory data
0	Options

Transfer order code															
569827		MS	12	-	LWS	-	-		U	-		-		_	

² **WP** Only with connecting plate AGF, AGG, AGH, AGI, AQT, AQU, AQV or AQW.