
Service unit combinations MSB-FRC, MS series





*	Festo	Core	Rang
---	-------	------	------

Worldwide:

Solves the majority of your automation tasks

Quickest delivery – wherever, whenever

Simply good: Expected high Festo quality Fast: Easy and fast to select

With the Festo Core Range, we have selected the most important products and functions from our broad product catalogue, and added the quickest delivery.

The Core Range offers you the best value for your automation tasks.



Service unit components of the MS series

Solutions for every application

With its large product range, highly effective components and a wide choice of functions, the MS series from Festo offers a complete concept for compressed air preparation. It is suitable for simple standard applications as well as application-specific solutions with very high quality requirements. Available as individual components, pre-assembled combinations ex-stock,

application-specific combinations or complete turnkey solutions. The five sizes in the MS series achieve maximum flow rates with minimum space requirements.

Freely combinable function modules

Pressure regulators, on/off and softstart valves with safety function, filters, pressure and flow sensors, dryers, sensors and lubricators can be assembled into a suitable solution for every task. With the modular structure the components can be combined as required. The simple connection system saves time because replacing individual modules does not require disassembling the entire combination. Many of the components are also UL and ATEX certified.


CAD models and configurator

Convenient tools for planning and selecting application-specific individual components and combinations. The product configurator lets you configure customised solutions quickly and transfer the order data without any hassle.

Engineering tools

Selection tool for choosing the right service unit combination without oversizing, and with the right air purity class:

→ www.festo.com/engineering/ service unit



Integrated sensors

Pressure and flow sensors

Safety functions

Soft-start/quick exhaust valves MS6-SV/MS9-SV

Energy savings

Service unit combinations MSE6

Intelligent mix of sizes



- · Maximum machine availability thanks to controlled processes
- Reliable compressed air preparation and supply for the system
- Integrated or stand-alone
- Easy to connect with M8/M12 plug



- · Fast and reliable exhausting of systems up to Performance Level e, certified to EN ISO 13849-1
- Integrated soft-start function



- · Fully automatic monitoring and regulation of compressed air supply
- · Automatic shut-off of the compressed air in stand-by mode
- Detection and notification of leak-
- Condition monitoring of relevant process data



- Optimum flow rate with a size that is up to 18% smaller
- Excellent energy efficiency
- Cost-optimised combinations save up to 30%!

Size	aı	Ш	er	eı	10	.e	S
Size							

Size differences									
Size		MS2	MS4	MS6	MS9	MS12			
Grid dimension	[mm]	25	40	62	90	124			
Connection sizes		M5, QS-6	G1/8, G1/4, G3/8	G1/4, G3/8, G1/2, G3/4	G1/2, G3/4, G1, G1 1/4, G1 1/2	G1, G1 1/4, G1 1/2, G2			
Standard nominal flow rate qnN ¹⁾	[l/min]	350	1800	6500	20000	22000			

Using pressure regulator MS-LR as an example

Note

Information

The next few pages provide a brief overview of the product range for the service unit components of the MS series.

You can find detailed information and all the technical data in the documentation for the relevant service unit component.

Accessories such as connecting plates or mounting brackets can be ordered either via the configurator or separately.

Design of a service unit

The order of the individual service unit components within a combination is relevant for safety and functionality. The service unit components cannot be combined in any order in the flow direction. They are subject to restrictions and rules.

The configurator for the service unit MSB is a reliable and convenient way of combining individual service unit components and it ensures compliance with the applicable rules. As a result, you get a fully assembled unit, including UL or ATEX certification, if necessary.

When combining a unit from individually configured and ordered service unit components, the points on the right must be adhered to under all circumstances.

- Regulators MS-LFR/LR/LRP/LRE are only permissible in the flow direction with the same or decreasing pressure regulation range
- Filters MS-LFR/LF/LFM/LFX are only permissible in the flow direction with an increasing grade of filtration
- Lubricators MS-LOE are not permitted in the flow direction upstream of a filter MS-LFR/LFM/LF/LFX, water separator MS-LWS or membrane air dryer MS-LDM1
- A micro filter MS-LFM must be installed in the flow direction upstream of an activated carbon filter MS-LFX or membrane air dryer MS-LDM1
- A flow sensor SFAM cannot be installed directly downstream of a regulator MS-LFR/LR; a branching module MS-FRM must be positioned between them
- A soft-start/quick exhaust valve MS-SV must be the last service unit component in the flow direction

ype	Description	Size	Pneumatic o	connection					
			Push-in	Female thread			Connecting plate with thread		
			connector	M	G	NPT	G	NPT	
Combinations									
Service unit com	binations MSB-FRC							Datasheets → Internet: ms	
	Combinations of filter regu-	4	-	_	1/8, 1/4	-	_	_	
	lator and lubricator	6	-	-	1/4, 3/8, 1/2	-	-	-	
Service unit com	binations MSB							Datasheets → Internet: ms	
	Certain combinations pre- defined	4	-	-	1/4	_	_	_	
		6	-	-	1/2	-	_	_	
Ballett.	Freely configurable combin-	4	_	-	1/8, 1/4	-	1/8, 1/4, 3/8	1/8, 1/4, 3/8	
	ations	6	-	-	1/4, 3/8, 1/2	_	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4	
		9	_	_	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2	
A.M.									
Service unit com	binations MSE6							Datasheets → Internet: mse	
	Combinations with fieldbus	6	-	-	-	-	1/2	_	
V Dealer	connection for measuring				·		·		
	pressure, flow rate and con-								
No. of Concession, Name of Street, or other Designation of Concession, Name of Street, or other Designation of Concession, Name of Street, Original Concession, Original Concessio	sumption	i							


Туре	Description	Size	Pneumatic o	Female thread			Connecting plate with thre	ad.
			connector	M	G	NPT	G Connecting plate with time	NPT
	1			IWI	-	I MI I	0	W I
ndividual dev								. 15
Filter regulato		1.	100.6	145	1	1	Datasheets → Internet: ms2-lfr; m	is4-lfr; ms6-lfr; ms9-lfr; ms12
	Filter and pressure regula-	2	QS-6	M5	-	-	-	-
8	tor in a single device, grade of filtration 5 or 40 µm	4	-	-	1/8, 1/4	-	1/8, 1/4, 3/8	1/8, 1/4, 3/8
	οι πιατιστίοι 3 οι 40 μπ	6	-	-	1/4, 3/8, 1/2	-	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
		9	-	-	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
- 4		12	-	-		-	1, 1 1/4, 1 1/2, 2	_
ilter regulato	rs MS-LFR-B						Datasheets	→ Internet: ms4-lfr-b; ms6-l
	Filter and pressure regula-	4	_	_	1/4	_	_	_
	tor in a single device in	6	-	_	1/2	-	_	_
0 7	polymer housing, grade of			1	1 .	1		
*								
ilters MS-LF							Datasheets → Internet	: ms4-lf; ms6-lf; ms9-lf; ms1
1	Grade of filtration 5 or	4	-	_	1/8, 1/4	-	1/8, 1/4, 3/8	1/8, 1/4, 3/8
1	40 μm	6	-	-	1/4, 3/8, 1/2	-	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
1		9	-	_	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
		12	-	-	_	-	1, 1 1/4, 1 1/2, 2	_
Fine and micro	filters MS-LFM						Datasheets → Internet: ms4-li	fm· ms6-lfm· ms9-lfm· ms12
ine unu inici	Grade of filtration 0.01 or	4	_	T_	1/8, 1/4	Ι_	1/8, 1/4, 3/8	1/8, 1/4, 3/8
100		6	-	-	1/4, 3/8, 1/2	_	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
•	1 1 UM				1/4, 5/0, 1/2			-
J	1 μm		1_	l_	3// 1	3// 1	1/2 3/4 1 11/4 11/2	1/2 3/4 1 11/4 11/2
	1 μm	9	_	_	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
	1 μm		-	-	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2 1, 1 1/4, 1 1/2, 2	
Activated carb	on filters MS-LFX	9			1		1, 1 1/4, 1 1/2, 2	- 4-lfx; ms6-lfx; ms9-lfx; ms12
Activated carb	on filters MS-LFX For removing liquid and	9 12 4			1		1, 1 1/4, 1 1/2, 2	_
Activated carb	on filters MS-LFX	9		-	-	-	1, 1 1/4, 1 1/2, 2 Datasheets → Internet: ms 1/8, 1/4, 3/8 1/4, 3/8, 1/2, 3/4	4-lfx; ms6-lfx; ms9-lfx; ms1: 1/8, 1/4, 3/8 1/4, 3/8, 1/2, 3/4
Activated carb	on filters MS-LFX For removing liquid and	9 12 4	-	-	1/8, 1/4	-	1, 1 1/4, 1 1/2, 2 Datasheets → Internet: ms 1/8, 1/4, 3/8	- 4-lfx; ms6-lfx; ms9-lfx; ms12 1/8, 1/4, 3/8
Activated carb	on filters MS-LFX For removing liquid and	9 12 4 6	-	-	1/8, 1/4 1/4, 3/8, 1/2	-	1, 1 1/4, 1 1/2, 2 Datasheets → Internet: ms 1/8, 1/4, 3/8 1/4, 3/8, 1/2, 3/4	4-lfx; ms6-lfx; ms9-lfx; ms12 1/8, 1/4, 3/8 1/4, 3/8, 1/2, 3/4
1	on filters MS-LFX For removing liquid and gaseous oil particles	9 12 4 6 9			1/8, 1/4 1/4, 3/8, 1/2 3/4, 1	- - - - 3/4, 1	1, 1 1/4, 1 1/2, 2 Datasheets → Internet: ms 1/8, 1/4, 3/8 1/4, 3/8, 1/2, 3/4 1/2, 3/4, 1, 1 1/4, 1 1/2 1, 1 1/4, 1 1/2, 2	-4-lfx; ms6-lfx; ms9-lfx; ms12 1/8, 1/4, 3/8 1/4, 3/8, 1/2, 3/4 1/2, 3/4, 1, 1 1/4, 1 1/2
Activated carb	on filters MS-LFX For removing liquid and gaseous oil particles ors MS-LWS	9 12 4 6 9 12			1/8, 1/4 1/4, 3/8, 1/2 3/4, 1	- - - - 3/4, 1	1, 1 1/4, 1 1/2, 2 Datasheets → Internet: ms 1/8, 1/4, 3/8 1/4, 3/8, 1/2, 3/4 1/2, 3/4, 1, 1 1/4, 1 1/2 1, 1 1/4, 1 1/2, 2 Datasheets → Internet: ms	- 4-lfx; ms6-lfx; ms9-lfx; ms12 1/8, 1/4, 3/8 1/4, 3/8, 1/2, 3/4 1/2, 3/4, 1, 1 1/4, 1 1/2 - et: ms6-lws; ms9-lws; ms12
1	on filters MS-LFX For removing liquid and gaseous oil particles	9 12 4 6 9		- - - - -	1/8, 1/4 1/4, 3/8, 1/2 3/4, 1	- - - - - 3/4, 1	1, 1 1/4, 1 1/2, 2 Datasheets → Internet: ms 1/8, 1/4, 3/8 1/4, 3/8, 1/2, 3/4 1/2, 3/4, 1, 1 1/4, 1 1/2 1, 1 1/4, 1 1/2, 2	-4-lfx; ms6-lfx; ms9-lfx; ms12 1/8, 1/4, 3/8 1/4, 3/8, 1/2, 3/4 1/2, 3/4, 1, 1 1/4, 1 1/2

Гуре	Description	Size	Pneumatic	connection				
			Push-in	Female thread	d		Connecting plate with three	ad
			connector	M	G	NPT	G	NPT
ndividual devic	es		'	'	<u>'</u>		<u>'</u>	<u>'</u>
essure regulat							Datasheets → Internet: ms2-lr;	; ms4-lr; ms6-lr; ms9-lr; ms12
	For setting the required	2	QS-6	M5	_	-	_	_
10.1	operating pressure,	4	-	-	1/8, 1/4	-	1/8, 1/4, 3/8	1/8, 1/4, 3/8
- 35	4 pressure regulation	6	_	-	1/4, 3/8, 1/2	-	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
2 2	ranges	9	-	-	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
		12	-	-	-	-	1, 1 1/4, 1 1/2, 2	-
ressure regulat	tors MS-I P-R						Datachoot	s → Internet: ms4-lr-b; ms6-
essure regular	For setting the required	4	T_	T_	1/4	T_		
	operating pressure, in a	6	 	<u> -</u>	1/2	-		
	polymer housing	-			1/2			
OE								
essure regulat							Datashee	ts → Internet: ms4-lrb; ms6
	For configuring a regulator	4	-	-	1/4	-	1/8, 1/4, 3/8	-
1 1	manifold with independent	6	_	_	1/2	_	1/4, 3/8, 1/2, 3/4	_
1	pressure regulation ranges.							
	Pressure output is to the							
	front or rear.							
recision pressu	ire regulators MS-LRP							Datasheets → Internet: ms6
	For precise setting of the re-	6	_	-	1/4, 3/8, 1/2	_	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
	quired operating pressure,					,		
	4 pressure regulation							
. (1	ranges,							
	pressure hysteresis							
	0.02 bar							
ecision pressu	ire regulators MS-LRPB						D	atasheets → Internet: ms6-li
	For configuring a regulator	6	-	_	1/2	-	1/4, 3/8, 1/2, 3/4	_
	manifold with independent							
- 44	pressure regulation ranges.							
2	Pressure output is to the							
	front or rear.							
ectric pressure	e regulators MS-LRE							Datasheets → Internet: ms6
No. of	Electrically adjustable pres-	6	-	_	1/4, 3/8, 1/2	_	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
	sure regulator,							
	4 pressure regulation							
0 1	ranges							
bricators MS-	LOE						Datasheets → Internet: ms4-l	ne· ms6-lne· ms9-lne· ms12-
-	Add a precisely adjustable	4	T_	T_	1/8, 1/4	T_	1/8, 1/4, 3/8	1/8, 1/4, 3/8
	amount of oil to the com-	6	-	_	1/4, 3/8, 1/2	-	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
	pressed air. The amount of	9	_	_	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
	pressed and the amount of							
	oil mist is proportional to			-		1		
	I '	12	-	-	-	-	1, 1 1/4, 1 1/2, 2	-

ype	Description	Size	Pneumatic					
			Push-in	Female thr	1		Connecting plate with thre	
			connector	M	G	NPT	G	NPT
dividual devic	es							
n/off valves M	S-EM						Datasheets → Internet: ms4-	em; ms6-em; ms9-em; ms12
	Manually actuated on/off	4	-	-	1/8, 1/4	-	1/8, 1/4, 3/8	1/8, 1/4, 3/8
	valve for pressurising and	6	_	-	1/4, 3/8, 1/2	-	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
2	exhausting pneumatic sys-	9	_	-	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
	tems.	12	-	_	_	-	1, 1 1/4, 1 1/2, 2	_
1/off valves M	S-FF						Datasheets → Internet· ms	4-ee; ms6-ee; ms9-ee; ms1
9	Electrically actuated on/off	4	T_	1_	1/8, 1/4	I_	1/8, 1/4, 3/8	1/8, 1/4, 3/8
	valve for pressurising and	6	-	-	1/4, 3/8, 1/2	-	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
	exhausting pneumatic sys-	9	-	-	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
.0]	tems.	12	 -	1_	-	_	1, 1 1/4, 1 1/2, 2	-
							2, 2 2, 1, 2 2, 2,	
. / . 65 ! 146						1	D. 1.	
n/off valves M		,		1	14	1		→ Internet: ms4-ee-b; ms6-
	Electrically actuated on/off valve in polymer housing	4	-	-	1/4	-		-
3	for pressurising and ex-	6	-	-	1/2	-	-	-
	hausting pneumatic sys-							
	tems.							
oft-start valves	MS-DL						Datasheets → In	ternet: ms4-dl; ms6-dl; ms1
100	Pneumatically actuated	4	-	-	1/8, 1/4	-	1/8, 1/4, 3/8	1/8, 1/4, 3/8
	soft-start valve for slow	6	-	-	1/4, 3/8, 1/2	-	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
(3)	pressurisation and exhaust	12	_	-	-	-	1, 1 1/4, 1 1/2, 2	_
*	of pneumatic installations.				'			'
oft-start valves	MC DE						Datachasts > Inte	ernet: ms4-de; ms6-de; ms12
uit-stait vaives	Electrically actuated soft-		1	T_	1/0 1/4	T_	· · · · · · · · · · · · · · · · · · ·	
	start valve for slowly pres-	6	 -		1/8, 1/4	- -	1/8, 1/4, 3/8	1/8, 1/4, 3/8
40	surising and exhausting	12	+	-	1/4, 3/8, 1/2	- -	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
	pneumatic systems.	12	-	-		-	1, 1 1/4, 1 1/2, 2	
n/off valves M	FDE D						Datachasta >	Internet: ms4-ede-b; ms6-ed
II/OII Valves IVI	Electrically actuated soft-	Ι,		1	111	1	i	
	start valve in polymer hous-	4	-	-	1/4	-	-	-
	ing for slowly pressurising	6	-	-	1/2	-	-	-
	and exhausting pneumatic							
	systems.							
oft-start/quick	exhaust valves MS-SV						Datash	eets → Internet: ms6-sv; ms
	For gradually increasing	6	-	_	1/2	-	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
	pressurisation and quick,	9	-	-	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
01	safe pressure reduction in							
M	pneumatic piping systems.							
H	Up to category 1, PL c.							
	Up to category 3, PL d.	6	Τ_	T_	1/2	Ī_	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
	Up to category 4, PL e in the		1-	1-	1/2	1-	1/4, 1/0, 1/2, 1/4	1/4, 2/0, 1/2, 2/4
1	case of optional extension.							
/ H								
	Up to category 4, PL e.	6	T_	1_	1/2	1_	1/4, 3/8, 1/2, 3/4	1_
	op to category 4, PL e.	0	1-	1-	1/2	1-	1/4, 5/0, 1/2, 3/4	
0 0								
200								
1000	l .	1						

Гуре	Description	Size	Pneumatic o	connection				
			Push-in	Female thre	ead		Connecting plate with thre	ad
			connector	M	G	NPT	G	NPT
ndividual dev	ices							
Membrane air	dryers MS-LDM1						Datasheets	→ Internet: ms4-ldm; ms6-ld
•	Wear-free membrane dryer	4	_	_	1/8, 1/4	-	1/8, 1/4, 3/8	1/8, 1/4, 3/8
	with internal air consump- tion	6	-	-	1/4, 3/8, 1/2	-	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
- 1								
Branching mo	dules MS-FRM						Datasheets → Internet: ms4-fr	m; ms6-frm; ms9-frm; ms12-fr
44	Compressed air distributors	4	_	_	1/8, 1/4	_	1/8, 1/4, 3/8	-
-	with 4 connections	6	-	-	1/4, 3/8, 1/2	-	1/4, 3/8, 1/2, 3/4	-
•		9	-	-	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
		12	-	-	_	-	1, 1 1/4, 1 1/2, 2	-
Distributor blo	ocks MS-FRM-FRZ					,	Datasheets → Ir	nternet: ms4-frm-frz; ms6-frm-
	Compressed air distributors	4	_	_	_	_	_	_
61	with 4 connections and half	6	-	1-	-	-	-	-
1	the grid width							
Flow sensors S	SFAM .							Datasheets → Internet: sfa
Total Control	For absolute flow rate infor-	6	-	-	-	_	1/2	1/2
	mation and cumulative air	9	-	-	-	-	1, 1 1/2	1, 1 1/2
	consumption measurement			-				

Peripherals overview



Moun	nting attachments and accessories	→ Page/Internet
[1]	Cover cap	ms4-end,
	MS4/6-END	ms6-end
[2]	Connecting plate SET	ms4-ag,
	MS4/6-AG	ms6-ag
[3]	Module connector	ms4-mv,
	MS4/6-MV	ms6-mv
[4]	Mounting bracket	ms4-wp,
	MS4/6-WP	ms6-wp
[5]	Mounting bracket	ms4-wp,
	MS4/6-WPB	ms6-wp
[6]	Mounting bracket	ms4-wp,
	MS4/6-WPE	ms6-wp
[7]	Mounting bracket	ms4-wp,
	MS4/6-WPM	ms6-wp
[8]	Padlock	17
	LRVS-D	

Type codes

001	Series
MSB	Service unit component MS series
002	Size
4	Grid dimension 40 mm
003	Pneumatic connection
1/8	Female thread G1/8
1/4	Female thread G1/4
004	Function
FRC	

005	Service unit component equipment	
J1	Filter regulator, 0.5 12 bar, 40 µm, plastic bowl with plastic bowl	
	guard, manual condensate drain, lockable rotary knob	
J2	Filter regulator, 0.5 12 bar, 40 µm, plastic bowl with plastic bowl	
	guard, fully automatic condensate drain, lockable rotary knob	
J3	Filter regulator, 0.5 12 bar, 5 µm, plastic bowl with plastic bowl	
	guard, manual condensate drain, lockable rotary knob	
J5	Filter regulator, 0.3 7 bar, 40 µm, plastic bowl with plastic bowl	
	guard, manual condensate drain, lockable rotary knob	
J120	Filter regulator, lockable, 0.3 7 bar, 40 µm, plastic bowl with plastic	
	bowl guard, manual condensate drain, MPa, lockable rotary knob	
M1	Lubricator, plastic bowl with plastic bowl guard	

006	Flow direction	
	Flow direction from left to right	
Z	Flow direction from right to left	


Type codes

001	Series
MSB	Service unit component MS series
002	Size
6	Grid dimension 62 mm
003	Pneumatic connection
1/4	Female thread G1/4
3/8	Female thread G3/8
1/2	Female thread G1/2
004	Function
FRC	


005	Service unit component equipment	
J1	Filter regulator, 0.5 12 bar, 40 µm, plastic bowl with plastic bowl	
	guard, manual condensate drain, lockable rotary knob	
J2	Filter regulator, 0.5 12 bar, 40 μm, plastic bowl with plastic bowl	
	guard, fully automatic condensate drain, lockable rotary knob	
J3	Filter regulator, 0.5 12 bar, 5 µm, plastic bowl with plastic bowl	
	guard, manual condensate drain, lockable rotary knob	
J5	Filter regulator, 0.3 7 bar, 40 µm, plastic bowl with plastic bowl	
	guard, manual condensate drain, lockable rotary knob	
J9	Filter regulator, 0.5 12 bar, 5 µm, metal bowl guard with manual	
	condensate drain, lockable rotary knob	
J10	Filter regulator, 0.5 12 bar, 5 µm, metal bowl with fully automatic	
	condensate drain, lockable rotary knob	
J11	Filter regulator, 0.5 12 bar, 40 µm, metal bowl guard with manual	
	condensate drain, lockable rotary knob	
J12	Filter regulator, 0.5 12 bar, 40 µm, metal bowl guard with fully au-	
	tomatic condensate drain, lockable rotary knob	
J120	Filter regulator, lockable, 0.3 7 bar, 40 µm, plastic bowl with plastic	
	bowl guard, manual condensate drain, MPa, lockable rotary knob	
M1	Lubricator, plastic bowl with plastic bowl guard	
M2	Lubricator, metal bowl	

006	Flow direction	
	Flow direction from left to right	
Z	Flow direction from right to left	

With manual rotary condensate drain



Fully automatic





Flow rate 850 ... 4800 l/min



Temperature range −10 ... +60°C



Operating pressure 1.5 ... 20 bar



www.festo.com



- Filter, regulator and lubricator functions in a single unit
- High flow rate and highly efficient in removing contaminants
- Good regulation characteristics with minimal pressure hysteresis
- Set values are secured by locking the rotary knob
- Lockable rotary knob
- Two pressure regulation ranges: 0.3°... 7 bar and 0.5 ... 12 bar
- Available with manual or integrated, fully automatic condensate drain
- Choice of filter inserts 5 μm or 40 μm
- New filter cartridges
 - → page 17
 Festo special oil → page 17

General technical data				
Size		MSB4	MSB6	
Pneumatic connection 1, 2		G1/8	-	
		G1/4	G1/4	
		-	G3/8	
		-	G1/2	
Design		Filter regulator with pressure gauge		
		Proportional standard mist lubricator		
Regulator function		Output pressure constant, with primary pressure compensation, with	return flow, with secondary exhausting	
Type of mounting		With accessories		
Mounting position		Vertical ±5°		
Grade of filtration	[µm]	5		
		40		
Air purity class at the output		Compressed air to ISO 8573-1:2010 [6:4:–] (grade of filtration 5 µm)		
		Compressed air to ISO 8573-1:2010 [7:4:-] (grade of filtration 40 µm	n)	
Bowl guard		Plastic bowl guard	Plastic bowl guard	
		_	Integrated as metal bowl	
Condensate drain		Manual		
		Fully automatic		
Actuator lock		Rotary knob with detent, can be locked using accessories		
Pressure regulation range	[bar]	0.3 7		
		0.5 12		
Display pressure		With pressure gauge		

Note: This product conforms to ISO 1179-1 and ISO 228-1.

Standard nominal flow rate qnN¹) [l/min]							
Size	e MSB4 MSB6						
Pneumatic connection G1/8 G1/4 G1/4 G3/8 G1/2					G1/2		
Pressure regulation range 0.3 7 bar							
Grade of filtration	40 μm	_	1400	_	_	4800	
Pressure regulation range 0.5 :	Pressure regulation range 0.5 12 bar						
Grade of filtration	5 μm	_	850	_	_	3600	
	40 μm	850	900	1900	3500	3700	

¹⁾ Measured at p1 = 10 bar and p2 = 6 bar, Δp = 1 bar.

Operating and environmental conditions						
Condensate drain		Manual	Manual			
Size		MSB4	MSB6	MSB4	MSB6	
Operating pressure	[bar]	1.5 14	1.5 20	2 12	2 12	
Operating medium		Compressed air to ISC	Compressed air to ISO 8573-1:2010 [-:4:-] Compressed air to ISO 8573-1:2010 [7:4:-]		0 8573-1:2010 [7:4:–]	
		Inert gases				
Note on the operating/		Lubricated operation	Lubricated operation possible (in which case lubricated operation will always be required)			
pilot medium						
Ambient temperature	[°C]	-10 +60	-10 +60			
Temperature of medium	[°C]	-10 +60				
Storage temperature	[°C]	-10 +60				
Corrosion resistance class CRC ¹)	2				
Food-safe ²⁾		See supplementary m	naterial information			

¹⁾ Corrosion resistance class CRC 2 to Festo standard FN 940070


Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

²⁾ Additional information: www.festo.com/catalogue/ms \rightarrow Support/Downloads.

Weight [g]					
Size	MSB4	MSB6			
With plastic bowl guard	500	1495			
With metal bowl	-	1713			

Materials

Sectional view




Service	Service unit				
[1]	Housing	Die-cast aluminium			
[2]	Rotary knob	PA/POM			
[3]	Plastic bowl guard	PC			
[4]	Metal bowl	Wrought aluminium alloy			
-	Seals	NBR			

Standard flow rate qn as a function of output pressure p2

Pressure regulation range 0.3 ... 7 bar $\,$ Grade of filtration 5 μm MSB4-1/4

Input pressure p1 = 10 bar


Grade of filtration 40 μm



Pressure regulation range 0.5 ... 12 bar $\,$ Grade of filtration 5 μm MSB4-1/8


Input pressure p1 = 10 bar


Grade of filtration 40 μm



MSB4-1/4

Input pressure p1 = 10 bar






Standard flow rate qn as a function of output pressure p2

Pressure regulation range 0.3 ... 7 bar $\,$ Grade of filtration 5 μm MSB6-1/2

Input pressure p1 = 10 bar


Grade of filtration 40 μm



Pressure regulation range 0.5 ... 12 bar $\,$ Grade of filtration 5 μm MSB6-1/4


Input pressure p1 = 10 bar

Grade of filtration 40 μm




MSB6-3/8


Input pressure p1 = 10 bar



MSB6-1/2

Input pressure p1 = 10 bar





Dimensions Download CAD data → www.festo.com With pressure gauge, display unit [bar] В1 B6 В2 В3 B5 7 5 \Box Γ_{2} 1 [1] Installation dimension Flow direction В1 В2 В3 В4 B5 В6 D1 L5 L6 L7 L8 Туре L1 L2 L3 L4 Condensate drain Manual Fully automatic MSB4-1/8 G1/8 80.4 40.2 21 57 29.7 201 87 80 25 17.7 20.4 167 53 MSB4-1/4 G1/4

G1/4

G3/8

G1/2

284.8

134.5

95.5

130

68

15.8

18.5

215.3

65.6

124

62

31

77

54

38.8

MSB6-1/4

MSB6-3/8

MSB6-1/2

 $[\]mid$ Note: This product conforms to ISO 1179-1 and ISO 228-1.

★ Core Range

Ordering data					
Size	Connection	Condensate drain	Grade of filtration [µm]	Part no.	Туре
Pressure regula	tion range 0.5 12 bar, p	plastic bowl guard, pressure gauge	with outer scale in bar and inner scale i	in psi	
Flow direction f	rom left to right				
MSB4	G1/4	Manual	40	★ 531117	MSB4-1/4-FRC5:J1M1
MSB6	G1/2	Manual	40	★ 530244	MSB6-1/2-FRC5:J1M1
Flow direction f	rom right to left				
MSB4	G1/4	Manual	40	531118	MSB4-1/4-FRC5:J1M1-Z
MSB6	G1/2	Manual	40	530245	MSB6-1/2-FRC5:J1M1-Z
Ordering data	1	1	1	1	
Size	Connection	Condensate drain	Grade of filtration [µm]	Part no.	Туре
Pressure regula	ition range 0.3 7 bar, pl	astic bowl guard, pressure gauge v	with outer scale in MPa		
MSB4	G1/4	Manual	40	8042669	MSB4-1/4-FRC13:J120M1
MSB6	G1/2	Manual	40	8042673	MSB6-1/2-FRC13:J120M1
Pressure regula	ntion range 0.3 7 bar, pl	astic bowl guard, pressure gauge	with outer scale in bar and inner scale in	ı psi	
MSB4	G1/4	Manual	40	531109	MSB4-1/4-FRC1:J5M1
MSB6	G1/2	Manual	40	530230	MSB6-1/2-FRC1:J5M1
Pressure regula	ntion range 0.5 12 bar. r	plastic bowl guard, pressure gauge	with outer scale in bar and inner scale i	in psi	
MSB4	G1/8	Manual	40	531133	MSB4-1/8-FRC5:J1M1
	G1/4		5	531121	MSB4-1/4-FRC7:J3M1
	G1/4	Fully automatic	40	531119	MSB4-1/4-FRC6:J2M1
MSB6	G1/4	Manual	40	530268	MSB6-1/4-FRC5:J1M1
	G3/8		40	530292	MSB6-3/8-FRC5:J1M1
	G1/2		5	530248	MSB6-1/2-FRC7:J3M1
	G1/2	Fully automatic	40	530246	MSB6-1/2-FRC6:J2M1
Droccure regula	ation range 0.5 12 har r	metal howl pressure gauge with o	uter scale in bar and inner scale in psi		
MSB6	G1/2	Manual	40	530252	MSB6-1/2-FRC9:J11M2
			5	530234	MSB6-1/2-FRC11:J9M2
		Fully automatic	40	530232	MSB6-1/2-FRC10:J12M2
			5	530236	MSB6-1/2-FRC12:J10M2

Accessories

Filter cartridges



Ordering data				
Size	Grade of filtration	Part no.	Туре	
	[µm]			
MS4	5 (colour: blue)	534501	MS4-LFP-C	
	40 (colour: white)	534502	MS4-LFP-E	
MS6	5 (colour: blue)	534499	MS6-LFP-C	
	40 (colour: white)	534500	MS6-LFP-E	

Special oil

Ordering data
Scope of delivery



1 litre		152811	OFSW-32			
Ordering data – Padlo	Ordering data – Padlock LRVS-D					
ordering data Tudio	Weight [g]	Part no.	Туре			
	120	193786	LRVS-D			

Part no.

Туре

Festo - Your Partner in Automation





1 Festo Inc.

5300 Explorer Drive Mississauga, ON L4W 5G4 Canada

Festo Customer Interaction Center

Tel: 1877 463 3786 Fax: 1877 393 3786



2 Festo Pneumatic

Av. Ceylán 3, Col. Tequesquináhuac 54020 Tlalnepantla, Estado de México

Multinational Contact Center

01 800 337 8669



3 Festo Corporation

1377 Motor Parkway Suite 310 Islandia, NY 11749



Regional Service Center

7777 Columbia Road Mason, OH 45040

Festo Customer Interaction Center

1 800 993 3786 1 800 963 3786 customer.service.us@festo.com

Connect with us









