

Flow Sensors MS6-SFE

Flow sensors MS6-SFE

Product overview



- Flow range 200 ... 5,000 l/min
- Switch outputs 2x PNP or 2x NPN
- Analogue output 0 ... 10 V or 4 ... 20 mA
- Freely selectable pulse output for consumption measurement
- Illuminated LCD display
- As an individual unit or for installation in MS series service unit combinations

Detailed product information

➔ www.festo.com/catalogue/ms6-sfe


Product overview								
Method of measurement	Measured variable	Type of mounting	Flow measuring range [l/min]	Pneumatic connection 1	Pneumatic connection 2	Electrical output		
						Digital	Analogue	
Flow sensor, thermal	Individual device							
	Flow	Via accessories	200 ... 5,000	G1/2, G3/4 ¹⁾	G1/2	2x PNP	0 ... 10 V	
							4 ... 20 mA	
	Consumption						2x NPN	0 ... 10 V
								4 ... 20 mA
	In MS series service unit combination							
Flow	In-line installation	200 ... 5,000	G1/2, G3/4 ²⁾	G1/2, G3/4 ²⁾		2x PNP	0 ... 10 V	
							4 ... 20 mA	
Consumption						2x NPN	0 ... 10 V	
							4 ... 20 mA	

1) Inlet section with female thread G1/2 and male thread G3/4

2) Dependent on connecting plate selected, must be ordered separately as an accessory ➔ 114

Flow sensors MS6-SFE

Type codes



Flow sensors MS6-SFE

Technical data


FESTO

Sensors
Flow sensors

1.3

Technical data		Individual device	In MS series service unit combination
Design			
Flow measuring range	[l/min]	200 ... 5,000 ¹⁾	
Pneumatic connection 1		G $\frac{1}{2}$, G $\frac{3}{4}$ ²⁾	G $\frac{1}{2}$, G $\frac{3}{4}$ ³⁾
Pneumatic connection 2		G $\frac{1}{2}$	G $\frac{1}{2}$, G $\frac{3}{4}$ ³⁾
Type of display		Illuminated LCD (optimised display)	
Accuracy ⁴⁾		+/- (3% o.m.v. + 0.3% FS)	
Electrical data			
Switch output		2x PNP 2x NPN	
Analogue output	[V]	0 ... 10	
	[mA]	4 ... 20	
Switching element function		N/O contact N/C contact	
Switching function		Threshold value with variable hysteresis Window comparator	
Operating voltage range DC	[V]	15 ... 30	
Max. output current	[mA]	≤ 100	
Electrical connection		Straight plug, M12x1, 5-pin	
Protection against short circuit		Yes	
Protection class		IP65	
Operating and environmental conditions			
Operating pressure	[bar]	0 ... 16	
Operating medium		Filtered compressed air, unlubricated, grade of filtration 40µm Nitrogen Air quality class 5:4:3 to DIN ISO 8573-1	
Ambient temperature	[°C]	0 ... 50	
CE mark (see declaration of conformity)		In accordance with EU EMC directive	
Certification		C-Tick	
Materials			
Housing		Die-cast aluminium, reinforced polyamide	

- 1) Restricted at operating pressure < 5 bar, diagram → www.festo.com
- 2) Inlet section with female thread G $\frac{1}{2}$ and male thread G $\frac{3}{4}$
- 3) Dependent on connecting plate selected, must be ordered separately as an accessory → 114
- 4) % o.m.v. = % of measured value
% FS = % of measuring range's final value (full scale)

Ordering data						
Variant	Flow measuring range [l/min]	Analogue output	Switch output			
			2x PNP		2x NPN	
			Part No.	Type	Part No.	Type
Individual device						
	200 ... 5,000	0 ... 10 V	538 418	MS6-SFE-F5-AGD-P2U-M12	538 420	MS6-SFE-F5-AGD-N2U-M12
		4 ... 20 mA	538 417	MS6-SFE-F5-AGD-P2I-M12	538 419	MS6-SFE-F5-AGD-N2I-M12
In MS series service unit combination						
	200 ... 5,000	0 ... 10 V	538 422	MS6-SFE-F5-P2U-M12	538 424	MS6-SFE-F5-N2U-M12
		4 ... 20 mA	538 421	MS6-SFE-F5-P2I-M12	538 423	MS6-SFE-F5-N2I-M12

Flow sensors MS6-SFE



Peripherals overview, sample applications



Peripherals overview

Individual device, with connecting plates and stabilizing attachment

For service unit combination, with laminar flow cartridge




Accessories	
1	Mounting bracket MS6-WB
2	Connecting plate MS6-AG... (included in scope of delivery for individual unit)
3	Module connector MS6-MV

Accessories	
4	Mounting bracket MS6-WP
5	Mounting bracket MS6-WPB
6	Mounting bracket MS6-WPM
7	Connecting cable NEBU-M12G5

Ordering data – Mounting attachments		
	Part No.	Type
	532 196	MS6-WB
	526 082	MS6-AGD
	526 083	MS6-AGE
	532 799	MS6-MV
	532 195	MS6-WP
	526 074	MS6-WPB
	526 073	MS6-WPM-D
	532 186	MS6-WPM-2D

Ordering data – Connecting cables			Technical data → 261	
	Number of wires	Cable length [m]	Part No.	Type
M12x1, straight socket				
	5	2.5	541 330	NEBU-M12G5-K-2.5-LE5
	5	5	541 331	NEBU-M12G5-K-5-LE5

Application example



- Compressed air consumption and function monitoring of various systems in the production process

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

United States

Customer Resource Center
502 Earth City Expy., Suite 125
Earth City, MO 63045

For ordering assistance, or to find
your nearest Festo Distributor,

Call: 1.800.99.FESTO

Fax: 1.800.96.FESTO

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO

Fax: 1.800.96.FESTO

Email: product.support@us.festo.com

Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788
www.festo.com/us

Sales Offices

Appleton

N. 922 Tower View Drive, Suite N
Greenville, WI 54942

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057

Detroit - Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326

New York

395 Moreland Road
Hauppauge, NY 11788

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550

Design and Manufacturing Operations



East: 395 Moreland Road, Hauppauge, NY 11788



Central: 1441 East Business Center Drive, Mt. Prospect, IL 60056



West: 4935 Southfront Road, Suite F, Livermore, CA 94550

Mexico

Headquarters

Festo Pneumatic, S.A.
Av. Ceylán 3, Col. Tequesquahuac
54020 Tlalnepantla, Edo. de México
Call: 011 52 [55] 53 21 66 00
Fax: 011 52 [55] 53 21 66 65
Email: festo.mexico@mx.festo.com
www.festo.com/mx



Canada

Headquarters

Festo Inc.
5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Call: 1.905.624.9000
Fax: 1.905.624.9001
Email: info.ca@ca.festo.com
www.festo.com/ca



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan
Latvia Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com