

Pressure regulators MS-LR/LRB/LRP/LRPB/LRE, MS series

FESTO



Key features

Service unit components of the MS series

Solutions for every application

With its large product range, highly effective components and a wide choice of functions, the MS series from Festo offers a complete concept for compressed air preparation. It is suitable for simple standard applications as well as for application-specific solutions with very high-quality requirements.

Available as individual components, pre-assembled combinations ex-stock, application-specific combinations or complete ready-to-install solutions. The five sizes of the MS series achieve maximum flow rates with minimum space requirements.

CAD models and configurator

Convenient tools for planning and selecting application-specific individual devices and combinations. The product configurator can be used to configure customised solutions quickly and to transfer the order data without any hassle.

Engineering tools

Selection tool for choosing the right service unit combination without oversizing, and with the right air purity class:

→ www.festo.com/engineering/wartungseinheit

Freely combinable functional modules

Pressure regulators, on/off and soft-start valves with safety function, filters, pressure and flow sensors, dryers, sensors and lubricators can be assembled into a suitable solution for every task. Thanks to the modular structure the components can be combined as required. The simple connection system saves time because there is no need to disassemble the entire combination when replacing individual modules.

Many of the components are also UL and ATEX certified.

Air quality

This program supports configuring an appropriate service unit. Please insert the required air cleanliness either by your application or an ISO code or by direct selection of air filters.

Selection criteria: Application

Filter combination is proposed based upon your selected application

- ☐ standard pneumatics
operation of valves and cylinders, e.g. in automotive industry, secondary packaging
- ☐ mining and building industry
applications without special air cleanliness requirements
- ☐ application of pressure operated tools and machines
pneumatic hammer, air engine, positioning with proportional valve
- ☐ electronic, flatpanel and solar industry,
textile and paper production
application with residual oil content <0.5 mg/m³
- ☐ painting, powder coating, air bearing
application with residual oil content <0.01 mg/m³
- ☐ food and beverage industry, optics
application with residual oil content <0.003 mg/m³
reduction of oil vapours and aromas

Selection criteria: ISO-class

Filter combination is proposed based upon the air cleanliness class according to ISO 8573-1:2010

particle : 4 * : oil



* Downstream from the compressor the water content is assumed to be ISO class 4, better classes can be achieved by applying an adsorption dryer PAD or a membrane dryer LDM

Direct filter selection

Independent selection of filter combination

- ☐ 40 µm Filter
- ☐ 5 µm Filter
- ☐ 1 µm Fine Filter
- ☐ 0.01 µm Micro Filter *
- ☐ Active Carbon Filter



* To enhance the filter lifetime and in consequence the maintenance interval arrange a 1 µm Fine Filter in front of the 0.01 µm Micro Filter as a preliminary filter.

Integrated sensors

Pressure and flow sensors

Safety functions

Soft-start/quick exhaust valves

MS6-SV/MS9-SV

Saving energy

Service unit combinations MSE6

Intelligent mix of sizes



- Maximum machine availability thanks to controlled processes
- Reliable air preparation and system supply
- Integrated or stand-alone
- Easy to connect with M8/M12 plug



- Fast and reliable exhausting of systems up to Performance Level e, certified to EN ISO 13849-1
- Integrated soft-start function



- Fully automatic monitoring and regulation of compressed air supply
- Compressed air is automatically shut off in stand-by mode
- Detection and notification of leakages
- Condition monitoring of relevant process data



- Optimum flow rate with a size that is up to 18% smaller
- Excellent energy efficiency
- Cost-optimised combinations – save up to 30%!

Size differences

Size		MS4	MS6	MS9	MS12
Grid dimension	[mm]	40	62	90	124
Connection sizes		G1/8, G1/4, G3/8	G1/4, G3/8, G1/2, G3/4	G1/2, G3/4, G1, G1 1/4, G1 1/2	G1, G1 1/4, G1 1/2, G2
Standard nominal flow rate q _N ¹⁾	[l/min]	1800	6500	20000	22000

1) Using pressure regulator MS-LR as an example

Key features

Note

Information

The next few pages provide a brief overview of the product range for the components of the MS series service units.

You can find detailed information and all the technical data in the documentation for the relevant service unit component.

Accessories such as connecting plates or mounting brackets can be ordered either via the configurator or separately.

Designing a service unit combination

The order of the individual components within a service unit combination is relevant for safety and functionality. The service unit components cannot be combined in any order in the flow direction. There are restrictions and rules.

The configurator for the service unit combination MSB is a reliable and convenient way of combining the individual service unit components and ensures compliance with the applicable rules. As a result, you get a fully assembled combination with UL or ATEX certification, if necessary. When combining a unit from individually configured and ordered service unit components, the points on the right must be adhered to under all circumstances.

- Regulators MS-LFR/LR/LRP are only permissible in the flow direction with the same or decreasing pressure regulation range
- Filters MS-LFR/LF/LFM/LFX are only permissible in the flow direction with an increasing grade of filtration
- Lubricators MS-LOE are not permitted in the flow direction upstream of a filter MS-LFR/LFM/LF/LFX, water separator MS-LWS or membrane air dryer MS-LDM1
- A micro filter MS-LFM must be installed in the flow direction upstream of an activated carbon filter MS-LFX or membrane air dryer MS-LDM1
- A flow sensor SFAM cannot be installed directly downstream of a regulator MS-LFR/LR; a branching module MS-FRM must be positioned between them
- A soft-start/quick exhaust valve MS-SV must be the last service unit component in the flow direction

Product range for service unit components MS series

Type	Description	Size	Pneumatic connection					
			Push-in connector	Female thread			Connecting plate with thread	
				M	G	NPT	G	NPT
Combinations								
Service unit combinations MSB-FRC Datasheets → Internet: msb								
	Combinations of filter regulator and lubricator	4	–	–	1/8, 1/4	–	–	–
		6	–	–	1/4, 3/8, 1/2	–	–	–
Service unit combinations MSB Datasheets → Internet: msb								
	Certain predefined combinations	4	–	–	1/4	–	–	–
		6	–	–	1/2	–	–	–
	Freely configurable combinations	4	–	–	1/8, 1/4	–	1/8, 1/4, 3/8	1/8, 1/4, 3/8
		6	–	–	1/4, 3/8, 1/2	–	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
		9	–	–	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
Service unit combinations MSE6 Datasheets → Internet: mse6								
	Combinations with fieldbus connection for measuring pressure, flow rate and consumption	6	–	–	–	–	1/2	–

Key features

Product range for service unit components MS series								
Type	Description	Size	Pneumatic connection					
			Push-in connector	Female thread			Connecting plate with thread	
				M	G	NPT	G	NPT
Individual devices								
Filter regulators MS-LFR			Datasheets → Internet: ms2-lfr; ms4-lfr; ms6-lfr; ms9-lfr; ms12-lfr					
	Filter and pressure regulator in a single device, grade of filtration 5 or 40 µm	2	QS-6	M5	–	–	–	–
		4	–	–	1/8, 1/4	–	1/8, 1/4, 3/8	1/8, 1/4, 3/8
		6	–	–	1/4, 3/8, 1/2	–	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
		9	–	–	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
		12	–	–	–	–	1, 1 1/4, 1 1/2, 2	–
Filter regulators MS-LFR-B			Datasheets → Internet: ms4-lfr-b; ms6-lfr-b					
	Filter and pressure regulator in a single device in polymer housing, grade of filtration 5 or 40 µm	4	–	–	1/4	–	–	–
		6	–	–	1/2	–	–	–
Filters MS-LF			Datasheets → Internet: ms4-lf; ms6-lf; ms9-lf; ms12-lf					
	Grade of filtration 5 or 40 µm	4	–	–	1/8, 1/4	–	1/8, 1/4, 3/8	1/8, 1/4, 3/8
		6	–	–	1/4, 3/8, 1/2	–	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
		9	–	–	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
		12	–	–	–	–	1, 1 1/4, 1 1/2, 2	–
Fine and micro filters MS-LFM			Datasheets → Internet: ms4-lfm; ms6-lfm; ms9-lfm; ms12-lfm					
	Grade of filtration 0.01 or 1 µm	4	–	–	1/8, 1/4	–	1/8, 1/4, 3/8	1/8, 1/4, 3/8
		6	–	–	1/4, 3/8, 1/2	–	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
		9	–	–	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
		12	–	–	–	–	1, 1 1/4, 1 1/2, 2	–
Activated carbon filters MS-LFX			Datasheets → Internet: ms4-lfx; ms6-lfx; ms9-lfx; ms12-lfx					
	For removing liquid and gaseous oil particles	4	–	–	1/8, 1/4	–	1/8, 1/4, 3/8	1/8, 1/4, 3/8
		6	–	–	1/4, 3/8, 1/2	–	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
		9	–	–	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
		12	–	–	–	–	1, 1 1/4, 1 1/2, 2	–
Water separator MS-LWS			Datasheets → Internet: ms6-lws; ms9-lws; ms12-lws					
	Removes condensate from compressed air, maintenance-free	6	–	–	1/4, 3/8, 1/2	–	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
		9	–	–	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
		12	–	–	–	–	1, 1 1/4, 1 1/2, 2	–

Key features

Product range for service unit components MS series								
Type	Description	Size	Pneumatic connection					
			Push-in connector	Female thread			Connecting plate with thread	
				M	G	NPT	G	NPT
Individual devices								
Pressure regulators MS-LR			Datasheets → Internet: ms2-lr; ms4-lr; ms6-lr; ms9-lr; ms12-lr					
	For setting the required operating pressure, 4 pressure regulation ranges	2	QS-6	M5	–	–	–	–
		4	–	–	1/8, 1/4	–	1/8, 1/4, 3/8	1/8, 1/4, 3/8
		6	–	–	1/4, 3/8, 1/2	–	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
		9	–	–	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
		12	–	–	–	–	1, 1 1/4, 1 1/2, 2	–
Pressure regulators MS-LR-B			Datasheets → Internet: ms4-lr-b; ms6-lr-b					
	For setting the required operating pressure, in polymer housing	4	–	–	1/4	–	–	–
		6	–	–	1/2	–	–	–
Pressure regulators MS-LRB			Datasheets → Internet: ms4-lrb; ms6-lrb					
	For configuring a regulator manifold with independent pressure regulation ranges. Pressure output is at the front or rear.	4	–	–	1/4	–	1/8, 1/4, 3/8	–
		6	–	–	1/2	–	1/4, 3/8, 1/2, 3/4	–
Precision pressure regulators MS-LRP			Datasheets → Internet: ms6-lrp					
	For precisely setting the required operating pressure, 4 pressure regulation ranges, pressure hysteresis 0.02 bar	6	–	–	1/4, 3/8, 1/2	–	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
Precision pressure regulators MS-LRPB			Datasheets → Internet: ms6-lrpb					
	For configuring a regulator manifold with independent pressure regulation ranges. Pressure output is at the front or rear.	6	–	–	1/2	–	1/4, 3/8, 1/2, 3/4	–
Lubricators MS-LOE			Datasheets → Internet: ms4-loe; ms6-loe; ms9-loe; ms12-loe					
	Add a precisely dosed amount of oil to the compressed air. The amount of oil mist is proportional to the compressed air flow rate.	4	–	–	1/8, 1/4	–	1/8, 1/4, 3/8	1/8, 1/4, 3/8
		6	–	–	1/4, 3/8, 1/2	–	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
		9	–	–	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
		12	–	–	–	–	1, 1 1/4, 1 1/2, 2	–

Key features


Product range for service unit components MS series								
Type	Description	Size	Pneumatic connection					
			Push-in connector	Female thread			Connecting plate with thread	
				M	G	NPT	G	NPT
Individual devices								
On/off valves MS-EM			Datasheets → Internet: ms4-em; ms6-em; ms9-em; ms12-em					
	Manually actuated on/off valve for pressurising and exhausting pneumatic systems.	4	–	–	1/8, 1/4	–	1/8, 1/4, 3/8	1/8, 1/4, 3/8
		6	–	–	1/4, 3/8, 1/2	–	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
		9	–	–	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
		12	–	–	–	–	1, 1 1/4, 1 1/2, 2	–
On/off valves MS-EE								
	Electrically actuated on/off valve for pressurising and exhausting pneumatic systems.	4	–	–	1/8, 1/4	–	1/8, 1/4, 3/8	1/8, 1/4, 3/8
		6	–	–	1/4, 3/8, 1/2	–	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
		9	–	–	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
		12	–	–	–	–	1, 1 1/4, 1 1/2, 2	–
On/off valves MS-EE-B								
	Electrically actuated on/off valve in polymer housing for pressurising and exhausting pneumatic systems.	4	–	–	1/4	–	–	–
		6	–	–	1/2	–	–	–
Soft-start valves MS-DL								
	Pneumatically actuated soft-start valve for slowly pressurising pneumatic systems.	4	–	–	1/8, 1/4	–	1/8, 1/4, 3/8	1/8, 1/4, 3/8
		6	–	–	1/4, 3/8, 1/2	–	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
		12	–	–	–	–	1, 1 1/4, 1 1/2, 2	–
Soft-start valves MS-DE								
	Electrically actuated soft-start valve for slowly pressurising pneumatic systems.	4	–	–	1/8, 1/4	–	1/8, 1/4, 3/8	1/8, 1/4, 3/8
		6	–	–	1/4, 3/8, 1/2	–	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
		12	–	–	–	–	1, 1 1/4, 1 1/2, 2	–
On/off valves MS-EDE-B								
	Electrically actuated soft-start valve in polymer housing for slowly pressurising and exhausting pneumatic systems.	4	–	–	1/4	–	–	–
		6	–	–	1/2	–	–	–
Soft-start/quick exhaust valves MS-SV								
	For building up pressure gradually and reducing pressure quickly and safely in pneumatic piping systems. Up to category 1, PL c.	6	–	–	1/2	–	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
		9	–	–	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
	Up to category 3, PL d. Up to category 4, PL e in the case of optional extension.	6	–	–	1/2	–	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
	Up to category 4, PL e.	6	–	–	1/2	–	1/4, 3/8, 1/2, 3/4	–

Key features

Product range for service unit components MS series								
Type	Description	Size	Pneumatic connection					
			Push-in connector	Female thread			Connecting plate with thread	
				M	G	NPT	G	NPT
Individual devices								
Membrane air dryer MS-LDM1 Datasheets → Internet: ms4-ldm; ms6-ldm								
	Wear-free membrane dryer with internal air consumption	4	–	–	1/8, 1/4	–	1/8, 1/4, 3/8	1/8, 1/4, 3/8
		6	–	–	1/4, 3/8, 1/2	–	1/4, 3/8, 1/2, 3/4	1/4, 3/8, 1/2, 3/4
Branching modules MS-FRM Datasheets → Internet: ms4-frm; ms6-frm; ms9-frm; ms12-frm								
	Compressed air distributors with 4 connections	4	–	–	1/8, 1/4	–	1/8, 1/4, 3/8	–
		6	–	–	1/4, 3/8, 1/2	–	1/4, 3/8, 1/2, 3/4	–
		9	–	–	3/4, 1	3/4, 1	1/2, 3/4, 1, 1 1/4, 1 1/2	1/2, 3/4, 1, 1 1/4, 1 1/2
		12	–	–	–	–	1, 1 1/4, 1 1/2, 2	–
Distributor blocks MS-FRM-FRZ Datasheets → Internet: ms4-frm-frz; ms6-frm-frz								
	Compressed air distributors with 4 connections and half the grid width	4	–	–	–	–	–	–
		6	–	–	–	–	–	–
Flow sensors SFAM Datasheets → Internet: sfam								
	For absolute flow rate information and cumulative air consumption measurement	6	–	–	–	–	1/2	1/2
		9	–	–	–	–	1, 1 1/2	1, 1 1/2
Proportional-pressure regulator VPPE Datasheets → Internet: vppe								
	Piloted pressure regulator with or without display	6	–	–	–	–	–	–
		9	–	–	–	–	–	–

Peripherals overview

Pressure regulator MS4/MS6-LR



Note



Additional accessories:

- Module connectors for combination with size MS4/MS6 or size MS9
→ Internet: amv, rmv, armv
- Adapters for mounting on profiles
→ Internet: ipm-80, ipm-40-80, ipm-80-80

Pressure regulator with rotary knob pressure gauge

MS4-LR-...-DM2

MS4-LR-...-DM1/MS6-LR-...-DM2



Peripherals overview

Mounting attachments and accessories ¹⁾		Individual device		Combination		→ Page/Internet
		Without connecting plate	With connecting plate	Without connecting plate	With connecting plate	
[1]	Pressure regulator MS4/MS6-LR	■	■	■	■	8
[2]	Mounting bracket MS4/6-WB	■	■	–	–	ms4-wb, ms6-wb
[3]	Mounting bracket MS4-WBM	■	■	–	–	ms4-wbm
[4]	Mounting bracket MS4/6-WR	■	■	–	–	ms4-wr, ms6-wr
[5]	Knurled nut (included in the scope of delivery) MS-LR	■	■	–	–	–
[6]	Padlock LRVS-D	■	■	■	■	106
[7]	Cover cap MS4/6-END	■	–	■	–	ms4-end, ms6-end
[8]	Module connector MS4/6-MV	–	■	■	■	ms4-mv, ms6-mv
[9]	Connecting plate SET MS4/6-AG...	–	■	–	■	ms4-ag, ms6-ag
	Connecting plate SET MS4/6-AQ...	–	■	–	■	ms4-aq, ms6-aq
[10]	Pressure sensor with LCD display AD11/AD12	■	■	■	■	26
[11]	Connecting cable NEBA-M8...-LE4/NEBA-M12...-LE4	■	■	■	■	106
[12]	Pressure sensor without display AD7 ... AD10	■	■	■	■	26
[13]	Connecting cable NEBA-M8...-LE3	■	■	■	■	106
[14]	Adapter for EN pressure gauge 1/8, 1/4 A8/A4	■	■	■	■	26
[15]	Pressure gauge MA	■	■	■	■	106
[16]	Cover plate VS	■	■	■	■	26
–	Mounting bracket MS4/6-WP/WPB/WPE/WPM	–	■	■	■	ms4-wp, ms6-wp

1) Connecting plates and certain mounting brackets can also be ordered via the modular product system → page 26

Type codes

001	Series	
MS	MS series	

002	Size	
4	Grid dimension 40 mm	

003	Function	
LR	Pressure regulator	

004	Pneumatic connection	
1/8	Female thread G1/8	
1/4	Female thread G1/4	
AGA	Sub-base G1/8	
AGB	Sub-base G1/4	
AGC	Sub-base G3/8	
AQK	Sub-base 1/8 NPT	
AQN	Sub-base 1/4 NPT	
AQP	Sub-base 3/8 NPT	

005	Pressure range/actuation	
D5	0.3 ... 4 bar, manually actuated	
D6	0.3 ... 7 bar, manually actuated	
D7	0.5 ... 12 bar, manually actuated	

006	Pressure gauge alternatives	
	None	
A4	Adapter for EN pressure gauge 1/4, without pressure gauge	
A8	Adapter for EN pressure gauge 1/8, without pressure gauge	
AD7	Pressure sensor with switching display, M8 plug, threshold value comparator, PNP, N/O	
AD8	Pressure sensor with switching display, M8 plug, threshold value comparator, PNP, N/C	
AD9	Pressure sensor with switching display, M8 plug, window comparator, PNP, N/O	
AD10	Pressure sensor with operational status indicator, M8 plug, window comparator, PNP, N/C	
AD11	Pressure sensor with LCD display, M12 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V, 4...20 mA	
AD12	Pressure sensor with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V, 4...20 mA	
RG	Integrated pressure gauge, red/green scale	
VS	Cover plate	

007	Alternative pressure gauge scale	
	MS pressure gauge	
PSI	psi	
MPA	MPa	

008	Secondary exhausting	
	With secondary exhausting	
OS	Without secondary exhaust	

009	Rotary knob alternative	
	None	
LD	Long rotary knob	
DM1	Rotary knob pressure gauge, small	
DM2	Rotary knob pressure gauge, large	

010	Alternative mounting position	
	None	
KD	Rotary knob underneath	

011	Lockability	
	None	
AS	Can be locked using accessories	
E11	With integrated lock	

012	Type of mounting	
	Without mounting bracket	
WR	Mounting bracket with knurled nut on regulator knob	
WP	Mounting bracket basic design	
WPM	Mounting bracket for hooking in service unit components	
WB	Mounting centrally at rear (wall mounting top and bottom), connecting plates not required	
WBM	Mounting centrally at rear (wall mounting top), connecting plates not required	

013	EU certification	
	None	
EX4	II 2GD	

014	UL certification	
	None	
UL1	cULus ordinary location for Canada and USA	

015	Flow direction	
	Flow direction from left to right	
Z	Flow direction from right to left	


Type codes

001	Series	
MS	MS series	
002	Size	
6	Grid dimension 62 mm	
003	Function	
LR	Pressure regulator	
004	Pneumatic connection	
1/4	Female thread G1/4	
3/8	Female thread G3/8	
1/2	Female thread G1/2	
AGB	Sub-base G1/4	
AGC	Sub-base G3/8	
AGD	Sub-base G1/2	
AGE	Sub-base G3/4	
AGF	Sub-base G1	
AQN	Sub-base 1/4 NPT	
AQP	Sub-base 3/8 NPT	
AQR	Sub-base 1/2 NPT	
AQS	Sub-base 3/4 NPT	
005	Pressure range/actuation	
D5	0.3 ... 4 bar, manually actuated	
D6	0.3 ... 7 bar, manually actuated	
D7	0.5 ... 12 bar, manually actuated	
D8	0.5 ... 16 bar, manually actuated	
006	Pressure gauge alternatives	
	None	
A4	Adapter for EN pressure gauge 1/4, without pressure gauge	
A8	Adapter for EN pressure gauge 1/8, without pressure gauge	
AD7	Pressure sensor with switching display, M8 plug, threshold value comparator, PNP, N/O	
AD8	Pressure sensor with switching display, M8 plug, threshold value comparator, PNP, N/C	
AD9	Pressure sensor with switching display, M8 plug, window comparator, PNP, N/O	
AD10	Pressure sensor with operational status indicator, M8 plug, window comparator, PNP, N/C	
AD11	Pressure sensor with LCD display, M12 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V, 4...20 mA	
AD12	Pressure sensor with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V, 4...20 mA	
RG	Integrated pressure gauge, red/green scale	
VS	Cover plate	

007	Alternative pressure gauge scale	
	MS pressure gauge	
PSI	psi	
MPA	MPa	
008	Secondary exhausting	
	With secondary exhausting	
OS	Without secondary exhaust	
009	Rotary knob alternative	
	None	
LD	Long rotary knob	
DM2	Rotary knob pressure gauge, large	
010	Alternative mounting position	
	None	
KD	Rotary knob underneath	
011	Lockability	
	None	
AS	Can be locked using accessories	
E11	With integrated lock	
012	Type of mounting	
	Without mounting bracket	
WR	Mounting bracket with knurled nut on regulator knob	
WP	Mounting bracket basic design	
WPM	Mounting bracket for hooking in service unit components	
WB	Mounting centrally at rear (wall mounting top and bottom), connecting plates not required	
013	EU certification	
	None	
EX4	II 2GD	
014	UL certification	
	None	
UL1	cULus ordinary location for Canada and USA	
015	Flow direction	
	Flow direction from left to right	
Z	Flow direction from right to left	

Datasheet

With pressure gauge



- - Flow rate
1000 ... 7500 l/min
- - Temperature range
-10 ... +60 °C
- - Operating pressure
0.8 ... 20 bar
- - www.festo.com



The pressure regulator maintains a constant working pressure (secondary side), independently of the pressure fluctuations in the system (primary side) and the air consumption.

- Good regulation characteristics with minimal hysteresis and input pressure compensation
- High flow rate with minimal pressure drop
- Available with and without secondary exhausting
- Actuator lock to protect the set values from being adjusted
- Four pressure regulation ranges: 0.3 ... 4 bar, 0.3 ... 7 bar, 0.5 ... 12 bar and 0.5 ... 16 bar
- Two pressure gauge connections for different installation options
- Return flow option for exhausting from output 2 to output 1 already integrated
- Optional pressure sensor
- Optional rotary knob pressure gauge
- Optional device variant EX4 for use in potentially explosive areas in zones 1, 2, 21 and 22

General technical data				
Size		MS4		MS6
Pneumatic connection 1, 2				
Female thread		G1/8 or G1/4		G1/4, G3/8 or G1/2
Connecting plate	[AG...]	G1/8, G1/4 or G3/8		G1/4, G3/8, G1/2, G3/4 or G1
	[AQ...]	1/8 NPT, 1/4 NPT or 3/8 NPT		1/4 NPT, 3/8 NPT, 1/2 NPT or 3/4 NPT
Design		Directly actuated diaphragm regulator		
Regulator function		Output pressure constant, with input pressure compensation, with return flow, with/without secondary exhausting		
Type of mounting		With accessories		
		In-line installation		
		Front panel mounting		
Mounting position		Any		
Actuator lock		Rotary knob with latch		
		Rotary knob with latch, can be locked using accessories		
		Rotary knob with integrated lock		
Pressure regulation range/ actuation	[D5]	[bar]	0.3 ... 4, manually actuated ¹⁾	
	[D6]	[bar]	0.3 ... 7, manually actuated ¹⁾	
	[D7]	[bar]	0.5 ... 12, manually actuated (0.5 ... 10 with pressure sensor or with UL certification) ¹⁾	
	[D8]	[bar]	–	0.5 ... 16, manually actuated (0.5 ... 10 with UL certification)
Max. pressure hysteresis		[bar]	0.25 (0.4 with rotary knob pressure gauge)	
Pressure indication		With pressure sensor for indicating the output pressure via LCD display and electrical output		
		With pressure sensor for indicating the output pressure via the switching status indicator and electrical output		
		Via pressure gauge for displaying the output pressure		
		With pressure gauge with red/green scale for indicating the output pressure		
		Via pressure gauge in the rotary knob for displaying the output pressure		
		Prepared for G1/8		–
		Prepared for G1/4		

1) MS4: the pressure regulation range for pressure regulators with rotary knob pressure gauge starts at 0.8 bar.

- - Note: This product conforms to ISO 1179-1 and ISO 228-1.

Datasheet

Standard nominal flow rate $q_{nN}^{1)}$ [l/min]							
Size	MS4			MS6			
Pneumatic connection	G1/8	G1/4	G3/8	G1/4	G3/8	G1/2	G3/4
Pressure regulation range	[D5]	1200 ²⁾	2100 ²⁾	–	2400 ²⁾	5500 ²⁾	7500 ²⁾
	[D6]	1150	1800	1800	3000	5800	6500
	[D7]	1000	1700 ³⁾	1700	2700	4500	5500
	[D8]	–	–	–	2200	4000	4500

- 1) Measured at $p_1 = 10$ bar and $p_2 = 6$ bar, $\Delta p = 1$ bar
2) Measured at $p_1 = 10$ bar and $p_2 = 3$ bar, $\Delta p = 1$ bar
3) With a rotary knob pressure gauge, $q_{nN} = 800$ l/min, $q_{n\max} = 2200$ l/min

Operating and environmental conditions		
Size	MS4	MS6
Operating pressure [bar]	0.8 ... 14 (0.8 ... 10) ¹⁾	
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]	
	Inert gases	
Note on the operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)	
Ambient temperature [°C]	–10 ... +60 (0 ... +50) ²⁾	
Temperature of medium [°C]	–10 ... +60 (0 ... +50) ²⁾	
Storage temperature [°C]	–10 ... +60	
Corrosion resistance class CRC ³⁾	2	
Food safe ⁴⁾	See supplementary material information	
UL certification ⁴⁾	c UL us - Recognized (OL)	

- 1) Value in brackets applies to MS4/MS6-LR with UL certification.
2) Value in brackets applies to MS4/MS6-LR with pressure sensor.
3) More information www.festo.com/x/topic/crc
4) More information: www.festo.com/catalogue/ms-lr → Support/Downloads.

ATEX	
EU certification	[EX4]
ATEX category for gas	II 2G
Type of ignition protection for gas	Ex h IIC T6 Gb X
ATEX category for dust	II 2D
Type of ignition protection for dust	Ex h IIIC T60°C Db X
Explosion-proof ambient temperature	–10 °C ≤ Ta ≤ +60 °C
Explosion protection certification outside the EU	EPL Db (GB) EPL Gb (GB)
CE marking (see declaration of conformity) ¹⁾	To EU Explosion Protection Directive (ATEX)
UKCA marking (see declaration of conformity) ¹⁾	To UK explosion regulations


- 1) More information: www.festo.com/catalogue/ms-lr → Support/Downloads.

Weight [g]		
Size	MS4	MS6
Pressure regulator	225	730
Pressure regulator with rotary knob with integrated lock	350	1000
Pressure regulator with connecting plates	355	1030
Connecting plates [AG...]/[AQ...]	128	300
Mounting bracket	[WBM]	–
	[WB]	121
	[WR]	90
	[WP]	76
	[WPM]	144

Datasheet

Materials

Sectional view




Pressure regulator		
[1]	Housing	Die-cast aluminium
[2]	Rotary knob	PA, POM
	Rotary knob with integrated lock	Aluminium
[3]	Diaphragms	NBR
[4]	Bottom cover	PET
[5]	Springs	Steel
-	Seals	NBR
Note on materials		RoHS-compliant
LABS (PWIS) conformity		VDMA24364-B1/B2-L


Standard flow rate q_n as a function of output pressure p_2 ($p_1 = 10$ bar)

Input pressure $p_1 = 10$ bar

MS4-LR-1/8




MS4-LR-1/4




1) There is a higher initial pressure drop in the characteristic curve for variant DM1/DM2.

MS6-LR-1/4



MS6-LR-3/8




Input pressure $p_1 = 10$ bar

— D6: 0.3 ... 7 bar
- - - D7: 0.5 ... 12 bar

MS6-LR-1/2

Input pressure $p_1 = 10$ bar



— D6: 0.3 ... 7 bar
- - - D7: 0.5 ... 12 bar


Datasheet

Dimensions – Basic version


Download CAD data → www.festo.com

- [] Integrated MS pressure gauge with standard scale
- [RG] Integrated MS pressure gauge with red/green scale
- [AS] Rotary knob with latch, can be locked using accessories

MS4



MS6



→ Flow direction


Type	B1	B2	B3		D1	D2 Ø	L1	L2	L3	L4
			Standard scale	Red/green scale						
MS4-LR-1/8	40	21	57	58.5	G1/8	37.2	59	27	60.2	–
MS4-LR-1/4					G1/4					
MS6-LR-1/4	62	31	77	78.5	G1/4	51.2	94	39	95.1	85
MS6-LR-3/8					G3/8					
MS6-LR-1/2					G1/2					

Note: This product conforms to ISO 1179-1 and ISO 228-1.

Datasheet

Dimensions – Alternative mounting position Download CAD data → www.festo.com

[KD] Rotary knob underneath



Type	B1	B2	B3		D1	D2 ø	L1	L2	L3	L4
			Standard scale	Red/green scale						
MS4-LR-1/8-...-KD	40	21	57	58.5	G1/8	37.2	59	27	60.2	–
MS4-LR-1/4-...-KD					G1/4					
MS6-LR-1/4-...-KD	62	31	77	78.5	G1/4	51.2	94	39	95.1	85
MS6-LR-3/8-...-KD					G3/8					
MS6-LR-1/2-...-KD					G1/2					

– † – Note: This product conforms to ISO 1179-1 and ISO 228-1.

Datasheet


Dimensions – Pressure gauge alternatives

Download CAD data → www.festo.com

[VS] Cover plate

[A8] Adapter for EN pressure gauge 1/8, without pressure gauge

[A4] Adapter for EN pressure gauge 1/4, without pressure gauge



→ Flow direction

Type	B2	B3	D1	D4
MS4-LR-1/8-...-VS	21	54	G1/8	–
MS4-LR-1/4-...-VS			G1/4	
MS4-LR-1/8-...-A8	21	58.5	G1/8	G1/8
MS4-LR-1/4-...-A8			G1/4	
MS4-LR-1/8-...-A4	21	58.5	G1/8	G1/4
MS4-LR-1/4-...-A4			G1/4	
MS6-LR-1/4-...-VS	31	76	G1/4	–
MS6-LR-3/8-...-VS			G3/8	
MS6-LR-1/2-...-VS			G1/2	
MS6-LR-1/4-...-A4	31	78.5	G1/4	G1/4
MS6-LR-3/8-...-A4			G3/8	
MS6-LR-1/2-...-A4			G1/2	

Note: This product conforms to ISO 1179-1 and ISO 228-1.

Datasheet

Dimensions – Pressure gauge alternatives

[AD7 ... 10] Pressure sensor without LCD display (switching status indicator only)

Technical drawing of pressure gauge alternatives. The front view shows dimensions B5 (width) and B6 (bottom width). The side view shows dimensions B2 (width), B3 (height), and D6 (depth). Arrows 1 and 2 indicate flow direction. A small cone symbol is shown below the side view.

Variant AD7:
SDE5-D10-O-...-P-M8 with 3-pin
M8x1 plug, threshold value compar-
ator, 1 switching output PNP, N/O
contact

Variant AD8:
SDE5-D10-C-...-P-M8 with 1x 3-pin
M8 plug, threshold value compar-
ator, 1 switching output PNP, N/C con-
tact

Variant AD9:
SDE5-D10-O3-...-P-M8 with 1x 3-pin
M8 plug, window comparator,
1 switching output PNP, N/O contact

Variant AD10:
SDE5-D10-C3-...-P-M8 with 1x 3-pin
M8 plug, window comparator,
1 switching output PNP, N/C contact

Download CAD data → www.festo.com

Datasheets → Internet: sde5

Type	B2	B3	B5	B6	D6
MS4-LR-...-AD7/AD8/AD9/AD10	21	59.1	32	16	M8x1
MS6-LR-...-AD7/AD8/AD9/AD10	31	79.1	51	16	M8x1

⚡ Note: This product conforms to ISO 1179-1 and ISO 228-1.

18

→Internet: www.festo.com/catalogue/...

Subject to change – 2025/11


Datasheet

Dimensions – Pressure gauge alternatives

Download CAD data → www.festo.com

[AD11/AD12] Pressure sensor with LCD display

Datasheets → Internet: spau



Variant AD11:

SPAU-P10R... (10 bar) for pressure range D5/D6

SPAU-P12R... (12 bar) for pressure range D7

SPAU-P16R... (16 bar) for pressure range D8

with plug M12, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA


Variant AD12:

SSPAU-P10R... (10 bar) for pressure range D5/D6

SPAU-P12R... (12 bar) for pressure range D7

SPAU-P16R... (16 bar) for pressure range D8

with plug M8, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA



→ Flow direction

Type	B2	B3	B4	B5	B6	D6	L5	L6
MS4-LR...-AD11	21	81.2	73.3	32	32	M12x1	41.2	39
MS4-LR...-AD12	21	81.2	73.3	32	32	M8x1	37.9	39
MS6-LR...-AD11	31	101.8	93.7	51	32	M12x1	41.2	39
MS6-LR...-AD12	31	101.8	93.7	51	32	M8x1	37.9	39


Note: This product conforms to ISO 1179-1 and ISO 228-1.

Datasheet

Dimensions – Pneumatic connection

Download CAD data → www.festo.com

[AG...]/[AQ...] Connecting plate



[1] Earthing screw M4x8
(only with MS4/6-...-EX)


Type	B1	B2	B3	B4	B5	D1	D2	L1	L2	≈ 1
MS4-LR...-AGA	83.4	21.5	12.5	21	72.5	G1/8	16.8	42	14.5	24
MS4-LR...-AGB						G1/4				21
MS4-LR...-AGC						G3/8				24
MS4-LR...-AQK						1/8-27 NPT				24
MS4-LR...-AQN						1/4-18 NPT				24
MS4-LR...-AQP						3/8-18 NPT				24
MS6-LR...-AGB	115	26.5	20.5	31	98.3	G1/4	24	62	15.5	34
MS6-LR...-AGC						G3/8				34
MS6-LR...-AGD						G1/2				26
MS6-LR...-AGE						G3/4				34
MS6-LR...-AQN						1/4-18 NPT				34
MS6-LR...-AQP						3/8-18 NPT				34
MS6-LR...-AQR						1/2-14 NPT				34
MS6-LR...-AQS						3/4-14 NPT				34

Dimensions – Type of mounting

Download CAD data → www.festo.com

[WB] Mounting bracket

[WBM] Mounting bracket




Type	B1	B2	B3	B4	L1	L2	L3	L4
MS4-LR...-WB	56	41	4	44.2	104.6	46.6	5.6	46.5
MS4-LR...-WBM	66.5	44	10	44	41.3	35	6.5	–
MS6-LR...-WB	79.4	62	4.5	53.8	157.6	71	6.6	71

Datasheet


Dimensions – Type of mounting

Download CAD data → www.festo.com

[WR] Mounting bracket



[WP] Mounting bracket




Type	B1	B2	B3	B4	B5	L1	L2	L3	L4
MS4-LR...-WR	68	38	14	41	–	52	44	7	–
MS4-LR...-WP	55.2	40.2	4	44	83.4	106	46.5	5.6	46.7
MS6-LR...-WR	70	38.2	14.2	40	–	67	57	7.1	–
MS6-LR...-WP	79	62	4.5	54	115	158	71	6.6	71

Dimensions – Type of mounting


Download CAD data → www.festo.com

[WPM] Mounting bracket

MS4



MS6



Type	B1	B2	B3	B4	B5	L1	L2	L3	L4
MS4-LR...-WPM	55.2	40.2	4	44	83.4	92.8	34.8	5.6	45.2
MS6-LR...-WPM	99	69	17.5	54	129	98.6	41.3	6.6	41.3

Datasheet

Dimensions – Rotary knob


Download CAD data → www.festo.com

For control panel installation

[] Rotary knob with latch


[AS] Rotary knob with latch,
can be locked using accessories

[E11] Rotary knob with integrated
lock



[LD] Rotary knob, long, with latch

[LD-AS] Rotary knob, long,
with latch, can be locked using
accessories



Type	B4	B5	D2	D3	L3	L8	L9	L10
MS4-LR...	–	–	37.2	M30x1.5	51.1	13	5	–
MS4-LR...-AS	48.6	30			60.2	13	5	
MS4-LR...-E11	–	–			76	14	6	
MS4-LR...-LD	–	–		–	51.1	–	–	76.8
MS4-LR...-LD-AS	48.6	30			60			85.7
MS6-LR...	–	–	51.2	M44x1	86	21	14	–
MS6-LR...-AS	64.4	38.8			95.1	12	5	
MS6-LR...-E11	–	–			110	21	14	
MS6-LR...-LD	–	–		–	86	–	–	139
MS6-LR...-LD-AS	64.4	38.8			95.5			148.5

Datasheet

Dimensions – Rotary knob pressure gauge

Download CAD data → www.festo.com




[DM1] Rotary knob pressure gauge, small

[DM2] Rotary knob pressure gauge, large

MS4


MS4

MS6



Note

Due to the protruding rotary knob, only a distributor block MS4-FRM-FRZ or a branching module MS4-FRM can be mounted as a directly adjacent service unit component.



→ Flow direction

Type	D2	D3	L3	L4	L8	L9
MS4-LR...-DM1	37.2	M30x1.5	54	59	13	6.7
MS4-LR...-DM2	51.2	M48x1.5	56	59	13	7
MS6-LR...-DM2	51	M44x1	84	94	25.4	18.4

Datasheet

Ordering data				
Pneumatic connection 1	Pressure regulation range	Flow direction	Part no.	Type
MS4-LR...				
G1/8	0.3 ... 4 bar	From left to right	611432	MS4-LR-1/8-D5-VS-DM1
			595546	MS4-LR-1/8-D5-VS-DM2
			8190232	MS4-LR-1/8-D5-VS-OS
			8190233	MS4-LR-1/8-D5-VS-OS-WR
			529421	MS4-LR-1/8-D5-AS
		From right to left	529422	MS4-LR-1/8-D5-AS-Z
	0.3 ... 7 bar	From left to right	543520	MS4-LR-1/8-D6-WR
			543519	MS4-LR-1/8-D6-A8
			8190234	MS4-LR-1/8-D6
			596080	MS4-LR-1/8-D6-RG
			564918	MS4-LR-1/8-D6-VS-DM1
			575246	MS4-LR-1/8-D6-VS-DM2
			529423	MS4-LR-1/8-D6-AS
			8232814	MS4-LR-1/8-D6-MPA
			8232813	MS4-LR-1/8-D6-E11
			8232816	MS4-LR-1/8-D6-VS-E11
		From right to left	529424	MS4-LR-1/8-D6-AS-Z
	0.5 ... 12 bar	From left to right	611577	MS4-LR-1/8-D7
			563993	MS4-LR-1/8-D7-VS-DM1
			529425	MS4-LR-1/8-D7-AS
			8232818	MS4-LR-1/8-D7-MPA
			8232819	MS4-LR-1/8-D7-VS
			8232817	MS4-LR-1/8-D7-E11
		From right to left	529426	MS4-LR-1/8-D7-AS-Z
G1/4	0.3 ... 4 bar	From left to right	589482	MS4-LR-1/4-D5
			578556	MS4-LR-1/4-D5-A8
			579184	MS4-LR-1/4-D5-RG
			611015	MS4-LR-1/4-D5-VS-DM1
			594803	MS4-LR-1/4-D5-VS-DM2
			8190235	MS4-LR-1/4-D5-WR
			529415	MS4-LR-1/4-D5-AS
		From right to left	529416	MS4-LR-1/4-D5-AS-Z
	0.3 ... 7 bar	From left to right	611578	MS4-LR-1/4-D6
			589294	MS4-LR-1/4-D6-A8
			8190236	MS4-LR-1/4-D6-A8-E11
			8190237	MS4-LR-1/4-D6-E11
			8190238	MS4-LR-1/4-D6-E11-WR
			567523	MS4-LR-1/4-D6-RG
			8190239	MS4-LR-1/4-D6-RG-E11
			8190240	MS4-LR-1/4-D6-RG-WR
			555873	MS4-LR-1/4-D6-VS-DM1
			555874	MS4-LR-1/4-D6-VS-DM2
			607246	MS4-LR-1/4-D6-WR
			529417	MS4-LR-1/4-D6-AS
			8232808	MS4-LR-1/4-D6-VS-E11
		From right to left	529418	MS4-LR-1/4-D6-AS-Z
	0.5 ... 12 bar	From left to right	8190241	MS4-LR-1/4-D7
			610772	MS4-LR-1/4-D7-A8
			8190242	MS4-LR-1/4-D7-VS-DM1
			578847	MS4-LR-1/4-D7-VS-DM2
			8190243	MS4-LR-1/4-D7-WR
			529419	MS4-LR-1/4-D7-AS
			8232810	MS4-LR-1/4-D7-MPA
			8232809	MS4-LR-1/4-D7-E11
			8232812	MS4-LR-1/4-D7-VS-E11
		From right to left	529420	MS4-LR-1/4-D7-AS-Z

Datasheet

Ordering data				
Pneumatic connection 1	Pressure regulation range	Flow direction	Part no.	Type
MS4-LR... (with connecting plates)				
G3/8	0.3 ... 7 bar	From left to right	8232823	MS4-LR-AGC-D6-VS
			8232820	MS4-LR-AGC-D6
			8232821	MS4-LR-AGC-D6-MPA
			8232822	MS4-LR-AGC-D6-MPA-AS
	0.5 ... 12 bar	From left to right	8232825	MS4-LR-AGC-D7-MPA-AS
			8232826	MS4-LR-AGC-D7-VS
			8232824	MS4-LR-AGC-D7
G1	0.3 ... 7 bar	From left to right	8232997	MS6-LR-AGF-D6
			8232998	MS6-LR-AGF-D6-MPA
			8232999	MS6-LR-AGF-D6-VS
	0.5 ... 12 bar	From left to right	8233000	MS6-LR-AGF-D7
			8233001	MS6-LR-AGF-D7-MPA
			8233002	MS6-LR-AGF-D7-VS

Ordering data				
Pneumatic connection 1	Pressure regulation range	Flow direction	Part no.	Type
MS6-LR...				
G1/4	0.3 ... 4 bar	From left to right	529995	MS6-LR-1/4-D5-AS
	0.3 ... 7 bar		529997	MS6-LR-1/4-D6-AS
			8232984	MS6-LR-1/4-D6-MPA
			8232985	MS6-LR-1/4-D6-VS
	0.5 ... 12 bar		529999	MS6-LR-1/4-D7-AS
			8232987	MS6-LR-1/4-D7-VS
			8232986	MS6-LR-1/4-D7-MPA
G3/8	0.3 ... 4 bar	From left to right	530001	MS6-LR-3/8-D5-AS
	0.3 ... 7 bar		530003	MS6-LR-3/8-D6-AS
			8232988	MS6-LR-3/8-D6-MPA
			8232989	MS6-LR-3/8-D6-VS
	0.5 ... 12 bar	From right to left	530004	MS6-LR-3/8-D6-AS-Z
		From left to right	530005	MS6-LR-3/8-D7-AS
			8232990	MS6-LR-3/8-D7-MPA
			8232991	MS6-LR-3/8-D7-VS
G1/2	0.3 ... 4 bar	From left to right	529989	MS6-LR-1/2-D5-AS
	0.3 ... 7 bar		529991	MS6-LR-1/2-D6-AS
			8232980	MS6-LR-1/2-D6-VS
	0.5 ... 12 bar	From right to left	529992	MS6-LR-1/2-D6-AS-Z
		From left to right	529993	MS6-LR-1/2-D7-AS
			8232982	MS6-LR-1/2-D7-MPA
			8232981	MS6-LR-1/2-D7-E11
		From right to left	529994	MS6-LR-1/2-D7-AS-Z

MS6-LR... (with connecting plates)				
G3/4	0.3 ... 7 bar	From left to right	8232992	MS6-LR-AGE-D6
			8232993	MS6-LR-AGE-D6-MPA
	0.5 ... 12 bar		8232996	MS6-LR-AGE-D7-VS
			8232994	MS6-LR-AGE-D7
			8232995	MS6-LR-AGE-D7-MPA

Ordering data – Modular product system

Ordering table					
Grid dimension	[mm]	40	62	Conditions	Code
Module no.		527690	527663		
Series	Standard				MS
Size	4	6			...
Function	Pressure regulator				-LR
Pneumatic connection	Female thread G1/8	–	[1]		-1/8
	Female thread G1/4	Female thread G1/4	[1]		-1/4
	–	Female thread G3/8	[1]		-3/8
	–	Female thread G1/2	[1]		-1/2
	Connecting plate G1/8	–			-AGA
	Connecting plate G1/4	Connecting plate G1/4			-AGB
	Connecting plate G3/8	Connecting plate G3/8			-AGC
	–	Connecting plate G1/2			-AGD
	–	Connecting plate G3/4			-AGE
	–	Connecting plate G1			-AGF
	Connecting plate 1/8 NPT	–	[1]		-AQK
	Connecting plate 1/4 NPT	Connecting plate 1/4 NPT	[1]		-AQN
	Connecting plate 3/8 NPT	Connecting plate 3/8 NPT	[1]		-AQP
	–	Connecting plate 1/2 NPT	[1]		-AQR
	–	Connecting plate 3/4 NPT	[1]		-AQS
Pressure regulation range/actuation	0.3 ... 4 bar, manually actuated				-D5
	0.3 ... 7 bar, manually actuated				-D6
	0.5 ... 12 bar, manually actuated				-D7
	–	0.5 ... 16 bar, manually actuated	[1] [4]		-D8
Pressure gauge alternatives	MS pressure gauge				
	Cover plate				-VS
	Adapter for EN pressure gauge 1/8, without pressure gauge	–			-A8
	Adapter for EN pressure gauge 1/4, without pressure gauge				-A4
	Integrated pressure gauge, red/green scale		[2] [3] [4]		-RG
	Pressure sensor with switching status indicator, plug M8, threshold value comparator, PNP, N/O contact		[1] [2] [5]		-AD7
	Pressure sensor with switching status indicator, plug M8, threshold value comparator, PNP, N/C contact		[1] [2] [5]		-AD8
	Pressure sensor with switching status indicator, M8 plug, window comparator, PNP, N/O contact		[1] [2] [5]		-AD9
	Pressure sensor with switching status indicator, M8 plug, window comparator, PNP, N/C contact		[1] [2] [5]		-AD10
	Pressure sensor with LCD display, M12 plug, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA		[2] [5]		-AD11
	Pressure sensor with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA		[2] [5]		-AD12

[1] 1/8, 1/4, 3/8, 1/2, AQK, AQN, AQP, AQR, AQS, D8, AD7 ... AD10, DM1, DM2, KD, E11, WPM

[2] RG, AD7 ... AD10, AD11/AD12, OS, KD, AS, WR, WB

[3] RG, OS, KD, AS

[4] D8, RG, OS, KD, AS

[5] AD7 ... AD10, AD11/AD12

Not with EU EX4 certification.

MS4: not with rotary knob alternative DM2.

Not with rotary knob alternative DM1.

MS6: not with rotary knob alternative DM2.

Measuring range max. 10 bar.

Not with pressure regulation range D8


Ordering data – Modular product system

Ordering table						
Grid dimension	[mm]	40	62	Conditions	Code	Enter code
Alternative pressure gauge scale	MS pressure gauge, bar					
	psi			[6]	-PSI	
	MPa			[7]	-MPA	
Secondary exhausting	With secondary exhausting					
	Without secondary exhausting			[2] [3] [4]	-OS	
Rotary knob alternative	None					
	Long rotary knob			[8]	-LD	
	Rotary knob pressure gauge, small	–		[1] [8] [9]	-DM1	
	Rotary knob pressure gauge, large			[1] [8] [9]	-DM2	
Alternative mounting position	None					
	Rotary knob underneath			[1] [2] [3] [4] [10]	-KD	
Locking option	None					
	Lockable using accessories			[2] [3] [4]	-AS	
	With integrated lock			[1]	-E11	
Type of mounting	Without mounting bracket					
	Mounting bracket with knurled nut for regulator head			[2] [11]	-WR	
	Mounting bracket standard design			[12]	-WP	
	Mounting bracket for hooking in service unit components			[1] [12]	-WPM	
	Mounting bracket centrally at the rear (wall mounting top and bottom), connecting plates not required			[2]	-WB	
	Mounting bracket centrally at the rear (wall mounting top), connecting plates not required	–			-WBM	
EU certification	None					
	II 2GD to EU Explosion Protection Directive (ATEX)				-EX4	
UL certification	None					
	cULus, ordinary location for Canada and USA				-UL1	
Flow direction	Flow direction from left to right					
	Flow direction from right to left				-Z	

- [6] PSI Not with pressure gauge alternatives VS, A8, A4, RG, AD7 ... AD10.
 [7] MPA Not with pressure gauge alternatives VS, A8, A4, AD7 ... AD10.
 Not with rotary knob alternative DM1, DM2.
 [8] LD, DM1, DM2 Not with locking option E11.
 [9] DM1, DM2 Can only be combined with pressure gauge alternatives VS, A8, A4, AD7 ... AD10.
 [10] KD Not with pressure gauge alternative RG.
 Not with alternative pressure gauge scale MPa.
 Not with mounting type WP.
 [11] WR Not with long rotary knob LD or rotary knob alternative DM2.
 [12] WP, WPM Only with connecting plate AGA, AGB, AGC, AGD, AGE, AQK, AQN, AQP, AQR or AQS.

Peripherals overview

Pressure regulator MS4/MS6-LRB with pressure output at the rear



Note


Additional accessories:

- Module connectors for combination with size MS4/MS6 or size MS9
→ Internet: amv, rmv, armv
- Adapters for mounting on profiles
→ Internet: ipm-80, ipm-40-80, ipm-80-80

Pressure regulator with rotary knob pressure gauge

MS4-LRB-...-DM1/

MS6-LRB-...-DM2




Peripherals overview

Mounting attachments and accessories		Individual device		Combination		→ Page/Internet
		Without connecting plate	With connecting plate	Without connecting plate	With connecting plate	
[1]	Pressure regulator MS4/MS6-LRB	■	■	■	■	28
[2]	Angled outlet block B...	■	■	■	■	46
[3]	Mounting bracket MS4/6-WP	–	■	■	■	ms4-wp, ms6-wp
[4]	Mounting bracket MS4/6-WPB	–	■	■	■	ms4-wp, ms6-wp
[5]	Mounting bracket MS4/6-WPE	–	■	■	■	ms4-wp, ms6-wp
[6]	Mounting bracket MS4/6-WPM	–	■	■	■	ms4-wp, ms6-wp
[7]	Padlock LRVS-D	■	■	■	■	106
[8]	Cover cap MS4/6-END	■	–	■	–	ms4-end, ms6-end
[9]	Module connector MS4/6-MV	–	■	■	■	ms4-mv, ms6-mv
[10]	Connecting plate SET MS4/6-AG...	–	■	–	■	ms4-ag, ms6-ag
[11]	Pressure sensor with LCD display AD11/AD12	■	■	■	■	46
[12]	Connecting cable NEBA-M8...-LE4/NEBA-M12...-LE4	■	■	■	■	106
[13]	Pressure sensor without display AD7 ... AD10	■	■	■	■	46
[14]	Connecting cable NEBA-M8...-LE3	■	■	■	■	106
[15]	Adapter for EN pressure gauge 1/8, 1/4 A8/A4	■	■	■	■	46
[16]	Pressure gauge MA	■	■	■	■	106
[17]	Cover plate VS	■	■	■	■	46

Peripherals overview

Pressure regulator MS4/MS6-LRB with pressure output at the front



Peripherals overview

Mounting attachments and accessories		Individual device		Combination		→ Page/Internet
		Without connecting plate	With connecting plate	Without connecting plate	With connecting plate	
[1]	Pressure regulator MS4/MS6-LRB	■	■	■	■	30
[2]	Mounting bracket MS4/6-WB	■	■	–	–	ms4-wb, ms6-wb
[3]	Mounting bracket MS4-WBM	■	■	–	–	ms4-wbm
[4]	Mounting bracket MS4/6-WR	■	■	–	–	ms4-wr, ms6-wr
[5]	Knurled nut (included in the scope of delivery) MS-LR	■	■	–	–	–
[6]	Padlock LRVS-D	■	■	■	■	106
[7]	Cover cap MS4/6-END	■	–	■	–	ms4-end, ms6-end
[8]	Module connector MS4/6-MV	–	■	■	■	ms4-mv, ms6-mv
[9]	Connecting plate SET MS4/6-AG...	–	■	–	■	ms4-ag, ms6-ag
[10]	Angled outlet block B...	■	■	■	■	46
[11]	Pressure sensor without display AD7 ... AD10	■	■	■	■	46
[12]	Connecting cable NEBA-M8...-LE3	■	■	■	■	106
[13]	Cover plate VS	■	■	■	■	46
[14]	MS pressure gauge (included in the scope of delivery)	■	■	■	■	–

Type codes

001	Series	
MS	MS series	
002	Size	
4	Grid dimension 40 mm	
003	Function	
LRB	Pressure regulator for manifold assembly	
004	Pneumatic connection	
1/4	Female thread G1/4	
AGA	Sub-base G1/8	
AGB	Sub-base G1/4	
AGC	Sub-base G3/8	
005	Pressure regulation range	
D5	0.3 ... 4 bar	
D6	0.3 ... 7 bar	
D7	0.5 ... 12 bar	
006	Pressure gauge alternatives	
	None	
A4	Adapter for EN pressure gauge 1/4, without pressure gauge	
A8	Adapter for EN pressure gauge 1/8, without pressure gauge	
AD7	Pressure sensor with switching display, M8 plug, threshold value comparator, PNP, N/O	
AD8	Pressure sensor with switching display, M8 plug, threshold value comparator, PNP, N/C	
AD9	Pressure sensor with switching display, M8 plug, window comparator, PNP, N/O	
AD10	Pressure sensor with operational status indicator, M8 plug, window comparator, PNP, N/C	
AD11	Pressure sensor with LCD display, M12 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V, 4...20 mA	
AD12	Pressure sensor with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V, 4...20 mA	
RG	Integrated pressure gauge, red/green scale	
VS	Cover plate	
007	Alternative pressure gauge scale	
	MS pressure gauge	
PSI	psi	
MPa	MPa	

008	Secondary exhausting	
	With secondary exhausting	
OS	Without secondary exhaust	
009	Rotary knob alternative	
	None	
LD	Long rotary knob	
DM1	Rotary knob pressure gauge, small	
010	Alternative mounting position	
	None	
KD	Rotary knob underneath	
011	Lockability	
	None	
AS	Can be locked using accessories	
E11	With integrated lock	
012	Alternative pressure outlet	
	None	
BC	Angled outlet block QS-6	
BD	Angled outlet block QS-8	
013	Type of mounting	
	Without mounting bracket	
WR	Mounting bracket with knurled nut on regulator knob	
WP	Mounting bracket basic design	
WPB	Mounting bracket for large wall gap	
WPM	Mounting bracket for hooking in service unit components	
WB	Mounting centrally at rear (wall mounting top and bottom), connecting plates not required	
WBM	Mounting centrally at rear (wall mounting top), connecting plates not required	
014	EU certification	
	None	
EX4	II 2GD	
015	UL certification	
	None	
UL1	cULus ordinary location for Canada and USA	
016	Outlet direction	
	Pressure output to the rear	
Z	Pressure output to the front	


Type codes

001	Series	
MS	MS series	
002	Size	
6	Grid dimension 62 mm	
003	Function	
LRB	Pressure regulator for manifold assembly	
004	Pneumatic connection	
1/2	Female thread G1/2	
AGB	Sub-base G1/4	
AGC	Sub-base G3/8	
AGD	Sub-base G1/2	
AGE	Sub-base G3/4	
AGF	Sub-base G1	
005	Pressure regulation range	
D5	0.3 ... 4 bar	
D6	0.3 ... 7 bar	
D7	0.5 ... 12 bar	
D8	0.5 ... 16 bar	
006	Pressure gauge alternatives	
	None	
A4	Adapter for EN pressure gauge 1/4, without pressure gauge	
A8	Adapter for EN pressure gauge 1/8, without pressure gauge	
AD7	Pressure sensor with switching display, M8 plug, threshold value comparator, PNP, N/O	
AD8	Pressure sensor with switching display, M8 plug, threshold value comparator, PNP, N/C	
AD9	Pressure sensor with switching display, M8 plug, window comparator, PNP, N/O	
AD10	Pressure sensor with operational status indicator, M8 plug, window comparator, PNP, N/C	
AD11	Pressure sensor with LCD display, M12 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V, 4...20 mA	
AD12	Pressure sensor with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V, 4...20 mA	
RG	Integrated pressure gauge, red/green scale	
VS	Cover plate	
007	Alternative pressure gauge scale	
	MS pressure gauge	
PSI	psi	
MPA	MPa	


008	Secondary exhausting	
	With secondary exhausting	
OS	Without secondary exhaust	
009	Rotary knob alternative	
	None	
LD	Long rotary knob	
DM2	Rotary knob pressure gauge, large	
010	Alternative mounting position	
	None	
KD	Rotary knob underneath	
011	Lockability	
	None	
AS	Can be locked using accessories	
E11	With integrated lock	
012	Alternative pressure outlet	
	None	
BD	Angled outlet block QS-8	
BE	Angled outlet block QS-10	
013	Type of mounting	
	Without mounting bracket	
WR	Mounting bracket with knurled nut on regulator knob	
WP	Mounting bracket basic design	
WPM	Mounting bracket for hooking in service unit components	
WB	Mounting centrally at rear (wall mounting top and bottom), connecting plates not required	
WBM	Mounting centrally at rear (wall mounting top), connecting plates not required	
014	EU certification	
	None	
EX4	II 2GD	
015	UL certification	
	None	
UL1	cULus ordinary location for Canada and USA	
016	Outlet direction	
	Pressure output to the rear	
Z	Pressure output to the front	

Datasheet

Without pressure gauge




With pressure gauge



-  Flow rate
300 ... 7300 l/min
-  Temperature range
-10 ... +60 °C
-  Operating pressure
0.8 ... 20 bar
-  www.festo.com



Several pressure regulators mounted next to one another to form a regulator manifold:



The pressure regulator is suitable for manifold assemblies with through air supply, for configuring a regulator manifold with separate, independent pressure regulation ranges. The pressure output is to the front or rear.

- Good regulation characteristics with minimal hysteresis and input pressure compensation
- Manifold assembly with through air supply
- For configuring a regulator manifold with independent pressure regulation ranges
- Actuator lock to protect the set values from being adjusted
- Available with and without secondary exhausting
- Four pressure regulation ranges: 0.3 ... 4 bar, 0.3 ... 7 bar, 0.5 ... 12 bar and 0.5 ... 16 bar
- Return flow option for exhausting from output 2 to output 1 already integrated
- Optional pressure sensor
- Optional rotary knob pressure gauge
- Optional device variant EX4 for use in potentially explosive areas in zones 1, 2, 21 and 22

General technical data			
Size		MS4	MS6
Pneumatic connection 1			
Female thread		G1/4	G1/2
Connecting plate [AG...]		G1/8, G1/4 or G3/8	G1/4, G3/8, G1/2, G3/4 or G1
Pneumatic connection 2			
Female thread		G1/4	G1/2
Angled outlet block		[BC]	–
		[BD]	QS-8
		[BE]	QS-10
Design		Directly actuated diaphragm regulator with through compressed air supply	
Regulator function		Output pressure constant, with input pressure compensation, with return flow, with/without secondary exhausting	
Type of mounting		With accessories	
		In-line installation	
		Front panel mounting	
Mounting position		Any	
Actuator lock		Rotary knob with latch	
		Rotary knob with latch, can be locked using accessories	
		Rotary knob with integrated lock	
Pressure regulation range/actuation		[D5] [bar]	0.3 ... 4, manually actuated ¹⁾
		[D6] [bar]	0.3 ... 7, manually actuated ¹⁾
		[D7] [bar]	0.5 ... 12, manually actuated (0.5 ... 10 with pressure sensor or with UL certification) ¹⁾
		[D8] [bar]	– 0.5 ... 16, manually actuated (0.5 ... 10 with UL certification)
Max. pressure hysteresis [bar]		0.25	0.25 (0.4 with rotary knob pressure gauge)
Pressure indication		With pressure sensor for indicating the output pressure via LCD display and electrical output	
		With pressure sensor for indicating the output pressure via the switching status indicator and electrical output	
		Via pressure gauge for displaying the output pressure	
		With pressure gauge with red/green scale for indicating the output pressure	
		Via pressure gauge in the rotary knob for displaying the output pressure	
		Prepared for G1/8	–
		Prepared for G1/4	

¹⁾ MS4: the pressure regulation range for pressure regulators with rotary knob pressure gauge starts at 0.8 bar.

† Note: This product conforms to ISO 1179-1 and ISO 228-1.

Datasheet

Standard nominal flow rate $q_{nN}^{(1)}$ [l/min]							
Size	MS4				MS6		
	Standard	Angled outlet block			Standard	Angled outlet block	
		[BC]: QS-6	[BD]: QS-8			[BD]: QS-8	[BE]: QS-10
Pressure regulation range	[D5]	1900 ²⁾	300 ²⁾	650 ²⁾	7300 ²⁾	600 ²⁾	750 ²⁾
	[D6]	1700	350	840	6300	880	1000
	[D7]	1500 ³⁾	350	640	5500	800	950
	[D8]	–	–	–	4500	750	850

- 1) Measured at $p_1 = 10$ bar and $p_2 = 6$ bar, $\Delta p = 1$ bar
2) Measured at $p_1 = 10$ bar and $p_2 = 3$ bar, $\Delta p = 1$ bar
3) With a rotary knob pressure gauge, $q_{nN} = 800$ l/min, $q_{n\max} = 2200$ l/min

Operating and environmental conditions		
Size	MS4	MS6
Operating pressure [bar]	0.8 ... 14 (0.8 ... 10) ¹⁾	
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]	
	Inert gases	
Note on the operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)	
Ambient temperature [°C]	–10 ... +60 (0 ... +50) ²⁾	
Temperature of medium [°C]	–10 ... +60 (0 ... +50) ²⁾	
Storage temperature [°C]	–10 ... +60	
Corrosion resistance class CRC ³⁾	2	
Food safe ⁴⁾	See supplementary material information	
UL certification ⁴⁾	c UL us - Recognized (OL)	

- 1) Value in brackets applies to MS4/MS6-LRB with UL certification.
2) Value in brackets applies to MS4/MS6-LRB with pressure sensor.
3) More information www.festo.com/x/topic/crc
4) More information: www.festo.com/catalogue/ms-lrb → Support/Downloads.

ATEX	
EU certification	[EX4]
ATEX category for gas	II 2G
Type of ignition protection for gas	Ex h IIC T6 Gb X
ATEX category for dust	II 2D
Type of ignition protection for dust	Ex h IIIC T60°C Db X
Explosion-proof ambient temperature	–10 °C ≤ Ta ≤ +60 °C
Explosion protection certification outside the EU	EPL Db (GB)
	EPL Gb (GB)
CE marking (see declaration of conformity) ¹⁾	To EU Explosion Protection Directive (ATEX)
UKCA marking (see declaration of conformity) ¹⁾	To UK explosion regulations


- 1) More information: www.festo.com/catalogue/ms-lrb → Support/Downloads.

Weight [g]		
Size	MS4	MS6
Pressure regulator	222	747
Pressure regulator with rotary knob with integrated lock	347	1017

Datasheet

Materials

Sectional view





Pressure regulator (manifold assembly)		
[1]	Housing	Die-cast aluminium
[2]	Rotary knob	PA, POM
	Rotary knob with integrated lock	Aluminium
[3]	Diaphragm	NBR
[4]	Bottom cover	PET
[5]	Springs	Steel
-	Seals	NBR
Note on materials		RoHS-compliant
LABS (PWIS) conformity		VDMA24364-B1/B2-L

Standard flow rate q_n as a function of output pressure p_2 ($p_1 = 10\text{ bar}$)

MS4-LRB-1/4

MS6-LRB-1/2

Input pressure $p_1 = 10\text{ bar}$




1) There is a higher initial pressure drop in the characteristic curve for variant DM1.

Datasheet

Dimensions – Basic version

Download CAD data → www.festo.com

- [] Integrated MS pressure gauge with standard scale
 [RG] Integrated MS pressure gauge with red/green scale
 [] Rotary knob with latch




Type	B1	B2	B3		D1	D2	L1	L2	L3	L4	L5
			Pressure gauge								
			Standard scale	Red/green scale							
MS4-LRB-1/4	40	21	57	58.5	G1/4	37.2	64.4	27	60.3	58.5	2
MS6-LRB-1/2	62	31	77	78.5	G1/2	51.2	94	39	95.1	85	5

† Note: This product conforms to ISO 1179-1 and ISO 228-1.

Datasheet

Dimensions – Alternative mounting position Download CAD data → www.festo.com

[KD] Rotary knob underneath



Type	B1	B2	B3	D1	D2	L1	L2	L3	L4	L5
MS4-LRB-1/4-...-KD	40	21	57	G1/4	37.2	64.4	27	60.3	58.5	2
MS6-LRB-1/2-...-KD	62	31	77	G1/2	51.2	94	39	95.1	85	5

† Note: This product conforms to ISO 1179-1 and ISO 228-1.

Datasheet


Dimensions – Angled outlet block

Download CAD data → www.festo.com


[BC]/[BD]/[BE] Angled outlet block

[] Pressure output at the rear

MS4



MS6



[1] Push-in connector QS

→ Flow direction

Type	B1	B2	B3	B6	B8	D1	D2 Ø	L1	L2	L3	L4	L6
MS4-LRB-1/4-...-BC/BD	40	21	57	21	–	G1/4	37.2	66.5	27	60.3	58.5	8
MS6-LRB-1/2-...-BD/BE	62	31	77	23	23.4	G1/2	51.2	94.9	39	95.1	85	10.4


Note: This product conforms to ISO 1179-1 and ISO 228-1.

Datasheet

Dimensions – Angled outlet block Download CAD data → www.festo.com

[BC]/[BD]/[BE] Angled outlet block
[Z] Pressure output to front

MS4 (not shown)
MS6



Type	B2	B7	B8	D1
MS4-LRB-1/4-...-BC/BD	21	75	–	G1/4
MS6-LRB-1/2-...-BD/BE	31	99	23.4	G1/2

† Note: This product conforms to ISO 1179-1 and ISO 228-1.

Datasheet


Dimensions – Pressure gauge alternatives

Download CAD data → www.festo.com

[VS] Cover plate

[A8] Adapter for EN pressure gauge 1/8, without pressure gauge

[A4] Adapter for EN pressure gauge 1/4, without pressure gauge



Type	B2	B3	D1	D4
MS4-LRB-1/4-...-VS	21	54	G1/4	–
MS4-LRB-1/4-...-A8	21	58.5	G1/4	G1/8
MS4-LRB-1/4-...-A4	21	58.5	G1/4	G1/4
MS6-LRB-1/2-...-VS	31	76	G1/2	–
MS6-LRB-1/2-...-A4	31	78.5	G1/2	G1/4

⚡ Note: This product conforms to ISO 1179-1 and ISO 228-1.

Datasheet

Dimensions – Pressure gauge alternatives

[AD7 ... 10] Pressure sensor without LCD display (switching status indicator only)

Variant AD7:
SDE5-D10-O-...-P-M8 with 3-pin
M8x1 plug, threshold value compar-
ator, 1 switching output PNP,
N/O contact

Variant AD8:
SDE5-D10-C-...-P-M8 with 1x 3-pin
M8 plug, threshold value comparator,
1 switching output PNP, N/C contact

Variant AD9:
SDE5-D10-O3-...-P-M8 with 1x 3-pin
M8 plug, window comparator,
1 switching output PNP, N/O contact

Variant AD10:
SDE5-D10-C3-...-P-M8 with 1x 3-pin
M8 plug, window comparator,
1 switching output PNP, N/C contact

Download CAD data → www.festo.com

Datasheets → Internet: sde5

Type	B2	B3	B5	B6	D6
MS4-LR-...-AD7/AD8/AD9/AD10	21	59.1	32	16	M8x1
MS6-LR-...-AD7/AD8/AD9/AD10	31	79.1	51	16	M8x1

⚡ Note: This product conforms to ISO 1179-1 and ISO 228-1.

42

→Internet: www.festo.com/catalogue/...

Subject to change – 2025/11


Datasheet

Dimensions – Pressure gauge alternatives

Download CAD data → www.festo.com

[AD11/AD12] Pressure sensor with LCD display

Datasheets → Internet: spau



Variant AD11:

SPAU-P10R... (10 bar) for pressure range D5/D6

SPAU-P12R... (12 bar) for pressure range D7

SPAU-P16R... (16 bar) for pressure range D8

with plug M12, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA


Variant AD12:

SPAU-P10R... (10 bar) for pressure range D5/D6

SPAU-P12R... (12 bar) for pressure range D7

SPAU-P16R... (16 bar) for pressure range D8

with plug M8, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA



→ Flow direction

Type	B2	B3	B4	B5	B6	D6	L5	L6
MS4-LR...-AD11	21	81.2	73.3	32	32	M12x1	41.2	39
MS4-LR...-AD12	21	81.2	73.3	32	32	M8x1	37.9	39
MS6-LR...-AD11	31	101.8	93.7	51	32	M12x1	41.2	39
MS6-LR...-AD12	31	101.8	93.7	51	32	M8x1	37.9	39

- ‡ - Note: This product conforms to ISO 1179-1 and ISO 228-1.

Datasheet


Dimensions – Rotary knob

Download CAD data → www.festo.com


For control panel installation

[] Rotary knob with latch

[AS] Rotary knob with latch,
can be locked using accessories

[E11] Rotary knob with integrated
lock


[LD] Rotary knob, long, with latch

[LD-AS] Rotary knob, long, with
latch, can be locked using accessories



Type	B4	B5	D2	D3	L3	L8	L9	L10
MS4-LRB-...	-	-	37.2	M30x1.5	51.1	13	5	-
MS4-LRB-...-AS	48.6	30			60.2	13	5	
MS4-LRB-...-E11	-	-			76	14	6	
MS4-LRB-...-LD	-	-		-	51.1	-	-	76.8
MS4-LRB-...-LD-AS	48.6	30			60	-	-	85.7
MS6-LRB-...	-	-	51.2	M44x1	86	21	14	-
MS6-LRB-...-AS	64.4	38.8			95.1	12	5	
MS6-LRB-...-E11	-	-			110	21	14	
MS6-LRB-...-LD	-	-		-	86	-	-	139
MS6-LRB-...-LD-AS	64.4	38.8			95.5	-	-	148.5

Datasheet


Dimensions – Rotary knob pressure gauge

Download CAD data → www.festo.com

[DM1] Rotary knob pressure gauge, small



[DM2] Rotary knob pressure gauge, large



→ Flow direction

Type	D2	D3	L3	L4	L8	L9
MS4-LRB-...-DM1	37.2	M30x1.5	54	58.5	13	6.7
MS6-LRB-...-DM2	51	M44x1	84	94	25	18

Ordering data

Pneumatic connection 1	Pressure regulation range	Flow direction	Part no.	Type
MS4-LRB...				
G1/4	0.3 ... 4 bar	From left to right	529471	MS4-LRB-1/4-D5-A8-AS
		From left to right	529473	MS4-LRB-1/4-D5-AS
		From left to right	529474	MS4-LRB-1/4-D5-AS-BD
	0.3 ... 7 bar	From left to right	529477	MS4-LRB-1/4-D6-A8-AS
		From left to right	529479	MS4-LRB-1/4-D6-AS
		From left to right	529480	MS4-LRB-1/4-D6-AS-BD
		From right to left	529481	MS4-LRB-1/4-D6-AS-BD-Z
		From right to left	529482	MS4-LRB-1/4-D6-VS-AS-Z
	0.5 ... 12 bar	From left to right	529483	MS4-LRB-1/4-D7-A8-AS
		From left to right	529485	MS4-LRB-1/4-D7-AS
		From left to right	529486	MS4-LRB-1/4-D7-AS-BD
MS6-LRB...				
G1/2	0.3 ... 4 bar	From left to right	530322	MS6-LRB-1/2-D5-AS
		From left to right	530320	MS6-LRB-1/2-D5-A4-AS
	0.3 ... 7 bar	From left to right	530326	MS6-LRB-1/2-D6-A4-AS
		From left to right	530328	MS6-LRB-1/2-D6-AS
		From left to right	530329	MS6-LRB-1/2-D6-AS-BD
		From right to left	530330	MS6-LRB-1/2-D6-AS-BD-Z
	0.5 ... 12 bar	From left to right	530332	MS6-LRB-1/2-D7-A4-AS
		From left to right	530334	MS6-LRB-1/2-D7-AS
		From left to right	530335	MS6-LRB-1/2-D7-AS-BD

Ordering data – Modular product system

Ordering table					
Grid dimension	[mm]	40	62	Conditions	Code
Module no.		527692	527665		
Series	Standard				MS
Size	4	6			...
Function	Pressure regulator for manifold assembly				-LRB
Pneumatic connection	Female thread G1/4	–	[1]		-1/4
	–	Female thread G1/2	[1]		-1/2
	Connecting plate G1/8	–			-AGA
	Connecting plate G1/4	Connecting plate G1/4			-AGB
	Connecting plate G3/8	Connecting plate G3/8			-AGC
	–	Connecting plate G1/2			-AGD
	–	Connecting plate G3/4			-AGE
	–	Connecting plate G1			-AGF
Pressure regulation range/actuation	0.3 ... 4 bar, manually actuated				-D5
	0.3 ... 7 bar, manually actuated				-D6
	0.5 ... 12 bar, manually actuated				-D7
	–	0.5 ... 16 bar, manually actuated	[1] [2]		-D8
Pressure gauge alternatives	MS pressure gauge				
	Cover plate		[3]		-VS
	Adapter for EN pressure gauge 1/8, without pressure gauge	–	[4]		-A8
	Adapter for EN pressure gauge 1/4, without pressure gauge		[4]		-A4
	Integrated pressure gauge, red/green scale		[2]		-RG
	Pressure sensor with switching status indicator, plug M8, threshold value comparator, PNP, N/O contact		[1] [5] [6]		-AD7
	Pressure sensor with switching status indicator, plug M8, threshold value comparator, PNP, N/C contact		[1] [5] [6]		-AD8
	Pressure sensor with switching status indicator, M8 plug, window comparator, PNP, N/O contact		[1] [5] [6]		-AD9
	Pressure sensor with switching status indicator, M8 plug, window comparator, PNP, N/C contact		[1] [5] [6]		-AD10
	Pressure sensor with LCD display, M12 plug, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA		[1] [4] [5]		-AD11
	Pressure sensor with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA		[1] [4] [5]		-AD12
Alternative pressure gauge scale	MS pressure gauge, bar				
	psi		[7]		-PSI
	MPa		[8]		-MPA

[1] 1/4, 1/2, D8, AD7 ... AD10, AD11/AD12, DM1, DM2, KD, E11, WPM

Not with EU EX4 certification.

[2] D8, RG, OS, KD, AS Not with rotary knob pressure gauge DM1, DM2.

[3] VS Must be selected if outlet direction Z is selected without alternative mounting position KD and without pressure output BC, BD, BE. Must be selected if alternative mounting position KD is selected without outlet direction Z and without pressure output BC, BD, BE.

[4] A8, A4, AD11/AD12 Not with outlet direction Z. In combination with outlet direction Z only with alternative mounting position KD.

[5] AD7 ... AD10, AD11/AD12 Measuring range max. 10 bar.

Not with pressure regulation range D8.

[6] AD7 ... AD10 In combination with outlet direction Z only with pressure output BC, BD, BE or in combination with outlet direction Z only with alternative mounting position KD.

[7] PSI Not with pressure gauge alternatives VS, A8, A4, RG, AD7 ... AD10. In combination with outlet direction Z only with pressure output BC, BD, BE.

[8] MPA Not with pressure gauge alternatives VS, A8, A4, AD7 ... AD10. Not with alternative mounting position KD. Not with rotary knob alternative DM1, DM2. In combination with outlet direction Z only with pressure output BC, BD, BE.


Ordering data – Modular product system

Ordering table						
Grid dimension	[mm]	40	62	Conditions	Code	Enter code
Secondary exhausting	With secondary exhausting					
	Without secondary exhausting			[2]	-OS	
Rotary knob alternative	None					
	Long rotary knob			[9]	-LD	
	Rotary knob pressure gauge, small		–	[1] [9] [10]	-DM1	
	–		Rotary knob pressure gauge, large		[1] [9] [10]	
Alternative mounting position	None					
	Rotary knob underneath			[1] [2] [11]	-KD	
Locking option	None					
	Lockable using accessories			[2]	-AS	
	With integrated lock			[1]	-E11	
Pressure output (p _{max} = 10 bar)	None					
	Angled outlet block QS-6		–		-BC	
	Angled outlet block QS-8		Angled outlet block QS-8		-BD	
	–		Angled outlet block QS-10		-BE	
Type of mounting	Without mounting bracket					
	Mounting bracket with knurled nut for regulator head			[12] [13]	-WR	
	Mounting bracket standard design			[14] [15]	-WP	
	Mounting bracket for hooking in service unit components			[1] [12] [14]	-WPM	
	Mounting bracket for large wall gap			[14] [16]	-WPB	
	Mounting bracket centrally at the rear (wall mounting top and bottom), connecting plates not required			[12]	-WB	
	Mounting bracket centrally at the rear (wall mounting top), connecting plates not required		–	[12]	-WBM	
EU certification	None					
	II 2GD to EU Explosion Protection Directive (ATEX)				-EX4	
UL certification	None					
	cULus, ordinary location for Canada and USA				-UL1	
Outlet direction	Pressure output at the rear					
	Pressure output at the front (without angled outlet block, no pressure gauge)				-Z	

- [9] LD, DM1, DM2 Not with locking option E11.
- [10] DM1, DM2 Can only be selected in combination with pressure gauge alternatives VS, A4, AD7 ... AD10.
- [11] KD Not with alternative pressure gauge scale MPa.
In combination with alternative pressure gauge scale PSI only with outlet direction Z and/or only with pressure output BC, BD, BE.
Not with mounting type WP, WPB.
In combination with mounting type WR, WPM, WB, WBM not with outlet direction Z.
Not with pressure gauge alternative RG.
In combination with pressure gauge alternatives A8, A4, only with outlet direction Z.
In combination with outlet direction Z not with alternative mounting position KD.
- [12] WR, WPM, WB, WBM
- [13] WR Only with outlet direction Z.
Not with long rotary knob LD or rotary knob alternative DM2.
- [14] WP, WPM, WPB Only with connecting plate AGA, AGB, AGC, AGD, AGE.
- [15] WP Only with outlet direction Z and/or only with pressure output BC, BD, BE.
- [16] WPB Not with outlet direction Z.
Not with pressure output BC, BD, BE.

Peripherals overview

Precision pressure regulator MS6-LRP



Note


Additional accessories:

- Module connectors for combination with size MS4/MS6 or size MS9
→ Internet: amv, rmv, armv
- Adapters for mounting on profiles
→ Internet: ipm-80, ipm-40-80, ipm-80-80

Manually actuated

Pneumatically actuated

Electrically actuated



Peripherals overview

Mounting attachments and accessories		Individual device		Combination		→ Page/Internet
		Without connecting plate	With connecting plate	Without connecting plate	With connecting plate	
[1]	Precision pressure regulator MS6-LRP	■	■	■	■	48
[2]	Mounting bracket MS6-WB	■	■	–	–	ms6-wb
[3]	Cover cap MS6-END	■	–	■	–	ms6-end
[4]	Module connector MS6-MV	–	■	■	■	ms6-mv
[5]	Connecting plate SET MS6-AG...	–	■	–	■	ms6-ag
	Connecting plate SET MS6-AQ...	–	■	–	■	ms6-aq
[6]	Pressure sensor with LCD display AD11/AD12	■	■	■	■	62
[7]	Connecting cable NEBA-M8...-LE4/NEBA-M12...-LE4	■	■	■	■	106
[8]	Pressure sensor without display AD7 ... AD10	■	■	■	■	62
[9]	Connecting cable NEBA-M8...-LE3	■	■	■	■	106
[10]	Pressure sensor without display AD7 ... AD10	■	■	■	■	79
[11]	Precision pressure gauge A8M/MAP	■	■	■	■	62, 106
[12]	Cover plate VS	■	■	■	■	62
[13]	Knurled nut (included in the scope of delivery) MS-LR	■	■	–	–	–
[14]	Mounting bracket MS6-WR	■	■	–	–	ms6-wr
[15]	Padlock LRVS-D	■	■	■	■	106
–	Mounting bracket MS6-WP/WPB/WPE/WPM	–	■	■	■	ms6-wp


Type codes

001	Series	
MS	MS series	
002	Size	
6	Grid dimension 62 mm	
003	Function	
LRP	Precision pressure regulator	
004	Pneumatic connection	
1/4	Female thread G1/4	
3/8	Female thread G3/8	
1/2	Female thread G1/2	
AGB	Sub-base G1/4	
AGC	Sub-base G3/8	
AGD	Sub-base G1/2	
AGE	Sub-base G3/4	
AGF	Sub-base G1	
005	Pressure regulation range	
D2	0.05 ... 0.7 bar	
D4	0.05 ... 2.5 bar	
D5	0.1 ... 4 bar	
D7	0.1 ... 12 bar	
PE10	0.1 ... 10 bar electrically actuated (pilot control using proportional-pressure regulator with LED indicator, 7-segment), set-point 0 ... 10V	
PI10	0.1 ... 10 bar electrically actuated (pilot control using proportional-pressure regulator with LED indicator, 7-segment), set-point 4 ... 20mA	
P0	Max. 12 bar, pneumatically actuated (pressure range determined by pilot regulator)	
006	Pressure gauge alternatives	
A4	Adapter for EN pressure gauge 1/4, without pressure gauge	
A8	Adapter for EN pressure gauge 1/8, without pressure gauge	
A8M	Adapter for EN pressure gauge 1/8, with precision pressure gauge	
AD7	Pressure sensor with switching display, M8 plug, threshold value comparator, PNP, N/O	
AD8	Pressure sensor with switching display, M8 plug, threshold value comparator, PNP, N/C	
AD9	Pressure sensor with switching display, M8 plug, window comparator, PNP, N/O	
AD10	Pressure sensor with operational status indicator, M8 plug, window comparator, PNP, N/C	
AD11	Pressure sensor with LCD display, M12 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V, 4...20 mA	
AD12	Pressure sensor with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V, 4...20 mA	
VS	Cover plate	


007	Rotary knob alternative	
	None	
LD	Long rotary knob	
008	Alternative mounting position	
	None	
KD	Rotary knob underneath	
009	Lockability	
	None	
AS	Can be locked using accessories	
E11	With integrated lock	
010	Type of mounting	
	Without mounting bracket	
WR	Mounting bracket with knurled nut on regulator knob	
WP	Mounting bracket basic design	
WPM	Mounting bracket for hooking in service unit components	
WB	Mounting centrally at rear (wall mounting top and bottom), connecting plates not required	
011	EU certification	
	None	
EX4	II 2GD	
012	UL certification	
	None	
UL1	cULus ordinary location for Canada and USA	
013	Flow direction	
	Flow direction from left to right	
Z	Flow direction from right to left	

Datasheet

Pressure regulation range/actuation,
manually actuated



Pressure regulation range/actuation,
pneumatically actuated



-  Flow rate
800 ... 5000 l/min
-  Temperature range
-10 ... +60 °C
-  Operating pressure
1 ... 14 bar
-  www.festo.com



The precision pressure regulator is suitable for sensitive applications requiring a pressure hysteresis of 0.02 bar. The output pressure p2 can be set within the pressure regulation range either manually using the rotary knob or pneumatically via pilot pressure p12 by an external pilot regulator (where possible using a precision pres-

sure regulator). When the input pressure p1 is switched off, the output pressure p2 is exhausted via port 3 (secondary exhausting).

- Good regulation characteristics with minimal hysteresis and input pressure compensation
- High flow rate with minimal pressure drop
- High secondary exhausting for ultra-fast reaction times
- Actuator lock to protect the set values from being adjusted
- Four pressure regulation ranges: 0.05 ... 0.7 bar, 0.05 ... 2.5 bar, 0.1 ... 4 bar and 0.1 ... 12 bar
- Optional pressure sensor
- Optional device variant EX4 for use in potentially explosive areas in zones 1, 2, 21 and 22

General technical data			
Size		MS6	
Pneumatic connection 1, 2			
Female thread		G1/4, G3/8 or G1/2	
Connecting plate	[AG...]	G1/4, G3/8, G1/2, G3/4 or G1	
	[AQ...]	1/4 NPT, 3/8 NPT, 1/2 NPT or 3/4 NPT	
Pneumatic connection 3 (secondary exhausting)		G1/4	
Pilot air port 12		G1/8 (MS6-LRP-...-PO)	
Design		Piloted precision diaphragm regulator	
Regulator function		Output pressure constant, with secondary exhausting	
Type of mounting	With accessories		
	In-line installation		
	Front panel mounting		
Mounting position		Any	
Actuator lock	Rotary knob with latch		
	Rotary knob with latch, can be locked using accessories		
	Rotary knob with integrated lock		
Pressure regulation range/ actuation ¹⁾	[D2]	[bar]	0.05 ... 0.7, manually actuated
	[D4]	[bar]	0.05 ... 2.5, manually actuated
	[D5]	[bar]	0.1 ... 4, manually actuated
	[D7]	[bar]	0.1 ... 12, manually actuated (0.1 ... 10 with pressure sensor or with UL certification)
	[PO]	[bar]	0.1 ... 12, pneumatically actuated (0.1 ... 10 with pressure sensor or with UL certification)
Max. pressure hysteresis		[bar]	0.02
Pressure indication		With pressure sensor for indicating the output pressure via LCD display and electrical output	
		With pressure sensor for indicating the output pressure via the switching status indicator and electrical output	
		Via precision pressure gauge for indicating the output pressure	
		Prepared for G1/8	
		Prepared for G1/4	

1) [D2]/[D4]/[D5]/[D7]: input pressure p1 ≥ output pressure p2 + 1 bar.

[PO]: pilot pressure p12 = output pressure p2 + max. 0.5 bar

• Note: This product conforms to ISO 1179-1 and ISO 228-1.

Datasheet

Flow rates					
Pressure regulation range		[D2]: 0.05 ... 0.7 bar		[D4]: 0.05 ... 2.5 bar	
				[D5]: 0.1 ... 4 bar	
				[D7]/[P0]: 0.1 ... 12 bar	
Standard nominal flow rate q _N [l/min]					
q _{NN} 1 → 2	G1/4	800 ¹⁾	1100 ²⁾	1400 ³⁾	3000 ⁴⁾
	G3/8	1100 ¹⁾	1400 ²⁾	1700 ³⁾	3300 ⁴⁾
	G1/2	1600 ¹⁾	2300 ²⁾	3000 ³⁾	5000 ⁴⁾
Secondary exhaust flow rate [l/min]					
q _N 2 → 3	≥ 220 ⁵⁾		≥ 450 ⁶⁾		≥ 650 ⁷⁾
				≥ 900 ⁸⁾	

1) Measured at p₁ = 10 bar and p₂ = 0.5 bar, Δp = 0.1 bar2) Measured at p₁ = 10 bar and p₂ = 1.5 bar, Δp = 0.1 bar3) Measured at p₁ = 10 bar and p₂ = 2.5 bar, Δp = 0.1 bar4) Measured at p₁ = 10 bar and p₂ = 6.0 bar, Δp = 0.1 bar5) Measured at p₁ = 10 bar and p₂ = 0.7 bar, Δp₂ = 0.1 bar6) Measured at p₁ = 10 bar and p₂ = 2.5 bar, Δp₂ = 0.1 bar7) Measured at p₁ = 10 bar and p₂ = 4.0 bar, Δp₂ = 0.1 bar8) Measured at p₁ = 10 bar and p₂ = 6.0 bar, Δp₂ = 0.1 bar

Operating and environmental conditions	
Operating pressure	[MPa] 0.1 ... 1.4 (0.1 ... 1) ¹⁾ (0.35 ... 1.1) ²⁾
	[bar] 1 ... 14 (1 ... 10) ¹⁾ (3.5 ... 11) ²⁾
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4], Inert gases
Note on the operating/pilot medium	Lubricated operation not possible
Ambient temperature	[°C] -10 ... +60 (0 ... +50) ³⁾
Temperature of medium	[°C] -10 ... +60 (0 ... +50) ³⁾
Storage temperature	[°C] -10 ... +60
Corrosion resistance class CRC ⁴⁾	2
UL certification ⁵⁾	c UL us - Recognized (OL)

1) Value in brackets applies to MS6-LRP with UL certification.

2) Value in brackets applies to MS6-LRP, electrically actuated

3) Value in brackets applies to MS6-LRP with pressure sensor.

4) More information www.festo.com/x/topic/crc5) More information: www.festo.com/catalogue/ms6-lrp → Support/Downloads.

Electrical data	
Pressure regulation range	[PE10] [PI10]
Operating voltage range DC	[V] 21.6 ... 26.4
Max. electrical power consumption	[W] 4.2
Max. current consumption	[A] 0.16
Nominal operating voltage DC	[V] 24 (Plug connector, M12x1, 5-pin, A-coded)
Residual ripple	10%
Analogue input signal range	
	[V] 0 ... 10
	[mA] -
	4 ... 20

ATEX	
EU certification	[EX4]
ATEX category for gas	II 2G
Type of ignition protection for gas	Ex h IIC T6 Gb X
ATEX category for dust	II 2D
Type of ignition protection for dust	Ex h IIIC T60°C Db X
Explosion-proof ambient temperature	-10 °C ≤ Ta ≤ +60 °C
Explosion protection certification outside the EU	EPL Db (GB) EPL Gb (GB)
CE marking (see declaration of conformity) ¹⁾	To EU Explosion Protection Directive (ATEX)
UKCA marking (see declaration of conformity) ¹⁾	To UK explosion regulations


1) More information: www.festo.com/catalogue/ms6-lrp → Support/Downloads.

Weight [g]	
Precision pressure regulator	1000
Precision pressure regulator with rotary knob with integrated lock	1120

Datasheet

Materials

Sectional view




Precision pressure regulator

[1]	Housing	Die-cast aluminium
[2]	Rotary knob	PA, POM
	Rotary knob with integrated lock	Aluminium
[3]	Diaphragms	NBR
[4]	Bottom cover	PC
[5]	Springs	Steel
–	Seals	NBR
Note on materials		RoHS-compliant
LABS (PWIS) conformity		VDMA24364-B1/B2-L


Standard flow rate q_n as a function of output pressure p_2 ($p_1 = 10$ bar)

MS6-LRP-1/4-D2




[D2]: 0.05 ... 0.7 bar

MS6-LRP-3/8-D2




[D2]: 0.05 ... 0.7 bar

MS6-LRP-1/2-D2



[D2]: 0.05 ... 0.7 bar

MS6-LRP-1/4-D4/D5




[D4]: 0.05 ... 2.5 bar

[D5]: 0.1 ... 4 bar

Datasheet


Standard flow rate q_n as a function of output pressure p_2 ($p_1 = 10$ bar)

MS6-LRP-3/8-D4/D5




— [D4]: 0.05 ... 2.5 bar
- · - · - [D5]: 0.1 ... 4 bar

MS6-LRP-1/2-D4/D5




— [D4]: 0.05 ... 2.5 bar
- · - · - [D5]: 0.1 ... 4 bar

MS6-LRP-1/4-D7/PO




— [D7]/[PO]: 0.1 ... 12 bar

MS6-LRP-3/8-D7/PO




— [D7]/[PO]: 0.1 ... 12 bar

MS6-LRP-1/2-D7/PO



— [D7]/[PO]: 0.1 ... 12 bar

MS6-LRP-1/2-PE10/PI10




— [PE10]/[PI10]: 0.01 ... 1 MPa


Datasheet

Internal air consumption q_n as a function of input pressure p_1

MS6-LRP-...-D2/D4



MS6-LRP-...-D5/D7/PO/PE10/PI10




Dimensions

Download CAD data → www.festo.com

[D2]/[D4]/[D5]/[D7] Pressure regulation range, manually actuated

[A8M] Adapter for EN pressure gauge 1/8, with precision pressure gauge

[AS] Rotary knob with latch, can be locked using accessories



Type	B1	B2	B3	B7	D1	D2 Ø	D4 Ø	L1	L2	L3	L4
MS6-LRP-1/4-D2/D4/D5/D7-A8M-AS	62	31	76	116	G1/4	51.2	40	123	68	95.5	114
MS6-LRP-3/8-D2/D4/D5/D7-A8M-AS					G3/8						
MS6-LRP-1/2-D2/D4/D5/D7-A8M-AS					G1/2						


• Note: This product conforms to ISO 1179-1 and ISO 228-1.

Datasheet

Dimensions

Download CAD data → www.festo.com

[PO] Pressure regulation range, pneumatically actuated
[VS] Cover plate




Type	B1	B2	B3	D1	D2	L1	L2	L4
MS6-LRP-1/4-PO-VS	62	31	76	G1/4	G1/8	136	81	127
MS6-LRP-3/8-PO-VS				G3/8				
MS6-LRP-1/2-PO-VS				G1/2				

⚡ Note: This product conforms to ISO 1179-1 and ISO 228-1.

Dimensions – Alternative mounting position

Download CAD data → www.festo.com

[KD] Rotary knob underneath



Type	B1	B2	B3	D1	D2 Ø	L1	L2	L3	L4
MS6-LRP-1/4-...-KD	62	31	76	G1/4	51.2	133	78	95.1	124
MS6-LRP-3/8-...-KD				G3/8					
MS6-LRP-1/2-...-KD				G1/2					

⚡ Note: This product conforms to ISO 1179-1 and ISO 228-1.

Datasheet


Dimensions – Pressure gauge alternatives

Download CAD data → www.festo.com

[VS] Cover plate

[A8] Adapter for EN pressure gauge 1/8, without pressure gauge

[A4] Adapter for EN pressure gauge 1/4, without pressure gauge




Type	B2	B3	D1	D4
MS6-LRP-1/4-...-VS	31	76	G1/4	-
MS6-LRP-3/8-...-VS			G3/8	
MS6-LRP-1/2-...-VS			G1/2	
MS6-LRP-1/4-...-A8	31	78.5	G1/4	G1/8
MS6-LRP-3/8-...-A8			G3/8	
MS6-LRP-1/2-...-A8			G1/2	
MS6-LRP-1/4-...-A4	31	78.5	G1/4	G1/4
MS6-LRP-3/8-...-A4			G3/8	
MS6-LRP-1/2-...-A4			G1/2	

⚡ Note: This product conforms to ISO 1179-1 and ISO 228-1.

Datasheet

Dimensions – Pressure gauge alternatives

[AD7 ... 10] Pressure sensor without LCD display (switching status indicator only)



Variant AD7:
SDE5-D10-O-...-P-M8 with 3-pin
M8x1 plug, threshold value com-
parator, 1 switching output PNP,
N/O contact

Variant AD8:
SDE5-D10-C-...-P-M8 with 1x 3-pin
M8 plug, threshold value comparator,
1 switching output PNP, N/C contact

Variant AD9:
SDE5-D10-O3-...-P-M8 with 1x 3-pin
M8 plug, window comparator,
1 switching output PNP, N/O contact

Variant AD10:
SDE5-D10-C3-...-P-M8 with 1x 3-pin
M8 plug, window comparator,
1 switching output PNP, N/C contact

Download CAD data → www.festo.com


Datasheets → Internet: sde5

Type	B2	B3	B5	B6	D6
MS6-LRP-...-AD7/AD8/AD9/AD10	31	79.1	51	16	M8x1

⚡ Note: This product conforms to ISO 1179-1 and ISO 228-1.

Dimensions – Pressure gauge alternatives

[AD11/AD12] Pressure sensor with LCD display



Variant AD11:
SPAU-P10R-MS-L-PNLK-M12 with
plug M12, 4-pin, IO-Link®, PNP,
NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA

Variant AD12:
SPAU-P10R-MS-L-PNLK-M8 with plug
M8, 4-pin, IO-Link®, PNP, NPN,
0 ... 10 V, 1 ... 5 V, 4 ... 20 mA

Download CAD data → www.festo.com

Datasheets → Internet: spau

Type	B2	B3	B4	B5	B6	D6	L5	L6
MS6-LRP-...-AD11	31	101.8	93.7	51	32	M12x1	41.2	39
MS6-LRP-...-AD12	31	101.8	93.7	51	32	M8x1	37.9	39

⚡ Note: This product conforms to ISO 1179-1 and ISO 228-1.

58

→Internet: www.festo.com/catalogue/...

Subject to change – 2025/11


Datasheet

Dimensions – Electrically actuated VPPE pilot control

[PE10/PI10] Proportional-pressure regulator with LED display

Download CAD data → www.festo.com

Datasheets → Internet: vppe



Variant PE10:
electrically actuated (pilot control using proportional-pressure regulator with LED display, 7-segment) 0 ... 10 V

Variant PI10:
electrically actuated (pilot control using proportional-pressure regulator with LED display, 7-segment)
setpoint value 4 ... 20 mA

Plug connector, M12x1, 5-pin, A-coded

→ Flow direction

Type	B1	B2	B3	B4	L1	L2	L3	L6
MS6-LRP-...-PE10/PI10	62	31	76	62	161	106	10	9

† Note: This product conforms to ISO 1179-1 and ISO 228-1.

Datasheet

Dimensions – Rotary knob


Download CAD data → www.festo.com

For control panel installation

[] Rotary knob with latch


[AS] Rotary knob with latch,
can be locked using accessories

[E11] Rotary knob with integrated
lock



[LD] Rotary knob, long, with latch

[LD-AS] Rotary knob, long, with
latch, can be locked using accessories



Type	B4	B5	D2	D3	L3	L8	L9	L10
MS6-LRP-...	–	–	51.2	M44x1	86	21	14	–
MS6-LRP-...-AS	64.4	38.8			95.1	12	5	
MS6-LRP-...-E11	–	–			110	21	14	
MS6-LRP-...-LD	–	–	51.2	–	86	–	–	139
MS6-LRP-...-LD-AS	64.4	38.8			95.5			148.5

Datasheet

Ordering data					
Pneumatic connection 1	Pressure regulation range	Analogue input signal range	Flow direction	Part no.	Type
Manually actuated					
G1/4	0.05 ... 0.7 bar	–	From left to right	538004	MS6-LRP-1/4-D2-A8
	0.05 ... 2.5 bar	–	From left to right	538006	MS6-LRP-1/4-D4-A8
	0.1 ... 4 bar	–	From left to right	538008	MS6-LRP-1/4-D5-A8
	0.1 ... 12 bar	–	From left to right	538010	MS6-LRP-1/4-D7-A8
G3/8	0.05 ... 0.7 bar	–	From left to right	538012	MS6-LRP-3/8-D2-A8
	0.05 ... 2.5 bar	–	From left to right	538014	MS6-LRP-3/8-D4-A8
	0.1 ... 4 bar	–	From left to right	538016	MS6-LRP-3/8-D5-A8
	0.1 ... 12 bar	–	From left to right	538018	MS6-LRP-3/8-D7-A8
G1/2	0.05 ... 0.7 bar	–	From left to right	538020	MS6-LRP-1/2-D2-A8
	0.05 ... 2.5 bar	–	From left to right	538022	MS6-LRP-1/2-D4-A8
	0.1 ... 4 bar	–	From left to right	538024	MS6-LRP-1/2-D5-A8
	0.1 ... 12 bar	–	From left to right	538026	MS6-LRP-1/2-D7-A8
Electrically actuated					
G1/2	0.01 ... 1 MPa	0 ... 10 V	From left to right	8203861	MS6-LRP-1/2-PE10-VS
	0.01 ... 1 MPa	4 ... 20 mA	From left to right	8203862	MS6-LRP-1/2-PI10-VS

Ordering data – Modular product system

Ordering table		Conditions	Code	Enter code
Grid dimension	[mm] 62			
Module no.	538028			
Series	Standard		MS	MS
Size	6		6	6
Function	Precision pressure regulator		-LRP	-LRP
Pneumatic connection	Female thread G1/4	[1]	- 1/4	
	Female thread G3/8	[1]	-3/8	
	Female thread G1/2	[1]	- 1/2	
	Connecting plate G1/4		-AGB	
	Connecting plate G3/8		-AGC	
	Connecting plate G1/2		-AGD	
	Connecting plate G3/4		-AGE	
	Connecting plate G1		-AGF	
	Connecting plate NPT1/4	[1]	-AQN	
	Connecting plate NPT3/8	[1]	-AQP	
	Connecting plate NPT1/2	[1]	-AQR	
	Connecting plate NPT3/4	[1]	-AQS	
Pressure regulation range/actuation	0.05 ... 0.7 bar, manually actuated		-D2	
	0.05 ... 2.5 bar, manually actuated		-D4	
	0.1 ... 4 bar, manually actuated		-D5	
	0.1 ... 12 bar, manually actuated		-D7	
	0.1 ... 12 bar, pneumatically actuated (pressure range determined by pilot regulator)	[1] [2]	-PO	
	0.01 ... 1 MPa, electrically actuated (pilot control using proportional-pressure regulator with LED display, 7-segment) 0 ... 10 V	[3]	-PE10	
	0.01 ... 1 MPa, electrically actuated (pilot control using proportional-pressure regulator with LED display, 7-segment) setpoint value 4 ... 20 mA	[3]	-PI10	
Pressure gauge alternatives	Cover plate		-VS	
	Adapter for EN pressure gauge 1/8, without pressure gauge		-A8	
	Adapter for EN pressure gauge 1/8, with precision pressure gauge		-A8M	
	Adapter for EN pressure gauge 1/4, without pressure gauge		-A4	
	Pressure sensor with switching status indicator, plug M8, threshold value comparator, PNP, N/O contact	[1] [5]	-AD7	
	Pressure sensor with switching status indicator, plug M8, threshold value comparator, PNP, N/C contact	[1] [5]	-AD8	
	Pressure sensor with switching status indicator, M8 plug, window comparator, PNP, N/O contact	[1] [5]	-AD9	
	Pressure sensor with switching status indicator, M8 plug, window comparator, PNP, N/C contact	[1] [5]	-AD10	
	Pressure sensor with LCD display, M12 plug, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA	[4]	-AD11	
	Pressure sensor with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA	[4]	-AD12	

[1] 1/4, 3/8, 1/2, Not with EU EX4 certification.

AQN, AQP, AQR,
AQS, PO,
AD7 ... AD10, KD,
E11, WPM

[2] PO Not with rotary knob alternative LD.

Not with locking options AS, E11.

Not with mounting type WR.

[3] PE10, PI10 Not with WR, AS, E11, EX4, UL1, LD

[4] AD11/AD12 Measuring range max. 10 bar.

Not with pressure regulation range/actuation D2, D4.

[5] AD7 ... AD10 Measuring range max. 10 bar.

Not with pressure regulation range/actuation D2.


Ordering data – Modular product system

Ordering table		Grid dimension	[mm]	62	Conditions	Code	Enter code
Rotary knob alternative	None						
	Long rotary knob			[6]		-LD	
Alternative mounting position	None						
	Rotary knob underneath			[1] [7]		-KD	
Locking option	None						
	Lockable using accessories					-AS	
	With integrated lock			[1]		-E11	
Type of mounting	Without mounting bracket						
	Mounting bracket with knurled nut for regulator head			[8]		-WR	
	Mounting bracket standard design			[9]		-WP	
	Mounting bracket for hooking in service unit components			[1] [9]		-WPM	
	Mounting bracket centrally at the rear (wall mounting top and bottom), connecting plates not required					-WB	
EU certification	None						
	II 2GD to EU Explosion Protection Directive (ATEX)					-EX4	
UL certification	None						
	cULus, ordinary location for Canada and USA					-UL1	
Flow direction	Flow direction from left to right						
	Flow direction from right to left					-Z	


- [6] LD Not with locking option E11.
 [7] KD Not with mounting type WP.
 [8] WR Not with rotary knob alternative LD.
 [9] WP, WPM Only with connecting plate AGB, AGC, AGD, AGE, AQN, AQP, AQR or AQS.

Peripherals overview

Precision pressure regulator MS6-LRPB with pressure output at the rear



Manually actuated Pneumatically actuated Electrically actuated



Peripherals overview

Mounting attachments and accessories		Individual device		Combination		→ Page/Internet
		Without connecting plate	With connecting plate	Without connecting plate	With connecting plate	
[1]	Precision pressure regulator MS6-LRPB	■	■	■	■	64
[2]	Angled outlet block B...	■	■	■	■	79
[3]	Mounting bracket MS6-WP	–	■	■	■	ms6-wp
[4]	Mounting bracket MS6-WPB	–	■	■	■	ms6-wp
[5]	Mounting bracket MS6-WPE	–	■	■	■	ms6-wp
[6]	Mounting bracket MS6-WPM	–	■	■	■	ms6-wp
[7]	Cover cap MS6-END	■	–	■	–	ms6-end
[8]	Module connector MS6-MV	–	■	■	■	ms6-mv
[9]	Connecting plate SET MS6-AG...	–	■	–	■	ms6-ag
[10]	Pressure sensor with LCD display AD11/AD12	■	■	■	■	79
[11]	Connecting cable NEBA-M8...-LE4/NEBA-M12...-LE4	■	■	■	■	106
[12]	Pressure sensor without display AD7 ... AD10	■	■	■	■	79
[13]	Connecting cable NEBA-M8...-LE3	■	■	■	■	106
[14]	Adapter for EN pressure gauge 1/8, 1/4 A8/A4	■	■	■	■	79
[15]	Precision pressure gauge A8M/MAP	■	■	■	■	79, 106
[16]	Cover plate VS	■	■	■	■	79
[17]	Padlock LRVS-D	■	■	■	■	106


 Note

Additional accessories:

- Module connectors for combination with size MS4/MS6 or size MS9
→ Internet: amv, rmv, armv
- Adapters for mounting on profiles
→ Internet: ipm-80, ipm-40-80, ipm-80-80

Peripherals overview


Precision pressure regulator MS6-LRPB with pressure output at the front



Manually actuated

Pneumatically actuated

Electrically actuated



Peripherals overview

Mounting attachments and accessories		Individual device		Combination		→ Page/Internet
		Without connecting plate	With connecting plate	Without connecting plate	With connecting plate	
[1]	Precision pressure regulator MS6-LRPB	■	■	■	■	64
[2]	Mounting bracket MS6-WB	■	■	–	–	ms6-wb
[3]	Cover cap MS6-END	■	–	■	–	ms6-end
[4]	Module connector MS6-MV	–	■	■	■	ms6-mv
[5]	Connecting plate SET MS6-AG...	–	■	–	■	ms6-ag
[6]	Angled outlet block B...	■	■	■	■	79
[7]	Pressure sensor without display AD7 ... AD10	■	■	■	■	79
[8]	Connecting cable NEBA-M8...-LE3	■	■	■	■	106
[9]	Cover plate VS	■	■	■	■	79
[10]	Mounting bracket MS6-WR	■	■	–	–	ms6-wr
[11]	Knurled nut (included in the scope of delivery) MS-LR	■	■	–	–	–
[12]	Padlock LRVS-D	■	■	■	■	106


Type codes

001	Series	
MS	MS series	
002	Size	
6	Grid dimension 62 mm	
003	Function	
LRPB	Precision pressure regulator for manifold installation	
004	Pneumatic connection	
1/2	Female thread G1/2	
AGB	Sub-base G1/4	
AGC	Sub-base G3/8	
AGD	Sub-base G1/2	
AGE	Sub-base G3/4	
AGF	Sub-base G1	
005	Pressure regulation range	
D2	0.05 ... 0.7 bar	
D4	0.05 ... 2.5 bar	
D5	0.1 ... 4 bar	
D7	0.1 ... 12 bar	
PE10	0.1 ... 10 bar electrically actuated (pilot control using proportional-pressure regulator with LED indicator, 7-segment), set-point 0 ... 10V	
PI10	0.1 ... 10 bar electrically actuated (pilot control using proportional-pressure regulator with LED indicator, 7-segment), set-point 4 ... 20mA	
P0	Max. 12 bar, pneumatically actuated (pressure range determined by pilot regulator)	
006	Pressure gauge alternatives	
A4	Adapter for EN pressure gauge 1/4, without pressure gauge	
A8	Adapter for EN pressure gauge 1/8, without pressure gauge	
A8M	Adapter for EN pressure gauge 1/8, with precision pressure gauge	
AD7	Pressure sensor with switching display, M8 plug, threshold value comparator, PNP, N/O	
AD8	Pressure sensor with switching display, M8 plug, threshold value comparator, PNP, N/C	
AD9	Pressure sensor with switching display, M8 plug, window comparator, PNP, N/O	
AD10	Pressure sensor with operational status indicator, M8 plug, window comparator, PNP, N/C	
AD11	Pressure sensor with LCD display, M12 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V, 4...20 mA	
AD12	Pressure sensor with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V, 4...20 mA	
VS	Cover plate	


007	Rotary knob alternative	
	None	
LD	Long rotary knob	
008	Alternative mounting position	
	None	
KD	Rotary knob underneath	
009	Lockability	
	None	
AS	Can be locked using accessories	
E11	With integrated lock	
010	Alternative pressure outlet	
	None	
BD	Angled outlet block QS-8	
BE	Angled outlet block QS-10	
011	Type of mounting	
	Without mounting bracket	
WR	Mounting bracket with knurled nut on regulator knob	
WP	Mounting bracket basic design	
WPB	Mounting bracket for large wall gap	
WPM	Mounting bracket for hooking in service unit components	
WB	Mounting centrally at rear (wall mounting top and bottom), connecting plates not required	
012	EU certification	
	None	
EX4	II 2GD	
013	UL certification	
	None	
UL1	cULus ordinary location for Canada and USA	
014	Outlet direction	
	Pressure output to the rear	
Z	Pressure output to the front	

Datasheet


Pressure regulation range/actuation,
manually actuated



Pressure regulation range/actuation,
pneumatically actuated



Several precision pressure regulators
mounted next to one another to form a
regulator manifold:



The precision pressure regulator is
suitable for sensitive applications
requiring a hysteresis of 0.02 bar.

-  - Flow rate
1600 ... 5000 l/min
-  - Temperature range
-10 ... +60 °C
-  - Operating pressure
1 ... 14 bar
-  - www.festo.com



The output pressure p2 can be set
within the pressure regulation range
either manually using the rotary knob
or pneumatically via pilot pressure p12
by an external pilot regulator (where
possible using a precision pressure
regulator). When the input pressure p1
is switched off, the output pressure p2
is exhausted via port 3 (secondary ex-
hausting).

- Good regulation characteristics with minimal hysteresis and input pressure compensation
- Manifold assembly with through air supply
- For configuring a regulator manifold with independent pressure regulation ranges
- Actuator lock to protect the set values from being adjusted
- Four pressure regulation ranges: 0.05 ... 0.7 bar, 0.05 ... 2.5 bar, 0.1 ... 4 bar and 0.1 ... 12 bar
- Optional pressure sensor
- Optional device variant EX4 for use in potentially explosive areas in zones 1, 2, 21 and 22

General technical data

Size	MS6	
Pneumatic connection 1		
Female thread	G1/2	
Connecting plate	[AG...]	G1/4, G3/8, G1/2, G3/4 or G1
Pneumatic connection 2		
Female thread	G1/2	
Angled outlet block	[BD]	QS-8
	[BE]	QS-10
Pneumatic connection 3	G1/4	
Pilot air port 12	G1/8 (MS6-LRPB-...-PO)	
Design	Piloted precision diaphragm regulator with through compressed air supply	
Regulator function	Output pressure constant, with secondary exhausting	
Type of mounting	With accessories In-line installation Front panel mounting	
Mounting position	Any	
Actuator lock	Rotary knob with latch Rotary knob with latch, can be locked using accessories Rotary knob with integrated lock	
Pressure regulation range/actuation ¹⁾	[D2] [bar]	0.05 ... 0.7, manually actuated
	[D4] [bar]	0.05 ... 2.5, manually actuated
	[D5] [bar]	0.1 ... 4, manually actuated
	[D7] [bar]	0.1 ... 12, manually actuated (0.1 ... 10 with pressure sensor AD... or with UL certification)
	[PO] [bar]	0.1 ... 12, pneumatically actuated (0.1 ... 10 with pressure sensor AD... or with UL certification)
Max. pressure hysteresis	[bar]	0.02

1) [D2]/[D4]/[D5]/[D7]: input pressure p1 ≥ output pressure p2 + 1 bar.

[PO]: pilot pressure p12 = output pressure p2 + max. 0.5 bar

• Note: This product conforms to ISO 1179-1 and ISO 228-1.

Datasheet

General technical data	
Size	MS6
Pressure indication	With pressure sensor for indicating the output pressure via LCD display and electrical output
	With pressure sensor for indicating the output pressure via the switching status indicator and electrical output
	Via pressure gauge for displaying the output pressure
	Prepared for G1/8
	Prepared for G1/4

Flow rates				
Pressure regulation range	[D2]: 0.05 ... 0.7 bar	[D4]: 0.05 ... 2.5 bar	[D5]: 0.1 ... 4 bar	[D7]/[P0]: 0.1 ... 12 bar
Standard nominal flow rate q _N [l/min]				
q _N 1 → 2	G1/2	1600 ¹⁾	2300 ²⁾	3000 ³⁾
Secondary exhaust flow rate [l/min]				
q _N 2 → 3	≥ 220 ⁵⁾	≥ 450 ⁶⁾	≥ 650 ⁷⁾	≥ 900 ⁸⁾

1) Measured at p₁ = 10 bar and p₂ = 0.5 bar, Δp = 0.1 bar2) Measured at p₁ = 10 bar and p₂ = 1.5 bar, Δp = 0.1 bar3) Measured at p₁ = 10 bar and p₂ = 2.5 bar, Δp = 0.1 bar4) Measured at p₁ = 10 bar and p₂ = 6.0 bar, Δp = 0.1 bar5) Measured at p₁ = 10 bar and p₂ = 0.7 bar, Δp₂ = 0.1 bar6) Measured at p₁ = 10 bar and p₂ = 2.5 bar, Δp₂ = 0.1 bar7) Measured at p₁ = 10 bar and p₂ = 4.0 bar, Δp₂ = 0.1 bar8) Measured at p₁ = 10 bar and p₂ = 6.0 bar, Δp₂ = 0.1 bar

Operating and environmental conditions	
Operating pressure	[MPa]
	0.1 ... 1.4 (0.1 ... 1) ¹⁾ (0.35 ... 1.1) ²⁾
	[bar]
	1 ... 14 (1 ... 10) ¹⁾ (3.5 ... 11) ²⁾
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
	Inert gases
Note on the operating/pilot medium	Lubricated operation not possible
Ambient temperature	[°C]
	−10 ... +60 (0 ... +50) ²⁾
Temperature of medium	[°C]
	−10 ... +60 (0 ... +50) ²⁾
Storage temperature	[°C]
	−10 ... +60
Corrosion resistance class CRC ³⁾	2
UL certification ⁴⁾	c UL us - Recognized (OL)

1) Value in brackets applies to MS6-LRPB with UL certification.

2) Value in brackets applies to MS6-LRPB, electrically actuated

3) Value in brackets applies to MS6-LRPB with pressure sensor.

4) More information www.festo.com/x/topic/crc5) More information: www.festo.com/catalogue/ms6-lrpb → Support/Downloads.

Electrical data	
Pressure regulation range	[PE10]
	[PI10]
Operating voltage range DC	[V]
	21.6 ... 26.4
Max. electrical power consumption	[W]
	4.2
Max. current consumption	[A]
	0.16
Nominal operating voltage DC	[V]
	24 (Plug connector, M12x1, 5-pin, A-coded)
Residual ripple	
	10%
Analogue input signal range	
	[V]
	0 ... 10
	[mA]
	–
	4 ... 20

ATEX	
EU certification	[EX4]
ATEX category for gas	II 2G
Type of ignition protection for gas	Ex h IIC T6 Gb X
ATEX category for dust	II 2D
Type of ignition protection for dust	Ex h IIIC T60°C Db X
Explosion-proof ambient temperature	−10 °C ≤ Ta ≤ +60 °C
Explosion protection certification outside the EU	EPL Db (GB) EPL Gb (GB)
CE marking (see declaration of conformity) ¹⁾	To EU Explosion Protection Directive (ATEX)
UKCA marking (see declaration of conformity) ¹⁾	To UK explosion regulations


1) More information: www.festo.com/catalogue/ms6-lrpb → Support/Downloads.

Datasheet

Weight [g]	
Precision pressure regulator	1000
Precision pressure regulator with rotary knob with integrated lock	1120

Materials

Sectional view




Precision pressure regulator (manifold assembly)

[1]	Housing	Die-cast aluminium
[2]	Rotary knob	PA, POM
	Rotary knob with integrated lock	Aluminium
[3]	Diaphragm	NBR
[4]	Bottom cover	PC
[5]	Springs	Steel
–	Seals	NBR
Note on materials		RoHS-compliant
LABS (PWIS) conformity		VDMA24364-B1/B2-L


Standard flow rate q_n as a function of output pressure p_2 ($p_1 = 10$ bar)

MS6-LRPB-1/2-D2



[D2]: 0.05 ... 0.7 bar


MS6-LRPB-1/2-D4/D5



[D4]: 0.05 ... 2.5 bar

[D5]: 0.1 ... 4 bar

MS6-LRPB-1/2-D7/PO



[D7]/[PO]: 0.1 ... 12 bar


Datasheet

Internal air consumption qn as a function of input pressure p1

MS6-LRPB-...-D2/D4




MS6-LRPB-...-D5/D7/P0



Dimensions

Download CAD data → www.festo.com

- [D2]/[D4]/[D5]/[D7] Pressure regulation range, manually actuated
- [A8M] Adapter for EN pressure gauge 1/8, with precision pressure gauge
- [BD]/[BE] Angled outlet block
- [AS] Rotary knob with latch, can be locked using accessories



Type	B1	B2	B3	B6	B7	B8	D1	D2 ø	D4 ø	L1	L2	L3	L4	L6
MS6-LRPB-1/2-D2/D4/D5/D7-A8M-BD/BE-AS	62	31	76	23	115	23.4	G1/2	51.2	40	124	68	95.1	114	10

• Note: This product conforms to ISO 1179-1 and ISO 228-1.

Datasheet


Dimensions

Download CAD data → www.festo.com

[PO] Pressure regulation range, pneumatically actuated

[VS] Cover plate

[BD]/[BE] Angled outlet block




Type	B1	B2	B3	B6	D1	D2	L1	L2	L4
MS6-LRPB-1/2-PO-VS-BD/BE	62	31	76	23	G1/2	G1/8	137	81	127

Note: This product conforms to ISO 1179-1 and ISO 228-1.

Dimensions – Alternative mounting position

Download CAD data → www.festo.com

[KD] Rotary knob underneath



Type	B1	B2	B3	B7	B8	D1	D2 Ø	D4 Ø	L1	L2	L3	L4	L6
MS6-LRPB-1/2-...-KD	62	31	99	138	23.4	G1/2	51.2	40	124	68	95.1	114	10

Note: This product conforms to ISO 1179-1 and ISO 228-1.

Datasheet

Dimensions – Pressure gauge alternatives

[VS] Cover plate

Download CAD data → www.festo.com

[A8] Adapter for EN pressure gauge 1/8, without pressure gauge

[A4] Adapter for EN pressure gauge 1/4, without pressure gauge

[1] Push-in connector

→ Flow direction

Type	B2	B3	B6	D1	D4
MS6-LRPB-1/2-...-VS	31	76	23	G1/2	–
MS6-LRPB-1/2-...-A8		78.5			G1/8
MS6-LRPB-1/2-...-A4		78.5			G1/4

– † – Note: This product conforms to ISO 1179-1 and ISO 228-1.


Datasheet

Dimensions – Pressure gauge alternatives

Download CAD data → www.festo.com

Datasheets → Internet: sde5

[AD7 ... 10] Pressure sensor without LCD display (switching status indicator only)



Variant AD7:
SDE5-D10-O-...-P-M8 with 3-pin
M8x1 plug, threshold value compar-
ator, 1 switching output PNP, N/O
contact

Variant AD8:
SDE5-D10-C-...-P-M8 with 1x 3-pin
M8 plug, threshold value comparator,
1 switching output PNP, N/C contact

Variant AD9:
SDE5-D10-O3-...-P-M8 with 1x 3-pin
M8 plug, window comparator,
1 switching output PNP, N/O contact

Variant AD10:
SDE5-D10-C3-...-P-M8 with 1x 3-pin
M8 plug, window comparator,
1 switching output PNP, N/C contact


→ Flow direction

Type	B2	B3	B5	B6	D6
MS6-LRPB-...-AD7/AD8/AD9/AD10	31	79.1	51	16	M8x1

Note: This product conforms to ISO 1179-1 and ISO 228-1.

[AD11/AD12] Pressure sensor with LCD display

Datasheets → Internet: spau



Variant AD11:
SPAU-P10R-MS-L-PNLK-M12 with
plug M12, 4-pin, IO-Link®, PNP,
NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA

Variant AD12:
SPAU-P10R-MS-L-PNLK-M8 with plug
M8, 4-pin, IO-Link®, PNP, NPN,
0 ... 10 V, 1 ... 5 V, 4 ... 20 mA

→ Flow direction

Type	B2	B3	B4	B5	B6	D6	L5	L6
MS6-LRPB-...-AD11	31	101.8	93.7	51	32	M12x1	41.2	39
MS6-LRPB-...-AD12	31	101.8	93.7	51	32	M8x1	37.9	39


Datasheet

Dimensions – Electrically actuated VPPE pilot control

Download CAD data → www.festo.com

[PE10/PI10] Proportional-pressure regulator with LED display
(with pressure output)

Datasheets → Internet: vppe



Variant PE10:
electrically actuated (pilot control using proportional-pressure regulator with LED display, 7-segment) 0 ... 10 V

Variant PI10:
electrically actuated (pilot control using proportional-pressure regulator with LED display, 7-segment)
setpoint value 4 ... 20 mA

Plug connector, M12x1, 5-pin, A-coded

Type	B1	B2	B3	B4	B6	L1	L2	L3	L6
MS6-LRPB-...-PE10/PI10	62	31	76	62	23	162	106	10	9


– Note: This product conforms to ISO 1179-1 and ISO 228-1.

Dimensions – Electrically actuated VPPE pilot control

Download CAD data → www.festo.com

[PE10/PI10] Proportional-pressure regulator with LED display
(without pressure output)

Datasheets → Internet: vppe



Variant PE10:
electrically actuated (pilot control using proportional-pressure regulator with LED display, 7-segment) 0 ... 10 V

Variant PI10:
electrically actuated (pilot control using proportional-pressure regulator with LED display, 7-segment)
setpoint value 4 ... 20 mA

Type	B1	B2	B3	B4	L1	L2	L3	L6
MS6-LRPB-...-PE10/PI10	62	31	76	62	161	106	10	9

– Note: This product conforms to ISO 1179-1 and ISO 228-1.


Datasheet

Dimensions – Rotary knob


For control panel installation

Download CAD data → www.festo.com

[] Rotary knob with latch

[AS] Rotary knob with latch,
can be locked using accessories[E11] Rotary knob with integrated
lock

[LD] Rotary knob, long, with latch

[LD-AS] Rotary knob, long,
with latch, can be locked using
accessories

Type	B4	B5	D2	D3	L3	L8	L9	L10
MS6-LRPB...	–	–	51.2	M44x1	86	21	14	–
MS6-LRPB...-AS	64.4	38.8			95.1	12	5	
MS6-LRPB...-E11	–	–			110	21	14	
MS6-LRPB...-LD	–	–		–	86	–	–	139
MS6-LRPB...-LD-AS	64.4	38.8			95.5			148.5

Datasheet

Ordering data					
Pneumatic connection 1	Pressure regulation range	Analogue input signal range	Flow direction	Part no.	Type
Manually actuated					
G1/2	0.05 ... 0.7 bar	–	From left to right	534865	MS6-LRPB-1/2-D2-A8-BD
	0.05 ... 2.5 bar	–	From left to right	534914	MS6-LRPB-1/2-D4-A8
	0.1 ... 4 bar	–	From left to right	534917	MS6-LRPB-1/2-D5-A8
	0.1 ... 12 bar	–	From left to right	534874	MS6-LRPB-1/2-D7-A8-BD
Electrically actuated					
G1/2	0.01 ... 1 MPa	0 ... 10 V	From left to right	8203863	MS6-LRPB-1/2-PE10-VS
	0.01 ... 1 MPa	4 ... 20 mA	From left to right	8203864	MS6-LRPB-1/2-PI10-VS

Ordering data – Modular product system

Ordering table		Conditions	Code	Enter code
Grid dimension	[mm] 62			
Module no.	535007			
Series	Standard		MS	MS
Size	6		6	6
Function	Precision pressure regulator for manifold assembly		-LRPB	-LRPB
Pneumatic connection	Female thread G1/2	[1]	- 1/2	
	Connecting plate G1/4		-AGB	
	Connecting plate G3/8		-AGC	
	Connecting plate G1/2		-AGD	
	Connecting plate G3/4		-AGE	
	Connecting plate G1		-AGF	
Pressure regulation range/actuation	0.05 ... 0.7 bar, manually actuated		-D2	
	0.05 ... 2.5 bar, manually actuated		-D4	
	0.1 ... 4 bar, manually actuated		-D5	
	0.1 ... 12 bar, manually actuated		-D7	
	0.1 ... 12 bar, pneumatically actuated (pressure range determined by pilot regulator)	[1] [2]	-PO	
	0.01 ... 1 MPa, electrically actuated (pilot control using proportional-pressure regulator with LED display, 7-segment) 0 ... 10 V	[3]	-PE10	
	0.01 ... 1 MPa, electrically actuated (pilot control using proportional-pressure regulator with LED display, 7-segment) setpoint value 4 ... 20 mA	[3]	-PI10	
Pressure gauge alternatives	Cover plate	[4]	-VS	
	Adapter for EN pressure gauge 1/8, without pressure gauge	[5]	-A8	
	Adapter for EN pressure gauge 1/8, with precision pressure gauge	[5]	-A8M	
	Adapter for EN pressure gauge 1/4, without pressure gauge	[5]	-A4	
	Pressure sensor with switching status indicator, plug M8, threshold value comparator, PNP, N/O contact	[1] [6] [7]	-AD7	
	Pressure sensor with switching status indicator, plug M8, threshold value comparator, PNP, N/C contact	[1] [6] [7]	-AD8	
	Pressure sensor with switching status indicator, M8 plug, window comparator, PNP, N/O contact	[1] [6] [7]	-AD9	
	Pressure sensor with switching status indicator, M8 plug, window comparator, PNP, N/C contact	[1] [6] [7]	-AD10	
	Pressure sensor with LCD display, M12 plug, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA	[1] [5] [6]	-AD11	
	Pressure sensor with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA	[1] [5] [6]	-AD12	

- [1] 1/2, PO, AD7 ... AD10, AD11/AD12, KD, E11, WPM Not with EU EX4 certification.
- [2] PO Not with long rotary knob LD.
Not with locking options AS, E11.
Not with mounting type WR.
- [3] PE10, PI10 Not with LD, WR, AS, E11, EX4, UL1
- [4] VS Must be selected with outlet direction Z without alternative mounting position KD or without alternative pressure output BD, BE.
Must be selected with alternative mounting position KD without outlet direction Z or without alternative pressure output BD, BE.
- [5] A8, A8M, A4, AD11/AD12 In combination with outlet direction Z only with alternative mounting position KD.
- [6] AD7 ... AD10, AD11/AD12 Measuring range max. 10 bar.
Not with pressure regulation range/actuation D2, D4.
- [7] AD7 ... AD10 In combination with outlet direction Z only with alternative pressure output BD, BE or in combination with outlet direction Z only with alternative mounting position KD


Ordering data – Modular product system

Ordering table		Grid dimension	[mm]	62	Conditions	Code	Enter code
Rotary knob	Standard						
	Long rotary knob			[8]		-LD	
Alternative mounting position	None						
	Rotary knob underneath			[1] [9]		-KD	
Locking option	None						
	Lockable using accessories					-AS	
	With integrated lock			[1]		-E11	
Alternative pressure output (p max = 10 bar)	None						
	Angled outlet block QS-8					-BD	
	Angled outlet block QS-10					-BE	
Type of mounting	Without mounting bracket						
	Mounting bracket with knurled nut for regulator head			[8] [11]		-WR	
	Mounting bracket standard design			[12] [13]		-WP	
	Mounting bracket for hooking in service unit components			[1] [8] [12]		-WPM	
	Mounting bracket for large wall gap			[12] [14]		-WPB	
	Mounting bracket centrally at the rear (wall mounting top and bottom), connecting plates not required			[8]		-WB	
EU certification	None						
	II 2GD to EU Explosion Protection Directive (ATEX)					-EX4	
UL certification	None						
	cULus, ordinary location for Canada and USA					-UL1	
Outlet direction	Pressure output at the rear						
	Pressure output at the front (without angled outlet block, no pressure gauge)					-Z	

- [8] LD Not with locking option E11.
- [9] KD In combination with pressure gauge alternatives A8, A4, AD7 ... AD10 only with outlet direction Z.
- [10] WR, WB, WPM Only with outlet direction Z.
Not with alternative mounting position KD.
- [11] WR Only with outlet direction Z.
Not with long rotary knob LD.
- [12] WP, WPM, WPB Only with connecting plate AGB, AGC, AGD or AGE.
- [13] WP Not with alternative mounting position KD.
Either only with outlet direction Z or only with alternative pressure output BD, BE.
- [14] WPB Not with alternative mounting position KD.
Not with alternative pressure output BD, BE.
Not with outlet direction Z.


Peripherals overview

Pressure regulator MS9-LR



 **Note**
Additional accessories:
• Module connectors for combination with size MS6, MS9 or MS12
→ Internet: rmv, armv

Manually actuated Pneumatically actuated Electrically actuated



Peripherals overview

Mounting attachments and accessories		Individual device			Combination	→ Page/ Internet
		With female thread	With connecting plate		Module without connecting thread, without connecting plate	
			Without EU certification	With EU certification		
[1]	Pressure regulator MS9-LR	■	■	■	■	82
[2]	Connecting plate SET MS9-AG...	–	■	■	■	ms9-ag
	Connecting plate SET MS9-AQ...	–	■	–	■	ms9-aq
[3]	Module connector MS9-MV	–	–	–	■	ms9-mv
[4]	Mounting bracket MS9-WP	■	■	■	■	ms9-wp
[5]	Mounting bracket MS9-WPB	■	■	■	■	ms9-wp
[6]	Mounting bracket MS9-WPM	■	■	–	■	ms9-wp
[7]	Adapter for EN pressure gauge 1/4 A4	■	■	■	■	94
[8]	Pressure gauge MA	■	■	■	■	106
[9]	Pressure sensor without display AD7 ... AD10	■	■	–	■	94
[10]	Connecting cable NEBA-M8...-LE3	■	■	–	■	106
[11]	MS pressure gauge AG	■	■	■	■	94
[12]	Cover plate VS	■	■	■	■	94
[13]	Padlock LRVS-D	■	■	■	■	106

Type codes

001	Series
MS	MS series

002	Size
9	Grid dimension 90 mm

003	Function
LR	Pressure regulator

004	Pneumatic connection
3/4	Female thread G3/4
1	Female thread G1
AGD	Sub-base G1/2
AGE	Sub-base G3/4
AGF	Sub-base G1
AGG	Connecting plate G1 1/4
AGH	Connecting plate G1 1/2
N3/4	Female thread 3/4 NPT
N1	Female thread 1 NPT
AQR	Sub-base 1/2 NPT
AQS	Sub-base 3/4 NPT
AQT	Sub-base 1 NPT
AQU	Sub-base 1 1/4 NPT
AQV	Sub-base 1 1/2 NPT
G	Module without connecting thread, without sub-base
NG	Module without connecting thread, without sub-base (inch)

005	Pressure regulation range
D5	0.3 ... 4 bar
D6	0.3 ... 7 bar
D7	0.5 ... 12 bar
D8	0.5 ... 16 bar
PE	0.1 ... 10 bar electrically actuated (pilot control using proportional-pressure regulator with LED indicator, 7-segment), set-point 0 ... 10V
PI	0.1 ... 10 bar electrically actuated (pilot control using proportional-pressure regulator with LED indicator, 7-segment), set-point 4 ... 20mA
PO	Max. 16 bar, pneumatically actuated (pressure range determined by pilot regulator)

006	Regulator type
	Pilot actuated
DI	Directly actuated

007	Pressure gauge alternatives
A4	Adapter for EN pressure gauge 1/4, without pressure gauge
AD7	Pressure sensor with switching display, M8 plug, threshold value comparator, PNP, N/O
AD8	Pressure sensor with switching display, M8 plug, threshold value comparator, PNP, N/C
AD9	Pressure sensor with switching display, M8 plug, window comparator, PNP, N/O
AD10	Pressure sensor with operational status indicator, M8 plug, window comparator, PNP, N/C
AG	MS pressure gauge
RG	Integrated pressure gauge, red/green scale
VS	Cover plate

008	Alternative pressure gauge scale
	MS pressure gauge
PSI	psi
BAR	bar
MPA	MPa

009	Secondary exhausting
	With secondary exhausting
OS	Without secondary exhaust

010	Alternative mounting position
	None
KD	Rotary knob underneath

011	Lockability
	None
AS	Can be locked using accessories
E11	With integrated lock

012	Type of mounting
	Without mounting bracket
WP	Mounting bracket basic design
WPB	Mounting bracket for large wall gap
WPM	Mounting bracket for hooking in service unit components


013	EU certification
	None
EX4	II 2GD

014	UL certification
	None
UL1	cULus ordinary location for Canada and USA


015	Flow direction
	Flow direction from left to right
Z	Flow direction from right to left

Datasheet


Pressure regulation range/actuation,
manually actuated



Pressure regulation range/actuation,
pneumatically actuated



Pressure regulation range/actuation,
electrically actuated



-  - Flow rate
11000 ... 26000 l/min
-  - Temperature range
-10 ... +60 °C
-  - Operating pressure
1 ... 20 bar
-  - www.festo.com



The pressure regulator maintains a constant output pressure p2, independently of pressure fluctuations in the system and air consumption. The output pressure p2 can be set within the pressure regulation range either manually using the rotary knob or pneumatically via pilot pressure p12 by an external pilot regulator. When the operating pressure is switched off, the output pressure p2 is exhausted via port 3 (secondary exhausting).

- Good regulation characteristics with minimal hysteresis and input pressure compensation
- High flow rate with minimal pressure drop
- Piloted or directly actuated diaphragm regulator or piloted precision piston regulator
- Four pressure regulation ranges: 0.5 ... 4 bar, 0.5 ... 7 bar, 0.5 ... 12 bar and 0.5 ... 16 bar
- Available with or without secondary exhausting
- Actuator lock to protect the set values from being adjusted
- Return flow option for exhausting from output 2 to output 1 already integrated
- Optional pressure sensor
- Optional device variant EX4 for use in potentially explosive areas in zones 1, 2, 21 and 22

General technical data

Pneumatic connection 1, 2		
Female thread		G3/4 or G1
Connecting plate	[AG...]	G1/2, G3/4, G1, G1 1/4 or G1 1/2
	[AQ...]	1/2 NPT, 3/4 NPT, 1 NPT, 1 1/4 NPT or 1 1/2 NPT
Module without connecting thread/connecting plate		[G]/[NG]
Pilot air port 12		G1/4 (MS9-LR...-PO)
Design		Piloted diaphragm regulator
		Directly actuated diaphragm regulator
		Piloted precision piston regulator
Regulator function	Piloted	Output pressure constant, with return flow, with input pressure compensation, with secondary exhausting
	Directly actuated	Output pressure constant, with return flow, with/without secondary exhausting
Type of mounting		With accessories
		In-line installation
		Front panel mounting
Mounting position		Any ¹⁾
Actuator lock		Rotary knob with latch, can be locked using accessories
		Rotary knob with integrated lock
Pressure regulation range/actuation	[D5]	[bar] 0.5 ... 4, manually actuated
	[D6]	[bar] 0.5 ... 7, manually actuated
	[D7]	[bar] 0.5 ... 12, manually actuated (0.5 ... 10 with pressure sensor)
	[D8]	[bar] 0.5 ... 16, manually actuated (0.5 ... 10 with pressure sensor)
	[PO]	[bar] 0.5 ... 16, pneumatically actuated ²⁾
	[PE10]	[MPa] 0.01 ... 1, electrically actuated (piloted using proportional pressure regulator), 0 ... 10 V
Max. pressure hysteresis	[...]	[bar] 0.4
	[PE/PI10]	[bar] 0.05

1) The pressure regulator must be mounted vertically when combined with a pressure sensor as condensate must not collect in the pressure sensor.

2) Output pressure p2 corresponds roughly to the applied pilot pressure p12.

† Note: This product conforms to ISO 1179-1 and ISO 228-1.

Datasheet

General technical data							
Pressure indication		With pressure sensor for indicating the output pressure via the switching status indicator and electrical output					
		Via pressure gauge for displaying the output pressure					
		With pressure gauge with red/green scale for indicating the output pressure					
		Prepared for G1/4					
Standard nominal flow rate qnN ¹⁾²⁾ [l/min]							
Design		Piloted diaphragm regulator		Directly actuated diaphragm regulator DI		Piloted precision piston regulator	
Pneumatic connection		G3/4, NPT3/4	G1, NPT1	G3/4, NPT3/4	G1, NPT1	G3/4, NPT3/4	G1, NPT1
Pressure regulation range	[D5]	19000 ³⁾	26000 ³⁾	14000 ³⁾	20000 ³⁾	–	–
	[D6]	17000	20000	14000	11000	–	–
	[D7]	17000	20000	–	–	–	–
	[D8]	17000	20000	–	–	–	–
	[PO]	21000	25000	–	–	–	–
	[PE10]	–	–	–	–	–	–
	[PI10]	–	–	–	–	–	–

1) All values $\pm 15\%$ 2) Measured at $p_1 = 10$ bar and $p_2 = 6$ bar, $\Delta p = 1$ bar3) Measured at $p_1 = 10$ bar and $p_2 = 4$ bar, $\Delta p = 1$ bar

Operating and environmental conditions			
EU certification / actuation		[]	[EX4] Electrically actuated
Operating pressure	[bar]	1 ... 20	
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
		Inert gases	
Note on the operating/ pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)	Lubricated operation not possible
Ambient temperature	[°C]	–10 ... +60 (0 ... +50) ¹⁾	
Temperature of medium	[°C]	–10 ... +60 (0 ... +50) ¹⁾	
Storage temperature	[°C]	–10 ... +60	
Corrosion resistance class CRC ²⁾		2 - Moderate corrosion stress	
UL certification ³⁾		c UL us - Recognized (OL)	

1) Value in brackets applies to MS9-LR with pressure sensor.

2) More information www.festo.com/x/topic/crc3) More information: www.festo.com/catalogue/ms9-lr → Support/Downloads.

Electrical data			
Pressure regulation range		[PE10]	[PI10]
Operating voltage range DC	[V]	21.6 ... 26.4	
Max. electrical power consumption	[W]	4.2	
Max. current consumption	[A]	0.16	
Nominal operating voltage DC	[V]	24 (Plug connector, M12x1, 5-pin, A-coded)	
Residual ripple		10%	
Analogue input signal range			
	[V]	0 ... 10	–
	[mA]	–	4 ... 20

Datasheet

ATEX	
EU certification	[EX4]
ATEX category for gas	II 2G
Type of ignition protection for gas	Ex h IIC T6 Gb X
ATEX category for dust	II 2D
Type of ignition protection for dust	Ex h IIIC T60°C Db X
Explosion-proof ambient temperature	$-10\text{ °C} \leq T_a \leq +60\text{ °C}$
Explosion protection certification outside the EU	EPL Db (GB) EPL Gb (GB)
CE marking (see declaration of conformity) ¹⁾	To EU Explosion Protection Directive (ATEX)
UKCA marking (see declaration of conformity) ¹⁾	To UK explosion regulations


1) More information: www.festo.com/catalogue/ms9-lr → Support/Downloads.

Weight [g]	
Pressure regulator	1400
Pressure regulator with rotary knob with integrated lock	1700

Datasheet

Materials

Sectional view




Pressure regulator		
[1]	Housing	Die-cast aluminium
[2]	Rotary knob	PA
	Rotary knob with integrated lock	Aluminium
[3]	Diaphragm	NBR
[4]	Valve tappet	Wrought aluminium alloy, NBR, POM
–	Covering	Reinforced PA
–	Connecting plate, module connector, mounting bracket	Die-cast aluminium
–	Seals	NBR
Note on materials		RoHS-compliant
LABS (PWIS) conformity		VDMA24364-B1/B2-L

Standard flow rate qn as a function of output pressure p2 (p1 = 10 bar)


Piloted diaphragm regulator

Pneumatic connection G3/4, NPT3/4




— [D5]: 0.5 ... 4 bar - - - [D7]: 0.5 ... 12 bar
 - . - . - [D6]: 0.5 ... 7 bar [D8]: 0.5 ... 16 bar

Pneumatic connection G1, NPT1




Directly actuated diaphragm regulator

Pneumatic connection G3/4, NPT3/4



— [D5]: 0.5 ... 4 bar
 - . - . - [D6]: 0.5 ... 7 bar

Pneumatic connection G1, NPT1




Datasheet

Standard flow rate q_n as a function of output pressure p_2 ($p_1 = 10$ bar)


External pilot regulator

Pressure regulation range, pneumatically actuated

Pneumatic connection G3/4, NPT3/4




Pneumatic connection G1, NPT1



Electrically actuated VPPE pilot control

Pneumatic connection G1, NPT1



MS9-LR-1-PE/PI (6 bar)

Datasheet

Dimensions – Basic version

[D5]/[D6]/[D7]/[D8] Pressure regulation range, manually actuated

[G]/[NG] Module without connecting thread, without connecting plate

[VS] Cover plate

[AS] Rotary knob with latch, can be locked using accessories

Download CAD data → www.festo.com

[PO] Pressure regulation range, pneumatically actuated

[G]/[NG] Module without connecting thread, without connecting plate

[VS] Cover plate

Type	B1	B2	B3	D3	L1		L2		L3
					Piloted	Directly actuated	Piloted	Directly actuated	
MS9-LR-G/NG-D5/D6/D7/D8	90	45	109	–	129	122	71.4	64	94.5
MS9-LR-G/NG-PO				G1/4	120	–	62	–	–

Dimensions – Electrically actuated VPPE pilot control

[PE10/PI10] Proportional-pressure regulator with LED display (without pressure output)

Download CAD data → www.festo.com

Datasheets → Internet: vppe

Type	B1	B2	B3	L1	L2	L3
MS9-LR-...-PE10/PI10	90	45	109	168	~110	10

† Note: This product conforms to ISO 1179-1 and ISO 228-1.

Datasheet


Dimensions – Pressure gauge alternatives

Download CAD data → www.festo.com

[AG] Integrated MS pressure gauge with standard scale

[A4] Adapter for EN pressure gauge 1/4, without pressure gauge

[RG] Integrated MS pressure gauge with red/green scale



Type	B2	B3	D2
MS9-LR-...-AG/RG	45	109	–
MS9-LR-...-A4		110	G1/4


Note: This product conforms to ISO 1179-1 and ISO 228-1.

Dimensions – Pressure gauge alternatives

Download CAD data → www.festo.com

[AD7 ... 10] Pressure sensor without LCD display (switching status indicator only)

Datasheets → Internet: sde5



Variant AD7:
SDE5-D10-O-...-P-M8 with 3-pin
M8x1 plug, threshold value compar-
ator, 1 switching output PNP,
N/O contact

Variant AD9:
SDE5-D10-O3-...-P-M8 with 1x 3-pin
M8 plug, window comparator,
1 switching output PNP, N/O contact

Variant AD8:
SDE5-D10-C-...-P-M8 with 1x 3-pin
M8 plug, threshold value comparator,
1 switching output PNP, N/C contact

Variant AD10:
SDE5-D10-C3-...-P-M8 with 1x 3-pin
M8 plug, window comparator,
1 switching output PNP, N/C contact

Type	B2	B3	D3
MS9-LR-...-AD7/AD8/AD9/AD10	45	112	M8


Datasheet

Dimensions – Connecting thread/connecting plate

Download CAD data → www.festo.com

[3/4]/[1]/[N3/4]/[N1] Female thread

[AG...]/[AQ...] Connecting plate



[1] Retaining screw M6xmin. 90 to DIN 912 (not included in the scope of delivery) for wall mounting without mounting bracket

[3] Earthing screw M4x8 (only with MS9-...-EX4)

→ Flow direction

Type	B4	B5	B6	B7		B8	D1	D4	D5	L4	L5	T1	≅ 1
					[EX4]						[EX4]		
MS9-LR-3/4	90	104	91.5	-	-	-	G3/4	11	6.5	66	-	6	-
MS9-LR-1							G1						
MS9-LR-AGD	-	-	-	112	122	132	G1/2	-	-	-	35	-	30
MS9-LR-AGE						132	G3/4						36
MS9-LR-AGF						142	G1						41
MS9-LR-AGG						162	G1 1/4						50
MS9-LR-AGH						176	G1 1/2						55
MS9-LR-N3/4	90	104	91.5	-	-	-	3/4 NPT	11	6.5	66	-	6	-
MS9-LR-N1							1 NPT						
MS9-LR-AQR	-	-	-	112	122	132	1/2 NPT	-	-	-	35	-	30
MS9-LR-AQS						132	3/4 NPT						36
MS9-LR-AQT						142	1 NPT						41
MS9-LR-AQU						162	1 1/4 NPT						50
MS9-LR-AQV						176	1 1/2 NPT						55

† Note: This product conforms to ISO 1179-1 and ISO 228-1.



Datasheet

Dimensions – Rotary knob

Download CAD data → www.festo.com

[AS] Rotary knob with latch, can be locked using accessories

[E11] Rotary knob with integrated lock



[2] Installation dimension

Type	B1	D1	D2	L2	L3	L4
MS9-LR...-AS	64.4	51.2	–	94.5	–	–
MS9-LR...-E11	–		M44x1	103.5	13.5	60

Ordering data

Design	Pressure regulation range	Analogue input signal range	Flow direction	Part no.	Type
Manually actuated					
Piloted diaphragm regulator	0.5 ... 4 bar	–	From left to right	564134	MS9-LR-G-D5-AG-BAR-AS
	0.5 ... 7 bar	–	From left to right	564136	MS9-LR-G-D6-AG-BAR-AS
	0.5 ... 12 bar	–	From left to right	564138	MS9-LR-G-D7-AG-BAR-AS
Directly actuated diaphragm regulator	0.5 ... 4 bar	–	From left to right	564135	MS9-LR-G-D5-DI-AG-BAR-AS
		–	From left to right	564140	MS9-LR-NG-D5-DI-AG-PSI-AS
	0.5 ... 7 bar	–	From left to right	564137	MS9-LR-G-D6-DI-AG-BAR-AS
		–	From left to right	564142	MS9-LR-NG-D6-DI-AG-PSI-AS
Electrically actuated					
Piloted precision piston regulator	0.01 ... 1 MPa	0 ... 10 V	From left to right	8203866	MS9-LR-G-PE10-VS
	0.01 ... 1 MPa	4 ... 20 mA	From left to right	8203865	MS9-LR-G-PI10-VS

Ordering data – Modular product system

Ordering table		Conditions	Code	Enter code
Grid dimension	[mm] 90			
Module no.	562530			
Series	Standard		MS	MS
Size	9		9	9
Function	Pressure regulator		-LR	-LR
Pneumatic connection	Female thread G3/4	[1]	-3/4	
	Female thread G1	[1]	-1	
	Connecting plate G1/2		-AGD	
	Connecting plate G3/4		-AGE	
	Connecting plate G1		-AGF	
	Connecting plate G1 1/4		-AGG	
	Connecting plate G1 1/2		-AGH	
	Female thread 3/4 NPT	[1]	-N3/4	
	Female thread 1 NPT	[1]	-N1	
	Connecting plate 1/2 NPT	[1]	-AQR	
	Connecting plate 3/4 NPT	[1]	-AQS	
	Connecting plate 1 NPT	[1]	-AQT	
	Connecting plate 1 1/4 NPT	[1]	-AQU	
	Connecting plate 1 1/2 NPT	[1]	-AQV	
	Module without connecting thread, without connecting plate	[1]	-G	
	Module without connecting thread, without connecting plate (inch)	[1]	-NG	
Pressure regulation range/actuation	0.5 ... 4 bar, manually actuated		-D5	
	0.5 ... 7 bar, manually actuated		-D6	
	0.5 ... 12 bar, manually actuated		-D7	
	0.5 ... 16 bar, manually actuated	[1]	-D8	
	Max. 16 bar, pneumatically actuated (pressure range determined by pilot regulator)	[2]	-PO	
	0.01 ... 1 MPa, electrically actuated (pilot control using proportional-pressure regulator with LED display, 7-segment) 0 ... 10 V	[3]	-PE10	
	0.01 ... 1 MPa, electrically actuated (pilot control using proportional-pressure regulator with LED display, 7-segment) setpoint value 4 ... 20 mA	[3]	-PI10	
Regulator type	Piloted			
	Directly actuated	[4]	-DI	
Pressure gauge/pressure gauge alternatives	MS pressure gauge		-AG	
	Cover plate		-VS	
	Adapter for EN pressure gauge 1/4, without pressure gauge		-A4	
	Integrated pressure gauge, red/green scale	[5]	-RG	
	Pressure sensor with switching status indicator, plug M8, threshold value comparator, PNP, N/O contact	[1] [6]	-AD7	
	Pressure sensor with switching status indicator, plug M8, threshold value comparator, PNP, N/C contact	[1] [6]	-AD8	
	Pressure sensor with switching status indicator, M8 plug, window comparator, PNP, N/O contact	[1] [6]	-AD9	
	Pressure sensor with switching status indicator, M8 plug, window comparator, PNP, N/C contact	[1] [6]	-AD10	

[1] 3/4, 1, N3/4, N1, Not with EU EX4 certification

AQR, AQS, AQT,
AQU, AQV, G, NG,
D8, AD7, AD8,
AD9, AD10, E11,
WPM

[2] PO Not with regulator type DI.
Not with locking options AS, E11.

[3] PE10, PI10 Not with DI, OS, E11, AS, EX4, UL1

[4] DI Not with pressure regulation range D7, D8.

[5] RG Not with alternative pressure gauge scale PSI, PSI scale is only used as an auxiliary scale.

[6] AD7 ... AD10 Measuring range max. 10 bar.

Ordering data – Modular product system

Ordering table					
Grid dimension	[mm]	90	Conditions	Code	Enter code
Alternative pressure gauge scale	psi		[7]	-PSI	
	MPa		[7]	-MPA	
	bar		[7]	-BAR	
Secondary exhausting	With secondary exhausting				
	Without secondary exhausting		[8]	-OS	
Alternative mounting position	None				
	Rotary knob underneath (connection underneath with PO)			-KD	
Locking option	Without (locking option AS is predefined)				
	Lockable using accessories			-AS	
	With integrated lock		[1]	-E11	
Type of mounting	Without mounting bracket				
	Mounting bracket standard design		[9]	-WP	
	Mounting bracket for hooking in service unit components		[1] [9]	-WPM	
	Mounting bracket for large wall gap		[9]	-WPB	
EU certification	None				
	II 2GD to EU Explosion Protection Directive (ATEX)			-EX4	
UL certification	None				
	cULus, ordinary location for Canada and USA			-UL1	
Flow direction	Flow direction from left to right				
	Flow direction from right to left			-Z	

[7] **PSI, MPA, BAR**


Not with pressure gauge alternatives VS, A4, AD7, AD8, AD9, AD10

[8] **OS** Only with regulator type DI[9] **WP, WPM, WPB**

Not with pneumatic connection G, NG


Peripherals overview

Pressure regulator MS12-LR



 **Note**
Additional accessories:
• Module connectors for combination with size MS9 → Internet: armv

Manually actuated Pneumatically actuated Electrically actuated



Peripherals overview

Mounting attachments and accessories		→ Page/Internet
[1]	Pressure regulator MS12-LR	96
[2]	Connecting plate SET MS12-AG...	ms12-ag
[3]	Mounting bracket MS12-WP	ms12-wp
[4]	Module connector MS12-MV	ms12-mv
[5]	Cover plate VS	105
[6]	Adapter for EN pressure gauge 1/4 A4	105
[7]	Pressure gauge MA	106
[8]	Padlock LRVS-D	106
[9]	Connecting cable NEBA-M12G...-LE4	106
[10]	Connecting cable NEBA-M12W...-LE4	106
[11]	Sensor socket NECB-M12G4-C2	106
[12]	Angled plug socket NECB-M12W4-C2	106


Type codes

001	Series	
MS	MS series	
002	Size	
12	Grid dimension 124 mm	
003	Function	
LR	Pressure regulator	
004	Pneumatic connection	
AGF	Sub-base G1	
AGG	Connecting plate G1 1/4	
AGH	Connecting plate G1 1/2	
AGI	Sub-base G2	
G	Module without connecting thread, without sub-base	
005	Pressure range/actuation	
D6	0.3 ... 7 bar, manually actuated	
D7	0.5 ... 12 bar, manually actuated	
D8	0.5 ... 16 bar, manually actuated	
PE6	0.15 ... 6 bar, solenoid actuated (pilot control by proportional-pressure regulator)	
PO	Max. 16 bar, pneumatically actuated (pressure range determined by pilot regulator)	


006	Pressure gauge alternatives	
	None	
A4	Adapter for EN pressure gauge 1/4, without pressure gauge	
VS	Cover plate	
007	Alternative pressure gauge scale	
	MS pressure gauge	
PSI	psi	
MPA	MPa	
008	Rotary knob alternative	
	None	
LD	Long rotary knob	
009	Type of mounting	
	Without mounting bracket	
WP	Mounting bracket basic design	
010	Flow direction	
	Flow direction from left to right	
Z	Flow direction from right to left	

Datasheet


Pressure regulation range/actuation,
manually actuated



Pressure regulation range/actuation,
pneumatically actuated



Pressure regulation range/actuation,
electrically actuated



-  Flow rate
12000 ... 22000 l/min
-  Temperature range
-10 ... +60 °C
-  Operating pressure
0.08 ... 2.1 MPa
-  www.festo.com

The pressure regulator maintains a constant output pressure p₂, independently of pressure fluctuations in the system and air consumption. The output pressure p₂ can be set within the pressure regulation range either manually using the rotary knob, pneumatically via pilot pressure p₁₂ by an external pilot regulator, or electrically via setpoint signals.



When the operating pressure or the voltage for the setpoint signals is switched off, the output pressure p₂ is exhausted via port 3 (secondary exhausting).

- Good regulation characteristics with minimal hysteresis and input pressure compensation
- High flow rate with minimal pressure drop
- Actuator lock to protect the set values from being adjusted
- With secondary exhausting
- Pressure gauge connection for different fitting options

General technical data

Pressure regulation range/actuation		[D6]	[D7]	[D8]	[PO]	[PE6]
Pneumatic connection 1, 2						
Connecting plate	[AG...]	G1, G1 1/4, G1 1/2 or G2				
Module without connecting thread/ connecting plate	[G]	-				
Pilot air port 12		G1/4 (MS12-LR-...-PO)				
Design		Pressure regulator with/without pressure gauge				
		Piloted diaphragm regulator (MS12-LR-...-D6/D7/D8/PE6)				
		Diaphragm regulator (MS12-LR-...-PO)				
Regulator function		Output pressure constant, with primary pressure compensation, with return flow, with secondary exhausting				
Type of mounting		With accessories				
		In-line installation				
Mounting position		Any				
Actuator lock		Rotary knob with latch, can be locked using accessories				
		Rotary knob with integrated lock				
Pressure regulation range	[MPa]	0.03 ... 0.7	0.05 ... 1.2	0.05 ... 1.6	0.05 ... 1.6	0.015 ... 0.6
	[bar]	0.3 ... 7	0.5 ... 12	0.5 ... 16	0.5 ... 16	0.15 ... 6
	[psi]	4.35 ... 102	7.25 ... 174	7.25 ... 232	7.25 ... 232	2.175 ... 87
Actuation		Manually actuated ¹⁾	Manually actuated ¹⁾	Manually actuated ¹⁾	Pneumatically actuated ¹⁾	Electrically actuated
Max. pressure hysteresis	[MPa]	0.04				0.004
	[bar]	0.4				0.04
	[psi]	5.8				0.58
Pressure indication		With pressure gauge				

1) Prerequisite: P₁ = P₂ + 1 bar.

• Note: This product conforms to ISO 1179-1 and ISO 228-1.

Datasheet

Flow rates		
Pressure regulation range/actuation		[D6]/[D7]/[D8]/[PO] ¹⁾ [PE6] ²⁾
Standard nominal flow rate q _N ³⁾ [l/min]		
q _N 1 → 2	G1	13000
	G1 1/4	13500
	G1 1/2	16000
	G2	22000
Secondary exhaust flow rate [l/min]		
q _N 2 → 3		≤ 600

1) Measured at p₁ = 10 bar and p₂ = 6 bar, Δp = 0.5 bar2) Measured at p₁ = 7 bar and p₂ = 6 bar, Δp = 0.5 bar

3) Dependent on the selected connecting plate; must be ordered separately as an accessory → Internet: ms12-ag

Electrical data		
Pressure regulation range/actuation		[PE6]
Operating voltage range	[V DC]	21.6 ... 26.4
Nominal operating voltage	[V DC]	24
Residual ripple	[%]	10
Analogue input signal range	[V]	0 ... 10
Max. current consumption	[A]	0.15
Max. electrical power consumption	[W]	3.6
Degree of protection		IP65

Operating and environmental conditions		
Pressure regulation range/actuation		[D6]/[D7]/[D8]/[PO] [PE6]
Operating pressure	[MPa]	0.08 ... 2.1
	[bar]	0.8 ... 21
	[psi]	11.6 ... 304.5
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]	
	Inert gases	
Ambient temperature	[°C]	-10 ... +60
Temperature of medium	[°C]	-10 ... +60
Storage temperature	[°C]	-10 ... +60
Corrosion resistance class CRC ¹⁾	2	
CE marking (see declaration of conformity) ²⁾	–	
UKCA marking (see declaration of conformity) ²⁾	To EU EMC Directive	
	To EU RoHS Directive	
KC marking	To UK EMC regulations	
	To UK RoHS regulations	
KC marking		KC EMC

1) More information www.festo.com/x/topic/crc2) More information: www.festo.com/catalogue/ms12-lr → Support/Downloads.


If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

Weight [g]	
Pressure regulator	4000
Pressure regulator with rotary knob with integrated lock	4300

Datasheet

Materials


Sectional view




Pressure regulator		
[1]	Housing	Die-cast aluminium
[2]	Rotary knob	Reinforced PA, POM
	Rotary knob with integrated lock	Wrought aluminium alloy
[3]	Bottom cover	Wrought aluminium alloy
[4]	Spring	Spring steel
[5]	Valve tappet	Wrought aluminium alloy, NBR, high-alloy stainless steel
–	Seals, diaphragm	NBR
Note on materials		RoHS-compliant
LABS (PWIS) conformity		VDMA24364-B1/B2-L

Standard flow rate q_n as a function of output pressure p_2 ($p_1 = 10$ bar) (MS12-LR-...-D6/D7/D8/PO only)


Pneumatic connection G1 with connecting plate
MS12-AGF




Pneumatic connection G1 1/4 with connecting plate
MS12-AGG



Pneumatic connection G1 1/2 with connecting plate
MS12-AGH




Pneumatic connection G2 with connecting plate
MS12-AGI



Datasheet


Standard flow rate qn as a function of output pressure p2 (p1 = 7 bar) (MS12-LR-...-PE6 only)
Pneumatic connection G1 1/2 with connecting plate MS12-AGH



Dimensions – Basic version

Download CAD data → www.festo.com

- [D6]/[D7]/[D8] Pressure regulation range, manually actuated
- [G] Module without connecting thread, without connecting plate
- [I] Integrated MS pressure gauge with standard scale
- [LD-AS] Rotary knob, long, with latch, can be locked using accessories



Type	B1	B2	B3	B4	D2 Ø	L1	L2	L3	L4
MS12-LR-...-D6/D7/D8	124	122	61	148	51.2	178	88	95	168

Datasheet

Dimensions – Pressure regulation range

Download CAD data → www.festo.com

[PO] Pressure regulation range, pneumatically actuated


[G] Module without connecting thread, without connecting plate

[] Integrated MS pressure gauge with standard scale

[PE6] Pressure regulation range, electrically actuated

[G] Module without connecting thread, without connecting plate

[] Integrated MS pressure gauge with standard scale



- [1] Suitable for
- Connecting cable
NEBA-M12G...-LE4/
NEBA-M12W...-LE4
 - Sensor socket NECB-M12G4-C2
 - Angled plug socket NECB-M12W4-C2

→ Flow direction


Type	B1	B2	B3	B4	B5	D3	L1	L2	L3	L4
MS12-LR...-PO	124	122	61	148	–	G1/4	181	91	–	171
MS12-LR...-PE6					50	M12	172	82	62.7	162

Dimensions – Pressure gauge alternatives

Download CAD data → www.festo.com

[VS] Cover plate

[A4] Adapter for EN pressure gauge 1/4, without pressure gauge




Type	B3	B4	D4
MS12-LR...-VS	61	148	–
MS12-LR...-A4	61	148	G1/4

Note: This product conforms to ISO 1179-1 and ISO 228-1.


Datasheet

Dimensions – Rotary knob

[LD-AS] Rotary knob, long, with latch, can be locked using accessories



[E11] Rotary knob with integrated lock





[2] Installation dimension

Download CAD data → www.festo.com

Type	B4	D2 Ø	L3	L8	L10
MS12-LR-...-LD-AS	64.4	51.2	95	12	–
MS12-LR-...-E11	–	51.8	112	–	60

Ordering data				
Design	Pressure regulation range	Flow direction	Part no.	Type
MS12-LR...				
Piloted diaphragm regulator	0.15 ... 6 bar	From left to right	564888	MS12-LR-G-PE6
	0.5 ... 12 bar	From left to right	537148	MS12-LR-G-D7-LD-AS
Diaphragm regulator	0.5 ... 16 bar	From left to right	541680	MS12-LR-G-PO


Ordering data – Modular product system


Ordering table		Grid dimension	[mm]	124	Conditions	Code	Enter code
Module no.		535021					
Series	Standard					MS	MS
Size	12					12	12
Function	Pressure regulator					-LR	-LR
Pneumatic connection	Connecting plate G1					-AGF	
	Connecting plate G1 1/4					-AGG	
	Connecting plate G1 1/2					-AGH	
	Connecting plate G2					-AGI	
	Module without connecting thread, without connecting plate					-G	
Pressure regulation range/actuation	0.3 ... 7 bar, manually actuated					-D6	
	0.5 ... 12 bar, manually actuated					-D7	
	0.5 ... 16 bar, manually actuated					-D8	
	Max. 16 bar, pneumatically actuated (pressure range determined by pilot regulator)			[1] [2]		-PO	
	0.15... 6 bar, electrically actuated (pilot control using proportional pressure regulator)			[1] [2]		-PE6	
Pressure gauge alternatives	MS pressure gauge						
	Cover plate					-VS	
	Adapter for EN pressure gauge 1/4, without pressure gauge					-A4	
Alternative pressure gauge scale	MS pressure gauge, bar						
	psi			[3]		-PSI	
	MPa			[3]		-MPA	
Rotary knob alternative	None						
	Long rotary knob			[2]		-LD	
Locking option	None			[4]			
	Lockable using accessories			[5]		-AS	
	With integrated lock					-E11	
Type of mounting	Without mounting bracket						
	Mounting bracket standard design			[6]		-WP	
Flow direction	Flow direction from left to right						
	Flow direction from right to left					-Z	

- [1] PO, PE6 Not with rotary knob alternative LD.
Not with locking option AS.
- [2] PO, PE6, LD Not with locking option E11.
- [3] PSI, MPA Not with pressure gauge alternatives VS, A4.
Must be selected if pressure regulation range/actuation PO, PE6 is selected.
Not with pressure regulation range/actuation D6, D7, D8.
- [4] Not with rotary knob alternative LD.
- [5] AS Only with rotary knob alternative LD.
- [6] WP Only with connecting plate AGF, AGG, AGH or AGI.

Accessories


Ordering data – Pressure gauge MA						
	Nominal size	Pneumatic connection	Display range		Part no.	Type
			[bar]	[psi]		
	Pressure gauge MA, EN 837-1				Datasheets → Internet: ma	
	40	R1/4	0 ... 16	0 ... 232	187080	MA-40-16-R1/4-EN
		G1/4	0 ... 16	0 ... 232	183901	MA-40-16-G1/4-EN
	Pressure gauge MA, EN 837-1, with red/green range				Datasheets → Internet: ma	
	40	R1/8	0 ... 16	–	525726	MA-40-16-R1/8-E-RG
	50	R1/4	0 ... 16	–	525729	MA-50-16-R1/4-E-RG
	Precision pressure gauge MAP, EN 837-1				Datasheets → Internet: map	
	40	R1/8	0 ... 1	0 ... 15	161126	MAP-40-1-1/8-EN
			0 ... 4	0 ... 58	162842	MAP-40-4-1/8-EN
			0 ... 6	0 ... 87	161127	MAP-40-6-1/8-EN
			0 ... 16	0 ... 232	161128	MAP-40-16-1/8-EN

Ordering data – Connecting cables NEBA, straight						
	Electrical connection 1, connector system	Electrical connection 2, connector system	Electrical connection 2, number of connections/cores	Cable length [m]	Part no.	Type
	M12x1, A-coded to EN 61076-2-101	Open end	4	2.5	8078239	NEBA-M12G5-U-2.5-N-LE4
				5	8078240	NEBA-M12G5-U-5-N-LE4
	M8x1, A-coded, to EN 61076-2-104		3	2.5	8078223	NEBA-M8G3-U-2.5-N-LE3
				5	8078224	NEBA-M8G3-U-5-N-LE3
			4	2.5	8078227	NEBA-M8G4-U-2.5-N-LE4

Ordering data – Connecting cables NEBA, angled						
	Electrical connection 1, connector system	Electrical connection 2, connector system	Electrical connection 2, number of connections/cores	Cable length [m]	Part no.	Type
	M12x1, A-coded to EN 61076-2-101	Open end	4	2.5	8078248	NEBA-M12W5-U-2.5-N-LE4
				5	8078249	NEBA-M12W5-U-5-N-LE4
	M8x1, A-coded, to EN 61076-2-104		3	2.5	8078230	NEBA-M8W3-U-2.5-N-LE3
				5	8078231	NEBA-M8W3-U-5-N-LE3
			4	2.5	8078233	NEBA-M8W4-U-2.5-N-LE4

Ordering data – Sensor socket NECB						
	Electrical connection				Part no.	Type
	M12x1, A-coded to EN 61076-2-101				8162290	NECB-M12G4-C2

Ordering data – Angled plug socket NECB						
	Electrical connection				Part no.	Type
	M12x1, A-coded to EN 61076-2-101				8162292	NECB-M12W4-C2

Ordering data – Padlock LRVS-D						
	Weight [g]				Part no.	Type
	120				193786	LRVS-D