


On/off valve MS4N-EE

FESTO



Characteristics


At a glance



Solenoid actuated on/off valve for pressurising and exhausting pneumatic systems

- Electric 3/2-way valve for pressurising and exhausting pneumatic systems
- A silencer can be attached or the exhaust air can be ducted at port 3
- Supply voltage 24 V DC, 110, 230 V AC
- Optionally with pressure gauge and pressure sensor
- With solenoid coil, without plug socket

Ordering data - modular system Link [ms4n-ee](#)



Configurable product
This product and all its product options can be ordered online via the configurator.

Pneumatic connection


By installing connecting plates it is easier to replace the module if necessary (e.g. when using piping).

Pressure gauge alternatives

- Key features [AG]/[RG]: integrated pressure gauges
- Key features [A4]/[A8]: Adapter for pressure gauge
- Key features [O.D.7]/[O.D.8]/[O.D.9]/[O.D.10]: simple pressure sensors for monitoring the system
- Key features [AD11]/[AD12]: functional pressure sensors for monitoring the system

Type of mounting

[WP] Mounting bracket basic design




- For connecting the modules for wall mounting
- In combination with connecting plate for wall mounting an individual unit
- In conjunction with mounting plate MS-AEND or wall mounting a single device
- Same wall distance for combinations of series MS4 and MS6

[WB] Mounting centrally at rear (wall mounting top and bottom), connecting plates not required



- For wall mounting

[WPM] Mounting bracket for hooking in service unit components



- For connecting the modules for wall mounting
- In combination with connecting plate MS4-AG... for mounting an individual device on a wall
- Fast hooking and unhooking

[WBM] Mounting centrally at rear (wall mounting top), connecting plates not required



- For wall mounting

Type code

001	Series	
MS	MS series	
002	Size	
4	Grid dimension 40 mm	
003	Thread type	
N	NPT thread	
004	Function	
EE	On/off valve, electric	
005	Pneumatic connection, inch	
1/8	Female thread NPT 1/8	
1/4	Female thread NPT 1/4	
AQK	Sub-base NPT1/8	
AQN	Sub-base NPT1/4	
AQP	Sub-base NPT3/8	
006	Supply voltage	
10V24	24 V DC, 10 bar, connection pattern to EN 175301	
10V24C	24 V DC, 10 bar (connection pattern to EN 175301) without manual override	
10V24D	24V DC, 10 bar, M12 (connection pattern according to IEC 61076-2-101) without manual override	
10V24F	24 V DC, 10 bar, M12 (connection pattern to IEC 61076-2-101). Non-detenting manual override on the pilot actuator	
10V24P	24 V DC, 10 bar, M12 (connection pattern to IEC 61076-2-101)	
V24	24 V DC (connection pattern to EN 175301)	
V24P	24 V DC plug, M12 socket adapter (connection pattern to IEC 61076-2-101)	
V110	110 V AC (connection pattern to EN 175301)	
V230	230 V AC (connection pattern to EN 175301)	
007	Silencer	
	None	
S	Silencer	

008	Pressure gauge alternatives	
	None	
A4	Adapter for EN pressure gauge 1/4, without pressure gauge	
A8	Adapter for EN pressure gauge 1/8, without pressure gauge	
AD7	Pressure sensor with switching display, M8 plug, threshold value comparator, PNP, N/O	
AD8	Pressure sensor with switching display, M8 plug, threshold value comparator, PNP, N/C	
AD9	Pressure sensor with switching display, M8 plug, window comparator, PNP, N/O	
AD10	Pressure sensor with operational status indicator, M8 plug, window comparator, PNP, N/C	
AD11	Pressure sensor with LCD display, M12 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V, 4...20 mA	
AD12	Pressure sensor with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V, 4...20 mA	
AG	MS pressure gauge	
RG	Integrated pressure gauge, red/green scale	

009	Alternative pressure gauge scale	
	MS pressure gauge	
BAR	bar	
MPA	MPa	

010	Type of mounting	
	Without mounting bracket	
WB	Mounting centrally at rear (wall mounting top and bottom), connecting plates not required	
WBM	Mounting centrally at rear (wall mounting top), connecting plates not required	
WP	Mounting bracket basic design	
WPM	Mounting bracket for hooking in service unit components	

011	Flow direction	
	Flow direction from left to right	
Z	Flow direction from right to left	

Datasheet

General technical data

Pneumatic connection, port 1 ¹⁾	1/8 NPT	1/4 NPT
Pneumatic connection, port 2	1/8 NPT	1/4 NPT
Pneumatic connection, port 3	G1/4	
Design	Piston gate valve	
lap	Overlap	
Type of mounting	Either: In-line installation With accessories	
Mounting position ²⁾	optional	
Valve function	3/2-way, closed, monostable	
Exhaust-air function	Without flow control option	
Manual override	Detenting, Non-detenting	
Type of actuation	Electric	
Type of reset	Mechanical spring	
Type of piloting	Pilot actuated	
Pilot air supply	Internal	
Flow direction	Non-reversible	

1) Via connecting plate [AQ...]: 1/8 NPT, 1/4 NPT or 3/8 NPT

2) Vertical mounting position for the on/off valve with pressure sensor, as no condensation must be allowed to accumulate in the pressure sensor.

Electrical data

Supply voltage	24 V DC, 10 bar, connection pattern to EN 175301	110 V AC (connection pattern to EN 175301)	230 V AC (connection pattern to EN 175301)
Characteristic coil data	24 V DC: 1.8 W	110 V AC: 50/60 Hz, pick-up power 3.0 VA, holding power 2.4 VA	230 V AC: 50/60 Hz, pick-up power 3.0 VA, holding power 2.4 VA
Electrical connection	Type C, Plugs, To DIN EN 175301-803, Square design		
Degree of protection	IP65		
Duty cycle	100%		

Flow characteristics

Pneumatic connection, port 1	1/8 NPT	1/4 NPT
Standard nominal flow rate (standardised to DIN 1343) ¹⁾	1,000 l/min	2,000 l/min
C value	4.5 l/sbar	9.5 l/sbar
b value	0.5	0.44

1) Measured at p1 = 6 bar and p2 = 5 bar, Δp = 1 bar.

Operating and environmental conditions

Supply voltage	24 V DC, 10 bar, connection pattern to EN 175301	110 V AC (connection pattern to EN 175301)	230 V AC (connection pattern to EN 175301)
Operating pressure	4 ... 10 bar	4 ... 14 bar	
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4], Inert gas		
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)		
Ambient temperature	-10 ... 50°C	-10 ... 60°C	
Media temperature	-10 ... 50°C	-10 ... 60°C	
Corrosion resistance class CRC ¹⁾	2 - Moderate corrosion stress		
Suitable for use with food ²⁾	See supplementary material information		

1) More information www.festo.com/x/topic/crc

2) More information www.festo.com/certificates/ms4-ee

Materials


Material housing	Die-cast aluminium
Material seals	NBR
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364-B1/B2-L

Dimensions

Dimensions – Basic type with female thread, with cover plate

Download CAD data www.festo.com

10V24D / 10V24F / 10V24P



- [1] Plug connection according to EN 175301-803
 [2] Solenoid actuator can be repositioned 180°, i.e. magnet faces forwards
 [3] PIN only for solenoid actuators 110 V and 230 V
 [4] Electrical connection M12x1 according to ISO 20401 suitable for EN 61076-2-101, 4-pin version for connecting cable NEBU M12
 [5] 1 -> 2: Flow direction


	B1	B2		B3		B4	B5	B6	B7	D1	D5	D7
		[V24] [V110] [V230]	[10V24] [10V24C] [10V24D] [10V24F] [10V24P]	[V24] [V110] [V230]	[10V24] [10V24C] [10V24D] [10V24F] [10V24P]							
	[inch]	[inch]		[inch]		[inch]	[inch]	[inch]	[inch]			
MS4N-EE-1/8	1,57	1,65	1,38	2,95	2,68	0,83	2,13	1,22	0,43	1/8 NPT	1/4 NPT	M12x1
MS4N-EE-1/4										1/4 NPT		

	L1				L2	L3	L7	L8	L9
	[V24] [V110] [V230]	[V24-EX2]	[10V24] [10V24C]	[10V24D] [10V24F] [10V24P]					
	[inch]				[inch]	[inch]	[inch]	[inch]	[inch]
MS4N-EE-1/8	5,62	6,30 ¹⁾	5,51	5,71	2,32	3,94	0,34	1,46	1,02
MS4N-EE-1/4									

1) Measured with plug socket MSSD-EB (included in the scope of delivery).

Dimensions

Dimensions – Basic type with female thread, with cover plate, V24P Download CAD data www.festo.com




	B6 [inch]	B7 [inch]	D7	L1 [inch]	L7 [inch]
MS4N-EE-1/8	1,22	0,43	M12x1	6,30 ¹⁾	0,87 ¹⁾
MS4N-EE-1/4					

1) Measured with plug socket MSSD-EB (included in the scope of delivery).

Dimensions

Dimensions – Integrated MS pressure gauge with standard scale / Integrated MS pressure gauge with red/green scale

Download CAD data www.festo.com




[1] 1 -> 2: Flow direction

	B2		B3		D1
	[V24] [V24P] [V110] [V230]	[10V24] [10V24C] [10V24D] [10V24F] [10V24P]	[V24] [V24P] [V110] [V230]	[10V24] [10V24C] [10V24D] [10V24F] [10V24P]	
	[inch]		[inch]		[inch]
MS4N-EE-1/8-...-AG	1,65	1,38	3,39	3,11	1/8 NPT
MS4N-EE-1/4-...-AG					1/4 NPT
MS4N-EE-1/8-...-RG	1,65	1,38	3,44	3,17	1/8 NPT
MS4N-EE-1/4-...-RG					1/4 NPT

Dimensions

Dimensions – Adapter for EN pressure gauge 1/8, without pressure gauge /
Adapter for EN pressure gauge 1/4, without pressure gauge

Download CAD data www.festo.com




	B2		B3		D1	D4
	[V24] [V24P] [V110] [V230]	[10V24] [10V24C] [10V24D] [10V24F] [10V24P]	[V24] [V24P] [V110] [V230]	[10V24] [10V24C] [10V24D] [10V24F] [10V24P]		
	[inch]		[inch]			
MS4N-EE-1/8-...-A8	1,65	1,38	3,13	2,85	1/8 NPT	1/8 NPT
MS4N-EE-1/4-...-A8					1/4 NPT	
MS4N-EE-1/8-...-A4	1,65	1,38	3,13	2,85	1/8 NPT	1/4 NPT
MS4N-EE-1/4-...-A4					1/4 NPT	

Dimensions

Dimensions – Pressure sensor with status indicator AD7, AD8, AD9, AD10


Download CAD data www.festo.com



	B2 [inch]	B3 [inch]	B5 [inch]	B6 [inch]	D6
MS4N-...-AD7, AD8, AD9, AD10	0,83	2,33	~1,26	0,63	M8x1

Dimensions


Dimensions – Pressure sensor with LCD display AD11, AD12 Download CAD data www.festo.com



	B2 [inch]	B3 [inch]	B4 [inch]	B5 [inch]	B6 [inch]	D6	L5 [inch]	L6 [inch]
MS4N-...-AD11	0,83	3,20	2,89	1,26	1,26	M12x1	1,62	1,53
MS4N-...-AD12						M8x1	1,49	

Dimensions

Dimensions – Silencer

[Download CAD data](#) www.festo.com


	D2 [inch]	L4 [inch]
MS4N-EE-....-S	0,79	2,17

Ordering data


Ordering data – Without silencer

	Pneumatic connection, port 1	Nominal operating voltage	Flow direction	Product weight	Part no.	Type
	1/8 NPT	24 V DC	From right to left	273 g	542591	MS4N-EE-1/8-10V24-Z
			From left to right		542589	MS4N-EE-1/8-10V24
		110 V AC/50-60 Hz			532084	MS4N-EE-1/8-V110
		230 V AC/50-60 Hz			532088	MS4N-EE-1/8-V230
	1/4 NPT	24 V DC	From right to left		542588	MS4N-EE-1/4-10V24
			From left to right		542590	MS4N-EE-1/4-10V24-Z
		110 V AC/50-60 Hz			532083	MS4N-EE-1/4-V110
		230 V AC/50-60 Hz			532087	MS4N-EE-1/4-V230

Ordering data – With silencer


	Pneumatic connection, port 1	Nominal operating voltage	Flow direction	Product weight	Part no.	Type
	1/8 NPT	24 V DC	From left to right	289 g	542610	MS4N-EE-1/8-10V24-S
			From right to left		542611	MS4N-EE-1/8-10V24-S-Z
		110 V AC/50-60 Hz	From left to right		538755	MS4N-EE-1/8-V110-S
		230 V AC/50-60 Hz			538757	MS4N-EE-1/8-V230-S
	1/4 NPT	24 V DC	From right to left		542609	MS4N-EE-1/4-10V24-S-Z
			From left to right		542608	MS4N-EE-1/4-10V24-S
		110 V AC/50-60 Hz			538749	MS4N-EE-1/4-V110-S
		230 V AC/50-60 Hz			538751	MS4N-EE-1/4-V230-S

Ordering data – Modular product system

	Short type code	Part no.	Type
	MS4N-EE	527710	MS4N-EE

Peripherals

Peripherals overview




Peripherals

Accessories		→ Link
Type/order code	Description	
[1] On/off valve MS4N-EE	On/off valve	ms4n-ee
[2] Module connector MS4-MV1	For connecting the modules	15
[3] Mounting bracket MS4-WP	Order code [WP]	15
[3] Mounting bracket MS4-WPM	Order code [WPM] (without illustration)	15
[4] Mounting bracket MS4-WB	Order code [WB]	15
[5] Mounting bracket MS4-WBM	Order code [WBM]	16
[6] Cover cap MS4-END	Can be used to cover the sides of the housing for the first and last modules if no connecting plates are used.	16
[7] Mounting plate MS4-AEND	Module connector MS4-MV1 [2] or mounting bracket MS4-WP, WPB, WPE, WPM [3] is required for mounting.	16
[8] Connecting plate SET MS4-AQ..	Order code [AQ..]	16
[9] Pressure sensor with LCD display SPAU	• Display module • Order code [AD11], [AD12]	ms4n-ee
[10] Connecting cable NEBA-M...G...-LE4, angled	Connecting cable for display module	17
[10] Connecting cable NEBA-M...G...-LE4, straight	Connecting cable for display module	17
[11] Pressure sensor with switching indicator SDE5	• Display module • Order code [AD7], [AD8], [AD9], [AD10]	ms4n-ee
[12] Connecting cable NEBA-M...G...-LE3, straight	Connecting cable for display module	17
[13] Adapter for EN pressure gauge 1/8, 1/4	Order code [A8], [A4]	ms4n-ee
[14] Pressure gauge MA	Built-in pressure indicator	16
[15] Pressure sensor SPAU-...-T	Display module	17
[16] Pressure gauge MS	Order code [AG], [RG]	ms4n-ee
[17] Silencer U	-	18
[17] Silencer S	Order code [S]	ms4n-ee
[18] On/off valve MS4-EE	Supply voltage [V24], [V24P], [10V24], [10V24C], [V110], [V230]	ms4n-ee
[19] On/off valve MS4-EE	Supply voltage [1024VD], [1024VF], [1024VP]	ms4n-ee
[20] Illuminating seal MEB-LD	Switching status indication	17
[21] Plug socket with cable KMEB	Connecting cable for valve coil	18
[22] Plug socket MSSD-EB	Connection socket for valve coil	18
[23] Locking clip CPV18-HV	Prevents the manual override from being activated	18
[24] Connecting cable NEBA-M12G5-LE4, straight	Connecting cable for valve coil	17
[25] Connecting cable NEBA-M12W5-LE4, angled	Connecting cable for valve coil	17

Accessories

Module connector MS4-MV1						
	Size	Material module connector	LABS (PWIS) conformity	Product weight	Part no.	Type
	4	POM, High-alloy stainless steel	VDMA24364-B1/B2-L	13 g	8119201	MS4-MV1

Mounting bracket MS4-WP...						
	Size	Material bracket	LABS (PWIS) conformity	Product weight	Part no.	Type
	4	Die-cast aluminium	VDMA24364-B1/B2-L	39 g	532184	MS4-WP

Mounting bracket MS4-WPM						
	Size	Material module connector	LABS (PWIS) conformity	Product weight	Part no.	Type
	4	POM, Steel	VDMA24364-B1/B2-L	45 g	526060	MS4-WPM-D

Mounting bracket MS4-WB						
	Size	Material bracket	LABS (PWIS) conformity	Product weight	Part no.	Type
	4	Steel	VDMA24364-B1/B2-L	46 g	532185	MS4-WB

Accessories

Mounting bracket MS4-WBM

	Size	Material bracket	LABS (PWIS) conformity	Product weight	Part no.	Type
	4	Steel	VDMA24364-B1/B2-L	48 g	526062	MS4-WBM

Cover cap MS4-END

	Size	Material housing	Part no.	Type
	4	PA-reinforced	538779	MS4-END

Mounting plate MS4-AEND

	Size	Product weight	Part no.	Type
	4	4 g	542966	MS4-AEND

Connecting plate SET MS4-AQ...

	Size	Pneumatic connection, port 1	Product weight	Part no.	Type
	4	1/8 NPT	128 g	526065	MS4N-AQK
		1/4 NPT		526066	MS4N-AQN
		3/8 NPT		526067	MS4N-AQP


Pressure gauge MA

	Pneumatic connection	Indicating range	Indicating range	Product weight	Part no.	Type
	R1/8		0 ... 16 bar	60 g	525726	MA-40-16-R1/8-E-RG
	R1/4	0 ... 232 psi		70 g	187080	MA-40-16-R1/4-EN

Accessories

Pressure sensor SPAU						
	Pneumatic connection	Switching output	Electrical connection 1, connector system	Product weight	Part no.	Type
	R1/8	2 x PNP or 2 x NPN, switchable	M12x1, A-coded to EN 61076-2-101	70 g	8001206	SPAU-P10R-T-R18M-L-PNLK-PNVBA-M12D
			M8x1, A-coded, to EN 61076-2-104		8001203	SPAU-P10R-T-R18M-L-PNLK-PNVBA-M8D
	R1/4		M12x1, A-coded to EN 61076-2-101		8001208	SPAU-P10R-T-R14M-L-PNLK-PNVBA-M12D
			M8x1, A-coded, to EN 61076-2-104		8001209	SPAU-P10R-T-R14M-L-PNLK-PNVBA-M8D

Connecting cable NEBA, straight						
	Electrical connection 1, connector system	Electrical connection 2, connector system	Electrical connection 2, number of connections/cores	Cable length	Part no.	Type
	M12x1, A-coded to EN 61076-2-101	Open end	3	2.5 m	8078236	NEBA-M12G5-U-2.5-N-LE3
				5 m	8078237	NEBA-M12G5-U-5-N-LE3
			4	2.5 m	8078239	NEBA-M12G5-U-2.5-N-LE4
				5 m	8078240	NEBA-M12G5-U-5-N-LE4
	M8x1, A-coded, to EN 61076-2-104		3	2.5 m	8078223	NEBA-M8G3-U-2.5-N-LE3
				5 m	8078224	NEBA-M8G3-U-5-N-LE3
			4	2.5 m	8078227	NEBA-M8G4-U-2.5-N-LE4
				5 m	8078228	NEBA-M8G4-U-5-N-LE4

Connecting cable NEBA, angled						
	Electrical connection 1, connector system	Electrical connection 2, connector system	Electrical connection 2, number of connections/ cores	Cable length	Part no.	Type
	M12x1, A-coded to EN 61076-2-101	Open end	3	2.5 m	8078245	NEBA-M12W5-U-2.5-N-LE3
				5 m	8078246	NEBA-M12W5-U-5-N-LE3
			4	2.5 m	8078248	NEBA-M12W5-U-2.5-N-LE4
				5 m	8078249	NEBA-M12W5-U-5-N-LE4
	M8x1, A-coded, to EN 61076-2-104		3	2.5 m	8078230	NEBA-M8W3-U-2.5-N-LE3
				5 m	8078231	NEBA-M8W3-U-5-N-LE3
			4	2.5 m	8078233	NEBA-M8W4-U-2.5-N-LE4
				5 m	8078234	NEBA-M8W4-U-5-N-LE4

Illuminating seal MEB-LD					
	Operational voltage range DC	Nominal operating voltage AC	Product weight	Part no.	Type
		230 V	0.6 g	151718	MEB-LD-230AC
	12 ... 24 V			151717	MEB-LD-12-24DC

Accessories

Plug socket with cable KMEB 230V AC					
	Nominal operating voltage AC	Cable length	Product weight	Part no.	Type
	230 V	2.5 m	125 g	151690	KMEB-1-230AC-2.5
		5 m	230 g	151691	KMEB-1-230AC-5

Plug socket with cable KMEB 24V DC					
	Nominal operating voltage DC	Cable length	Product weight	Part no.	Type
	24 V	2.5 m	120 g	547268	KMEB-3-24-2.5-LED
				547270	KMEB-3-24-2.5
		5 m	125 g	151688	KMEB-1-24-2.5-LED
			230 g	547271	KMEB-3-24-5
				151689	KMEB-1-24-5-LED
				547269	KMEB-3-24-5-LED

Plug socket MSSD-EB					
	Electrical connection	Cable fitting	Product weight	Part no.	Type
		Pg7	11 g	539712	MSSD-EB-M12
	3-pin, Socket, Angled socket, Type C, To DIN EN 175301-803, To DIN EN 61984, Square design MSEB, Square design MSN2			151687	MSSD-EB

Silencer U						
	Pneumatic connection	Sound pressure level	Flow rate to atmosphere	Product weight	Part no.	Type
	G1/4	80 dB(A)	2,440 l/min	17 g	6842	U-1/4-B

Locking clip CPV18-HV					
	Short type code	LABS (PWIS) conformity	Product weight	Part no.	Type
	CPV18	VDMA24364-B1/B2-L	0.53 g	530056	CPV18-HV