


On/off valve MS6N-EM

FESTO



Characteristics

At a glance




Manually actuated on/off valve for pressurising and exhausting pneumatic systems.

- The valve is switched by turning the rotary knob
- A silencer can be attached or the exhaust air can be ducted at port 3
- Optionally with pressure gauge and pressure sensor

Ordering data - modular system

Link [ms6n_em1](#)



Configurable product

This product and all its product options can be ordered online via the configurator.

Pneumatic connection

By installing connecting plates it is easier to replace the module if necessary (e.g. when using piping).


Pressure gauge alternatives

- Key features [AG]/[RG]: integrated pressure gauges
- Key features [A4]/[A8]: Adapter for pressure gauge
- Key features [O.D7]/[O.D.8]/[O.D.9]/[O.D.10]: simple pressure sensors for monitoring the system
- Key features [AD11]/[AD12]: functional pressure sensors for monitoring the system

Type of mounting

[WP]

Mounting bracket basic design



- For connecting the modules for wall mounting
- In combination with connecting plate for wall mounting an individual unit
- In conjunction with mounting plate MS-AEND or wall mounting a single device
- Same wall distance when used in combination with series MS4 and MS6

[WB]

Mounting centrally at rear (wall mounting top and bottom), connecting plates not required



- For wall mounting

[WPM]

Mounting bracket for hooking in service unit components



- For connecting the modules for wall mounting
- In combination with connecting plate MS4-AG... for mounting an individual device on a wall
- Fast hooking and unhooking

Type code

001	Series	
MS	MS series	
002	Size	
6	Grid dimension 62 mm	
003	Thread type	
N	NPT thread	
004	Function	
EM1	On/off valve, manual	
005	Pneumatic connection, inch	
1/4	Female thread NPT 1/4	
3/8	Female thread NPT 3/8	
1/2	Female thread NPT 1/2	
AQN	Sub-base NPT1/4	
AQP	Sub-base NPT3/8	
AQR	Sub-base NPT1/2	
AQS	Sub-base NPT3/4	
006	Rotary knob colour	
	Standard (black/blue)	
R	Red	
007	Silencer	
	None	
S	Silencer	

008	Pressure gauge alternatives	
	None	
A4	Adapter for EN pressure gauge 1/4, without pressure gauge	
AD7	Pressure sensor with switching display, M8 plug, threshold value comparator, PNP, N/O	
AD8	Pressure sensor with switching display, M8 plug, threshold value comparator, PNP, N/C	
AD9	Pressure sensor with switching display, M8 plug, window comparator, PNP, N/O	
AD10	Pressure sensor with operational status indicator, M8 plug, window comparator, PNP, N/C	
AD11	Pressure sensor with LCD display, M12 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V, 4...20 mA	
AD12	Pressure sensor with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V, 4...20 mA	
AG	MS pressure gauge	
RG	Integrated pressure gauge, red/green scale	

009	Alternative pressure gauge scale	
	MS pressure gauge	
BAR	bar	
MPA	MPa	

010	Type of mounting	
	Without mounting bracket	
WB	Mounting centrally at rear (wall mounting top and bottom), connecting plates not required	
WP	Mounting bracket basic design	
WPM	Mounting bracket for hooking in service unit components	

011	Flow direction	
	Flow direction from left to right	
Z	Flow direction from right to left	

Datasheet

General technical data

Pneumatic connection, port 1 ¹⁾	1/4 NPT	3/8 NPT	1/2 NPT
Pneumatic connection, port 2	1/4 NPT	3/8 NPT	1/2 NPT
Pneumatic connection, port 3	1/2 NPT, Integrated silencer, Not ducted		
Design	Rotary switching valve		
Type of mounting	Either: Inline installation With accessories		
Mounting position ²⁾	Any		
Valve function	3/2-way, double solenoid		
Exhaust-air function	Cannot be throttled		
Type of actuation	Manual		
Type of piloting	Direct		
Flow direction	Non-reversible		

1) Via connecting plate [AQ...]; 1/4 NPT, 3/8 NPT, 1/2 NPT or 3/4 NPT

2) The on/off valve must be mounted vertically when combined with a pressure sensor as condensate must not collect in the pressure sensor.

Flow characteristics

Pneumatic connection, port 1	1/4 NPT	3/8 NPT	1/2 NPT
Standard nominal flow rate (standardised to DIN 1343) ¹⁾	3,000 l/min	5,500 l/min	8,700 l/min
C value	10.7 l/sbar	21.2 l/sbar	30.8 l/sbar
b value	0.56	0.49	0.57

1) Measured at p1 = 6 bar and p2 = 5 bar, Δp = 1 bar.

Operating and environmental conditions

Pneumatic connection, port 1	1/4 NPT	3/8 NPT	1/2 NPT
Operating pressure	0 ... 18 bar		
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4], Inert gas		
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)		
Ambient temperature	-10 ... 60°C		
Media temperature	-10 ... 60°C		
Corrosion resistance class CRC ¹⁾	2 - Moderate corrosion stress		
Suitable for use with food ²⁾	See supplementary material information		

1) More information www.festo.com/x/topic/crc

2) More information www.festo.com/certificates/ms6n-em1


Materials

Material housing	Die-cast aluminium
Material seals	TPE-U(PU)
Note on materials	RoHS compliant
LABS (PWIS) conformity	VDMA24364-B1/B2-L

Dimensions

Dimensions – Basic type with female thread, with cover plate


Download CAD data www.festo.com



	B1 [inch]	B2 [inch]	B3 [inch]	B4 [inch]	B5 [inch]	B6 [inch]	D1	D5	L1 [inch]	L2 [inch]	L4 [inch]	L7 [inch]
MS6N-EM1-1/4	2,44	1,22	2,99	1,77	0,39	0,94	1/4 NPT	1/2 NPT	5,93	1,53	3,33	1,11
MS6N-EM1-3/8							3/8 NPT					
MS6N-EM1-1/2							1/2 NPT					

Dimensions

Dimensions – Integrated MS pressure gauge with standard scale / Integrated MS pressure gauge with red/green scale www.festo.com




	B2 [inch]	B3 [inch]	D1
MS6N-EM1-1/4-...-AG	1,22	3,03	1/4 NPT
MS6N-EM1-3/8-...-AG			3/8 NPT
MS6N-EM1-1/2-...-AG			1/2 NPT
MS6N-EM1-1/4-...-RG	1,22	3,09	1/4 NPT
MS6N-EM1-3/8-...-RG			3/8 NPT
MS6N-EM1-1/2-...-RG			1/2 NPT

Dimensions

Dimensions – Adapter for EN pressure gauge 1/4, without pressure gauge


Download CAD data www.festo.com



	B2 [inch]	B3 [inch]	D1	D4
MS6N-EM1-1/4-...-A4	1,22	3,09	1/4 NPT	1/4 NPT
MS6N-EM1-3/8-...-A4			3/8 NPT	
MS6N-EM1-1/2-...-A4			1/2 NPT	

Dimensions


Dimensions – Pressure sensor with status indicator AD7, AD8, AD9, AD10 Download CAD data www.festo.com



	B2 [inch]	B3 [inch]	B5 [inch]	B6 [inch]	D6
MS6N-....AD7, AD8, AD9, AD10	1,22	3,11	~2,01	0,63	M8x1

Dimensions

Dimensions – Silencer Download CAD data www.festo.com




	D2 [inch]	L4 [inch]
MS6N-EM1-....S	1,10	4,29

Ordering data


Ordering data – Without silencer					
	Pneumatic connection, port 1	Flow direction	Product weight	Part no.	Type
	1/4 NPT	From right to left	580 g	541296	MS6N-EM1-1/4-Z
		From left to right		541293	MS6N-EM1-1/4
	3/8 NPT	From right to left		541297	MS6N-EM1-3/8
		From left to right		541300	MS6N-EM1-3/8-Z
	1/2 NPT	From left to right		541289	MS6N-EM1-1/2
		From right to left		541292	MS6N-EM1-1/2-Z

Ordering data – With silencer					
	Pneumatic connection, port 1	Flow direction	Product weight	Part no.	Type
	1/4 NPT	From right to left	655 g	541295	MS6N-EM1-1/4-S-Z
		From left to right		541294	MS6N-EM1-1/4-S
	3/8 NPT	From right to left		541298	MS6N-EM1-3/8-S
		From left to right		541299	MS6N-EM1-3/8-S-Z
	1/2 NPT	From left to right		541291	MS6N-EM1-1/2-S-Z
		From right to left		541290	MS6N-EM1-1/2-S

Ordering data – Modular product system			
	Short type code	Part no.	Type
	MS6N-EM1	541301	MS6N-EM1

Peripherals

Peripherals overview



Accessories		→ Link
Type/order code	Description	
[1] On/off valve MS6N-EM1	On/off valve	ms6n-em1
[2] Module connector MS6-MV1	For connecting the modules	13
[3] Mounting bracket MS6-WP	Order code [WP]	13
[3] Mounting bracket MS6-WPM	Order code [WPM] (without illustration)	13
[4] Mounting bracket MS6-WB	Order code [WB]	13
[5] Mounting bracket MS4-WBM	Not available for this size	-
[6] Cover cap MS6-END	Can be used to cover the sides of the housing for the first and last module if no connecting plates are used.	14
[7] Mounting plate MS6-AEND	Module connector MS4-MV1 [2] or mounting bracket MS4-WP, WPB, WPE, WPM [3] is required for mounting.	14

Peripherals

Accessories		→ Link
Type/order code	Description	
[8] Connecting plate SET MS6-AQ...	Order code [AQ...]	14
[9] Padlock LRVS-D	When closed, the rotary knob can be secured with a padlock	16
[10] Pressure sensor with LCD display SPAU	• Display module • Order code [AD11], [AD12]	ms6n-em1
[11] Connecting cable NEBA-M...G...-LE4, straight	Connecting cable for display module	15
[11] Connecting cable NEBA-M...G...-LE4, angled	Connecting cable for display module	15
[12] Pressure sensor with switching status indicator SDE5	• Display module • Order code [AD7], [AD8], [AD9], [AD10]	ms6n-em1
[13] Connecting cable NEBA-M...G...-LE3, straight	Connecting cable for display module	15
[14] Adapter for EN pressure gauge 1/8, 1/4	Order code [A8], [A4]	ms6n-em1
[15] Pressure gauge MA	Built-in pressure indicator	14
[16] Pressure sensor SPAU-...-T	Display module	15
[17] Pressure gauge MS	Order code [AG], [RG]	ms6n-em1
[18] Silencer S	Order code [S]	ms6n-em1
[18] Silencer U	-	15

Accessories

Module connector MS6-MV1						
	Size	Material module connector	LABS (PWIS) conformity	Product weight	Part no.	Type
	6	POM, High-alloy stainless steel	VDMA24364-B1/B2-L	33 g	8119204	MS6-MV1

Mounting bracket MS6-WP...						
	Size	Material bracket	LABS (PWIS) conformity	Product weight	Part no.	Type
	6	Die-cast aluminium	VDMA24364-B1/B2-L	76 g	532195	MS6-WP

Mounting bracket MS6-WPM						
	Size	Material module connector	LABS (PWIS) conformity	Product weight	Part no.	Type
	6	Die-cast aluminium	VDMA24364-B1/B2-L	144 g	526073	MS6-WPM-D
				154 g	532186	MS6-WPM-2D

Mounting bracket MS6-WB						
	Size	Material bracket	LABS (PWIS) conformity	Product weight	Part no.	Type
	6	Steel	VDMA24364-B1/B2-L	121 g	532196	MS6-WB

Accessories

Cover cap MS6-END						
	Size	Material housing	LABS (PWIS) conformity	Part no.	Type	
	6	Reinforced PA	VDMA24364-B1/B2-L	538780	MS6-END	

Mounting plate MS6-AEND						
	Size	Material housing	LABS (PWIS) conformity	Product weight	Part no.	Type
	6	Reinforced PA	VDMA24364-B1/B2-L	11.1 g	535408	MS6-AEND1


Connecting plate SET MS6-AQ...						
	Size	Pneumatic connection, port 1	Material sub-base	Product weight	Part no.	Type
	6	1/4 NPT	Die-cast aluminium	300 g	526076	MS6N-AQN
		3/8 NPT			526077	MS6N-AQP
		1/2 NPT			526078	MS6N-AQR
		3/4 NPT			526079	MS6N-AQS


Pressure gauge MA						
	Pneumatic connection	Indicating range	Indicating range	Product weight	Part no.	Type
	R1/8	0 ... 232 psi	0 ... 16 bar	60 g	525726	MA-40-16-R1/8-E-RG
	R1/4			75 g	525729	MA-50-16-R1/4-E-RG
				70 g	187080	MA-40-16-R1/4-EN

Pressure sensor SPAU						
	Pneumatic connection	Switching output	Electrical connection 1, connector system	Product weight	Part no.	Type
	R1/8	2 x PNP or 2 x NPN, switchable	M12x1, A-coded to EN 61076-2-101	70 g	8001206	SPAU-P10R-T-R18M-L-PNLK-PNVBA-M12D

Accessories

Pressure sensor SPAU						
	Pneumatic connection	Switching output	Electrical connection 1, connector system	Product weight	Part no.	Type
	R1/8	2 x PNP or 2 x NPN, switchable	M8x1, A-coded, to EN 61076-2-104	70 g	8001203	SPAU-P10R-T-R18M-L-PNLK-PNVBA-M8D
	R1/4		M12x1, A-coded to EN 61076-2-101		8001208	SPAU-P10R-T-R14M-L-PNLK-PNVBA-M12D
			M8x1, A-coded, to EN 61076-2-104		8001209	SPAU-P10R-T-R14M-L-PNLK-PNVBA-M8D

Connecting cable NEBA, straight						
	Electrical connection 1, connector system	Electrical connection 2, connector system	Electrical connection 2, number of connections/cores	Cable length	Part no.	Type
	M12x1, A-coded to EN 61076-2-101	Open end	3	2.5 m	8078236	NEBA-M12G5-U-2.5-N-LE3
				5 m	8078237	NEBA-M12G5-U-5-N-LE3
			4	2.5 m	8078239	NEBA-M12G5-U-2.5-N-LE4
				5 m	8078240	NEBA-M12G5-U-5-N-LE4
	M8x1, A-coded, to EN 61076-2-104		3	2.5 m	8078223	NEBA-M8G3-U-2.5-N-LE3
				5 m	8078224	NEBA-M8G3-U-5-N-LE3
			4	2.5 m	8078227	NEBA-M8G4-U-2.5-N-LE4
				5 m	8078228	NEBA-M8G4-U-5-N-LE4

Connecting cable NEBA, angled						
	Electrical connection 1, connector system	Electrical connection 2, connector system	Electrical connection 2, number of connections/ cores	Cable length	Part no.	Type
	M12x1, A-coded to EN 61076-2-101	Open end	3	2.5 m	8078245	NEBA-M12W5-U-2.5-N-LE3
				5 m	8078246	NEBA-M12W5-U-5-N-LE3
			4	2.5 m	8078248	NEBA-M12W5-U-2.5-N-LE4
				5 m	8078249	NEBA-M12W5-U-5-N-LE4
	M8x1, A-coded, to EN 61076-2-104		3	2.5 m	8078230	NEBA-M8W3-U-2.5-N-LE3
				5 m	8078231	NEBA-M8W3-U-5-N-LE3
			4	2.5 m	8078233	NEBA-M8W4-U-2.5-N-LE4
				5 m	8078234	NEBA-M8W4-U-5-N-LE4

Silencer U						
	Pneumatic connection	Flow rate to atmosphere	Sound pressure level	Product weight	Part no.	Type
	G1/2	7,500 l/min	81 dB(A)	75 g	6844	U-1/2-B

Accessories

Padlock LRV5-D				
	LABS (PWIS) conformity	Product weight	Part no.	Type
	VDMA24364-B1/B2-L	120 g	193786	LRVS-D