



Compact cylinders ADNGF, standard hole pattern

FESTO




Key features

At a glance With guide rod and yoke plate ADNGF-...	With guide rod, yoke plate and through piston rod ADNGF-...-S2
--	---



With through piston rod and stroke adjustment
ADNGF-...-KE



- Einstellbereich der ausgefahrenen Endlage

Cushioning types		
	Cushioning P	Cushioning PPS
Operating mode	• The drive is fitted with polymer elastic end-position cushioning	• The drive has self-adjusting, pneumatic end-position cushioning
Application	• Small loads • Low speeds • Small cushioning capacity	• Larger loads • Higher speeds • Larger cushioning capacity
Advantages	• No adjustment required • Saves time	• No adjustment required • Bis zu 4 mal höheres Dämpfungsvermögen als ADNGF-...-P • Saves time • Reduces noise


Variants from the modular product system		
Symbol	Key features	Description
	S2 Through piston rod	The piston rod can be used for attachment at both ends of the cylinder
	...KE Hubeinstellung	Continuous piston rod with adjustment element mounted on one side. To limit the extended end position and to set a precise position.
	S6 Heat-resistant seals	Temperature resistance up to max. 120°C
	TL Captive rating plate	Laser-etched rating plate. Easy identification for spare parts, even after years in a harsh environment

Type codes

001	Series	
ADNGF	Compact cylinder, double-acting, standard hole pattern	
002	Piston diameter	
12	12	
16	16	
20	20	
25	25	
32	32	
40	40	
50	50	
63	63	
80	80	
100	100	
003	Stroke	
...	1 ... 400	

004	Cushioning	
P	Elastic cushioning rings/plates on both sides	
PPS	Pneumatic cushioning, self-adjusting at both ends	
005	Position sensing	
A	For proximity sensor	
006	Piston rod type	
	At one end	
S2	Through piston rod	
007	Temperature range	
	Standard	
S6	Heat-resistant seals max. 120 °C	
008	Captive rating plate	
	Rating plate, glued	
TL	Laser etched rating plate	

Peripherals overview




Peripherals overview


Mounting attachments and accessories		Description	→ Page/Internet
[1]	Compact cylinder ADNGF	Double-acting	6
[2]	One-way flow control valve GRLA/GRLZ	For regulating speed	23
[3]	Push-in fitting QS	For connecting tubing with standard O.D.	qs
[4]	Flange mounting FNC	For end caps	15
[5]	Swivel flange SNCL/SNCL-...-R3	For end caps	16
[6]	Swivel flange SNCB/SNCB-...-R3	For end caps	20
[7]	Multi-position kit DPNA	zum Verbinden zweier Zylinder mit gleichem Kolben-Ø zu einem Mehrstellungszyylinder	19
[8]	Trunnion flange ZNCF/CRZNG	For end caps	21
[9]	Trunnion support LNZG	For trunnion flange ZNCF/CRZNG	22
[10]	Swivel flange SNCS/CRSNCS/SNCS-...-R3	For end caps	17
[11]	Clevis foot LBG/LBG-...-R3	For swivel flange SNCS	18
[12]	Proximity switch SME-8	Can be integrated in the cylinder profile barrel	24
[13]	Proximity switch SME/SMT-8M	Can be integrated in the cylinder profile barrel	24
[14]	Slot cover ABP-5-S	For protecting the sensor cables and the sensor slots from contamination	25
[15]	Proximity switch SMPO-8E	Pneumatic output signal	25
[16]	Mounting kit SMB-8E	For proximity switch SMPO-8E	25

Datasheet

P cushioning



PPS cushioning



-  - Durchmesser
12 ... 100 mm
-  - Hublänge
1 ... 400 mm
-  - www.festo.com



General technical data

General technical data										
Kolben-ø	12	16	20	25	32	40	50	63	80	100
Pneumatic port	M5	M5	M5	M5	G1/8	G1/8	G1/8	G1/8	G1/8	G1/8
Design	Piston									
	Piston rod									
	Cylinder barrel									
Operating mode	Double-acting									
Cushioning										
P	Elastic cushioning rings/plates at both ends									
PPS	–		pneumatische Dämpfung beidseitig selbststellend							
Cushioning length										
PPS	[mm]	–	3	3.5	4	5	6	7	7.5	10
Position sensing	Via proximity switch									
Type of mounting	with through hole / internal thread / accessories									
Mounting position	Any									

Operating and environmental conditions

Kolben-ø	12	16	20	25	32	40	50	63	80	100
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]									
Note on the operating/ pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)									
Operating pressure										
in [MPa]										
–	0.15 ... 1			0.1 ... 1						
PPS	–		0.19 ... 1				0.14 ... 1			
S2, KE	0.15 ... 1				0.1 ... 1					
in [bar]										
–	1.5 ... 10			1 ... 10						
PPS	–		1.9 ... 10				1.4 ... 10			
S2, KE	1.5 ... 10				1 ... 10					
in [psi]										
–	21, 76 ... 145			14.5 ... 145						
PPS	–		27.56 ... 145				20.31 ... 145			
S2, KE	21, 76 ... 145				14.5 ... 145					
Umgebungstemperatur ¹⁾ [°C]										
–	–20 ... +80									
S6	0 ... +120									
Corrosion resistance class CRC ²⁾	2 - Moderate corrosion stress									

1) Note operating range of proximity switches

2) More information www.festo.com/x/topic/crc

Datasheet

Weight [g]										
Kolben-Ø	12	16	20	25	32	40	50	63	80	100
ADNGF-...										
Product weight with 0 mm stroke	76	88	153	203	310	432	656	930	1465	2205
Additional weight per 10 mm stroke	14	16	26	30	37	46	63	72	97	116
Moving mass with 0 mm stroke	23	31	58	73	125	174	291	400	761	1066
Additional mass per 10 mm stroke	4	6	11	11	17	17	28	28	43	43
ADNGF-...-S2										
Product weight with 0 mm stroke	78	92	160	214	313	435	667	941	1466	2212
Additional weight per 10 mm stroke	16	19	31	35	43	52	74	83	115	134
Moving mass with 0 mm stroke	26	36	67	79	131	173	296	406	775	1071
Additional mass per 10 mm stroke	10	16	26	26	40	40	67	67	103	103
ADNGF-...-KE										
Product weight with 0 mm stroke	92	106	190	244	382	504	778	1052	–	–
Additional weight per 10 mm stroke	17	20	33	36	46	55	79	88	–	–
Moving mass with 0 mm stroke	26	50	97	109	200	242	407	517	–	–
Additional mass per 10 mm stroke	6	10	17	17	26	26	44	44	–	–
ADNGF-...-PPS										
Product weight with 0 mm stroke	–	–	150	218	317	442	672	947	1474	2228
Additional weight per 10 mm stroke	–	–	26	30	37	46	63	72	97	116
Moving mass with 0 mm stroke	–	–	57	95	132	185	307	417	770	1089
Additional mass per 10 mm stroke	–	–	11	11	17	17	28	28	43	43


Datasheet

Forces [N] and impact energy [J]										
Kolben-Ø	12	16	20	25	32	40	50	63	80	100
Theoretical force at 6 bar, advancing										
–	68	121	188	295	483	754	1178	1870	3016	4712
S2	51	90	141	247	415	686	1057	1750	2827	4524
Theoretical force at 6 bar, retracting										
–	51	90	141	247	415	686	1057	1750	2827	4524
S2	51	90	141	247	415	686	1057	1750	2827	4524
Max. impact energy in the end positions										
–	0.07	0.15	0.2	0.3	0.4	0.7	1.0	1.3	1.8	2.5
KE	0.055	0.12	0.16	0.24	0.32	0.56	0.8	1.0	–	–
S6	0.035	0.075	0.1	0.15	0.2	0.35	0.5	0.65	0.9	1.25


 **Note**
The maximum impact energy is still maintained in combination with cushioning PPS.

Max. energy conversion capacity [J]								
Kolben-Ø	20	25	32	40	50	63	80	100
For cushioning PPS	0.65	0.8	1	1.7	2.8	4.8	8	12

Max. transverse force Fq as a function of projection x




Drehmoment M in Abhängigkeit von der Hublänge l



Datasheet

Materials



Compact cylinder		Basic version	S6
[1]	Cover		
	Ø 12 ... 80	Anodised aluminium	
	Ø 100	Coated die-cast aluminium	
[2]	Cylinder barrel	Anodised aluminium	
[3]	Piston rod	High-alloy steel	
[4]	Flange screws		
	Ø 12 ... 16	High-alloy steel	
	Ø 20 ... 63	Galvanised steel	
	Ø 80 ... 100	Standard screws, galvanised steel	
– Stroke setting ADNGF-...-KE			
	Stop element	PE-UHMW	
	Threaded coupling	Aluminium	
–	Seals	Polyurethane	Fluoro rubber

Datasheet


Dimensions – Basic version

Download CAD data → www.festo.com

Ø 12 ... 63


Ø 32 ... 63

Ø 12 ... 25 Ø 12



+ = plus stroke length

Ø 80 ... 100



+ = plus stroke length

Ø [mm]	BG min.	D1 Ø H9	D4 ±0.1	D5 Ø	D6	D7 Ø H9	D8	E	EE	FB Ø H8	G	J2	J3
12	17	9	12	6 ^{F9}	M3	–	–	27.5 ^{+0.3}	M5	3	10.5	2	–
16			14					29 ^{+0.3}			11	2.6	
20	19.5		17	9 ^{F9}	M4			35.5 ^{+0.3}		4	12		
25			22		M5	14		39.5 ^{+0.3}	G1/8	5		6	
32	26		28			17		47 ^{+0.3}			15		
40			33					54.5 ^{+0.3}				8	
50	27	12	42	12 ^{F9}	M6	22		65.5 ^{+0.3}		6			
63			50					75.5 ^{+0.3}				11.5	
80	17		65	15	M8	24	15	95.5 ^{+0.6}		8	16.5		
100	21.5		80		M10			113.5 ^{+0.6}		10	21.5	20	


Ø [mm]	PW +0.2	ME	MM Ø h8	PL +0.2	RT	ST h13	T1	T2 +0.1	TG ±0.2	WH +1.3	PPS +1.4	ZA ±0.6	ZB +1.2	PPS +1.3
12	3.5	6	6	6	M4	5	–	2.1	16	4.2	–	35	39.2	–
16			8			7			18	4.7			39.7	
20	5	8	10		M5	9			22	5.5	5.5	37	42.5	42.5
25							5		26		5.5	39	44.5	45.3
32		10	12	8.2	M6	10	6		32.5	6	6.5	44	50	50.6
40									38	6.1	6.6	45	51.1	51.7
50		12	16		M8	13	7.5	2.6	46.5	7.7	8.2		52.7	53.2
63									56.5	7.5	8	49	56.5	57
80	2.6	14	20		M10	17	10.5		72	8.9	9.4	54	62.9	63.4
100				10.5					89	9	9.8	67	76	76.8

Datasheet

Dimensions – Variants

Download CAD data → www.festo.com


S2 – Through piston rod



+ = plus stroke length

++ = plus 2x stroke length

KE – Hubeinstellung




+ = plus stroke length


++ = plus 2x stroke length

ø [mm]	AF min.	A3	D10 ø	KF	T4	WH		ZM		KE 1	KE 2
						+1.3	PPS +1.4		PPS		
12	8	28	15	M3	1.5	4.2	–	44.5 ^{+0.5}	–	13	10
16	10			M4		4.7		45.7 ^{+0.5}			
20	14	32	20	M6	2.6	5.5	5.5	49.5 ^{+0.5}	49.5 ^{+0.5}	17	13
25							5.5	51.5 ^{+0.5}	51.5 ^{+0.5}		
32	16	37	30	M8	3.3	6	6.5	57.5 ^{+0.5}	58.6 ^{+0.6}	24	17
40						6.1	6.6	58.6 ^{+0.6}	59.7 ^{+0.7}		
50	20	41	35	M10	4.7	8.2	8.2	62.0 ^{+0.6}	63.1 ^{+0.7}	30	19
63						8.1	8	65.4 ^{+0.6}	66.5 ^{+0.7}		
80						8.9	9.4	73.2 ^{+0.6}	74.3 ^{+0.7}		
100						9	9.8	86.4 ^{+0.6}	88 ^{+0.7}		

Datasheet

Ordering data						
Type	Kolben-ø	Stroke [mm]	P – Elastic cushioning rings/plates at both ends		PPS – Pneumatic cushioning, self-adjusting at both ends	
	[mm]	[mm]	Part no.	Type	Part no.	Type
	12	5	554205	ADNGF-12-5-P-A	–	
		10	554206	ADNGF-12-10-P-A		
		15	554207	ADNGF-12-15-P-A		
		20	554208	ADNGF-12-20-P-A		
		25	554209	ADNGF-12-25-P-A		
		30	554210	ADNGF-12-30-P-A		
		40	554211	ADNGF-12-40-P-A		
	16	5	554212	ADNGF-16-5-P-A	–	
		10	554213	ADNGF-16-10-P-A		
		15	554214	ADNGF-16-15-P-A		
		20	554215	ADNGF-16-20-P-A		
		25	554216	ADNGF-16-25-P-A		
		30	554217	ADNGF-16-30-P-A		
		40	554218	ADNGF-16-40-P-A		
		50	554219	ADNGF-16-50-P-A		
	20	5	554220	ADNGF-20-5-P-A	–	
		10	554221	ADNGF-20-10-P-A		
		15	554222	ADNGF-20-15-P-A		
		20	554223	ADNGF-20-20-P-A		
		25	554224	ADNGF-20-25-P-A		
		30	554225	ADNGF-20-30-P-A		
		40	554226	ADNGF-20-40-P-A		
		50	554227	ADNGF-20-50-P-A		
		60	554228	ADNGF-20-60-P-A		
	25	5	554229	ADNGF-25-5-P-A	–	
		10	554230	ADNGF-25-10-P-A		
		15	554231	ADNGF-25-15-P-A		
		20	554232	ADNGF-25-20-P-A		
		25	554233	ADNGF-25-25-P-A		
		30	554234	ADNGF-25-30-P-A		
		40	554235	ADNGF-25-40-P-A		
		50	554236	ADNGF-25-50-P-A		
		60	554237	ADNGF-25-60-P-A		
	32	5	554238	ADNGF-32-5-P-A	–	
		10	554239	ADNGF-32-10-P-A		
		15	554240	ADNGF-32-15-P-A		
		20	554241	ADNGF-32-20-P-A		
		25	554242	ADNGF-32-25-P-A		
		30	554243	ADNGF-32-30-P-A		
		40	554244	ADNGF-32-40-P-A		
		50	554245	ADNGF-32-50-P-A		
		60	554246	ADNGF-32-60-P-A		
		80	554247	ADNGF-32-80-P-A		
					577208	ADNGF-20-10-PPS-A
					577209	ADNGF-20-15-PPS-A
					577210	ADNGF-20-20-PPS-A
					577211	ADNGF-20-25-PPS-A
					577212	ADNGF-20-30-PPS-A
					577213	ADNGF-20-40-PPS-A
					577214	ADNGF-20-50-PPS-A
					577215	ADNGF-20-60-PPS-A
					577216	ADNGF-25-10-PPS-A
					577217	ADNGF-25-15-PPS-A
					577218	ADNGF-25-20-PPS-A
					577219	ADNGF-25-25-PPS-A
					577220	ADNGF-25-30-PPS-A
					577221	ADNGF-25-40-PPS-A
					577222	ADNGF-25-50-PPS-A
					577223	ADNGF-25-60-PPS-A
					574022	ADNGF-32-10-PPS-A
					574023	ADNGF-32-15-PPS-A
					574024	ADNGF-32-20-PPS-A
					574025	ADNGF-32-25-PPS-A
					574026	ADNGF-32-30-PPS-A
					574027	ADNGF-32-40-PPS-A
					574028	ADNGF-32-50-PPS-A
					574029	ADNGF-32-60-PPS-A
					574030	ADNGF-32-80-PPS-A

Datasheet

Ordering data						
Type	Kolben-ø	Stroke [mm]	P – Elastic cushioning rings/plates at both ends		PPS – Pneumatic cushioning, self-adjusting at both ends	
	[mm]	[mm]	Part no.	Type	Part no.	Type
	40	5	554248	ADNGF-40-5-P-A	–	
		10	554249	ADNGF-40-10-P-A	574031	ADNGF-40-10-PPS-A
		15	554250	ADNGF-40-15-P-A	574032	ADNGF-40-15-PPS-A
		20	554251	ADNGF-40-20-P-A	574033	ADNGF-40-20-PPS-A
		25	554252	ADNGF-40-25-P-A	574034	ADNGF-40-25-PPS-A
		30	554253	ADNGF-40-30-P-A	574035	ADNGF-40-30-PPS-A
		40	554254	ADNGF-40-40-P-A	574036	ADNGF-40-40-PPS-A
		50	554255	ADNGF-40-50-P-A	574037	ADNGF-40-50-PPS-A
		60	554256	ADNGF-40-60-P-A	574038	ADNGF-40-60-PPS-A
		80	554257	ADNGF-40-80-P-A	574039	ADNGF-40-80-PPS-A
	50	5	554258	ADNGF-50-5-P-A	–	
		10	554259	ADNGF-50-10-P-A	574040	ADNGF-50-10-PPS-A
		15	554260	ADNGF-50-15-P-A	574041	ADNGF-50-15-PPS-A
		20	554261	ADNGF-50-20-P-A	574042	ADNGF-50-20-PPS-A
		25	554262	ADNGF-50-25-P-A	574043	ADNGF-50-25-PPS-A
		30	554263	ADNGF-50-30-P-A	574044	ADNGF-50-30-PPS-A
		40	554264	ADNGF-50-40-P-A	574045	ADNGF-50-40-PPS-A
		50	554265	ADNGF-50-50-P-A	574046	ADNGF-50-50-PPS-A
		60	554266	ADNGF-50-60-P-A	574047	ADNGF-50-60-PPS-A
		80	554267	ADNGF-50-80-P-A	574048	ADNGF-50-80-PPS-A
	63	10	554268	ADNGF-63-10-P-A	574049	ADNGF-63-10-PPS-A
		15	554269	ADNGF-63-15-P-A	574050	ADNGF-63-15-PPS-A
		20	554270	ADNGF-63-20-P-A	574051	ADNGF-63-20-PPS-A
		25	554271	ADNGF-63-25-P-A	574052	ADNGF-63-25-PPS-A
		30	554272	ADNGF-63-30-P-A	574053	ADNGF-63-30-PPS-A
		40	554273	ADNGF-63-40-P-A	574054	ADNGF-63-40-PPS-A
		50	554274	ADNGF-63-50-P-A	574055	ADNGF-63-50-PPS-A
		60	554275	ADNGF-63-60-P-A	574056	ADNGF-63-60-PPS-A
	80	10	554277	ADNGF-80-10-P-A	574058	ADNGF-80-10-PPS-A
		15	554278	ADNGF-80-15-P-A	574059	ADNGF-80-15-PPS-A
		20	554279	ADNGF-80-20-P-A	574060	ADNGF-80-20-PPS-A
		25	554280	ADNGF-80-25-P-A	574061	ADNGF-80-25-PPS-A
		30	554281	ADNGF-80-30-P-A	574062	ADNGF-80-30-PPS-A
		40	554282	ADNGF-80-40-P-A	574063	ADNGF-80-40-PPS-A
		50	554283	ADNGF-80-50-P-A	574064	ADNGF-80-50-PPS-A
		60	554284	ADNGF-80-60-P-A	574065	ADNGF-80-60-PPS-A
	100	10	554286	ADNGF-100-10-P-A	–	
		15	554287	ADNGF-100-15-P-A	577225	ADNGF-100-15-PPS-A
		20	554288	ADNGF-100-20-P-A	577226	ADNGF-100-20-PPS-A
		25	554289	ADNGF-100-25-P-A	577227	ADNGF-100-25-PPS-A
		30	554290	ADNGF-100-30-P-A	577228	ADNGF-100-30-PPS-A
		40	554291	ADNGF-100-40-P-A	577229	ADNGF-100-40-PPS-A
		50	554292	ADNGF-100-50-P-A	577230	ADNGF-100-50-PPS-A
		60	554293	ADNGF-100-60-P-A	577231	ADNGF-100-60-PPS-A
		80	554294	ADNGF-100-80-P-A	577232	ADNGF-100-80-PPS-A

Bestellangaben – Produktbaukasten

Ordering table														
Size	12	16	20	25	32	40	50	63	80	100	Condi- tions	Code	Enter code	
Module no.	537123	537124	537125	537126	537127	537128	537129	537130	537131	537132				
Function	Compact cylinder, double-acting, standard hole pattern											ADNGF	ADNGF	
Size [mm]	12	16	20	25	32	40	50	63	80	100		-...		
Stroke [mm]	1 ... 200		3 ... 200		5 ... 300					5 ... 400			-...	
Cushioning	Elastic cushioning rings/plates at both ends											-P		
	–		Pneumatic cushioning, self-adjusting at both ends								[1]	-PPS		
Position sensing	Via proximity switch											-A	-A	
Hubeinstellung, advancing [mm]	0 ... 10 mm								–		[2]	-10KE		
Piston rod type	Through piston rod										[3]	-S2		
Temperature resistance	Heat-resistant seals max. 120 °C										[4]	-S6		
Captive rating plate	Laser-etched rating plate											-TL		

[1] **PPS** Not compatible with S6 minimum stroke 5 mm

[2] **10KE** Nicht mit S2, S6



[3] **S2** Minimum stroke 5 mm from size 25
Max. Hub: 250 mm

[4] **S6** Max. Hub: 250 mm

Accessories

Flange mounting FNC

Material:
Galvanised steel
RoHS-compliant



Dimensions and ordering data

Dimensions and ordering data


für ø	E	FB ø	MF	R	TF	UF	ZF	CRC ¹⁾	Weight	Part no.	Type
[mm]						±1			[g]		
12	28	5.5	8	—	40	50	48	1 - low	79	537245	FNC-12
16	29				43	55		1 - low	88	537246	FNC-16
20	36	6.6			55	70	51	1 - low	141	537247	FNC-20
25	40				60	76	53	1 - low	165	537248	FNC-25
32	45	7	10	32	64	80	60	1 - low	221	174376	FNC-32
40	54	9		36	72	90	61	1 - low	291	174377	FNC-40
50	65		12	45	90	110	65	1 - low	536	174378	FNC-50
63	75	50		100	120	69	1 - low	679	174379	FNC-63	
80	93	12	16	63	126	150	79	1 - low	1495	174380	FNC-80
100	110	14		75	150	175	92	1 - low	2041	174381	FNC-100

1) More information www.festo.com/x/topic/crc

Accessories

Schwenkflansch
SNCL/SNCL-...-R3

Material:
SNCL 12 ... 25:
Wrought aluminium alloy
SNCL 32 ... 100:
Die-cast aluminium
SNCL-...-R3:
Wrought aluminium alloy with protect-
ive coating
RoHS-compliant



+ = plus stroke length

Dimensions and ordering data								
für Ø	CD	E	EW	FL	L	MR	TG	XC
[mm]	Ø H9			±0.2				
12	6	25 _{-0.6}	12 _{H12}	16	10	6	16	56
16		27.5 _{-0.6}					18	
20	8	34.5 _{-0.6}	16 _{H12}	20	14	8	22	63
25		38.5 _{-0.6}					26	
32	10	45 _{+0.2/-0.5}	26 _{-0.2/-0.6}	22	13	10	32.5	72
40	12	54 _{-0.5}	28 _{-0.2/-0.6}	25	16	12	38	76
50		64 _{-0.6}	32 _{-0.2/-0.6}	27			46.5	
63	16	75 _{-0.6}	40 _{-0.2/-0.6}	32	21	16	56.5	89
80		93 _{-0.8}	50 _{-0.2/-0.6}	36			72	
100	20	110 _{+0.3/-0.8}	60 _{-0.2/-0.6}	41	27	20	89	117


für Ø	Basic version				R3 – High corrosion protection			
	CRC ¹⁾	Weight [g]	Part no.	Type	CRC ¹⁾	Weight [g]	Part no.	Type
[mm]								
12	2 - moderate	20	537790	SNCL-12	3 - stark	20	537794	SNCL-12-R3
16	2 - moderate	21	537791	SNCL-16	3 - stark	21	537795	SNCL-16-R3
20	2 - moderate	38	537792	SNCL-20	3 - stark	38	537796	SNCL-20-R3
25	2 - moderate	41	537793	SNCL-25	3 - stark	41	537797	SNCL-25-R3
32	1 - low	71	174404	SNCL-32	–	–	–	
40	1 - low	95	174405	SNCL-40	–	–	–	
50	1 - low	158	174406	SNCL-50	–	–	–	
63	1 - low	225	174407	SNCL-63	–	–	–	
80	1 - low	436	174408	SNCL-80	–	–	–	
100	1 - low	606	174409	SNCL-100	–	–	–	

1) More information www.festo.com/x/topic/crc

Accessories

Swivel flange
SNCS/CRSNCS/SNCS-...-R3

Material:
SNCS 32 ... 50:
Die-cast aluminium
SNCS 63 ... 100:
Wrought aluminium alloy
CRSNCS 32 ... 80:
High-alloy stainless steel
SNCS-...-R3 100:
Aluminium-Knetlegierung mit
Schutzüberzug
RoHS-compliant



Dimensions and ordering data							
für Ø	CN Ø		E		EP	EX	FL
[mm]	ADNGF-...	ADNGF-...-R3	ADNGF-...	ADNGF-...-R3	±0.2		±0.2
32	10 ^{+0.013}	10+0.015/-0.04	45+0.2/-0.5	45 _{-0.5}	10.5	14	22
40	12 ^{+0.015}	12+0.018/-0.04	54 _{-0.5}	54 _{-0.5}	12	16	25
50	16 ^{+0.015}	16+0.018/-0.04	64 _{-0.6}	64 _{-0.6}	15	21	27
63	16 ^{+0.015}	16+0.018/-0.04	74.5±0.5	75 _{-0.6}	15	21	32
80	20 ^{+0.018}	20+0.021/-0.04	92.2±0.8	93 _{-0.8}	18	25	36
100	20 ^{+0.018}	20+0.021/-0.04	109+1/-0.7	109+1/-0.7	18	25	41

für Ø	LT	MS		RA		TG	XC
		ADNGF-...	ADNGF-...-R3	ADNGF-... +1	ADNGF-...-R3 +1		
[mm]							
32	13	15 ^{+0.5}	15 ^{+0.5}	14.5	14.5	32.5	72.2
40	16	17 ^{+0.5}	17 ^{+0.5}	17.5	17.5	38	75.2
50	16	20 ^{+0.5}	20 ^{+0.5}	18.5	19	46.5	80.2
63	21	23 _{-0.5}	22 ^{+0.5}	23	23	56.5	89.2
80	22	28 _{-0.5}	27 ^{+0.5}	25	25	72	99
100	27	30±0.5	30±0.5	95	100	89	117

für Ø	Basic version				High corrosion protection			
	CRC ¹⁾	Weight [g]	Part no.	Type	CRC ¹⁾	Weight [g]	Part no.	Type
[mm]								
32	1 - low	86	174397	SNCS-32	4 - very high	161	2895920	CRSNCS-32
40	1 - low	122	174398	SNCS-40	4 - very high	239	2895921	CRSNCS-40
50	1 - low	216	174399	SNCS-50	4 - very high	403	2895922	CRSNCS-50
63	2 - moderate	281	174400	SNCS-63	4 - very high	576	2895923	CRSNCS-63
80	2 - moderate	557	174401	SNCS-80	4 - very high	1173	2895924	CRSNCS-80
100	2 - moderate	683	174402	SNCS-100	3 - stark	684	2895925	SNCS-100-R3

1) More information www.festo.com/x/topic/crc

Accessories

Clevis foot LBG/LBG-...-R3


The pivot pin is secured against rotation with a spring pin.

Material:

LBG 32 ... 63: Stainless steel casting

LBG 80 ... 100: Spheroidal graphite cast iron

LBG-...-R3: High-alloy stainless steel
RoHS-compliant



Dimensions and ordering data

für Ø [mm]	CL	CM	EK Ø	FL	GL	HB Ø	L2	LE	MR	RF	RG	S1 Ø	UK	UX
32	28	14.1	10	32	16	6.8	35	24	12	42	20	4.8	56	36
40	30	16.1	12	36	20	6.8	39	26	14	44	26	5.8	58	41.5
50	40	21.1	16	45	25	9.2	50	33	15	56	31	5.8	70	47
63	40	21.1	16	50	25	9.2	50	38	17	56	31	7.8	70	49
80	50	25.1	20	63	30	11	60	49	17	70	36	7.8	89	55
100	50	25.1	20	71	41	11	60	56	20	70	46	9.8	89	65

für Ø [mm]	Basic version				R3 – High corrosion protection			
	CRC ¹⁾	Weight [g]	Part no.	Type	CRC ¹⁾	Weight [g]	Part no.	Type
32	2 - moderate	220	31761	LBG-32	3 - stark	220	2078790	LBG-32-R3
40	2 - moderate	300	31762	LBG-40	3 - stark	300	2078792	LBG-40-R3
50	2 - moderate	540	31763	LBG-50	3 - stark	540	2078794	LBG-50-R3
63	2 - moderate	580	31764	LBG-63	3 - stark	580	2078795	LBG-63-R3
80	1 - low	1050	31765	LBG-80	3 - stark	1050	2078797	LBG-80-R3
100	1 - low	1375	31766	LBG-100	3 - stark	1375	2078799	LBG-100-R3

1) More information www.festo.com/x/topic/crc

Accessories



Multi-position kit DPNA

Material:

Flange: Wrought aluminium alloy


Screws: Galvanised steel

RoHS-compliant



Dimensions and ordering data							
für Ø [mm]	L2	B1	Max. Gesamthublänge [mm]	CRC ¹⁾	Weight [g]	Part no.	Type
12	35	13	600	2 - moderate	28	537263	DPNA-12
16	35				33	537264	DPNA-16
20	37				50	537265	DPNA-20
25	39				60	537266	DPNA-25
32	44	15	800		99	537267	DPNA-32
40	45				129	537268	DPNA-40
50	45				196	537269	DPNA-50
63	49				249	537270	DPNA-63
80	54	17	1000		474	537271	DPNA-80
100	67	19.5			712	537272	DPNA-100

1) More information www.festo.com/x/topic/crc




Note

The maximum total stroke length must not be exceeded when combining cylinders and multi-position kits.

Accessories

Schwenkflansch
SNCB/SNCB-...-R3

Material:
SNCB: Die-cast aluminium
SNCB-...-R3: Die-cast aluminium with
protective coating
RoHS-compliant



Dimensions and ordering data

für Ø	CB	E	EK Ø	FL	L	MR	TG	UB	XC
[mm]	H14		H9/e8	±0.2		-0.5		h14	
32	26	45+0.2/-0.5	10	22	13	8.5	32.5	45	72
40	28	54 _{-0.5}	12	25	16	12	38	52	76
50	32	64 _{-0.6}	12	27	16	12	46.5	60	80
63	40	75 _{-0.6}	16	32	21	16	56.5	70	89
80	50	93 _{-0.8}	16	36	22	16	72	90	99
100	60	110+0.3/-0.8	20	41	27	20	89	110	117

für Ø [mm]	Basic version				R3 – High corrosion protection			
	CRC ¹⁾	Weight [g]	Part no.	Type	CRC ¹⁾	Weight [g]	Part no.	Type
32	1 - low	103	174390	SNCB-32	3 - stark	100	176944	SNCB-32-R3
40	1 - low	155	174391	SNCB-40	3 - stark	151	176945	SNCB-40-R3
50	1 - low	233	174392	SNCB-50	3 - stark	228	176946	SNCB-50-R3
63	1 - low	375	174393	SNCB-63	3 - stark	371	176947	SNCB-63-R3
80	1 - low	636	174394	SNCB-80	3 - stark	632	176948	SNCB-80-R3
100	1 - low	1035	174395	SNCB-100	3 - stark	986	176949	SNCB-100-R3

1) More information www.festo.com/x/topic/crc

Accessories


Trunnion flange ZNCF/CRZNG

Material:

ZNCF: Stainless steel casting

CRZNG: Electropolished stainless steel casting

RoHS-compliant



Dimensions and ordering data									
für Ø	C2)	C3)	TD Ø e9	TK	TL	TM	US	XH	XL
[mm]									
32	71	86	12	16	12	50	45	2	52
40	87	105	16	20	16	63	54	4	55
50	99	117	16	24	16	75	64	4	57
63	116	136	20	24	20	90	75	4	61
80	136	156	20	28	20	110	93	5	81
100	164	189	25	38	25	132	110	10	86



für Ø [mm]	Basic version				R3 – High corrosion protection			
	CRC ¹⁾	Weight [g]	Part no.	Type	CRC ¹⁾	Weight [g]	Part no.	Type
32	2 - moderate	150	174411	ZNCF-32	4 - very high	150	161852	CRZNG-32
40	2 - moderate	285	174412	ZNCF-40	4 - very high	285	161853	CRZNG-40
50	2 - moderate	473	174413	ZNCF-50	4 - very high	473	161854	CRZNG-50
63	2 - moderate	687	174414	ZNCF-63	4 - very high	687	161855	CRZNG-63
80	2 - moderate	1296	174415	ZNCF-80	4 - very high	1296	161856	CRZNG-80
100	2 - moderate	2254	174416	ZNCF-100	4 - very high	2254	161857	CRZNG-100

1) More information www.festo.com/x/topic/crc

Accessories

Trunnion support LNZZ


Werkstoff:
Lagerstück: Aluminium, eloxiert
Plain bearing: Plastic
RoHS-compliant



Dimensions and ordering data																
für Ø	CR	DA	FK	FN	FS	H1	HB	KE	NH	TH	UL	CRC ¹⁾	Weight	Part no.	Type	
[mm]	Ø D11	Ø H13	Ø ±0.1				Ø H13			±0.2			[g]			
32	12	11	15	30	10.5	15	6.6	6.8	18	32	46	2 - moderate	83	32959	LNZZ-32	
40, 50	16	15	18	36	12	18	9	9	21	36	55	2 - moderate	129	32960	LNZZ-40/50	
63, 80	20	18	20	40	13	20	11	11	23	42	65	2 - moderate	178	32961	LNZZ-63/80	
100	25	20	25	50	16	24.5	14	13	28.5	50	75	2 - moderate	306	32962	LNZZ-100/125	

1) More information www.festo.com/x/topic/crc

Accessories

Ordering data – One-way flow control valves			Datenblätter → Internet: grl		
	Connection		Material	Part no.	Type
	für Ø	für Schlauch-Außen-Ø			
For exhaust air					
	12, 16, 20, 25	3	Metal design	193137	GRLA-M5-QS-3-D
		4		193138	GRLA-M5-QS-4-D
		6		193139	GRLA-M5-QS-6-D
	32, 40, 50, 63, 80, 100	3		193142	GRLA-1/8-QS-3-D
		4		193143	GRLA-1/8-QS-4-D
		6		193144	GRLA-1/8-QS-6-D
		8		193145	GRLA-1/8-QS-8-D
For supply air					
	12, 16, 20, 25	3	Metal design	193153	GRLZ-M5-QS-3-D
		4		193154	GRLZ-M5-QS-4-D
		6		193155	GRLZ-M5-QS-6-D
	32, 40, 50, 63, 80, 100	3		193156	GRLZ-1/8-QS-3-D
		4		193157	GRLZ-1/8-QS-4-D
		6		193158	GRLZ-1/8-QS-6-D
		8		193159	GRLZ-1/8-QS-8-D

Accessories

Ordering data – Proximity switch for T-slot, magneto-resistive

Datenblätter → Internet: smt


Accessing data	Type of mounting	Switching out-put	Electrical connection	Cable length [m]	Part no.	Type
N/O						
	Inserted in the slot from above, flush with the cylinder profile, short design	PNP	Cable, 3-core	2.5	574335	SMT-8M-A-PS-24V-E-2.5-OE
			Plug M8x1, 3-pin	0.3	574334	SMT-8M-A-PS-24V-E-0.3-M8D
			1x M12 plug, 3-pin	0.3	574337	SMT-8M-A-PS-24V-E-0.3-M12
		NPN	Cable, 3-core	2.5	574338	SMT-8M-A-NS-24V-E-2.5-OE
			1x M8 plug, 3-pin	0.3	574339	SMT-8M-A-NS-24V-E-0.3-M8D
N/C						
	Inserted in the slot from above, flush with the cylinder profile, short design	PNP	Cable, 3-core	7.5	574340	SMT-8M-A-PO-24V-E-7.5-OE

Ordering data – Proximity switch for T-slot, magnetic reed


Datenblätter → Internet: sme

Ordering data	Proximity switch for 1 slot, magnetic reed	Type of mounting	Switching output	Electrical connection	Cable length [m]	Part no.	Type
N/O							
	Inserted in the slot from above, flush with the cylinder profile	Contacting	Cable, 3-core	2.5	543862	SME-8M-DS-24V-K-2.5-OE	
				5.0	543863	SME-8M-DS-24V-K-5.0-OE	
			Cable, 2-core	2.5	543872	SME-8M-ZS-24V-K-2.5-OE	
			Plug M8x1, 3-pin	0.3	543861	SME-8M-DS-24V-K-0.3-M8D	
	Inserted in the slot lengthwise, flush with the cylinder profile	Contacting	Cable, 3-core	2.5	150855	SME-8-K-LED-24	
			Plug M8x1, 3-pin	0.3	150857	SME-8-S-LED-24	
N/C							
	Inserted in the slot lengthwise, flush with the cylinder profile	Contacting	Cable, 3-core	7.5	160251	SME-8-O-K-LED-24	

Connecting cables NEBA, straight, M8 connection


	Electrical connection 1, connection technology	Electrical connection 2, connection technology	Electrical connection 2, number of pins/cores	Cable length	Part no.	Type
	M8x1 A-coded to EN 61076-2-104	Open end	3	2.5 m	8078223	NEBA-M8G3-U-2.5-N-LE3
				5 m	8078224	NEBA-M8G3-U-5-N-LE3

Connecting cables NEBA, straight, M12 connection


	Electrical connection 1, connection technology	Electrical connection 2, connection technology	Electrical connection 2, number of pins/cores	Cable length	Part no.	Type
	M12x1, A-coded to EN 61076-2-101	Open end	3	2.5 m	8078236	NEBA-M12G5-U-2.5-N-LE3
				5 m	8078237	NEBA-M12G5-U-5-N-LE3

Accessories

Connecting cables NEBA, angled, M8 connection

	Electrical connection 1, connection technology	Electrical connection 2, connection technology	Electrical connection 2, number of pins/cores	Cable length	Part no.	Type
	M8x1 A-coded to EN 61076-2-104	Open end	3	2.5 m	8078230	NEBA-M8W3-U-2.5-N-LE3
				5 m	8078231	NEBA-M8W3-U-5-N-LE3

Connecting cables NEBA, angled, M12 connection

	Electrical connection 1, connection technology	Electrical connection 2, connection technology	Electrical connection 2, number of pins/cores	Cable length	Part no.	Type
	M12x1, A-coded to EN 61076-2-101	Open end	3	2.5 m	8078245	NEBA-M12W5-U-2.5-N-LE3
				5 m	8078246	NEBA-M12W5-U-5-N-LE3

Ordering data – Proximity switch, cuboid shape, pneumatic

Datenblätter → Internet: smpo

	Pneumatic port	Part no.	Type
3/2-way valve, normally closed			
	Female thread M5	178563	SMPO-8E

Ordering data – Mounting kit for proximity switch SMPO-8E

Datenblätter → Internet: smb

	Mounting	Part no.	Type
	Clamped in T-slot	178230	SMB-8E

Ordering data – Slot cover for T-slot

	Mounting	Length	Part no.	Type
	Insertable	2x 0.5 m	151680	ABP-5-S