

Proximity switch SMEO-1

FESTO



Type code

001	Series	
SMEO-1	Proximity switch, block design, magnetic, reed	
002	Temperature range	
S6	Heat-resistant seals max. 120 °C	
003	Electrical connection, cable length	
S	Plug M8x1 with cable, 0.3 m	
K5	Cable, 5.0 m	

004	Switching status indication	
	None	
LED	Yellow LED	
005	Rated operating voltage	
24	24 V DC	
230	230 V AC	
006	Generation	
B	Series B	
C	Series C	

Datasheet

General technical data

Design	Block design
Mounting position	optional
Based on standard	–
Approval	RCM trademark
CE mark (see declaration of conformity)	To EU EMC Directive, To EU Low Voltage Directive, In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC, To UK RoHS instructions, To UK regulations for electrical equipment
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364-B2-L

Input signal/measuring element

Measured variable	Position
Measuring principle	Magnetic reed
Ambient temperature	-50 ... 120°C
Ambient temperature with moving cable	-40 ... 120°C

Switching output

Switching output	Contacting, bipolar	
Switching element function	N/O contact	
Hysteresis	–	
Repetition accuracy	0.2 mm	
Switch-on time	0.5 ms	≤0.5 ms
Switch-off time	0.03 ms	–
Max. switching frequency	500 Hz	
Max. output current	1 A	
Max. switching capacity DC	27 ... 40 W	27 W
Voltage drop	≤4.5 V	–
Inductive protective circuit	–	

Output, further data

Short circuit current rating	no
Overload protection	Not available

Electronics

Operational voltage range DC	0 ... 200 V
Residual ripple	–
Reverse polarity protection	no

Datasheet

Electromechanics

Electrical connection 1, connection type	Cable	Plugs
Electrical connection 1, function	Switching output, Power supply	
Electrical connection 1, connector system	Open end	M8x1, A-coded, to EN 61076-2-104
Electrical connection 1, number of connections/cores	2, 3	3
Electrical connection 1, used connections/cores	2, 3	
Electrical connection 1, type of mounting	–	Snap-locking, Screw-type lock, Not rotatable
Electrical connection 1, compatible type of mounting	–	Compatible with latching lock, Compatible with rotatable screw-type lock
Connection outlet orientation	In-line	
Cable length	2.5 ... 5 m	–
Cable characteristic	–	
Cable sheath colour	Grey	–
Material cable sheath	PVC, TPE-S, TPE-U(PUR)	–
Material insulating sheath	–	
Wire ends	–	

Display/operation

Switching status indication	Yellow LED
-----------------------------	------------

Mechanics

Electrical connection 1, connection type	Cable	Plugs
Type of mounting	With accessories	
Product weight	85 ... 130 g	20 g
Material housing	Epoxy resin, PC, PET, Reinforced PET, Steel, TPE-O, Die-cast zinc	Epoxy resin, PET, Steel, Die-cast zinc
Housing colour	Black	


Immission/Emission

Degree of protection	IP67
Corrosion resistance class CRC ¹⁾	1 - Low corrosion stress

¹⁾ More information www.festo.com/x/topic/kbk

Dimensions

Dimensions – SMEO-1 – cable


 Download CAD data www.festo.com


- [1] Connecting cable
[2] Yellow light emitting diode

	B1	B2	D1 Ø	D2	H1	H2	L2	L3
	-0,2	±0,3	+0,3		±0,2	±0,1	±0,2	-0,1
SMEO-1-S6-C	16	14	4,2	M4	15,5	8,5	34	17
SMEO-1-B								
SMEO-1-LED-24-K5-B								
SMEO-1-LED-230-B								
SMEO-1-LED-230-K5-B								
SMEO-1-LED-24-B								

Dimensions


Dimensions – SMEO-1-S – plug M8x1 Download CAD data www.festo.com



	B1 -0,2	B2 ±0,3	B3	D2	H1 ±0,2	H2 ±0,1	L1 ±0,2	L2 ±0,2	L3 -0,1	L4
SMEO-1-S-LED-24-B	16	14	~27,5	M4	15,5	8,5	42	34	17	~54,5
SMEO-1-S-24-B										

Dimensions

Dimensions – Mounting kit SMB-1


[Download CAD data](http://www.festo.com) www.festo.com


[1] Proximity switch SMEO, SMT0, SMPO-1

		B1	D1 Ø	H1	L1
SMB-1	32 ... 100	9	6	15,5	34

Dimensions


Dimensions – Mounting kit SMB-2-B/SMB-3-B Download CAD data www.festo.com



		B1	B2	H1	H2	L1	L2
SMB-2-B	32 ... 50	18	11	23	11,6	34	22
SMB-3-B	63 ... 100	26,8	13,7	26	10,8	34	22

Dimensions

Dimensions – Mounting kit SMBU

[Download CAD data](http://www.festo.com)


[1] Proximity switch SMEO, SMT0, SMPO-1


		B1	B2	H1	L1	L2
SMBU-1-B	32 ... 50	19	8,5	30	34	22
SMBU-2-B	63 ... 100	31	13,5	34	34	22
SMBU-3-B	125	31	13,5	37	34	22

Ordering data

Ordering data								
	Electrical connection 1, connection type	Electrical connection 1, number of connections/cores	Switching output	Cable length	Part no.	Type		
	Cable	2	Contacting, bipolar	2.5 m	30457	SMEO-1-B		
					151673	SMEO-1-S6-C		
					151671	SMEO-1-LED-230-B		
				5 m	160998	SMEO-1-LED-230-K5-B		
		3	NPN	2.5 m	151684	SMTO-1-NS-K-LED-24-C		
					151683	SMTO-1-PS-K-LED-24-C		
					30459	SMEO-1-LED-24-B		
			Contacting, bipolar	5 m	151672	SMEO-1-LED-24-K5-B		
				Plugs	NPN		151686	SMTO-1-NS-S-LED-24-C
							151685	SMTO-1-PS-S-LED-24-C
	150847	SMEO-1-S-24-B						
	PNP		150848		SMEO-1-S-LED-24-B			

Peripherals

Peripherals overview



Accessories			→ Link
Type/order code	Description		
[1]	Connecting cable NEBA, socket, M8x1, 3-pin, angled	Angled socket, M8x1, 3-pin	13
[2]	Connecting cable NEBA, socket M8x1, 3-pin, straight	Straight socket, M8x1 3-pin	13
[3]	Proximity switch SMEO-1, magnetic reed, with cable	Magnetic reed, with cable	smeo-1
[3]	Proximity switch SMEO-1, magnetic reed, with plug M8x1	Magnetic reed, with plug M8x1	smeo-1
[4]	Mounting kit SMB-1	• For drives with Ø 6 mm tie rod or mounting strip • For standards-based cylinder DSBG	13
[5]	Standards-based cylinder DSBG	Ø 32 ... 125 mm	-
[6]	Flat cylinder DZH	Ø 32 ... 63 mm	-
[7]	Standards-based cylinder	Ø 32 ... 125 mm	-


Peripherals


Accessories		→ Link
Type/order code	Description	
[8] Mounting kit SMBU	For standards-based cylinder DNU	13
[9] Mounting kit SMB-2-B, SMB-3-B	For standards-based cylinder DSBC	13
[10] Standards-based cylinder DSBG	Ø 32 ... 125 mm	↗


Accessories

Connecting cable NEBA, socket M8x1, 3-pin, angled						
	Connection technology left, field device side	Electrical connection 1, cable outlet	Connection technology right, controller side	Cable length	Part no.	Type
	Socket M8x1 A-coded, EN 61076-2-104	Angled	Open end	2.5 m	8078230	NEBA-M8W3-U-2.5-N-LE3
				5 m	8078231	NEBA-M8W3-U-5-N-LE3

Connecting cable NEBA, socket M8x1, 3-pin, straight						
	Connection technology left, field device side	Electrical connection 1, cable outlet	Connection technology right, controller side	Cable length	Part no.	Type
	Socket M8x1 A-coded, EN 61076-2-104	Straight	Open end	2.5 m	8078223	NEBA-M8G3-U-2.5-N-LE3
				5 m	8078224	NEBA-M8G3-U-5-N-LE3

Mounting kit SMB-1				
	Size	RoHS status	Part no.	Type
	1	RoHS compliant without exemption	11886	SMB-1

Mounting kit SMB-2-B, SMB-3-B				
	Size	RoHS status	Part no.	Type
	2	RoHS compliant without exemption	36162	SMB-2-B
	3		36163	SMB-3-B

Mounting kit SMBU				
	Size	RoHS status	Part no.	Type
	1	RoHS compliant without exemption	36173	SMBU-1-B
	2		36174	SMBU-2-B
	3		152828	SMBU-3-B