


Ball valve actuator unit VZBC

FESTO



Characteristics

At a glance

- Electric or pneumatic actuation
- Flange hole pattern according to ISO 5211
- Connection pattern to NAMUR VDI/VDE 3845
- Corrosion-resistant and acid-resistant versions
- Versions with ATEX certification
- Combination of a pneumatic quarter-turn actuator and a ball valve
- The flow is fully opened or closed in both directions
- Sensor boxes or limit switches for sensing the end positions can be mounted directly on the actuator unit

Design type

- 2-way ball valve actuator units made of stainless steel or brass with pipe thread or with weld ends
- 2-way ball valve actuator units made of stainless steel in compact design

Type code

001	Series	
VZBC	Ball valve	
002	Nominal diameter DN	
15	15 mm	
20	20 mm	
25	25 mm	
32	32 mm	
40	40 mm	
50	50 mm	
65	65 mm	
80	80 mm	
100	100 mm	
003	Process valve connection type 1	
F	Pipe fitting to DIN 2633/DIN 2501	
004	Process valve connection type 2	
F	Pipe fitting to DIN 2633/DIN 2501	
005	Nominal pressure [bar]	
16	16	
40	40	
006	Valve function	
22	2/2-way	
007	Flanged connection	
F0304	Hole pattern 03 and 04	
F0405	Hole pattern 04 and 05	
F0507	Hole pattern 05 and 07	
F07	Hole pattern 07	
F0710	Hole pattern 07 and 10	
008	Housing material	
V4	Stainless steel (chrome-nickel-molybdenum, austenitic/1.4401, 1.4404 (AISI 316L), 1.4408)	

009	Shut-off element material	
V4	Stainless steel (chrome-nickel-molybdenum, austenitic/1.4401, 1.4404 (AISI 316L), 1.4408)	
010	Sealant	
T	PTFE	
011	Drive	
PP	DAPS, double-acting	
PS	DAPS, single-acting	
012	Torque [Nm]	
15	15	
30	30	
53	53	
60	60	
90	90	
106	106	
180	180	
240	240	
013	Swivel direction	
R	Right	
014	Nominal swivel angle [°]	
90	90	
015	Spring ID	
	None	
4	4	
016	End-position adjustment	
C	Closing	

Datasheet

General technical data, 2-way

Nominal size DN	15	20	25	32	40	50	65	80	100
Type of mounting	In-line installation								
Mounting position	optional								
Design	2-way ball valve, Semi-rotary drive								
Type of actuation	Pneumatic								
Switching position indicator	Slot direction = flow direction								
Nominal pressure PN	40						16		
Flow rate Kv	19.4 m³/h	45.6 m³/h	71.5 m³/h	105 m³/h	170 m³/h	275 m³/h	507 m³/h	905 m³/h	1,414 m³/h

Operating and environmental conditions, 2-way

Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Operating pressure	6 ... 8.4 bar
Ambient temperature	-10 ... 80°C
Media temperature ¹⁾	-10 ... 200°C
Medium	Compressed air to ISO 8573-1:2010 [:-:-], Inert gases, Water – no water vapour, Neutral fluids
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC ²⁾	3 - high corrosion stress

1) As a function of operating pressure

2) Corrosion resistance class CRC 3 to Festo standard FN 940070 High corrosion stress. Outdoor exposure under moderate corrosive conditions. External visible parts with primarily functional surface requirements that are in direct contact with a normal industrial atmosphere.

ATEX, 2-way


Max. surface temperature assembly	TX
explosion group assembly	IIC, IIIC
Explosion ambient temperature	-10°C ≤ Ta ≤ +60°C

Materials, 2-way

Material housing	High-alloy stainless steel
Material number housing	1.4408
Material ball	High-alloy stainless steel
Material shaft	High-alloy stainless steel
Material number shaft	1.4401
Material seals	PTFE, PTFE reinforced
Note on materials	RoHS-compliant

Dimensions


Dimensions – 2-way, stainless steel, DAPS, double-acting

Download CAD data www.festo.com

	B1	D1 ø	H1	H2	H3	L1	L2	⌀ 2
VZBC-15-FF-40-22-F0304-V4V4T-PP15-R-90-C	52,2	15	112,2	88	20	159	40	8
VZBC-20-FF-40-22-F0304-V4V4T-PP30-R-90-C	59,2	20	123,5	95,8	20	174	44	9
VZBC-25-FF-40-22-F0405-V4V4T-PP30-R-90-C	59,2	25	123,8	96,1	20	174	53	9
VZBC-32-FF-40-22-F0405-V4V4T-PP60-R-90-C	70,4	32	139,4	106,7	20	198	58,4	10
VZBC-40-FF-40-22-F0507-V4V4T-PP60-R-90-C	70,4	38	146,7	114	20	198	62	10
VZBC-50-FF-40-22-F0507-V4V4T-PP106-R-90-C	83,3	50	168,8	130,3	20	237,1	78	12
VZBC-65-FF-16-22-F07-V4V4T-PP180-R-90-C	107,5	64	212,5	161,5	30	289,9	100	15
VZBC-80-FF-16-22-F07-V4V4T-PP180-R-90-C	107,5	76	229,5	178,5	30	289,9	120	15
VZBC-100-FF-16-22-F0710-V4V4T-PP240-R-90-C	111,1	96	243,1	192,1	30	313,6	152	15


Dimensions


Dimensions – 2-way, stainless steel, DAPS, single-acting

Download CAD data www.festo.com


	B1	D1 Ø	H1	H2	H3	L1	L2	$\varnothing 2$
VZBC-15-FF-40-22-F0304-V4V4T-PS15-R-90-4-C	59,2	15	119,2	91,5	20	233,3	40	9
VZBC-20-FF-40-22-F0304-V4V4T-PS30-R-90-4-C	70,4	20	134,7	102	20	259	44	10
VZBC-25-FF-40-22-F0405-V4V4T-PS30-R-90-4-C	70,4	25	135	102,3	20	259	53	10
VZBC-32-FF-40-22-F0405-V4V4T-PS53-R-90-4-C	83,3	32	152,3	113,8	20	304,3	58,4	12
VZBC-40-FF-40-22-F0507-V4V4T-PS53-R-90-4-C	83,3	38	159,6	121,1	20	304,3	62	12
VZBC-50-FF-40-22-F0507-V4V4T-PS90-R-90-4-C	107,5	50	193	142	30	393,7	78	15
VZBC-65-FF-16-22-F07-V4V4T-PS180-R-90-4-C	118	64	223	167	30	474	100	19
VZBC-80-FF-16-22-F07-V4V4T-PS180-R-90-4-C	118	76	241	185	30	474	120	19
VZBC-100-FF-16-22-F0710-V4V4T-PS240-R-90-4-C	134,9	96	266,9	204,9	30	520,5	152	19


Ordering data

DAPS double-acting			
	Nominal size DN	Part no.	Type
	15	1913365	VZBC-15-FF-40-22-F0304-V4V4T-PP15-R-90-C
	20	1913367	VZBC-20-FF-40-22-F0304-V4V4T-PP30-R-90-C
	25	1913368	VZBC-25-FF-40-22-F0405-V4V4T-PP30-R-90-C
	32	1913369	VZBC-32-FF-40-22-F0405-V4V4T-PP60-R-90-C
	40	1913370	VZBC-40-FF-40-22-F0507-V4V4T-PP60-R-90-C
	50	1913371	VZBC-50-FF-40-22-F0507-V4V4T-PP106-R-90-C
	65	1913372	VZBC-65-FF-16-22-F07-V4V4T-PP180-R-90-C
	80	1913373	VZBC-80-FF-16-22-F07-V4V4T-PP180-R-90-C
	100	1913374	VZBC-100-FF-16-22-F0710-V4V4T-PP240-R-90-C

DAPS single-acting			
	Nominal size DN	Part no.	Type
	15	1915401	VZBC-15-FF-40-22-F0304-V4V4T-PS15-R-90-4-C
	20	1915402	VZBC-20-FF-40-22-F0304-V4V4T-PS30-R-90-4-C
	25	1915403	VZBC-25-FF-40-22-F0405-V4V4T-PS30-R-90-4-C
	32	1915404	VZBC-32-FF-40-22-F0405-V4V4T-PS53-R-90-4-C
	40	1915406	VZBC-40-FF-40-22-F0507-V4V4T-PS53-R-90-4-C
	50	1915407	VZBC-50-FF-40-22-F0507-V4V4T-PS90-R-90-4-C
	65	1915408	VZBC-65-FF-16-22-F07-V4V4T-PS180-R-90-4-C
	80	1915409	VZBC-80-FF-16-22-F07-V4V4T-PS180-R-90-4-C
	100	1915410	VZBC-100-FF-16-22-F0710-V4V4T-PS240-R-90-4-C

Peripherals

Peripherals overview



Accessories			→ Link
Type/order code	Description		
[1] Ball valve actuator unit VZBC	Combination of double-acting or single-acting quarter-turn actuator DAPS and 2-way ball valve, stainless steel, compact design		vzbc
[2] Positioner CMSX	For controlling the position of quarter-turn actuators in process automation systems		cmsx
[3] Sensor boxes SRBG	For electrical feedback and position monitoring of process valves actuated by quarter turn actuators		srbg
[4] Limit switch box SRBK	SRBK-CA4-... Variants with pre-assembled position		srbk
[5] Sensor boxes SRBC	For electrical feedback and position monitoring of process valves actuated by quarter turn actuators		srbc
[6] Solenoid valve NVF3	For F solenoid coil and explosion-proof F solenoid coil		nvf3
[7] Solenoid valves VSNC	For single-acting and double-acting quarter turn actuators with a connection pattern to VDI/VDE 3845		vsnc
[8] Solenoid valves VOFC	Solenoid valve with solenoid coil, NAMUR connection pattern		vofc

Peripherals

Accessories		→ Link
Type/order code	Description	
[9] Solenoid valves VOFD	Solenoid valve with solenoid coil, NAMUR connection pattern	vofd