


Proximity switch SME-10M

FESTO



Type code

001	Series	
SME	Proximity sensor	
002	Design type	
10	For round slot	
003	Sensor version	
M	Inserted in the slot from above	
004	Switching output	
DS	3-wire N/O contact	
ZS	2-wire N/O contact	
005	Rated operating voltage	
24	24 V DC	
006	Cable characteristic	
	None	
E	Suitable for energy chains/robots	

007	Cable length [m]	
	0.2 ... 10 m	
0,3	0.3 m	
2,5	2.5 m	
008	Display	
L	LED	
009	Cable outlet	
L	Longitudinal	
010	Cable identification	
	With label holder	
N	Without label holder	
011	Connection technology	
OE	Open end	
M8	M8, snap-on flange	
M8D	M8, rotatable thread	
M12	M12, rotatable thread	

Datasheet

General technical data

Design	For C-slot
Mounting position	optional
Conforms to standard	EN 60947-5-2
Approval	RCM trademark
Instructions on use	https://www.festo.com/Drive-Sensor-Overview
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC, To UK RoHS instructions
Note on materials	RoHS-compliant Free of halogen
LABS (PWIS) conformity	VDMA24364-B2-L

Input signal/measuring element

Measured variable	Position
Measuring principle	Magnetic reed
Ambient temperature	-40 ... 70°C

Switching output

Switching output	3-wire N/O contact [DS]	2-wire N/O contact [ZS]
Switching output	Contacting, bipolar	
Switching element function	N/O contact	
Repetition accuracy	0.2 mm	
Switch-on time	≤1.2 ms	
Switch-off time	≤1 ms	
Max. output current	300 mA	100 mA
Max. switching frequency	50 Hz	
Max. switching capacity DC	9 W	3 W
Voltage drop	≤1.5 V	≤4.5 V

Output, further data

Short circuit current rating	no
Overload protection	No

Electronics

Operational voltage range DC	5 ... 30 V
Operational voltage range AC	5 ... 30 V
Reverse polarity protection	Bipolar, no
Switching status indication	Yellow LED

Electromechanics

Electrical connection 1, connection type	Cable	Cable with plug	
Switching output	3-wire N/O contact [DS]	2-wire N/O contact [ZS]	3-wire N/O contact [DS]
Electrical connection 1, function	Switching output, Power supply	Switching output	Switching output, Power supply
Electrical connection 1, number of connections/cores	3	2	3
Electrical connection 1, used connections/cores	3	2	3
Connection outlet orientation	In-line		
Cable length	2.5 m	0.3 m	
Material cable sheath	TPE-U(PUR)		
Electrical connection 1, connector system	Open end		M8x1, A-coded, to EN 61076-2-104

Datasheet

Mechanics

Electrical connection 1, connector system	M8x1, A-coded, to EN 61076-2-104	Open end
Electrical connection 1, type of mounting	Screw-type lock, Rotatable	–
Electrical connection 1, compatible type of mounting	Compatible with rotatable/non-rotatable screw-type lock	–
Type of mounting	Screw-clamped, Insertable in the slot from above	
Material housing	PA-reinforced High-alloy stainless steel	
Corrosion resistance class CRC	2 - Moderate corrosion stress	3 - high corrosion stress

Display/operation

Switching status indication	Yellow LED
-----------------------------	------------


Immission/emission

Ambient temperature with moving cable	-20 ... 70°C
Degree of protection	IP65, IP68

Dimensions

Dimensions – SME-10M-...-L, connection outlet direction lengthways

Download CAD data www.festo.com




- [1] Yellow light emitting diode
- [2] SME-10M
- [3] Inscription label holder
- [4] Connecting cables
- [5] Cable open end
- [6] Plug M8x1, snap collar
- [7] Plug M8x1, rotatable thread
- [8] Plug M12x1
- [9] L1 cable length

	B1	D1	D2	D3	H1	L2	L3	L4	L5	L6	L7	⌀
SME-10M-...-OE	3	2,15	-	-	4,6	50	26,6	24,6	23	50	7	1,5
SME-10M-...-M8D			M8x1	8,5		-						
SME-10M-...-M8			M8x1	9,6		-						
SME-10M-...-M12			M12x1	15		-						

Dimensions

Dimensions – Mounting SMBN-10


Download CAD data www.festo.com



	D1	B1	H1	L1	$\varnothing 1$
SMBN-10	M3	9,3	8,6	19	1,5

Dimensions


Dimensions – Positioning element SMM

Download CAD data www.festo.com

	B1	D1	H1	H2	L1	∅1
SMM-10	3,75	3,0	12,23	7,6	4,0	1,5


Ordering data

Ordering data					
	Electrical connection 1, connector system	Cable length	Product weight	Part no.	Type
	M8x1, A-coded, to EN 61076-2-104	0.3 m	6.7 g	551367	SME-10M-DS-24V-E-0,3-L-M8D
	Open end	2.5 m	14.6 g	551369	SME-10M-ZS-24V-E-2,5-L-OE
			16.8 g	551365	SME-10M-DS-24V-E-2,5-L-OE

Modular product system – ordering information					
	Design	Switching output	Switching element function	Part no.	Type
	For C-slot	Contacting, bipolar	N/O contact	551364	SME-10M


Peripherals

Peripherals overview



Accessories			→ Link
Type/order code	Description		
[1]	Proximity switch SMT-10G-...-OE	Can be inserted into the slot from above, flush with the cylinder profile, with cable	sme-10
[2]	Connecting cable NEBA-M8	Straight socket	10
[3]	Connecting cable NEBA-M8	Angled socket	10
[4]	Proximity switch SMT-10G-...-M...	Can be inserted into the slot from above, flush with the cylinder profile, with cable and plug	sme-10
[5]	Drives with round slot	–	–
[6]	Mounting kit SMBN-10	For mounting proximity switches on drives with T-slot	10
[7]	Drives with T-slot	–	–
[8]	Round cylinder	–	–
[9]	Semi-rotary drive DSM	–	dsm
[10]	Mounting kit WSM-...-SME-10	Mounting kit for mounting proximity switches on semi-rotary drive DSM	10


Accessories

Mounting SMBN-10					
	Size	Design	Material housing	Part no.	Type
	10	For T-slot	Wrought aluminium alloy, Anodised	537809	SMBN-10

Positioning element SMM					
	Size	Design	Material housing	Part no.	Type
	10	For C-slot	Wrought aluminium alloy, Anodised	547942	SMM-10

Connecting cable M8x1, straight socket					
	Cable structure	Cable length	Product weight	Part no.	Type
	3 x 0.25 mm ²	2.5 m	50 g	8078223	NEBA-M8G3-U-2.5-N-LE3
		5 m	96 g	8078224	NEBA-M8G3-U-5-N-LE3

Connecting cable M8x1, angled socket					
	Cable structure	Cable length	Product weight	Part no.	Type
	3 x 0.25 mm ²	2.5 m	50 g	8078230	NEBA-M8W3-U-2.5-N-LE3
		5 m	96 g	8078231	NEBA-M8W3-U-5-N-LE3

Mounting kit SMBN-10					
	Size	Part no.	Type		
	10	537809	SMBN-10		

Mounting kit for semi-rotary drive DSM					
	Size	Part no.	Type		
	6	173205	WSM-6-SME-10		
	8	173206	WSM-8-SME-10		
	10	173207	WSM-10-SME-10		