


# ISO cylinder DSBC-100-400-PPSA-N3

Part number: 1384900

**FESTO**



## Data sheet

| Feature                                                      | Value                                                                                      |
|--------------------------------------------------------------|--------------------------------------------------------------------------------------------|
| Stroke                                                       | 400 mm                                                                                     |
| Piston diameter                                              | 100 mm                                                                                     |
| Piston rod thread                                            | M20x1.5                                                                                    |
| Cushioning                                                   | Self-adjusting pneumatic end-position cushioning                                           |
| Mounting position                                            | optional                                                                                   |
| Conforms to standard                                         | ISO 15552                                                                                  |
| Piston-rod end                                               | Male thread                                                                                |
| Design                                                       | Piston<br>Piston rod<br>Profile barrel                                                     |
| Position detection                                           | Via proximity switch                                                                       |
| Variants                                                     | Piston rod at one end                                                                      |
| Operating pressure                                           | 0.04 MPa...1.2 MPa<br>0.4 bar...12 bar                                                     |
| Mode of operation                                            | Double-acting                                                                              |
| Operating medium                                             | Compressed air to ISO 8573-1:2010 [7:4:4]                                                  |
| Note on operating and pilot medium                           | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC                               | 2 - Moderate corrosion stress                                                              |
| LABS (PWIS) conformity                                       | VDMA24364-B1/B2-L                                                                          |
| Ambient temperature                                          | -20 °C...80 °C                                                                             |
| Impact energy in end positions                               | 2.5 J                                                                                      |
| Cushioning length                                            | 31 mm                                                                                      |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke  | 4418 N                                                                                     |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 4712 N                                                                                     |
| Moving mass                                                  | 2560 g                                                                                     |
| Moving mass for 0 mm stroke                                  | 1000 g                                                                                     |
| Additional moving mass per 10 mm stroke                      | 39 g                                                                                       |
| Product weight                                               | 7705 g                                                                                     |
| Basic weight for 0 mm stroke                                 | 3665 g                                                                                     |
| Additional weight per 10 mm stroke                           | 101 g                                                                                      |

| Feature                     | Value                                            |
|-----------------------------|--------------------------------------------------|
| Type of mounting            | Either:<br>Via female thread<br>With accessories |
| Pneumatic connection        | G1/2                                             |
| Note on materials           | RoHS-compliant                                   |
| Material cover              | Coated die-cast aluminium                        |
| Material piston seal        | TPE-U(PU)                                        |
| Material piston             | Wrought aluminium alloy                          |
| Material piston rod         | High-alloy steel                                 |
| Material piston rod wiper   | TPE-U(PU)                                        |
| Buffer seal material        | TPE-U(PU)                                        |
| Material of cushioning boss | POM                                              |
| Material cylinder barrel    | Smooth-anodised wrought aluminium alloy          |
| Material nut                | Galvanised steel                                 |
| Material bearing            | POM                                              |
| Material collar screws      | Galvanised steel                                 |