

Radial gripper HGR-40-A



Part number: 161832

FESTO

Self-centring, can be used as internal and external gripper, 182° opening angle, with facility for proximity position sensing.

Minimum operating pressure is increased to as high as > 4 bar in the event of increased device temperature.

Products to be discontinued. Available until 2011.



Data sheet

Feature	Value
Size	40
Max. replacement accuracy	0.2 mm
Max. opening angle	180 deg
Repetition accuracy, gripper	≤ 0.1 mm
Number of gripper fingers	2
Mode of operation	double-acting
Gripper function	radial
Design structure	Rack and pinion
Position detection	For proximity sensor
Operating pressure	2 ... 8 bar
Max. operating frequency of gripper	4 Hz
Min. opening time at 6 bar	105 ms
Min. closing time at 6 bar	100 ms
Operating medium	Filtered compressed air
Corrosion resistance classification CRC	2
Ambient temperature	5 ... 60 °C
Total gripping torque at 6 bar, opening	600 Ncm
Total gripping torque at 6 bar, closing	500 Ncm
Max. force on gripper jaw Fz static	83 N
Max. torque at gripper Mx static	1.9 Nm
Max. torque at gripper My static	9.9 Nm
Max. torque at gripper Mz static	6.7 Nm
Product weight	710 g
Mounting type	with internal (female) thread
Pneumatic connection	G1/8
Materials note	Free of copper and PTFE
Materials information for cover cap	POM
Materials information, housing	Wrought Aluminium alloy Hard anodised
Materials information for gripper jaws	Wrought Aluminium alloy Hard anodised