

# Compact cylinder AEVULQ-32-20-P-A

Part number: 157045

FESTO



## Data sheet

| Feature  | Value  |
|--|--|
| Stroke   | 20 mm  |
| Piston diameter  | 32 mm  |
| Cushioning   | Elastic cushioning rings/plates at both ends   |
| Mounting position  | optional   |
| Mode of operation  | Pushing<br>Single-acting   |
| Piston-rod end   | Female thread  |
| Design   | Piston<br>Piston rod   |
| Position detection   | Via proximity switch   |
| Variants   | Piston rod at one end  |
| Protection against torque/guide                              | Square piston rod  |
| Operating pressure   | 0.1 MPa...1 MPa<br>1 bar...10 bar<br>14.5 psi...145 psi                                    |
| Operating medium   | Compressed air to ISO 8573-1:2010 [7:4:4]  |
| Note on operating and pilot medium                           | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC                               | 2 - Moderate corrosion stress  |
| LABS (PWIS) conformity                                       | VDMA24364-B1/B2-L  |
| Ambient temperature  | -20 °C...80 °C   |
| Impact energy in end positions                               | 0.4 J  |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 450 N  |
| Moving mass for 0 mm stroke                                  | 49 g   |
| Additional moving mass per 10 mm stroke                      | 9 g  |
| Basic weight for 0 mm stroke                                 | 300 g  |
| Additional weight per 10 mm stroke                           | 40 g   |
| Type of mounting   | Either:<br>With through-hole<br>With accessories   |
| Pneumatic connection   | G1/8   |
| Material collar screws                                       | Galvanised steel   |
| Material cover   | Wrought aluminium alloy  |

| <b>Feature</b>           | <b>Value</b>               |
|--------------------------|----------------------------|
| Material dynamic seals   | NBR<br>TPE-U(PU)           |
| Material piston rod      | High-alloy stainless steel |
| Material cylinder barrel | Wrought aluminium alloy    |