



# Linear drive DGPL-18- -PPV-A-GF-B

Part number: 161974  
Product to be discontinued

For proximity sensing, rodless, with positive-locking connection between piston and driver and adjustable end-position cushioning at both ends.

Type to be discontinued. Available until 2014. See Support Portal for alternative products.



Exemplary representation

## Data sheet

Feature	Value
Stroke	10 ... 1,800 mm
Piston diameter	18 mm
Cushioning	PPV: Pneumatic cushioning adjustable at both ends YXR: Shock absorber, hard characteristic curve
Assembly position	Any
Guide	Plain-bearing guide
Driver principle	positive-locking (slot)
Position detection	For proximity sensor
Operating pressure	2 ... 8 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:::]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2
Ambient temperature	-10 ... 60 °C
Cushioning length	16 mm
Theoretical force at 6 bar, return stroke	153 N
Theoretical force at 6 bar, advance stroke	153 N
Moving mass	300 g
Moving mass with 0 mm stroke	300 g
Basic weight for 0 mm stroke	750 g
Additional mass factor per 10 mm of stroke	22 g
alternative connections	See product drawing
Pneumatic connection	M5
Materials information for cover	Aluminium casting coated
Materials information for seals	NBR TPE-U(PU)
Materials information, housing	Aluminium Anodised