


compact cylinder DMM-32- -P-A-S6

Part number: 158554


FESTO

For proximity sensing, with elastic cushioning rings in end positions, wide range of mounting options.

Other stroke lengths on request. Available only in standard stroke lengths 5, 10, 15, 20, 25, 30, 40, 50 mm.



Exemplary representation



Data sheet

Feature	Value
Stroke	1 ... 50 mm
Piston diameter	32 mm
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Mode of operation	double-acting
Design structure	Piston Piston rod Profile barrel
Position detection	For proximity sensor
Variants	Heat resistant seals, max. 120°C
Operating pressure	0.6 ... 10 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Ambient temperature	-20 ... 120 °C
Tightening torque of the drive mounting	9 Nm +10 %
Theoretical force at 6 bar	483 N
Theoretical force at 6 bar, return stroke	415 N
Theoretical force at 6 bar, advance stroke	483 N
Mounting type	Optional with through hole with internal (female) thread
Pneumatic connection	G1/8
Material cover	Brass
Material seals	FPM
Material housing	Wrought Aluminium alloy Anodised
Material piston rod	High alloy steel, non-corrosive